



LIST OF PARTS PER BEARING.					
REF.	PART NO.	PART NAME	Nº OFF	MATERIAL	REMARKS
1	D526/901T	CASING BOTTOM. AS DRAWN	1	CAST STEEL	WHITEMETAL LINED & FACED.
2	D526/901H	CASING BOTTOM. OPP. HAND	1	"	"
3	D726/251	CASING TOP	1	"	"
4	F807/5B	INSPECTION DOOR	1	PERSEFLEX	"
5	255M/26000	JOURNAL PAD	5	GUNMETAL	WHITE METAL LINED.
6	F74/62	JOURNAL PAD STOP	2	"	"
7	F80/2076	OIL THROWER RING	1	ALUM. ALLOY	"
8	F87/34	OIL SCRAPER	1	GUNMETAL	"
9	F820/344	OIL DEFLECTOR	2	ALUM. ALLOY	STD. Nº 3 / 5/8"
10	F820/227	OIL LEVEL GAUGE	1	PERSEFLEX	STD. 4" (UNQ)
11	F825/295	OIL DRAIN PLUG	1	MILD STEEL	STD. 3/4" N.P.T.
12		WING NUTS.	2	MANG. BRONZE	STD. 1/2" UNC
13		STUDS	2	MILD STEEL	STD. 1/2" UNC x 2" LONG
14		JOINT BOLTS & NUTS	4	"	STD. 1/2" UNC x 10 1/2" LONG
15		JOINT BOLT & NUTS	2	"	STD. 1 1/2" UNC x 12 1/2" LONG
16		ROUND HEAD SCREWS	4	"	STD. 5/16" UNC x 3/4" LONG
17		TAP BOLTS	4	"	STD. 7/8" UNC x 7" LONG
18	F87/197	TUBEPLATE	2	R.N. BRASS	"
19		TUBES	3	CUPRO-NICKEL	EACH 3/4" DIA. x 18 SWG x 3'-7 1/2" LONG.
20		METALLIC PACKING RING	12	"	CRANE Nº 601C - 885 7/8" DIA. x 1/4" x 1/4" THK.
21		FIBRE PACKING RING	6	"	CRANE Nº 602 - 885 7/8" DIA. x 3/4" x 1/4" THK.
22		FERRULES	6	CUPRO-NICKEL	CRANE PACKING LTD. DRG. Nº Z1938
23		STUDS & NUTS	8	MILD STEEL	STD. 1/2" UNC x 3" LONG.
24		C/SK. SCREWS	4	"	STD. 1/2" UNC x 1 1/2" LONG.
25	F218/18	TUBE GUARD	1	"	SECURED BY 1" STD 1/2" DIA. SPRING WASHER.
26		WASHER	2	"	STD. 1/2" DIA.
27		DOWEL	2	CARBON STEEL	STD. 1/2" DIA. x 1 1/2" LONG - DRIVING FIT IN CASING TOP.
28	F875/372	JOINT	2	INVAR. VEE	JOINTING
29	F250/37	SPRING	1	SPRING STEEL	STANDARD (CRANE) - 56 MON. DIA. x 20 SWG x 1 1/2" FREE.
30	F252/259	RESTRICTION PLATE	1	MILD STEEL	"
31		OIL INLET STUDS & NUTS	1	"	STD. 1/2" UNC x 1 1/2" LONG
31		OIL OUTLET STUDS & NUTS	1	"	STD. 1/2" UNC x 1 1/2" LONG

DATE	ORDER Nº	FOR MESSRS	ENG. Nº	NO. OF SHIPS	REPTS.	REMARKS
29 MAR 65	66562	CANADIAN VICKERS LTD.	HULL 286	-	-	CANADIAN DOT. THIS ORDER ONLY. DRAWING OF BEARING.
24 JUN 65	67765	"	"	"	"	REWORKED BEARING. THIS BEARING IS NOT TO BE USED IN THE 1/2" DIA. HOLE. IT IS TO BE USED IN THE 1/2" DIA. HOLE. IT IS TO BE USED IN THE 1/2" DIA. HOLE.

**MICHELL AFTERMOST BEARING (TRAILING)**  
SELF LUBRICATING TYPE MAT. WATER COOLED BY TUBES.  
SCALE: 1/4 SIZE & AS MARKED.  
**26MAT/44769/2**  
MICHELL BEARINGS, LTD. NEWCASTLE-UPON-TYNE.  
DR. TR. M.C. 18 MAY 65.

26MAT/44769/2

1/2 OIL INLET & OUTLET CONNECTIONS MODIFIED 28/6/65.

1 - 1 JUNE 65 - DRAWING FINISHED OFF.