

Environment  
CanadaEnvironnement  
Canada

Canada

[Back to home page](#)

## Report

### Tank System Information

#### Tank System Description

EC #:  
00001128  
Internal Number

Description:  
Shammattawa, MB - Fuel Tank

#### Contact Information

##### Owner

Royal Canadian Mounted Police  
73 Leikin Dr  
M1-4 Mailstop #18  
Ottawa  
Ontario  
K1A 0R2  
Tel: (613) 843-5516  
Fax: (613) 825-7518

##### Tank Operator

Royal Canadian Mounted Police  
73 Leikin Dr  
M1-4 Mailstop #18  
Ottawa  
Ontario  
K1A 0R2  
Tel: (613) 843-5516  
Fax: (613) 825-7518

##### Contact

Rod Savard  
11140-109 Street  
Edmonton  
Alberta  
Tel: (780) 670-8580

##### Contact

Rod Savard  
11140-109 Street  
Edmonton  
Alberta  
Tel: (780) 670-8580

##### Land Owner

Federal entity under Financial Administration Act

##### Months of service

January  
February  
March  
April

May  
June  
July  
August  
September  
October  
November  
December

**System Location**

**Tank System Location**

General Delivery  
Shammattawa  
Manitoba

**System Record Location**

General Delivery  
Shammattawa  
Manitoba

**Emergency Plan Location**

General Delivery  
Shammattawa  
Manitoba  
Details:

**Miscellaneous Information**

Tank Use:

Name of Tank Manufacturer:

Year of Manufacture:

Certification # of System Installer:

Certification # of System Remover:

**Tank 1 of 1**

**Tank Information**

Tank Description:

Tank Internal Number:

Type of Tank:

Aboveground

ULC or API Standard Number:

ULC-S653

Year of installation:

1996

Material of construction:

Steel

Overfill Protection:

- Method – trained personnel in attendance at all times

Type of pump:

No oil-water separator

Spill Containment:

Spill box at fill point (aboveground tank)

Product Stored:

Gasoline

Tank Capacity:

24100 L

Transfer area:

Drip pan, secondary containment provided at truck, trained personnel

Tank Leak Detection:

- Interstitial monitoring – double walled tank

Corrosion Protection:

- Painted

Secondary Containment:

- Double Walled

### **Piping for tank 1**

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Steel

Corrosion Protection:

- Painted

Secondary Containment:

- None