

Environment  
CanadaEnvironnement  
Canada

Canada

[Back to home page](#)

## Report

### Tank System Information

#### Tank System Description

EC #:  
00001176  
Internal Number

Description:  
Island Lake, MB - Small Tank

#### Contact Information

##### Owner

Royal Canadian Mounted Police  
73 Leikin Dr  
M1-4 Mailstop #18  
Ottawa  
Ontario  
K1A 0R2  
Tel: (613) 843-5516  
Fax: (613) 825-7518

##### Tank Operator

Royal Canadian Mounted Police  
73 Leikin Dr  
M1-4 Mailstop #18  
Ottawa  
Ontario  
K1A 0R2  
Tel: (613) 843-5516  
Fax: (613) 825-7518

##### Contact

Rod Savard  
11140-109 Street  
Edmonton  
Alberta  
Tel: (780) 670-8580

##### Contact

Rod Savard  
11140-109 Street  
Edmonton  
Alberta  
Tel: (780) 670-8580

##### Land Owner

Federal entity under Financial Administration Act

##### Months of service

January  
February  
March  
April

May  
June  
July  
August  
September  
October  
November  
December

**System Location**

**Tank System Location**

General Delivery  
Stevenson Island  
Manitoba

**System Record Location**

General Delivery  
Stevenson Island  
Manitoba

**Emergency Plan Location**

General Delivery  
Stevenson Island  
Manitoba  
Details:

**Miscellaneous Information**

Tank Use:

Name of Tank Manufacturer:

Year of Manufacture:

Certification # of System Installer:

Certification # of System Remover:

**Tank 1 of 1**

**Tank Information**

Tank Description:

Tank Internal Number:

Type of Tank:

Aboveground

ULC or API Standard Number:

ULC-S653

Year of installation:

2008

Material of construction:

Steel

Overfill Protection:

- Overfill ball float valve
- Method – trained personnel in attendance at all times

Type of pump:  
No oil-water separator  
Spill Containment:  
Spill box at fill point (aboveground tank)  
Product Stored:  
Gasoline  
Tank Capacity:  
4500 L  
Transfer area:  
Spill box, secondary containment provided at truck, trained personnel  
Tank Leak Detection:  

- Interstitial monitoring – double walled tank

Corrosion Protection:  

- Painted

Secondary Containment:  

- Double Walled

### **Piping for tank 1**

Type of Piping:  
Aboveground  
Piping diameter:  
2 inch  
Piping Leak Detection:  

- Visual inspection

Leak detection for sumps:  

- No sump for storage tank system

Material of construction:  

- Steel

Corrosion Protection:  

- Coating – bonded plastic, resin, epoxy or polyurethane coated

Secondary Containment:  

- None