

Environment
CanadaEnvironnement
Canada

Canada

[Back to home page](#)

Report

Tank System Information

Tank System Description

EC #:
00035160
Internal Number

Description:
Aklavik Detachment Heating Oil Tank

Contact Information

Owner

Royal Canadian Mounted Police
73 Leikin Dr
M1-4 Mailstop #18
Ottawa
Ontario
K1A 0R2
Tel: (613) 843-5516
Fax: (613) 825-7518

Tank Operator

GNWT
Stuart Hodgson Building
Box 1320
Yellowknife
Northwest Territories
X1A 2L9

Contact

Rod Savard
11140-109 Street
Edmonton
Alberta
Tel: (780) 670-8580

Contact

Dennis Pascal
Bag Service #1
106 Vetran's Way
Inuvik
Northwest Territories
X0E 0T0
Tel: (867) 777-7152

Land Owner

Months of service

January
February
March
April

May
June
July
August
September
October
November
December

System Location

Tank System Location

34 Tornow Avenue
Aklavik
Northwest Territories

System Record Location

34 Tornow Avenue
Aklavik
Northwest Territories

Emergency Plan Location

34 Tornow Avenue
Aklavik
Northwest Territories
Details:

Miscellaneous Information

Tank Use:

Name of Tank Manufacturer:

Year of Manufacture:

Certification # of System Installer:

Certification # of System Remover:

Tank 1 of 2

Tank Information

Tank Description:
Main heating oil tank
Tank Internal Number:

Type of Tank:
Aboveground
ULC or API Standard Number:
ULC-S601
Year of installation:
2006
Material of construction:
Steel
Overfill Protection:
• Overfill ball float valve
Type of pump:

No pump

Spill Containment:

Other, tank is in containment tub

Product Stored:

Heating oil

Tank Capacity:

2500 L

Transfer area:

Tank is contained in a tub to prevent spillage into the environment.

Tank Leak Detection:

- Other (specify), visual inspection

Corrosion Protection:

- Painted

Secondary Containment:

- Double Walled

Piping for tank 1

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Other (specify), visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Black Iron

Corrosion Protection:

- Painted

Secondary Containment:

- Other impermeable barrier (specify), visual inspection

Tank 2 of 2

Tank Information

Tank Description:

Heating oil day tank

Tank Internal Number:

Type of Tank:

Aboveground

ULC or API Standard Number:

ULC-C80-1

Year of installation:

2015

Material of construction:

Steel

Overfill Protection:

- None

Type of pump:

No pump

Spill Containment:

None

Product Stored:

Heating oil

Tank Capacity:

400 L

Transfer area:

tank is inside a building and is not directly filled.

Tank Leak Detection:

- Other (specify), visual inspection

Corrosion Protection:

- Non-corroding material

Secondary Containment:

- Double Walled
- Other impermeable barrier (specify), MPI insulated group high density polyethelene inner tank with galvanized steel welded outer tank

Piping for tank 2

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Other (specify), visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Black Iron

Corrosion Protection:

- Painted

Secondary Containment:

- Other impermeable barrier (specify), visual inspection