

Environment
CanadaEnvironnement
Canada

Canada

[Back to home page](#)

Report

Tank System Information

Tank System Description

EC #:
00001323
Internal Number

Description:
Fort Simpson, NT - Heating Oil

Contact Information

Owner

Royal Canadian Mounted Police
73 Leikin Dr
M1-4 Mailstop #18
Ottawa
Ontario
K1A 0R2
Tel: (613) 843-5516
Fax: (613) 825-7518

Tank Operator

GNWT
Stuart Hodgson Building
Box 1320
Yellowknife
Northwest Territories
X1A 2L9

Contact

Rod Savard
11140-109 Street
Edmonton
Alberta
Tel: (780) 670-8580

Contact

Les Wright
Box 240
1st Floor Milton Building
Fort Simpson
Northwest Territories
X0E 0N0
Tel: (867) 695-7240

Land Owner

Months of service

January
February
March
April

May
June
July
August
September
October
November
December

System Location

Tank System Location

General Delivery
Fort Simpson
Northwest Territories

System Record Location

General Delivery
Fort Simpson
Northwest Territories

Emergency Plan Location

General Delivery
Fort Simpson
Northwest Territories
Details:

Miscellaneous Information

Tank Use:

Name of Tank Manufacturer:

Year of Manufacture:

Certification # of System Installer:

Certification # of System Remover:

Tank 1 of 2

Tank Information

Tank Description:
Main Supply Tank
Tank Internal Number:

Type of Tank:
Aboveground
ULC or API Standard Number:
ULC-S601
Year of installation:
1999
Material of construction:
Steel
Overfill Protection:
• Overfill ball float valve
Type of pump:

No oil-water separator

Spill Containment:

Spill box at fill point (aboveground tank)

Product Stored:

Heating oil

Tank Capacity:

4500 L

Transfer area:

Portable containment at truck and fill point, trained personnel in constant attendance

Tank Leak Detection:

- Tank precision leak detection test
- Visual inspection

Corrosion Protection:

- Painted

Secondary Containment:

- Double Walled

Piping for tank 1

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Copper
- Black Iron

Corrosion Protection:

- Painted
- None

Secondary Containment:

- None

Tank 2 of 2

Tank Information

Tank Description:

Day Tank

Tank Internal Number:

Type of Tank:

Aboveground

ULC or API Standard Number:

ULC-S602

Year of installation:

Unknown

Material of construction:

Steel

Overfill Protection:

- Overfill ball float valve

Type of pump:

No oil-water separator

Spill Containment:

Other, Inside Building

Product Stored:

Heating oil

Tank Capacity:

909 L

Transfer area:

See Main Tank Description

Tank Leak Detection:

- Tank precision leak detection test
- Visual inspection

Corrosion Protection:

- Painted

Secondary Containment:

- Double Walled

Piping for tank 2

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Steel

Corrosion Protection:

- Painted

Secondary Containment:

- Other impermeable barrier (specify), Inside building
- None