

Environment
CanadaEnvironnement
Canada

Canada

[Back to home page](#)

Report

Tank System Information

Tank System Description

EC #:
00001307
Internal Number

Description:
Inuvik, NT - Detachment

Contact Information

Owner

Royal Canadian Mounted Police
73 Leikin Dr
M1-4 Mailstop #18
Ottawa
Ontario
K1A 0R2
Tel: (613) 843-5516
Fax: (613) 825-7518

Tank Operator

GNWT
Stuart Hodgson Building
Yellowknife
Northwest Territories
X1A 2L9

Contact

Rod Savard
11140-109 Street
Edmonton
Alberta
Tel: (780) 670-8580

Contact

Richard Ross
Bag Service #1
Veteran's Way
Inuvik
Northwest Territories
Tel: (867) 678-0428

Land Owner

Months of service

January
February
March
April
May
June

July
August
September
October
November
December

System Location

Tank System Location

General Delivery
Inuvik
Northwest Territories
X0E 0T0

System Record Location

General Delivery
Inuvik
Northwest Territories
X0E 0T0

Emergency Plan Location

General Delivery
Inuvik
Northwest Territories
X0E 0T0
Details:

Miscellaneous Information

Tank Use:

Name of Tank Manufacturer:

Year of Manufacture:

Certification # of System Installer:

Certification # of System Remover:

Tank 1 of 2

Tank Information

Tank Description:
Main Supply Tank
Tank Internal Number:

Type of Tank:
Aboveground
ULC or API Standard Number:
ULC-S601
Year of installation:
1994
Material of construction:
Steel
Overfill Protection:

- None

- Overfill alarm and overfill automatic shutoff

Type of pump:

No pump

Spill Containment:

Other, Spill containment tray and portable containment device

Product Stored:

Heating oil

Tank Capacity:

4545 L

Transfer area:

June 12, 2012

Tank Leak Detection:

- Visual inspection

Corrosion Protection:

- Painted

Secondary Containment:

- Impermeable Liner with double bottom tank (field erected tank)

Piping for tank 1

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Copper
- Black Iron

Corrosion Protection:

- None

Secondary Containment:

- None

Tank 2 of 2

Tank Information

Tank Description:

Inside Day Tank

Tank Internal Number:

Type of Tank:

Aboveground

ULC or API Standard Number:

ULC-S602

Year of installation:

2016

Material of construction:

Steel

Overfill Protection:

- Overfill alarm and overfill automatic shutoff

Type of pump:

No pump

Spill Containment:

Other, Located indoors in a contained area.

Product Stored:

Heating oil

Tank Capacity:

1360 L

Transfer area:

Tank contained inside a building.

Tank Leak Detection:

- Continuous external tank leak monitoring (Sensor cable system)

Corrosion Protection:

- Painted

Secondary Containment:

- Double Walled
- Containment tank assembly

Piping for tank 2

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Black Iron

Corrosion Protection:

- None

Secondary Containment:

- None