

Environment
CanadaEnvironnement
Canada

Canada

[Back to home page](#)

Report

Tank System Information

Tank System Description

EC #:
00001312
Internal Number

Description:
Paulatuk, NT

Contact Information

Owner

Royal Canadian Mounted Police
73 Leikin Dr
M1-4 Mailstop #18
Ottawa
Ontario
K1A 0R2
Tel: (613) 843-5516
Fax: (613) 825-7518

Tank Operator

GNWT
Stuart Hodgson Building
Box 1320
Yellowknife
Northwest Territories
X1A 2L9

Contact

Rod Savard
11140-109 Street
Edmonton
Alberta
Tel: (780) 670-8580

Contact

Dennis Pascal
Bag Service #1
106 Vetran's Way
Inuvik
Northwest Territories
X0E 0T0
Tel: (867) 777-7152

Land Owner

Months of service

January
February
March
April

May
June
July
August
September
October
November
December

System Location

Tank System Location

54 Hamlet Street
Paulatuk
Northwest Territories

System Record Location

54 Hamlet Street
Paulatuk
Northwest Territories

Emergency Plan Location

54 Hamlet Street
Paulatuk
Northwest Territories
Details:

Miscellaneous Information

Tank Use:

Name of Tank Manufacturer:

Year of Manufacture:

Certification # of System Installer:

Certification # of System Remover:

Tank 1 of 2

Tank Information

Tank Description:
Main Supply Tank
Tank Internal Number:

Type of Tank:
Aboveground
ULC or API Standard Number:
ULC-C142.22 (withdrawn-rectangular part of S601)
Year of installation:
2004
Material of construction:
Steel
Overfill Protection:
• Overfill ball float valve
Type of pump:

No oil-water separator

Spill Containment:

Spill box at fill point (aboveground tank)

Product Stored:

Heating oil

Tank Capacity:

4510 L

Transfer area:

Spill pans on site for truck and tank, standard operating procedures.

Tank Leak Detection:

- Interstitial monitoring – double walled tank

Corrosion Protection:

- Painted

Secondary Containment:

- Double Walled

Piping for tank 1

Type of Piping:

Aboveground

Piping diameter:

2 inch

Piping Leak Detection:

- Visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Black Iron

Corrosion Protection:

- None

Secondary Containment:

- None

Tank 2 of 2

Tank Information

Tank Description:

Day Tank

Tank Internal Number:

Type of Tank:

Aboveground

ULC or API Standard Number:

ULC-S602

Year of installation:

2004

Material of construction:

Steel

Overfill Protection:

- None

Type of pump:

No pump

Spill Containment:

None

Product Stored:

Heating oil

Tank Capacity:

680 L

Transfer area:

June 12, 2012

Tank Leak Detection:

- Visual inspection

Corrosion Protection:

- Painted

Secondary Containment:

- None

Piping for tank 2

Type of Piping:

Aboveground

Piping diameter:

0.5 inch

Piping Leak Detection:

- Visual inspection

Leak detection for sumps:

- No sump for storage tank system

Material of construction:

- Black Iron

Corrosion Protection:

- Coating – bonded plastic, resin, epoxy or polyurethane coated

Secondary Containment:

- None