

**F6855-170003:**

**Question:**

I have a couple of questions I am hoping you can offer clarification on with regards to the above noted Solicitation Number.

1. Could you please confirm capacity as this seems very low for that HP rating.
2. Would you accept a variable frequency drive rather than a dual speed motor?

**Answer:**

1. Pump capacity is 100 long tonnes per hour at high speed and 50 long tonnes per hour at low speed.
2. Variable speed drive will be acceptable if cabling is shielded from interference. Pump must function when installed in same location as existing and the controller must be located above the waterline for remote operation in a flooded condition.