

Catalog Number
Notes
Type

FEATURES & SPECIFICATIONS

INTENDED USE

Provides general illumination in residential and light commercial applications. Ideal for use where dust, dirt, humidity, moisture and cold temperatures are present. Perfect for indoor and outdoor use.

CONSTRUCTION

The high-impact polycarbonate lens allows for bright illumination. Fully gasketed to protect against wet, cold and dusty environments. Starts down to 0°F (-18°C).

OPTICS

Contains 4000K LEDs that produce approximately 1800 lumens at 50,000 hours life. CRI = 88.

ELECTRICAL

Fixture operates at 120 volts, 60 HZ and ensures no flickering and quiet operation without interfering with other home electronics. Standard input wattage is 24 watts, 75 lumens per watt.

INSTALLATION

Mounting hardware and watertight fitting for 3/8" conduit included.

LISTINGS

cUL listed to U.S. and Canadian safety standards. IP65 rated. ENERGY STAR® certified.

WARRANTY

5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.

Indoor/Outdoor General Purpose

XWLED

4' SLIM LED WET LIGHT
HIGH-PERFORMANCE LED




Specifications

Width: 2-3/8 (6.0)

Height: 3 (7.6)

Length: 47-1/2 (121)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: XWLED4 120

XWLED4		120	
Series	CRI	Color temperature	Voltage
XWLED4 4' LED wet light	(blank) 88 CRI	(blank) 4000K	120 120-volt residential electronic driver