



**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS À:**  
**Bid Receiving Public Works and Government**  
**Services Canada/Réception des soumissions Travaux**  
**publics et Services gouvernementaux Canada**  
**Room 100,**  
**167 Lombard Ave.**  
**Winnipeg**  
**Manitoba**  
**R3B 0T6**  
**Bid Fax: (204) 983-0338**

## **SOLICITATION AMENDMENT**

## **MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

### **Comments - Commentaires**

**Vendor/Firm Name and Address**  
**Raison sociale et adresse du**  
**fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**  
Public Works and Government Services Canada -  
Western Region  
Room 100  
167 Lombard Ave.  
Winnipeg  
Manitoba  
R3B 0T6

|   |   |
|---|---|
| <b>Title - Sujet</b><br>Computed Radiography Scanner  |   |
| <b>Solicitation No. - N° de l'invitation</b><br>W7702-175837/A  | <b>Amendment No. - N° modif.</b><br>001                                   |
| <b>Client Reference No. - N° de référence du client</b><br>W7702-175837   | <b>Date</b><br>2016-12-19   |
| <b>GETS Reference No. - N° de référence de SEAG</b><br>PW-\$WPG-201-10049   |   |
| <b>File No. - N° de dossier</b><br>WPG-6-39144 (201)  | <b>CCC No./N° CCC - FMS No./N° VME</b>                                    |
| <b>Solicitation Closes - L'invitation prend fin</b><br><b>at - à 02:00 PM</b><br><b>on - le 2017-01-05</b>  | <b>Time Zone</b><br><b>Fuseau horaire</b><br>Central Standard Time<br>CST |
| <b>F.O.B. - F.A.B.</b><br><b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/> |   |
| <b>Address Enquiries to: - Adresser toutes questions à:</b><br>Loxton, Ashley   | <b>Buyer Id - Id de l'acheteur</b><br>wpg201                              |
| <b>Telephone No. - N° de téléphone</b><br>(204) 510-9537 ( )  | <b>FAX No. - N° de FAX</b><br>(204) 983-7796                              |
| <b>Destination - of Goods, Services, and Construction:</b><br><b>Destination - des biens, services et construction:</b>   |   |

**Instructions: See Herein**

**Instructions: Voir aux présentes**

|  |  |
|--|--|
| <b>Delivery Required - Livraison exigée</b>  | <b>Delivery Offered - Livraison proposée</b> |
| <b>Vendor/Firm Name and Address</b><br><b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>   |  |
| <b>Telephone No. - N° de téléphone</b><br><b>Facsimile No. - N° de télécopieur</b>   |  |
| <b>Name and title of person authorized to sign on behalf of Vendor/Firm</b><br><b>(type or print)</b><br><b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b><br><b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b> |  |
| <b>Signature</b>   | <b>Date</b>                                  |

Solicitation No. - N° de l'invitation  
W7702-175837/A  
Client Ref. No. - N° de réf. du client  
W7702-175837

Amd. No. - N° de la modif.  
AMD001  
File No. - N° du dossier  
WPG-6-39144

Buyer ID - Id de l'acheteur  
WPG201  
CCC No./N° CCC - FMS No./N° VME

---

**This amendment No. 001 is raised to address questions and changes regarding Solicitation W7702-175837/A as follows:**

**PART A: QUESTIONS AND ANSWERS**

**Q1.** The mandatory Technical Criteria ITEM 1.3 is asking for: Must have (1) High Resolution Display Monitor capable of providing auto calibration to surrounding light. Minimum 5 mega pixel, 21 inches.

Auto calibration to surrounding light is somewhat confusing... since computer monitor cannot adjust their brightness to the surrounding light? Can you explain?

The standard 5MP monitor we sell with our system has an integrated front sensor allowing the monitor to self-calibrate to DICOM Part 14 standard... and therefore want to be sure this is what you are asking for here???

**A1.** Must have (1) High Resolution Display Monitor with built in sensor(s) to allow for self-calibration. The sensor is capable of measuring ambient light. Minimum 5 mega pixel, 21 inches.

**PART B: REVISIONS**

**Refer to Annex A Requirement,**

**Compliance Matrix - Item 1.3**

**DELETE:** Must have (1) High Resolution Display Monitor capable of providing auto calibration to surrounding light. Minimum 5 mega pixel, 21 inches.

**INSERT:** Must have (1) High Resolution Display Monitor with built in sensor(s) to allow for self-calibration. The sensor is capable of measuring ambient light. Minimum 5 mega pixel, 21 inches.

**ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED**