

REF. DRAWING E3

1. In Detail #1 the 400A-3P breaker shown for the new CDP '6B' shall be provided in this tender package by the electrical contractor. There is existing space in the existing CDP. The 250A-3P and 400A-3P for Panel 'A' and xfmr are existing to remain.

2. Include the following fixture schedule:

Fixture type 'AA'

Luminaire: surface led strip light mounted to corridor wall, 1219mm length c/w frosted lens, 180deg beam spread. All 'AA' fixtures shall be mounted at the same height, final mounting height shall be as high as possible coordinated with ductwork on site.

Lamp: 40 watt, minimum 4000 lumen led module with remote phosphor technology, 3500k, minimum 85 CRI, 50,000 hours at 70% lumen maintenance.

Driver: over-voltage, over-current and short circuit protected, 120 volt, <20% THD.

Manufacturer:

Cooper Metalux #SNLED series

Or approved equal.

Fixture type 'BB'

Luminaire: suspended led strip light, 1219mm length c/w frosted lens, 180deg beam spread. Provide chain hanger to mount fixture at 2440mm A.F.F. unless otherwise noted. Coordinate final mounting height and locations with mechanical ductwork on site.

Lamp: 40 watt, minimum 4000 lumen led module with remote phosphor technology, 3500k, minimum 85 CRI, 50,000 hours at 70% lumen maintenance.

Driver: over-voltage, over-current and short circuit protected, 120 volt, <20% THD.

Manufacturer:

Cooper Metalux #SNLED series

Or approved equal.

Type 'EX' - existing fixture to remain.

Type 'REM' - existing fixture to be removed.

Type 'REL' - relocated fixture.

END OF ADDENDUM NO. 1