



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Travaux publics et Services gouvernementaux
Canada

Place Bonaventure, portail Sud-Est

800, rue de La Gauchetière Ouest

7^{ème} étage

Montréal

Québec

H5A 1L6

FAX pour soumissions: (514) 496-3822

SOLICITATION AMENDMENT

MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Travaux publics et Services gouvernementaux Canada

Place Bonaventure, portail Sud-Est

800, rue de La Gauchetière Ouest

7^{ème} étage

Montréal

Québec

H5A 1L6

| | |
|---|--|
| Title - Sujet Tracteurs | |
| Solicitation No. - N° de l'invitation 21301-174809/B | Amendment No. - N° modif. 001 |
| Client Reference No. - N° de référence du client 21301-17-4809 | Date 2017-02-12 |
| GETS Reference No. - N° de référence de SEAG PW-\$MTA-160-14213 | |
| File No. - N° de dossier MTA-6-39226 (160) | CCC No./N° CCC - FMS No./N° VME |
| Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2017-02-21 | |
| Time Zone Fuseau horaire Heure Normale du l'Est HNE | |
| F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/> | |
| Address Enquiries to: - Adresser toutes questions à: Asquino, Carolina | Buyer Id - Id de l'acheteur mta160 |
| Telephone No. - N° de téléphone (514) 496-3549 () | FAX No. - N° de FAX (514) 496-3822 |
| Destination - of Goods, Services, and Construction: Destination - des biens, services et construction: | |

Instructions: See Herein

Instructions: Voir aux présentes

| | |
|--|--|
| Delivery Required - Livraison exigée | Delivery Offered - Livraison proposée |
| Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur | |
| Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur | |
| Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie) | |
| Signature | Date |

AMENDMENT 001

This amendment is raised to answer a question received and modify the financial evaluation and basis of selection criteria.

Question & Answer

Q1. At page 18 of 26, at section 3, number 2 (Minimum 60 liters fuel tank) we have 50 liters.

A1. The 50 liters fuel tank is acceptable.

The RFP is amended as follows:

1) Under ANNEX "A" REQUIREMENT, under item 5.0 Technical specification:

DELETE: In its entirety

INSERT:

- 1- Bidder must write the data and characteristics in the boxes reserved for bidder, and provide details if necessary
- 2- Failure by bidders/suppliers to indicate whether their proposed equipment deviates from the requirements of this standard will oblige them to meet these requirements.
- 3- The following specifications are the minimum requirements that the bidders proposed products must satisfy.

| | |
|--|--|
| 1. Description 1- Minimum overall length of 3600 mm 2- Minimum overall wheel base of 1600 mm 3- <u>Maximum overall width of 1,321 mm with snow tires</u> 4- <u>Maximum overall height of 2,210mm with snow tires</u> 5- Minimum operating weight of 2,475 Kg With snow tire. | _____ mm / _____ in _____ mm / _____ in _____ mm / _____ in _____ mm / _____ in _____ Kg / _____ lb |
| 2. Motor 1- Supercharged engine 2- <u>Four (4) cylinders minimum</u> 3- Displacement of 3319 cc 4- <u>Net Power of maximum : 87 cv at 2500 rpm</u> 5- Net torque of maximum 290 Nm/revolution at 1850 rpm. | Brand _____ Model _____ _____ cylinders _____ CC _____ Hp at _____ Rpm _____ Nm/trev at _____ Rpm |
| 3. Fuel 1- <u>Diesel type</u> 2- Minimum 50 liters fuel tank 3- Replaceable fuel filter | _____ litres |
| 4. Lubrication 1- Pressurized system 2- Minimum 6.0 litres oil reservoir | _____ litres |

| | |
|--|--|
| 3- Full flow oil filter 4- Replaceable oil filter | |
| 5. Cooling system 1- Pressurized pump and radiator with permanent-type antifreeze that is rated to -40 C 2- The system must keep the temperature at its normal level under all operating conditions. | |
| 6. Electric system 1- 12 volts electrical system 2- Minimum 55 amp alternator 3- 1500 watts engine block heater 4- 102 DBA audible reverse warning device | _____ volts _____ amp _____ watts _____ DBA |
| 7. Transmission 1- <u>Hydrostatic transmission with Three (3) electrical connections , with forward/reverse directional control, device on dashboard and Joystick</u> 2- Travel speed : 0 – 40 km/hr. | |
| 8. Direction 1- <u>Hydraulic with two (2) rams</u> | |
| 9. Brakes 1- <u>Service brakes on all four (4) wheels</u> 2- <u>Hand –and band-operated parking brake on the transmission</u> | |
| 10. Tires 1- Four (4) turf tires brand new with rims 2- Four(4) snow tires brand new with rims | |
| 11. Hydraulic system 1- System with an ability to operate the main system and other auxiliary systems 2- Gear pump with 9 GPM total capacity 3- Replaceable hydraulic filter 4- Five (5) rear hydraulic outlets with three (3) joystick control 5- Three (3) front hydraulic with joystick control. 6- <u>Proportional –style joystick</u> 7- Each front and rear hydraulic outlet must be equipped with a rapid coupling. | |
| 12. Cabin 1- <u>Manufacturer cabin. Overall maximum height of 87” (2,210 mm)</u> 2- Anti spill protective structure that meets safety standards 3- Interior covering made of simulated leather and molded plastic. 4- Floor covered in rubberized mat 5- <u>Driving system on a rotating turret for changing the drive direction in seconds. Simply rotate 180 degrees the seat -wheel-dashboard-pedal to be in the opposite driving position.</u> 6- Two (2) fully windowed access doors gas cylinder-stabilised opening 7- One (1) stroboscopic amber revolving light that does not exceed the maximum height of the cabin. 8- Rear window that can open upward and has gas | |

| | |
|--|--|
| <p>cylinder that keep it in an open position</p> <p>9- Front window wiper with windshield washer</p> <p>10- Rear window wiper with windshield washer</p> <p>11- Two (2) Exterior rear-view mirrors in each direction</p> <p>12- Pressurized heating with air filter outside the cabin with positionable vents inside the cabin for maximum distribution</p> <p>13- Four (4) air inlets (minimum) inside to bring fresh air from outside</p> <p>14- Original manufacturer air conditioner</p> <p>15- Adjustable seat with pneumatic suspension</p> <p>16- Retractable seat belt</p> <p>17- Adjustable wheel</p> <p>18- Retractable sun visor</p> <p>19- AM-FM radio + speaker</p> <p>20- Front-end weights will be provided with the tractor (original equipment)</p> | |
| <p>13. Light and lighting</p> <p>1- Ceiling with switch</p> <p>2- Two (2) double intensity halogen lamps on the tractor wings</p> <p>3- Two (2) halogen lamps on the upper front part of the cabin</p> <p>4- Two (2) halogen lamps on the upper rear part of the cabin</p> <p>5- Two (2) front signal and hazard lights installed on the machine</p> <p>6- Two (2) rear signal and hazard lights installed</p> <p>7- Brake lights</p> <p>8- Licence plate lighting</p> <p>9- A slow vehicle triangle at the rear</p> <p>10- All lights and other accessories comply with the requirements of the Québec Highway safety code</p> | |
| <p>14. Dashboard and equipment</p> <p>1- Fuel gauge</p> <p>2- Cooling system temperature gauge</p> <p>3- Warning lights for :</p> <ul style="list-style-type: none"> -Engine oil pressure -Clogged air filter -Park brake -signal lights -Power take off in operation -Front light intensity level <p>4- Electronic control monitor with selector to view :</p> <ul style="list-style-type: none"> -Time -Time of use -Engine Rpm -Power take off speed | |

Solicitation No. - N° de l'invitation
21301-174809/B
Client Ref. No. - N° de réf. du client
21301-17-4809

Amd. No. - N° de la modif.
001
File No. - N° du dossier
MTA-6-39226

Buyer ID - Id de l'acheteur
MTA160
CCC No./N° CCC - FMS No./N° VME

| | |
|---|--|
| <p>-Speed travel</p> <ol style="list-style-type: none"> 5. Dashboard illuminated at night 6. Stop/start key 7. Backup alarm 8. Electronic Horn 9. Fuel gauge | |
| <p>15. Power take-off</p> <ol style="list-style-type: none"> 1- Shaft-540 RPM ,1 3/8 in in diameter with 6 splines 2- One (1) power takeoff will need to be installed at the rear 3- Safety guard covering the power takeoff | |
| <p>16. Threes (3) points attachment</p> <ol style="list-style-type: none"> 1- Category 2 attachment 2- Lifting capacity of 2300 kg 3- Independent control for lifting and automatic lowering of equipment | |
| <p>17. Sidewalk snow blower-full flight augers</p> <ol style="list-style-type: none"> 1- <u>(54'') inches working width or not exceed the width of the tractor</u> 2- Characteristics : <ul style="list-style-type: none"> • Replaceable bottom scraper blades in reversible standard steel • 2 serrated full-flight augers • Fixed lateral blades in standard steel • Quick adjusting steel skid shoes • Cute rotation kit for hydraulic motor • Hydraulic motor for rotating the chute • Balanced rotor and auger. 3- Telescopic industrial chute whose height varies between 74 inches and no more than 86 inches | |
| <p>18. Snow pushers with closed top</p> <ol style="list-style-type: none"> 1- Front mounted 54 inches width or not exceed the width of the tractor 2- Closed tops and wings 3- Quick attachments for the tractor | |
| <p>19. Three (3) deck mower</p> <ol style="list-style-type: none"> 1- Mounted at the rear of the tractor 2- <u>Total size from 177 to 185 inches width</u> 3- <u>Consisting of three (3) different tray, two of which are foldable for transport from one point to another.</u> 4- Shaft rotation speed of 540 rpm 5- Approximated weight of the mower will be 3,500 pounds | |
| <p>20. Painting</p> <ol style="list-style-type: none"> 1- The vehicle must be prepared in accordance with trade practice 2- The hood, cabin roof and the front blade must be in the manufacturer's standard color | |

Note: Specifications in **bold** see Annex C – Technical mandatory criteria

ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME.