



RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
Bid Receiving Public Works and Government
Services Canada/Réception des
soumissions/Travaux publics et Services
gouvernementaux Canada
The Cambridge Building
3 Queen Street/3, rue Queen
Charlottetown
Prince Edward Island
C1A 4A2

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

All enquiries are to be submitted in writing to the Contracting Authority, Darlene Reay, either by facsimile or by e-mail at:
darlene.reay@pwgsc.gc.ca.

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Public Works and Government Services Canada
The Cambridge Building
3 Queen Street/3 rue, Queen
PO Box 1268/CP 1268
Charlottetown
Prince Ed
C1A 4A2

Title - Sujet Designated Support Space	
Solicitation No. - N° de l'invitation ED001-172941/A	Amendment No. - N° modif. 002
Client Reference No. - N° de référence du client R.086261.003	Date 2017-02-20
GETS Reference No. - N° de référence de SEAG PW-\$PWC-008-4093	
File No. - N° de dossier PWC-6-39194 (008)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2017-03-01	Time Zone Fuseau horaire Atlantic Standard Time AST
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Reay, D (PWC)	Buyer Id - Id de l'acheteur pwc008
Telephone No. - N° de téléphone (902) 566-7518 ()	FAX No. - N° de FAX (902) 566-7514
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

The following changes in the tender documents are effective immediately. This addendum will form part of the contract documents.

This Addendum is raised to provide the following answers to questions provided by bidders.

Q1

We were looking through the documents and can't find any specification for pipe or duct insulation. Can we have this provided?

A1

SPECIFICATION

a)

Delete Section 00 01 11 List of Contents (3 pages)

And Replace with attached revised Section 00 01 11 List of Contents (3 pages)

b)

Insert attached Section 23 07 13 Duct Insulation (7 pages)

c)

Insert attached Section 23 07 15 Thermal Insulation for Piping (7 pages)

<u>Section</u>	<u>Title</u>	<u>Pages</u>
<u>Division 01 - General Requirements</u>		
01 11 00	Summary of Work	5
01 14 00	Work Restrictions	4
01 31 19	Project Meetings	3
01 32 16.07	Construction Progress Schedule - Bar (GANTT) Chart	4
01 33 00	Submittal Procedures	6
01 35 21	LEED Requirements	8
01 35 29.06	Health and Safety Requirements	4
01 35 73	Procedures for Deconstruction of Structures	5
01 41 00	Regulatory Requirements	1
01 45 00	Quality Control	4
01 47 17	Sustainable Requirements: Contractor's Verification	5
01 52 00	Construction Facilities	4
01 56 00	Temporary Barriers and Enclosures	2
01 61 00	Common Product Requirements	6
01 71 00	Examination and Preparation	2
01 73 00	Execution	3
01 74 11	Cleaning	3
01 74 21	Construction/Demolition Waste Management and Disposal	3
01 77 00	Closeout Procedures	2
01 78 00	Closeout Submittals	8
01 91 13	General Commissioning (CX) Requirements	11
01 91 41	Commissioning: Training	4
<u>Division 02 - Existing Conditions</u>		
02 41 99	Demolition for Minor Works	3
02 81 01	Hazardous Materials	4
<u>Division 05 - Metals</u>		
05 50 00	Metal Fabrications	7
<u>Division 06 - Wood, Plastics, and Composites</u>		
06 40 00	Architectural Woodwork	10
06 65 00	Solid Polymer Fabrications	6
<u>Division 07 - Thermal and Moisture Protection</u>		
07 21 16	Blanket Insulation	3
07 84 00	Firestopping	6
07 92 00	Joint Sealers	10
<u>Division 08 - Openings</u>		
08 11 00	Steel Doors and Frames	10
08 14 10	Wood Doors	4
08 70 05	Cabinet and Miscellaneous Hardware	4
08 71 00	Door Hardware	6
08 80 50	Glazing	6
<u>Division 09 - Finishes</u>		
09 21 99	Partitions for Minor Works	6
09 51 95	Linear Metal Ceilings	6

09 51 99	Acoustical Ceilings Ceilings for Minor Works	5
09 68 00	Carpeting	6
09 91 99	Painting for Minor Works	8

Division 10 - Specialties

10 22 26	Operable Partitions	4
----------	---------------------	---

Division 21 - Fire Suppression

21 05 01	Common Work Results - Mechanical	5
21 05 05	Common Work Results for Fire Suppression	5
21 13 13	Wet Pipe Sprinkler Systems	14

Division 22 - Plumbing

22 05 00	Common Work Results for Plumbing	5
22 11 16	Domestic Water Piping	4
22 13 17	Draingage Waste and Vent Piping - Cast Iron, Copper and Stainless Steel	3
22 42 01	Plumbing Specialties and Accessories	6
22 47 00	Drinking Fountains and Water Fountains	3

Division 23 - Heating, Ventilating and Air-Conditioning (HVAC)

23 05 00	Common Work Results for HVAC	5
23 05 01	Use of HVAC Systems During Construction	2
23 05 19.01	Thermometers and Pressure Gauges - Piping Systems	3
23 05 23.01	Valves - Bronze	5
23 05 29	Hangers and supports for HVAC Piping Equipment	9
23 05 53.01	Mechanical Identification	7
23 05 93	Testing, Adjusting and balancing for HVAC	7
23 05 94	Pressure Testing of Ducted Air Systems	4
23 07 13	Duct Insulation	7
23 07 15	Thermal Insulation for Piping	7
23 08 01	Performance Verification Mechanical Piping Systems	2
23 31 13.01	Metal Ducts - Low Pressure to 500 Pa	7
23 33 00	Air Duct Accessories	7
23 33 14	Dampers - Balancing	3
23 33 16	Dampers - Fire and Smoke	6
23 33 46	Flexible Ducts	4
23 33 53	Duct Liners	5
23 37 13	Diffusers, Registers and Grilles	4
23 82 19	Fan Coil Units	3

Division 25 - Integrated Automation

25 01 11	EMCS: Start-up, Verification and Commissioning	8
25 01 12	EMCS: Training	3
25 05 01	EMCS: General Requirements	10
25 05 02	EMCS: Submittals and Review Process	8
25 05 03	EMCS: Project Record Documents	4
25 05 54	EMCS: Identification	3
25 30 02	EMCS: Field Control Devices	6

Division 26 - Electrical

26 05 00	Common Work Results for Electrical	13
26 05 20	Wire and Box Connectors 0-1000 V	2
26 05 21	Wires and Cables 0-1000V	3
26 05 28	Grounding - Secondary	3
26 05 29	Hangers and Supports for Electrical Systems	2
26 05 31	Splitters, Junction, Pull boxes and Cabinets	2
26 05 32	Outlet Boxes, Conduit Boxes and Fittings	2
26 05 34	Conduits, Conduit Fastenings and Conduit Fittings	3
26 27 26	Wiring Devices	3
26 28 21	Moulded Case Circuit Breakers	3
26 28 23	Disconnect Switches - Fused and Non-Fused	2
26 29 03	Control Devices	2
26 50 00	Lighting	3
26 52 00	Unit Equipment for Emergency	3
26 53 00	Exit Lights	2

Division 27 - Communications

27 05 26	Grounding and Bonding for Communications Systems	2
27 05 28	Pathways for Communications Systems	2
27 10 05	Structured Cabling for Communications Systems	5

Division 28 - Electronic Safety and Security

28 31 02	Multiplex Fire Alarm System	5
----------	-----------------------------	---

DRAWINGS

Architectural

A0	COVER SHEET
A1	DEMOLITION & KEY PLANS
A2	PARTITION PLANS & WALL TYPES
A3	RCP & DETAILS
A4	SECTIONS, DETAILS & SCHEDULES
A5	MILLWORK ELEVATIONS
A6	MILLWORK SECTIONS
A7	MILLWORK SECTIONS & DETAILS
A8	WALL SECTIONS & DETAILS

Mechanical

H1	LOWER LEVEL HVAC PARTIAL PLAN
H2	UPPER LEVEL HVAC PARTIAL PLAN
H3	FAN COIL DETAILS
H4	FIRE PROTECTION

Electrical

E1	DEMOLITION PLAN
E2	LIGHTING PLAN
E3	POWER & SYSTEM PLANS
E4	PANEL SCHEDULES
E5	SYMBOL LEGEND

PART 1 GENERAL

1.1 REFERENCES

- .1 American Society of Heating, Refrigeration and Air Conditioning Engineers (ASHRAE)
 - .1 ANSI/ASHRAE/IESNA 90.1, SI; Energy Standard for Buildings Except Low-Rise Residential Buildings.
- .2 American Society for Testing and Materials International, (ASTM)
 - .1 ASTM B209M, Specification for Aluminum and Aluminum Alloy Sheet and Plate (Metric).
 - .2 ASTM C335, Test Method for Steady State Heat Transfer Properties of Horizontal Pipe Insulation.
 - .3 ASTM C411, Test Method for Hot-Surface Performance of High-Temperature Thermal Insulation.
 - .4 ASTM C449/C449M, Standard Specification for Mineral Fiber-Hydraulic-Setting Thermal Insulating and Finishing Cement.
 - .5 ASTM C547, Specification for Mineral Fiber Pipe Insulation.
 - .6 ASTM C553, Specification for Mineral Fiber Blanket Thermal Insulation for Commercial and Industrial Applications.
 - .7 ASTM C612, Specification for Mineral Fiber Block and Board Thermal Insulation.
 - .8 ASTM C795, Specification for Thermal Insulation for Use with Austenitic Stainless Steel.
 - .9 ASTM C921, Standard Practice for Determining Properties of Jacketing Materials for Thermal Insulation.
- .3 Canadian General Standards Board (CGSB)
 - .1 CGSB 51-GP-52Ma, Vapour Barrier, Jacket and Facing Material for Pipe, Duct and Equipment Thermal Insulation.
- .4 Thermal Insulation Association of Canada (TIAC): National Insulation Standards.
- .5 Underwriters Laboratories of Canada (ULC)
 - .1 CAN/ULC-S102, Surface Burning Characteristics of Building Materials and Assemblies.
 - .2 CAN/ULC-S701, Thermal Insulation Polystyrene, Boards and Pipe Covering.
- .6 Model National Energy Code of Canada for Buildings (MNECB)

1.2 DEFINITIONS

- .1 For purposes of this section:
 - .1 "CONCEALED" - insulated mechanical services and equipment in suspended ceilings and non-accessible chases and furred-in spaces.
 - .2 "EXPOSED" - will mean "not concealed" as defined herein.
 - .3 Insulation systems - insulation material, fasteners, jackets, and other accessories.
- .2 TIAC Codes:
 - .1 CRD: Commercial Round Ductwork,
 - .2 CRF: Commercial Rectangular Finish.

1.3 SHOP DRAWINGS

- .1 Submit shop drawings in accordance with Section 01 33 00 - Submittal Procedures.
- .2 Submit for approval manufacturer's catalogue literature related to installation, fabrication for duct jointing recommendations.

1.4 SAMPLES

- .1 Submit samples in accordance with Section 01 33 00 - Submittal Procedures.
- .2 Submit for approval: complete assembly of each type of insulation system, insulation, coating, and adhesive proposed. Mount sample on 12 mm plywood board. Affix typewritten label beneath sample indicating service.

1.5 MANUFACTURERS' INSTRUCTIONS

- .1 Submit manufacturer's installation instructions in accordance with Section 01 33 00 - Submittal Procedures.
- .2 Installation instructions to include procedures used and installation standards achieved.

1.6 QUALIFICATIONS

- .1 Installer: certified in performing work of this section, and have at least 5 years' successful experience in this size and type of project, qualified to standards of TIAC.

1.7 DELIVERY, STORAGE AND HANDLING

- .1 Deliver materials to site in original factory packaging, labelled with manufacturer's name, address.
- .2 Protect from weather and construction traffic.
- .3 Protect against damage from any source.
- .4 Store at temperatures and conditions recommended by manufacturer.

1.8 WASTE MANAGEMENT AND DISPOSAL

- .1 Remove from site and dispose of packaging materials at appropriate recycling facilities.
- .2 Collect and separate for disposal, paper, plastic, polystyrene, corrugated cardboard packaging material in appropriate on-site bins for recycling in accordance with Waste Management Plan.
- .3 Divert unused metal materials from landfill to metal recycling facility approved by Departmental Representative.
- .4 Divert unused adhesive material from landfill to official hazardous material collections site approved by Departmental Representative.
- .5 Do not dispose of unused adhesive materials into sewer systems, into lakes, streams, onto ground or in other locations where it will pose health or environmental hazard.

PART 2 PRODUCTS

2.1 FIRE AND SMOKE RATING

- .1 In accordance with CAN/ULC-S102:
 - .1 Maximum flame spread rating: 25.
 - .2 Maximum smoke developed rating: 50.

2.2 INSULATION

- .1 Mineral fibre: as specified includes glass fibre, rock wool, slag wool.
- .2 Thermal conductivity ("k" factor) not to exceed specified values at 24°C mean temperature when tested in accordance with ASTM C335.

- .3 TIAC Code C-1: Rigid mineral fibre board to ASTM C612, with factory applied vapour retarder jacket to CGSB 51-GP-52Ma (as scheduled in PART 3 of this Section).
- .4 TIAC Code C-2: Mineral fibre blanket to ASTM C553 faced with factory applied vapour retarder jacket to CGSB 51-GP-52Ma (as scheduled in PART 3 of this section).
 - .1 Mineral fibre: to ASTM C553.
 - .2 Jacket: to CGSB 51-GP-52Ma.
 - .3 Maximum "k" factor: to ASTM C553.

2.3 JACKETS

- .1 Canvas:
 - .1 220 gm/m² cotton, plain weave, treated with dilute fire retardant lagging adhesive to ASTM C921.
- .2 Lagging adhesive: Compatible with insulation.
- .3 Aluminum:
 - .1 To ASTM B209 with moisture barrier as scheduled in PART 3 of this section.
 - .2 Thickness: 0.40 mm sheet.
 - .3 Finish: Stucco embossed or corrugated.
 - .4 Jacket banding and mechanical seals: 12 mm wide, 0.5 mm thick stainless steel.
- .4 Stainless steel:
 - .1 Type: 304 or 316 where additional corrosion protection is required.
 - .2 Thickness: 0.25 mm sheet.
 - .3 Finish: Corrugated or stucco embossed.
 - .4 Jacket banding and mechanical seals: 12mm wide, 0.5 mm thick stainless steel.
- .5 Exterior insulation jacket:
 - .1 Exterior duct insulation to be made weatherproof by applying flexible weatherproofing jacket. Jacket to consist of a multi-ply embossed UV-resistant aluminum foil/polymer laminate to which is applied a layer of rubberized asphalt specially formulated for use on insulated duct and piping applications.

2.4 ACCESSORIES

- .1 Vapour retarder lap adhesive:
 - .1 Water based, fire retardant type, compatible with insulation.

- .2 Indoor Vapour Retarder Finish:
 - .1 Vinyl emulsion type acrylic, compatible with insulation.
- .3 Insulating Cement: hydraulic setting on mineral wool, to ASTM C449.
- .4 ULC Listed Canvas Jacket:
 - .1 220 gm/m² cotton, plain weave, treated with dilute fire retardant lagging adhesive to ASTM C921.
- .5 Outdoor Vapour Retarder Mastic:
 - .1 Vinyl emulsion type acrylic, compatible with insulation.
 - .2 Reinforcing fabric: Fibrous glass, untreated 305 g/m².
- .6 Tape: self-adhesive, aluminum, reinforced, 75 mm wide minimum.
- .7 Contact adhesive: quick-setting
- .8 Canvas adhesive: washable.
- .9 Tie wire: 1.5 mm stainless steel.
- .10 Banding: 12 mm wide, 0.5 mm thick stainless steel.
- .11 Facing: 25 mm galvanized steel hexagonal wire mesh stitched on one face of insulation.
- .12 Fasteners: 4 mm diameter pins with 35 mm diameter or square clips, length to suit thickness of insulation.

PART 3 EXECUTION

3.1 PRE-INSTALLATION REQUIREMENTS

- .1 Pressure testing of ductwork systems complete, witnessed and certified.
- .2 Surfaces clean, dry, free from foreign material.

3.2 INSTALLATION

- .1 Install in accordance with TIAC National Standards.
- .2 Apply materials in accordance with manufacturer's instructions and as indicated.

- .3 Use two layers with staggered joints when required nominal thickness exceeds 75 mm.
- .4 Maintain uninterrupted continuity and integrity of vapour retarder jacket and finishes.
 - .1 Hangers, supports to be outside vapour retarder jacket.
- .5 Supports, Hangers in accordance with Section 23 05 29 - Hangers and Supports for HVAC Piping and Equipment
 - .1 Apply high compressive strength insulation where insulation may be compressed by weight of ductwork.
- .6 Fasteners: At 300 mm oc in horizontal and vertical directions, minimum two rows each side.

3.3 DUCTWORK INSULATION SCHEDULE

- .1 Insulation types and thicknesses: Conform to following Table:

	TIAC Code	Vapour Retarder	Thickness (mm)
Rectangular cold and dual temperature supply air ducts (exposed)	C-1	yes	50
Round cold and dual temperature supply air ducts (concealed)	C-2	yes	50
Rectangular warm air ducts (exposed)	C-1	no	25
Round warm air ducts (exposed)	C-1	no	25
Rectangular cold and dual temperature supply air ducts (concealed)	C-2	Yes	25
Round cold and dual temperature supply air ducts (exposed)	C-1	yes	50
Rectangular warm air ducts (concealed)	C-2	No	25
Round warm air ducts (concealed)	C-2	No	25
Supply, return and exhaust ducts exposed in space being served			none
Outside air ducts to mixing plenum	C-1	yes	50
Mixing plenums	C-1	yes	25
Exhaust duct between dampers and louvers	C-1	no	50

	TIAC Code	Vapour Retarder	Thickness (mm)
Rectangular ducts outside	C-1	special	50
Round ducts outside	C-1	special	50

.3 Exposed round ducts 600 mm and larger, smaller sizes where subject to abuse:

.1 Use TIAC code C-1 insulation, scored to suit diameter of duct.

.2 Finishes: Conform to following table:

	TIAC Code	
	Rectangular	Round
Indoor, concealed	None	none
Indoor, exposed within mechanical room	CRF/1	CRD/2
Indoor, exposed elsewhere	CRF/2	CRD/3
Outdoor, exposed to precipitation	CRF/3	CRD/4
Outdoor, elsewhere	CRF/4	CRD/5

.3 Weatherproof exterior jacket as specified in Part 2 is acceptable on exterior duct applications provided insulation is rigid and faced.

END OF SECTION

1 GENERAL

1.01 SUMMARY

.1 Section Includes:

- .1 Thermal insulation for piping and piping accessories in commercial type applications.

1.02 REFERENCES

- .1 American Society of Heating, Refrigeration and Air Conditioning Engineers (ASHRAE)
 - .1 ASHRAE Standard 90.1-01, Energy Standard for Buildings Except Low-Rise Residential Buildings (IESNA co-sponsored; ANSI approved; Continuous Maintenance Standard).
- .2 American Society for Testing and Materials International (ASTM)
 - .1 ASTM B 209M-04, Standard Specification for Aluminum and Aluminum Alloy Sheet and Plate Metric.
 - .2 ASTM C 335-04, Standard Test Method for Steady State Heat Transfer Properties of Horizontal Pipe Insulation.
 - .3 ASTM C 411-04, Standard Test Method for Hot-Surface Performance of High-Temperature Thermal Insulation.
 - .4 ASTM C 449/C 449M-00, Standard Specification for Mineral Fiber-Hydraulic-Setting Thermal Insulating and Finishing Cement.
 - .5 ASTM C 533-2004, Calcium Silicate Block and Pipe Thermal Insulation.
 - .6 ASTM C 547-2003, Mineral Fiber Pipe Insulation.
 - .7 ASTM C 795-03, Standard Specification for Thermal Insulation for Use in Contact with Austenitic Stainless Steel.
 - .8 ASTM C 921-03a, Standard Practice for Determining the Properties of Jacketing Materials for Thermal Insulation.
- .3 Canadian General Standards Board (CGSB)
 - .1 CGSB 51-GP-52Ma-89, Vapour Barrier, Jacket and Facing Material for Pipe, Duct and Equipment Thermal Insulation.
 - .2 CAN/CGSB-51.53-95, Poly (Vinyl Chloride) Jacketting Sheet, for Insulated Pipes, Vessels and Round Ducts
- .4 Department of Justice Canada (Jus)
 - .1 Canadian Environmental Assessment Act (CEAA), 1995, c. 37.
 - .2 Canadian Environmental Protection Act (CEPA), 1999, c. 33.
 - .3 Transportation of Dangerous Goods Act (TDGA), 1992, c. 34.
- .5 Health Canada/Workplace Hazardous Materials Information System (WHMIS)
 - .1 Material Safety Data Sheets (MSDS).

- .6 Manufacturer's Trade Associations
 - .1 Thermal Insulation Association of Canada (TIAC): National Insulation Standards (Revised 2004).
- .7 Underwriters' Laboratories of Canada (ULC)
 - .1 CAN/ULC-S102-03, Surface Burning Characteristics of Building Materials and Assemblies.
 - .2 CAN/ULC-S701-01, Thermal Insulation, Polystyrene, Boards and Pipe Covering.
 - .3 CAN/ULC-S702-1997, Thermal Insulation, Mineral Fibre, for Buildings
 - .4 CAN/ULC-S702.2-03, Thermal Insulation, Mineral Fibre, for Buildings, Part 2: Application Guidelines.

1.03 DEFINITIONS

- .1 For purposes of this section:
 - .1 "CONCEALED" - insulated mechanical services in suspended ceilings and non-accessible chases and furred-in spaces.
 - .2 "EXPOSED" - will mean "not concealed" as specified.
- .2 TIAC ss:
 - .1 CRF: Code Rectangular Finish.
 - .2 CPF: Code Piping Finish.

1.04 ACTION AND INFORMATIONAL SUBMITTALS

- .1 Submittals: in accordance with Section 01 33 00 - Submittal Procedures.
- .2 Product Data:
 - .1 Submit manufacturer's printed product literature, specifications and datasheet in accordance with Section 01 33 00 - Submittal Procedures. Include product characteristics, performance criteria, and limitations.
 - .1 Submit two copies of Workplace Hazardous Materials Information System (WHMIS) Material Safety Data Sheets (MSDS) in accordance with Section 01 33 00 - Submittal Procedures.
- .3 Shop Drawings:
 - .1 Submit shop drawings in accordance with Section 01 33 00 - Submittal Procedures.
- .4 Samples:
 - .1 Submit samples in accordance with Section 01 33 00 - Submittal Procedures.
 - .2 Submit for approval: complete assembly of each type of insulation system, insulation, coating, and adhesive proposed. Mount sample on 12 mm plywood board. Affix label beneath sample indicating service.

1.05 QUALITY ASSURANCE

- .1 Qualifications:
- .2 Installer: specialist in performing work of this Section, and have at least 3 years successful experience in this size and type of project, qualified to standards of TIAC.

1.06 DELIVERY, STORAGE AND HANDLING

- .1 Packing, shipping, handling and unloading:
 - .1 Deliver, store and handle in accordance with manufacturer's written instructions and Section 01 61 00 - Common Product Requirements.
 - .2 Deliver, store and handle materials in accordance with manufacturer's written instructions.
 - .3 Deliver materials to site in original factory packaging, labelled with manufacturer's name, address.
- .2 Storage and Protection:
 - .1 Protect from weather, construction traffic.
 - .2 Protect against damage.
 - .3 Store at temperatures and conditions required by manufacturer.
- .3 Waste Management and Disposal:
 - .1 Remove from site and dispose of packaging materials at appropriate recycling facilities.
 - .2 Separate for reuse and recycling and place in designated containers Steel, Metal, Plastic waste in accordance with Waste Management Plan.
 - .3 Place excess or unused insulation and insulation accessory materials in designated containers.
 - .4 Dispose of unused adhesive material at official hazardous material collections site approved by Departmental Representative.

2 PRODUCTS

2.01 FIRE AND SMOKE RATING

- .1 In accordance with CAN/ULC-S102.
 - .1 Maximum flame spread rating: 25.
 - .2 Maximum smoke developed rating: 50.

2.03 INSULATION

- .1 Mineral fibre specified includes glass fibre, rock wool, slag wool.

Designated Support Space 1 st Floor JCB R.086261.003	Thermal Insulation for Piping	Section 23 07 15 Page 4 January, 2017
---	----------------------------------	---

- .2 Thermal conductivity ("k" factor) not to exceed specified values at 24 degrees C mean temperature when tested in accordance with ASTM C 335.
- .3 TIAC Code A-1: rigid moulded mineral fibre without factory applied vapour retarder jacket.
 - .1 Mineral fibre: to CAN/ULC-S702.
 - .2 Maximum "k" factor: to CAN/ULC-S702.
- .4 TIAC Code A-3: rigid moulded mineral fibre with factory applied vapour retarder jacket.
 - .1 Mineral fibre: to CAN/ULC-S702.
 - .2 Jacket: to CGSB 51-GP-52Ma.
 - .3 Maximum "k" factor: to CAN/ULC-S702.
- .5 TIAC Code C-2: mineral fibre blanket faced with factory applied vapour retarder jacket (as scheduled in PART 3 of this section).
 - .1 Mineral fibre: to CAN/ULC-S702.
 - .2 Jacket: to CGSB 51-GP-52Ma.
 - .3 Maximum "k" factor: to CAN/ULC-S702.

2.04 INSULATION SECUREMENT

- .1 Tape: self-adhesive, aluminum, reinforced, 50 mm wide minimum.
- .2 Contact adhesive: quick setting.
- .3 Canvas adhesive: washable.
- .4 Tie wire: 1.5 mm diameter stainless steel.
- .5 Bands: stainless steel, 19mm wide, 0.5 mm thick.

2.05 CEMENT

- .1 Thermal insulating and finishing cement:
 - .1 Hydraulic setting on mineral wool, to ASTM C 449/C 449M.

2.06 VAPOUR RETARDER LAP ADHESIVE

- .1 Water based, fire retardant type, compatible with insulation.

2.07 INDOOR VAPOUR RETARDER FINISH

- .1 Vinyl emulsion type acrylic, compatible with insulation.

2.08 JACKETS

- .1 Polyvinyl Chloride (PVC):
 - .1 One-piece moulded type and sheet to CAN/CGSB-51.53 with

- pre-formed shapes as required.
- .2 Colours: by Departmental Representative.
- .3 Minimum service temperatures: -20 degrees C.
- .4 Maximum service temperature: 65 degrees C.
- .5 Moisture vapour transmission: 0.02 perm.
- .6 Thickness: 0.3 mm.
- .7 Fastenings:
 - .1 Use solvent weld adhesive compatible with insulation to seal laps and joints.
 - .2 Tacks.
 - .3 Pressure sensitive vinyl tape of matching colour.
- .2 Canvas:
 - .1 220 and 120 gm/m² cotton, plain weave, treated with dilute fire retardant lagging adhesive to ASTM C 921.
 - .2 Lagging adhesive: compatible with insulation.

3 EXECUTION

3.01 MANUFACTURER'S INSTRUCTIONS

- .1 Compliance: comply with manufacturer's written recommendations or specifications, including product technical bulletins, handling, storage and installation instructions, and datasheet.

3.02 PRE-INSTALLATION REQUIREMENT

- .1 Pressure testing of piping systems and adjacent equipment to be complete, witnessed and certified.
- .2 Surfaces clean, dry, free from foreign material.

3.03 INSTALLATION

- .1 Install in accordance with TIAC National Standards.
- .2 Apply materials in accordance with manufacturer's instructions and this specification.
- .3 Use two layers with staggered joints when required nominal wall thickness exceeds 75 mm.
- .4 Maintain uninterrupted continuity and integrity of vapour retarder jacket and finishes.
 - .1 Install hangers, supports outside vapour retarder jacket.
- .5 Supports, Hangers:
 - .1 Apply high compressive strength insulation, suitable for service, at oversized saddles and shoes where insulation saddles have not been provided.

3.04 REMOVABLE, PRE-FABRICATED, INSULATION AND ENCLOSURES

- .1 Application: at valves, flanges and unions at equipment.
- .2 Design: to permit movement of expansion joint and to permit periodic removal and replacement without damage to adjacent insulation.
- .3 Insulation:
 - .1 Insulation, fastenings and finishes: same as system.
 - .2 Jacket: PVC.

3.05 PIPING INSULATION SCHEDULES

- .1 Includes valves, valve bonnets, strainers, flanges and fittings unless otherwise specified.
- .2 TIAC Code: A-1.
 - .1 Securements: SS wire at 300 mm on center.
 - .2 Seals: lap seal adhesive, lagging adhesive.
 - .3 Installation: TIAC Code 1501-H.
- .4 TIAC Code: A-3.
 - .1 Securements: SS wire at 300 mm on center.
 - .2 Seals: VR lap seal adhesive, VR lagging adhesive.
 - .3 Installation: TIAC Code: 1501-C.
- .5 Thickness of insulation as listed in following table.
 - .1 Run-outs to individual units and equipment not exceeding 4000 mm long.
 - .2 Do not insulate exposed runouts to plumbing fixtures, chrome plated piping, valves, fittings.

Application	Temp Degrees C	TIAC Code	Pipe Sizes (NPA) and Insulation Thickness (mm)				
			to 1	1 1/4 to 2	2 1/2 to 4	5 to 6	8 & over
Hot Water Heating	60 - 94	A-1	25	38	38	38	38
Hot Water Heating	up to 59	A-1	25	25	25	25	38
Chilled Water	4-13	A-3	25	25	25	25	25

Designated Support Space	Thermal Insulation	Section 23 07 15
1 st Floor JCB	for Piping	Page 7
R.086261.003		January, 2017

Chilled Water	below 4	A-3	25	25	38	38	38
Dom-estic CWS		A-3	25	25	25	25	25

.8 Finishes:

- .1 Exposed indoors: PVC jacket.
- .2 Exposed in mechanical rooms: PVC jacket.
- .3 Concealed, indoors: canvas on valves, fittings. No further finish.
- .4 Use vapour retarder jacket on TIAC code A-3 insulation compatible with insulation.
- .5 Installation: to appropriate TIAC code CRF/1 through CPF/5.

3.06 CLEANING

- .1 Proceed in accordance with Section 01 74 11 - Cleaning.
- .2 Upon completion and verification of performance of installation, remove surplus materials, excess materials, rubbish, tools and equipment.

END OF SECTION