



**Correctional Service Canada
Scope of Work**

Project Name: Warkworth Institution Door Replacements – Door & Hardware Schedule

Project Number: 460-2608-0

Institution: Warkworth (Medium Security)

Building WW02

Door 110

1	Single Door 14Ga Insulated	36"W x 84"H
1	Frame Size	64"W x 90"H
2	Tempered Insulated Half Side Lites	125mm W
2	Tempered Insulated Half Lites in Door	125mm W 600mm H
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Threshold	
1	Strike Plate	

NOTE: Reuse Existing Electric Strike and Lock.

Building WW07

Door 101

1	Single Door 14Ga Insulated	44"W x 90 1/2"H
1	Frame Size	67"W x 92 1/2"H
2	Tempered Insulated Half Side Lites	125mm W
2	Tempered Insulated Half Lites in Door	125mm W 600mm H
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	

NOTE: Reuse Existing Lock. Add Strike Shield to lock.

Building WW07

Door 122

1	Single Door 14Ga Insulated	36"W x 90"H
1	Frame Size	67"W x 112"H
2	14Ga Insulated Side Panels	
1	14Ga Insulated Transom	
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	
1	Lockset - Locks to be keyed both sides.	FG80 Deadlock



**Correctional Service Canada
Scope of Work**

Building WW07
Door 124

1	Single Door 14Ga Insulated	36"W x 90"H
1	Frame Size	67"W x 112"H
2	14Ga Insulated Side Panels	
1	14Ga Insulated Transom	
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	
1	Lockset - Locks to be keyed both sides	FG80 Deadlock or Equal

Building WW07
Door 145

1	Single Door 14Ga Insulated	43"W x 89"H
1	Frame Size	67"W x 112"H
2	Tempered Insulated Half Side Lites	125mm W
2	Tempered Insulated Half Lites in Door	125mm W 600mm H
1	14Ga Insulated Transom	
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	

NOTE: Reuse Existing Lock.

Building WW07
Door 153

1	Single Door 14Ga Insulated	43"W x 89"H
1	Frame Size	67"W x 112"H
2	Tempered Insulated Half Side Lites	125mm W
2	Tempered Insulated Half Lites in Door	125mm W 600mm H
1	14Ga Insulated Transom	
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	

NOTE: Reuse Existing Lock.



**Correctional Service Canada
Scope of Work**

Building WW12
Door 101

1	Double Door 14Ga Insulated	36"W x 89"H
1	Frame Size	66"W x 92"H
2	Tempered Insulated Half Lites	125mm W
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls - On Active Door Only	
1	Stainless Steel Kick Plate	
1	Panic Bar	
1	Head & Foot Bolt - One Door Only	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	
1	Lockset - Keyed Both Side	FG80 Deadlock

NOTE: Second Door Width Is Determined By Remaining Width In Frame. Provide Astragal on non-active door.

Building WW12
Door 132

1	Double Door 14Ga Insulated	36"W x 89"H
1	Frame Size	63"W x 93"H
1	Tempered Insulated Half Lite In Each Door	125mm W
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls - On active Door Only	
1	Stainless Steel Kick Plate	
1	Head & Foot Bolt - One Door Only	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Lockset - Keyed Both Side	FG80 Deadlock

**NOTE: Second Door Width Is 24"W
Provide Astragal on non-active door.**

Building WW14
Door 108

1	Single Door 14Ga Insulated	35 1/2"W x 79 1/2"H
	Frame Size	40"W x 82"H
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	
1	Lockset - Keyed Both Sides	FG80 Deadlock



**Correctional Service Canada
Scope of Work**

Building WW16
Door 106

1	Single Door 14Ga Insulated	35 1/2"W x 79 1/2"H
1	Frame Size	40"W x 82"H
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	
1	Lockset - Keyed Both Sides	FG80 Deadlock

Building WW18
Door 111

1	Single Door 14Ga Insulated	36"W x 80"H
1	Frame Size	40"W x 82"H
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
2	Stainless Steel Door Pulls	
1	Stainless Steel Kick Plate	
1	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	

NOTE: Reuse Existing Lock.

Building WW26
Door 117

1	Double Door 14Ga Insulated	36"W x 84"H
1	Frame Size	94"W x 86"H
2	Tempered Insulated Half Side Lites	125mm W
4	Tempered Insulated Half Lites	125mm W
3	Heavy Duty Surface Mounted Hinges - Southern Folger 205	
4	Stainless Steel Door Pulls	
4	Stainless Steel Kick Plate	
1	Head & Foot Bolt - One Door Only	
2	Heavy Duty Door Closer	
1	Weather Strip & Sweep Kit	
1	Thermally Broken Threshold	
1	Lockset - Keyed Both Side	FG80 Deadlock

NOTE: Provide Astragal, increase jamb depth, provide exterior rain-drip and interior batten at head.
