

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
1.1	AIRR-01	Air Compressor	Commercially Available	Portable Air Compressor Unit See AAIR-02, AAIR-03	Dewalt	D55151		- Includes air gun and retractable cord - ensure 120 volt connection is provided - 14 Amp - 2.5 HP - 4 Gallon Oiled Twin Hot Dog Compressor	1
1.2	AIRR-02	Air Compressor Hose	Commercially Available	Portable Air Compressor Hose Portable Hose See AAIR-01, AAIR-03	Dewalt	DWFP1450D		50ft Air Hose to suit AIRR-01	1
1.3	AIRR-03	Air Compressor Reel	Commercially Available	Portable Air Compressor Hose Reel for Hose Storage See AAIR- 02, AAIR-03	Speedaire	SDR2CUA7		- 50ft air hose reel - wall mounted to suit AIRR-01	1
2.0	BAGG-01	Blue Bag	Commercially Available	Security Blue Bag	The RO-EL Group	100 - RLG52106	Color: Blue	- Re-useable zip closure security bag minimum 2000 trips - Tamper evident zipper closure - Weight capacity 3.2 kg (7 lbs) - Construction: Water-resistant polyvinyl chloride (PVC)-coated nylon - Size: 279-330mm (11-13") W x 381-432mm (15-17") H - Includes a reversible address label - Colour: Blue	100
3.0	BBRD-01	Bulletin Board	Commercially Available	Bulletin Board with Frame	Forbo Linoleum Inc.	Bulletin Board	Extruded Aluminum Frame, Finish: Satin Anodize. Tack board Colour: 2182 Potato Skin.	- Size: 1000mm (40") W x915mm (36") H - Extruded Aluminum Frame with Satin Anodize Finish - Hardboard backing: 6-7mm (1/4") thickness - Frame width: maximum 51mm (2") - Frame thickness: 8mm (5/16") - Tack board surface: Linoleum, self-healing, minimum 6mm (1/4) - colour: 30% Warm Grey	3
4.0	BBRD-02	Bulletin Board	Commercially Available	Mobile Bulletin Board / white board	Egan	Egan Dimension Mobile	One side Egan Fabric, one side EVS Surface, powdercoated White Frame	- 915mmWx1524mmHx600mm deep - powdercoated aluminum frame - magnetic white board surface - tackable surface - locking casters.	1
5.0	BEDD-01	Medical Bed	Commercially Available	Manual Bed Package with Innerspring Mattress and Full- Length Rails	Seers Medical	SKN: V-SM2670 - Medicare 2 Section Mobile Treatment Table	Colour: Black	- Table supplied with side support rails and a paper holder - fitted fold up / down side support rails - purpose made precision bearings on all pivot points - lifting capacity of 240 kg - adjustable foot section with positive and negative angle - Manual Operated (26"Wx78"Lx30"H) - 120V Power Supply - colour: Black	1
6.0	BNCH-01	Bench	Commercially Available	Gathering space seating Blok - group of four seats (without backrests) of 30"x30" each - center table top of 12"x30", rift cut white oak. -2 x the group, Overall dimension - 112"x60"	Davis Furniture	Model: Blok, number to suit configuration	Rift cut white oak pallet, dark bronze leg finish to match project control sample; Momentum textiles, Bravo II, black.	Rift cut white oak veneer solid bench top c/w four cushion seats and centre 305mm clear surface table Overall dimension 40mm thick bench x 762mm wide x 2844mm long x 425mm high to top of cushion Set back solid plate dark bronze legs at each end with finish to match bronze project control sample Upholstery: Momentum textiles, Bravo II, black Multi-density foam Support beams as required for minimum legs plates Refer to plan drawing	8

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
7.0	BNCH-02	Bench	Commercially Available	Gathering space seating Blok - Model: group of three seats (with backrests) of 30"x30" each and two seats (without backrests) - Enter table top of 30"x30", rift cut white oak. - Overall dimension – 180"x30"	Davis Furniture	Model: Blok, number to suit configuratio	Rift cut white oak pallet, dark bronze leg finish to match project control sample; Momentum textiles, Bravo II, black.	Rift cut white oak veneer solid bench top c/w three cushion seats with back rest, two cushion seats without back rest and centre 762mm clear surface table Overall dimension 40mm thick bench x 762mm wide x 4572mm long x 425mm high to top of cushion Set back solid plate dark bronze legs at each end with finish to match bronze project control sample Upholstery: Momentum textiles, Bravo II, black Multi-density foam Support beams as required for minimal legs Refer to plan drawing	2
8.0	BNCH-03	Bench	Commercially Available	Gathering space seating Blok - group of two seats (with backrests) of 30"x30" each and one seat (without backrests) - End table top of 30"x30" and in between table top of 12"x30", rift cut white oak. - Overall dimension – 112"x30"	Davis Furniture	Model: Blok, number to suit configuration	Rift cut white oak pallet, dark bronze leg finish to match project control sample; Momentum textiles, Bravo II, black.	Rift cut white oak veneer solid bench top c/w three cushion seats and end 1066mm clear surface table Overall dimension 40mm thick bench x 762mm wide x 3352mm long x 425mm high to top of cushion Set back solid plate dark bronze legs at each end with finish to match bronze project control sample Upholstery: Momentum textiles, Bravo II, black Multi-density foam Support beams as required for minimal legs Refer to plan drawing	1
9.0	BNCH-04	Bench	Commercially Available	Gathering space seating Blok - Model: group of three seats (without backrests) of 30"x30" each and two seats (with backrests) - Enter table top of 30"x30", rift cut white oak. - Overall dimension – 180"x30" 425mm	Davis Furniture	Model: Blok, number to suit configuratio	Rift cut white oak pallet, dark bronze leg finish to match project control sample; Momentum textiles, Bravo II, black.	Rift cut white oak veneer solid bench top c/w two cushion seats with back rest, three cushion seats without back rest and centre 762mm clear surface table Overall dimension 40mm thick bench x 762mm wide x 4572mm long x 425mm high to top of cushion Set back solid plate dark bronze legs at each end with finish to match bronze project control sample Upholstery: Momentum textiles, Bravo II, black Multi-density foam Support beams as required for minimal legs Refer to plan drawing	1
10.0	BNCH-05	Bench	Commercially Available	Gathering space seating Blok - group of five seats (without backrests) of 30"x30" each - Enter table top of 30"x30", rift cut white oak. - 2 x the group, Overall dimension – 180"x60"	Davis Furniture	Model: Blok, number to suit configuratio	Rift cut white oak pallet, dark bronze leg finish to match project control sample; Momentum textiles, Bravo II, black.	Rift cut white oak veneer solid bench top c/w 5 cushion seats without back rest and centre 762mm clear surface table Overall dimension 40mm thick bench x 762mm wide x 4572mm long x 425mm high to top of cushion Set back solid plate dark bronze legs at each end with finish to match bronze project control sample Upholstery: Momentum textiles, Bravo II, black Multi-density foam Support beams as required for minimal legs Refer to plan drawing	2
11.1	BROM-01	Broom	Commercially Available	Broom w/Vinyl Handle See BROM-02	Atlas Graham	Broom Head: Trailblazer Upright Broom Head #772 48" Broom Handle: Aluminum Handle with Threaded Tip #2408		- To be compatible with BROM-02 - Aluminum with nylon tip - 1194-1245mm (47-49") long handle Head: - Fine synthetic fibre bristles - Fibres to be fused into the block - Water and chemical resistant	6
11.2	BROM-02	Dust Pan	Commercially Available	Dust Pan, Long Handle See BROM-01	Rubbermaid Commercial Products	FG253100BLA Size: 287mm (11.3") x 325mm (12.8") x 127mm (5")	Colour: black	- To be compatible with BROM-01 - Adjustable handle grip - to include rear wheels - Size: 279-330mm (11-13") x 305-356mm (12-14") x 102-152mm (4-6") - Handle length: minimum 762mm (30") - Colour: Black	9
12.1	BROM-03	Broom	Commercially Available	Dust Mop	Rubbermaid Commercial Products	Rubbermaid J253 Twisted loop dust mop	Colour: Black	Twisted loop dust mop 61cm x 12.7cm	4
12.2	BROM-04	Broom	Commercially Available	Dust Mop, Long Handle	Rubbermaid Commercial Products	M253 Snap-on Wire dust mop frame	Colour: Black	To to suit BROM-03	4

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
13.1	BROM-05	Broom	Commercially Available	Dust Mop	Rubbermaid Commercial Products	Rubbermaid J255 Twisted Loop Blend Dust Mops	Colour: Black	Twisted Loop Dust Mop 91.4cm x 12.7cm	4
13.2	BROM-06	Broom	Commercially Available	Dust Mop, Long Handle	Rubbermaid Commercial Products	Rubbermaid M255 Snap-on wire dust mop frame	Colour: Black	To to suit BROM-05	4
14.0	CAGE-01	Security Cages	Commercially Available	Security Cages - Storage Unit	Metro Storage Systems	Cage: SEC55LC Shelf: A2448NC	Finish: Chrome	- 713mmWx 1285mmL x 1739mmH, - heavy duty model with wrap around bumpers and 5" (127mm) diameter casters. - To Include: Intermediate Shelves - 2 (two) adjustable shelves Security cages must have heavy duty base, 2 fix caster wheels and 2 swivel caster wheels ,	8
15.0	CAGE-02	Flood Cages	Commercially Available	Flood Cages - Storage Unit	Metro Storage Systems	Cage: SEC53LC Shelf: A2436NC	Finish: Chrome	- Wrap around bumpers - 5" (127mm) diameter casters. - Heavy duty applications: 900lbs. (408kg) total unit capacity evenly distributed - To Include: Intermediate Shelves - 2 (two) adjustable shelves. - Heavy-duty chrome construction - Open wire mesh - Lockable - Size: 713 W x 980 L x 1739mmH	1
16.0	CART-01	Cleaning Cart	Commercially Available	High Capacity Cleaning Cart	Rubbermaid Commercial Products	9T72 - FG9T7200BLA High Capacity Cleaning Cart High Capacity Vinyl Replacement Bag: 9T80 Size: 1264mm (49.8") L x 552mm (21.8") D x 975mm (38.4") H	Cart: Black, Bags: Yellow	- High Capacity Cleaning Cart, - To include heavy duty zippered vinyl bag - Three (3) shelves - Minimum 5 cu.ft. of storage space - Fits a 889mm (35") x 1270mm (50") replacement garbage bag - Locking bucket attachment - Includes two (2) removable minimum 9.4 liter (10 quart) caddies - Rubber tool grips hold handles upright, 4" swivel caster and 8" wheels	6
17.0	CHRS-02	Sofa	Commercially Available	3 Seater Sofa	Teknion	Vignette - NVBS D-V496-C	Momentum textiles, Bravo II line, colour Bark, leg finish chrome	- 3 seater sofa fully upholstered - 711mm x 2108mm X 736mm H, - tested for up to 250lbs without deforming, - high density block foam w/ plywood frame construction	2
18.0	CLMP-01	Clamps	Commercially Available	Wall Mounted Mat Clamps	Hamel Manufacturing	825SD	Stainless Steel	- Four (4) - Durable decal - Durable block - Formed top - Stainless steel spring - Welded axle - Wall mountable - Size: minimum 3mm (1/8") x 38mm (1 1/2") base - Stainless Steel - colour black	1
19.0	CPUH-01	CPU Holder	Commercially Available	Undermount CPU Holder	Richelieu	Ergo 500735190	Colour: black	- Plastic side clamp with knob control - Side-mountable - Adjustable width: 89-236mm (3.5" to 9.3") - Adjustable height: 343-572mm (13.5" to 22.5") - Adjustable depth: 376-566mm (14.8" to 22.3") - 406-457mm (16-18") plastic glide track - Weight capacity: 85lbs	7
20.0	CURT-01	Vinyl Curtain	Commercially Available	Heavy Duty Curtain w/ Track	TMI Group of Companies	Clean Screen Curtain	Colour: Clear	- Clear USDA low temperature grade, - non-porous, - 0.40" thick clear flexible PVC curtains - stainless steel grommets and round rod track - sliding track hardware - 4400mmWx3900mmH approx.	1

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
21.1	DOLL-01	Barrel Dolly	Commercially Available	Square Heavy Duty Dolly Suitable for Recycle Barrel Containers	Rubbermaid Commercial Products	3530 BRUTE Square Dolly - FG353000BLA Brute Dolly	Colour: Black	<ul style="list-style-type: none"> - Capacity up to 300lb continuous Static Load Rating, - Containers Size: 438mm (17.2") W x 438mm (17.2") D x 159mm (6.2") H Square - To be compatible with carrying corresponding RECY-02 units, - All plastic construction - Rust, chip and dent resistant - Heavy-duty rubber wheels with swivel capabilities 	6
21.2	RECY-02	Recycling Barrel Container	Commercially Available	Square Recycling Container without Lid See DOLL-01 Heavy Duty	Rubbermaid Commercial Products	3536-73 BRUTE (FG353673) Square Recycling Container without Lid Size: 597mm (23.5") W x 597mm (23.5") D x 737mm (29") H	Color: Blue.	<ul style="list-style-type: none"> - Must be compatible with DOLL-01 - Square shaped - Contains post-consumer recycled resin (PCR) construction - Size: 584-635mm (23-25") L x 584-635mm (23-25") W x 711-762mm (28-30") H - Volume capacity : minimum 152 litres (40 gal) - Universal recycling symbol printed in white on side of recycling container - Colour: Blue with white printing 	6
22.1	DOLL-02	Barrel Dolly	Commercially Available	Round Heavy Duty Dolly Suitable for Waste Barrel Containers	Rubbermaid Commercial Products	2640 BRUTE Dolly - FG264000BLA Brute Dolly	Colour: Black	<ul style="list-style-type: none"> - Capacity up to 350lb continuous Static Load Rating, - Round - To be compatible with corresponding WAST-02 - All plastic construction - Rust, chip and dent resistant - Heavy-duty rubber wheels with swivel capabilities - Size: 445-470mm (17.5-18.5") DIA. x 168mm (6.6") H 	3
22.2	WAST-02	Garbage Barrel	Commercially Available	Container without Lid – Round See DOLL-02	Rubbermaid Commercial Products	BRUTE 2632 (FG263200 Gray) Contracted: 410-2632 Gray/06 410-2640BL A/02 Capacity: 32 gallons	Colour: Gray	<ul style="list-style-type: none"> - Capacity: minimum 121 liters (32 gallon) - Must accept 889mm (35") x 1270mm (50") garbage bags - All-plastic construction: rust, chip, peel and dent resistant - Reinforced rims - Built-in handles - Double-ribbed base - No lid - Meets Hazard Analysis and Critical Control Points (HACCP) guidelines - Size: 533-584mm (21-23") diameter x 686-737mm (27-29") H - Colour: Gray 	3
23.0	ESCL-01	Escalator Cleaner	Commercially Available	Floor Model Escalator Cleaner	Windsor Industries Inc.	Treadway 1.310-108.0		<ul style="list-style-type: none"> - Foot pedal operated brake and brush heads - Tank-in-tank system - Floor model - Short brush head - One-button operation - Handle folds down - at least Four (4) hoses - Two (2) counter-rotating, motor-driven roller brushes - Centering skid - Outboard deflectors 	1

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
24.0	FILE-01	Filing Cabinet	Commercially Available	4 Drawer Lateral Filing Cabinet	Artopex	47-41-036-3333-1CW	Colour: Black, Laminate top and edging: Black, pulls: black	<ul style="list-style-type: none"> - 889-940mm (35-37") W x minimum 457mm (18") D x 1346-1397mm (53-55") H - Four (4) - 610mm (12") H high drawer lateral file with fixed front - Integrated full-width rectangular pull - steel construction - Invisible welds - Full-height lateral reinforcement - Double-thickness floor - Safety system prevents two drawers from opening at once - Lock - Accessible levellers - Ball bearing suspension - Side-to-side hanging bars and chrome lock - Counterweight - To include laminate top - Colour: Black - sample to be approved by technical authority after contract award 	5
25.0	FILE-02	Filing Cabinet	Commercially Available	2 Drawer Lateral Filing Cabinet	Artopex	47 Series: 47-25-036-33-3067	Colour: Black, Laminate top and edging: Black, pulls: black	<ul style="list-style-type: none"> - 889-940 mm (35-37 ") W x minimum 457mm (18") D x 635-685mm (25-27") H - Two (2) drawer lateral file with fixed front - Integrated full-width rectangular pull - steel construction - Invisible welds - Full-height lateral reinforcement - Double-thickness floor - Safety system prevents two drawers from opening at once - Lock - Accessible levellers - Ball bearing suspension - Side-to-side hanging bars and chrome lock - Counterweight - To include laminate top 	1
26.0	FLOR-01	Floor Auto Scrubber	Commercially Available	Walk Behind Battery Powered Automatic Scrubber Dryer	Taski Swingo 1255B	Taski Swingo 1255B. Floor Scrubber dryer model		<ul style="list-style-type: none"> - Must have gel batteries, self-propel, - hour meter gage, - off board chargers, - 2 brush pads and 2 pad holders required - 67" L X 22" W X 33" H - No specific colour required; - 3m power cord (Retractable built-in cord for charging) 	3
27.0	FLOR-02	Floor Burnisher	Commercially Available	Battery Powered Floor Burnisher with Dust Control Polisher	Tennant	Tennant B5		<ul style="list-style-type: none"> - 20 inch pad. battery powered floor burnisher with dust control polisher, - must have gel batteries, self-propel, - hour meter gage, - off board chargers - No specific colour required. 	2
28.0	FLOR-03	Floor Burnisher	Commercially Available	High RPM Cord-Electric Floor Burnisher	Pacific Floor Care	B-1500 (495460 : Cast Alum. Base)		<ul style="list-style-type: none"> - Cast Alum. Base. 1500 RPM, 67"x22"x33". - Incl. natural fiber burnishing pads; - Hand held - impact resistant polyethylene base construction - Minimum 508mm (20") pad diameter - Productivity per hour: minimum 844 sq.m. (9,090 sq.ft.) - Dual switch levers with safety lock-out switch - Steel-plated handle tube - Carbon brush wear indicator light 	3

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
29.0	FLOR-04	Floor Buffer	Commercially Available	Handheld Cord -Electric Dual Speed Polisher	Dustbane Products Inc.	Integra 19915 (19" TX)		<ul style="list-style-type: none"> - Hand held - Adjustable handle - Rotationally molded, - polyethylene base: 480mm (19") - Two finger operation trigger - Speed: 175-320 rpm - Motor Power: permanent magnet, minimum 1.5 hp (3200 rpm) - Volt: 115 AC - Amps: Low: 10 A, High: 13 A - Gear box 	1
30.0	FLOR-05	Floor Sweeper	Commercially Available	Battery Powered Vacuum Sweeper	Advance	Advance SW900 Floor Sweeper.		<ul style="list-style-type: none"> - Must have gel batteries, - self-propel 55" L x 37" W x 43" H (1390 x 950 x 1100mm), - 24" Working width, - No specific colour required. 	3
31.0	FRIG-01	Refrigerator	Commercially Available	Refrigerator	Whirlpool	WRT541SZDW	Colour: Black	<ul style="list-style-type: none"> - ADA compliant, - Automatic temperature control - Reversible door - Adjustable temperature control, - Range capacity: 20.28 cu. ft. to 21.3 cu.ft - Energy star certified - Range. width: 760mm (30) to 831mm (32.75") - Range height: 1651mm (65") to 1682mm (66") - 29.2"Wx28.6"Dx86.5"H (740 W x 725 D x 2195 H mm) 	2
32.0	FRIG-02	Refrigerator	Commercially Available	29" standing commercial grade beverage refrigerator 1 door 5 chromed steel shelves , adjustable	KingsBottle	KBU650	Colour: stainless steel	<ul style="list-style-type: none"> - beverage refrigerator - 1 door - double layer tempered glass - 2 year warranty (included) - adjustable 5 chromed steel shelves - digital thermostatic control 	1
33.0	FRIG-03	Refrigerator	Commercially Available	Display beverage cooler	KingsBottle	KBU-56-BP	Colour: Black	<ul style="list-style-type: none"> - Black Finish - commercial grade under counter beverage cooler - 2 self-closing doors, heated LOW-E glass with stainless steel frame - chrome shelves - front venting heat dispersions - Noise levels to not exceed 68 dB - LED lights - temperature controller - energy saving management - commercial grade stainless steel exterior and interior - 35.4" W X 20.9 D X 33" H (900 X 736 X 838mm H) 	1
34.0	GARM-01	Garment Rack	Commercially Available	Mobile Garment Rack	Quality Fabricators Z Racks	The Heritage 360729 Z-Rack	Colour: Black	<ul style="list-style-type: none"> - Multi-purpose garment truck designed to handle both standing and flat packed merchandise - Brake Casters, Top & Bottom shelves, 63"Lx23"Wx78"H; Steel construction - Two (2) shelves - Uprights with 500lb Capacity - 127mm (5") non-marking Casters, - Revolving Bumpers for wall protection - Steering Handle - nestable - powder coated finish in black - See LAUN-01 for hangers. 	12

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALLY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
35.0	HOLD-01	Utility Holder	Commercially Available	Mop and Broom holder Three (3) holder wall mounted	Bradley Corp.	9953 Three (3) Mop / Broom Holders Size: 610mm (24") W x 70mm (2.75") D x 102mm (4") H	Colour/Finish: stainless steel satin finish	<ul style="list-style-type: none"> - Three (3) Mop / Broom Holders - Wall mounted Backplate - Size: 584-635mm (23-25") W x 51-102mm (2-4") D x 76-127mm (3-5") H - Minimum thickness 22 gauge stainless steel - Exposed surfaces stainless steel - Spring-activated rubber cams on plated steel retainers - Holds a mop or broom with a diameter between 16mm (5/8") and 25.4mm (1") 	7
36.0	HOOK-01	Coat Hook	Commercially Available	Wall Mounted Coat Hook	Mockett	CH53 Satin	Colour/Finish: nickel finish	<ul style="list-style-type: none"> - multi-level square plate coat hook - 3.75"H x 2.75" W x 2" projection - Stainless steel with satin nickel finish - Concealed fasteners - No pointed corners 	6
37.0	HOSE-01	Hose	Commercially Available	Utility Hose	Acklands Grainger	WWG3LFX9 Manufacturer #: 3LFX9 UNSPSC #: 40142008 Rubber Utility Hose - 1200mm (4') supply / fill hose - Includes brass faucet adapter	Colour: Black	<ul style="list-style-type: none"> - Rubber utility hose - 1200mm (48") length - To include brass faucet adapter to attach to slop sinks or other - Colour: Black 	7
38.0	KEYB-01	Keyboard Tray	Commercially Available	Keyboard Tray System	ISE Group Inc.	Leader 4 - SKATE Skate Platform with A-LSTL Keyboard Arm Leader Standard Series with Lever free Spring-Assisted Arm	Satin black powder coated arm finish	<ul style="list-style-type: none"> - Leader 4 - SKATE Skate Platform with A-LSTL Keyboard Arm - Leader Standard Series with Lever free Spring-Assisted Arm - low profile arm with superior knee clearance - lift and lock for effortless height adjustment - single surface keyboarding and mounting - +10deg to -20 deg tilt range. - Track: 597mm (23.5") Corner: 457mm to 559mm (18" to 22") Size: 686mm (27") L x 305mm (12") D 	12
39.0	LADD-01	Ladder	Commercially Available	Extra-Heavy Duty Aluminium Step	Featherlite Industrial Ladders	3400 Series: 3408 Type 1A Capacity 136 kg (300 lbs) 2438mm (8 ft.) H ladder		<ul style="list-style-type: none"> - Extra-Heavy Duty aluminum ladder - Size: minimum 2440mm (8') - Open height: 2286-2337mm (90-92") - Heavy duty aluminum step - Minimum 76mm (3") slip-resistant serrated aluminum steps - Co-polymer utility top - Hinged utility tray - Zinc-coated steel spreader arms - Meets or exceeds CSA (Canadian Standards Association) Grade 1A, ANSI Type 1A - Load capacity: minimum 136 kg (300 lbs) - No specific colour required. 	3
40.0	LADD-02	Ladder	Commercially Available	Extra-Heavy Duty Aluminium Step	Featherlite Industrial Ladders	3400 Series: 3406 Type 1A Capacity 136 kg (300 lbs.) 1829mm (6 ft.) ladder		<ul style="list-style-type: none"> - Heavy Duty Aluminium ladder - Size: minimum 1830mm (6') x 533mm (21") W - Open height: 1702-1753mm (67-69") - Minimum 76mm (3") slip-resistant serrated aluminum steps - Co-polymer utility top - Hinged utility tray - Zinc-coated steel spreader arms - Meets or exceeds CSA (Canadian Standards Association) Grade 1A, ANSI Type 1A - Load capacity: minimum 136 kg (300 lbs.) 	4
41.0	LADD-03	Ladder Hook	Commercially Available	Ladder Hook	Racor	Tornado - 00525 Ladder Hooks	No applicable	<ul style="list-style-type: none"> - 30lbs capacity – 7" long hooks – rubber coated hook 	7
42.0	LADD-04	Mobile Step Ladder	Commercially Available	4 Step Rolling Safety Ladder	Uline	H-1934	Colour: Blue	<ul style="list-style-type: none"> - Two 5" wheels and two 6" rear rigid casters - 24" wide perforated metal steps - 400lbs Capacity - 4 step. - Overall Height 78" (1980), 34" W (864) X 37" D (940mm). 	2

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
43.0	LAMP-01	Task Light	Commercially Available	Portable Desk Lamp	Humanscale	Element Vision: EV-N-B-B LED Light	Colour: Black.	<ul style="list-style-type: none"> - Passive infrared motion sensor for automatically turns off and on - Black finish, round desktop base - One-touch positioning - Seven settings for dimmability - Multiple mounting options - Maximum reach of 28" (710mm) and working height of 18" (460mm) - Light output: 225 lumens - Efficacy: 32 lumens per watt - 3000k colour temperature - 5 years warranty - 4 per box. 	12
44.0	LAUN-01	Hanger	Commercially Available	Metal Coat Hanger See GARM-01	Richelieu	Metal Hanger - 301606140	Finish: Chrome finish	<ul style="list-style-type: none"> - if box of 10, 39 boxes are required. (Must have in total at least 390 hangers.) - Metal hanger - chrome finish - 35.35 mm Width, 175 H x 450 L mm 	39
45.0	MATS-01	Slush Mat	Commercially Available	High Resistance Carpet Mat	Tandus Centiva	Abrasive Action II #02578	6' Roll - Powerbon Cushion Backing - Colour: Charcoal #19100	<ul style="list-style-type: none"> - 6' roll, 0.384" (9.75mm) thickness - Non-woven synthetic fiber - 24 oz per sq yd - 8.0 stitches per inch - 1.187 average pile height - Textured pattern - Colour: Charcoal, refer to drawings for area and extent. 	505
46.0	MOPB-01	Bucket and Wringer	Commercially Available	Downpress Bucket & Wringer	Vileda Professional	Downpress Wringer: 134710 Bucket:134725	Wringer: Blue. Bucket: Blue w/ 3" casters	<ul style="list-style-type: none"> - Wringer & Bucket to be compatible - 24.6-37.8 liter (26-40 quart) capacity - Molded graduations to facilitate accurate measurements - Flared base - Opening for mop access with the wringer attached - Injection molded with high density polymer - Gears and pressure plates are fiber-reinforced nylon - Wrings all wet mops from 340 g to 900 g (12 oz. to 32 oz.) - Downward pressure style - 3" Castors Wringer: 	4
47.1	MOPH-01	Mop Head	Commercially Available	Large MicroFiber Tube Mop See MOPH 02	Rubbermaid Commercial Products	T813-06	Color: Gray, 1" headband, 6 per pack.	<ul style="list-style-type: none"> - To be compatible with MOPH-02 - 1" Headband and tailband construction - 19-32mm (0.75-1.25") PVC mesh Headband - Striped tube design - Machine washable - To withstand laundry cycles at 200F with detergents and bleach - Microfiber yarn tube mop - Requires no adapters or new flat-mopping handles or frames - 6 per pack, or 24 total - No specific colour required 	4
47.2	MOPH-02	Mop Handle	Commercially Available	Plastic Mop Handle Fiberglass? See MOPH 01	Impact Products	#84 Mop Handle Size: 1372mm (54") L	Fiberglass Handle . Color: Orange. 12 per Case	<ul style="list-style-type: none"> - To be compatible with MOPH-01 - 178-203mm (7-8") Head - Injection molded head - Rust and corrosion resistant - Fibreglass shaft - Non-marring - Size: 1346-1397mm L - Weight: maximum 0.9 Kg (2lbs) - 12 per case - Material: Fibreglass - Colour: No specific colour required 	4

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
48.0	OHSE-03	Transport Chair (Wheelchair)	Commercially Available	Folding Ultralight Transport Chair	Airgo	Comfort Plus: 700-846	Colour: black	<ul style="list-style-type: none"> - Minimum weight capacity: 300lbs - 19" Seat Width - Detachable flip-back armrests - Fold down back - Removeable push-in and swing-away foot rests - Foot rests with heel loops - Seatbelt - Dual locking rear wheels - Chip resistant finish - Maximum chair weight: 10kg (22lbs) - No specific colour required. 	9
49.1	OHSE-11	Medical Bag	Commercially Available	Medical Bag w/ Vinyl Base	Acklands Grainger	FTMY2037174B	Vinyl Base, Padded Interior. Colour: Red	<ul style="list-style-type: none"> - Supplier to store OHSE-06, OSHE-08, OHSE-09 INSIDE OHSE-11 - Colour: Red 	1
49.2	OHSE-06	Defibrillator	Commercially Available	Automated External Defibrillator (AED)	Cardiac Science	Powerheart AED G3 (9300A-1001)	Fully Automatic with Ready Kit. 80mmX310mmX270mmt	<ul style="list-style-type: none"> AED unit: <ul style="list-style-type: none"> - Operations: Fully automatic - Allowable energy range (J): Escalating Variable Energy (VE) 95J to 351J - Escalating variable energy (VE) 95J to 351J - Factory default: 200VE, 300VE, 300VE - Voice prompts: Voice prompts guide user through CPR process - Text screen: Displays text prompts to guide user through rescue process and rescue information for EMS responders - Visible indicators: status indicator, battery status indicator, service indicator, pad indicator, text display - Audible alerts: voice prompt, system alert - Synchronized shock: Built-in automatic synchronization feature - Pacemaker pulse detection - Programmable - Pediatric capability Lithium battery - Canada Labour Code Level C Padded Kit - Unitized Packaging Colour: Red 	2
49.3	OHSE-08	First aid kit	Commercially Available	Canada Labour Code Level C Workplace Padded Kit	St-John Ambulance	NO-CLC-PA-3	Colour: Red	<ul style="list-style-type: none"> - Canada Labour Code Level C Padded Kit - Unitized Packaging Colour: Red 	2
49.4	OHSE-09	First Aid Blanket	Commercially Available	First Aid Blanket	Safety Media Inc.	AA92	Colour: Gray	<ul style="list-style-type: none"> - Fabric: 50% wool, 50% multi-blend fiber content - Machine washable - Size: 1500-1549mm (59-61") W x 2108-2159mm (83-85") L - No specific colour required. 	2
50.0	OHSE-07	First Aid-Backboard	Commercially Available	Complete with Restraints, three (3) qty per backboard	Ferno	Backboard: IE8050 - Millennia Boards Restraints: RS7734 Backboard	Backboard: Blue.	<ul style="list-style-type: none"> Backboard: - Size: 432-483mm (17-19") W x 1803-1854mm (71-73") D x 38-64mm (1.5-2.5") H - Contoured shape - Load capacity: 159kg (350 lbs) - Construction: Plastic and foam-filled - Contains five pairs of X-ray translucent polycarbonate speed clip pins, offset - X-ray translucent - Weight 5-6 kg (11-13.2 lbs) - Restraints: - Qty. Three (3) - Nylon / polyester webbing, minimum width 51mm (2") - Quick-release, automotive-type, corrosion-resistant coated metal buckle - 18" Restraints: Black Plastic w/ Two Piece 7" Speed-Clip - Nylon/Polyester 	1
51.0	OHSE-10	Anti-Fatigue Mat	Commercially Available	Anti-Fatigue Mat	Crown Mats and Matting	#540 Supreme with Zedlan Foam Backing.	Colour: Steel Gray	<ul style="list-style-type: none"> - 915mm x 1524mm - Zedlan foam backing - slip-resistant surface and for cart traffic 	3

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
52.0	OHSE-12	Evacuation Chair	Commercially Available	EZ Glide with PowerTraxx	Ferno	PT5910	37.5" (953)H, 20" (516) W, 10" (254) Folded Depth	<ul style="list-style-type: none"> - Evacuation chair with wall mounted storage and backing - Metal frame construction - 5 position lift bar - Rechargeable battery - Wireless motor controls - Electronic brake - Four inh fron swivel wheels - Extra tall six inch rear wheels - 37.5" (953)H, 20" (516) W, 10" (254) Folded Depth 	1
53.0	OHSE-13	Anti-Fatigue Mat	Commercially Available		Crown	540 Supreme with Zedlan Foam Backing.	Colour: Steel Gray	<ul style="list-style-type: none"> - standard 5/8" thickness - Diamond pattern vinyl and slip-resistant surface that can tolerate cart traffic - PVC top material, High-grade foam backing - 2' x 3' 	4
54.0	OHSE-14	Safety Dome Mirror	Commercially Available	Safety Dome Mirror interior convex mirror	Uline	H-1548 Convex		<ul style="list-style-type: none"> - 2-way, wide angle 160° view - Indoor adjustable swivel and surface mount - 26" diameter - To include mounting hardware kit 	7
55.0	PALL-02	Stackable cage	Commercially Available	Stackable distribution cage - Fully Collapsible with Fold down rear gate	Retailquip	Standard stillage SmartCube		<ul style="list-style-type: none"> - Stackable distribution cage - Fully Collapsible with Fold down rear gate and outward swinging front gate - durable galvanized finish - 93kg total weight with and fold-down height of 400mm - size: 1017mm x 1224mm x 1210mm. 	16
56.0	PALL-03	Caged Carrier	Commercially Available	Metal pallet cage for transport	Novodinamica	303x Series	Powder coated steel. Colour: Grey	<ul style="list-style-type: none"> - Powder coated steel pallet cage C/w dropped down loading pad - 1280mm L x 900mm 	10
57.0	PLAT-01	Aerial Platform	Commercially Available	Aerial Work Platform	Genie	AWP-20S		<ul style="list-style-type: none"> - D/C model unit (standard) - 20' Total Platform Height - 350lbs Lift Capacity (159kg) - Ensure aerial platform battery is gel battery - standard base. 	2
58.0	POST-01	Mail Sorting Unit	Commercially Available	Mail Sorting Unit	Mayline Group	Satellite Sorter: SA3680G1LAM Kwik-File Two (2) Columns at 11" wide Size: 914mm (36") L x 635mm (25") D x 2032mm (80") H	c/w high-pressure laminate work surface. Metal: Black. HPL Colour: Black with black edging	<ul style="list-style-type: none"> - 279mm (11") and 305mm (12") W pockets for mail sorting - Minimum 25mm (1") thick high-pressure laminate work surface is 660-711mm (26-28") D and adjusts within cabinet on 12.7mm (1/2") H increments - All-welded steel cabinet construction - Steel back panel of cabinet has one (1) 70-83mm (2.75-3.25") diameter cable management cut-out - Shelves adjust on 12.7mm (1/2") H increments - Size: 889-940mm (35-37") W x 508-559mm (20-22") D x 2007-2057mm (79-81") H - Finish: Black Edging: Black 	1
59.0	POWR-01	Power / Surge Bar	Commercially Available	Electric Power Bar - Surge Protector with (8) Multi-colored Sockets	Kensington Computer Products Group	Smart Socket: K6269INA Premium Adapter	Colour: Gray with multi coloured outlets	<ul style="list-style-type: none"> - Size: 63.5-76mm(2.5"-3") D x 152-193.5mm (6"-7.62") W x 330-376mm (13"-14.8") H - Eight (8) outlet strip surge protector - Minimum 3090 joules of dissipation - EMI/RFI noise filtration - Right-angle plug - Recessed on/off switch - 2400mm (8'-0") to 3048mm (10'-0") cord - Color-coded rings with matching cord labels - Minimum \$50,000 limited connected equipment warranty - Colour: Gray with multi coloured outlets 	13

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
60.0	RECY-01	Recycling Container	Commercially Available	Recycling and Waste	Rubbermaid Commercial Products	2956-73 Desk-side recycling container Desk-side recycling container	Colour: Blue with white printing	<ul style="list-style-type: none"> - Contains post-consumer recycled resin (PCR) - Size: 342mm-394mm (13.5-15.5")L x 228mm-279.4mm (9-11")L x 355mm-406mm (14-16")H - Minimum capacity: 27 litres (28-1/8 qt.) - Universal recycling symbol printed in white on side of recycling container - Colour: Blue with white printing 	24
61.0	RECY-04	Recycling Bins	Commercially Available	Easy Access Starcarts	Rubbermaid Commercial Products	Waste Mega Brute Model: 9W71 Mobile waste Collector 3 Pack 9W71 Mobile Waste Collector 3 Pack	Colour: Gray	<ul style="list-style-type: none"> - Corner pattern casters. - 63"x31"x69" - high capacity: carries up to 120 gallons or 400 lbs - Storage area for cleaning supplies - Include a 55-gallon can liner - Lid cover 	4
62.0	RECY-05	Recycling Bin	Commercially Available	Medium Rigid Liner	Rubbermaid Commercial Products	3566 Rigid Liner (FG356600)	Colour: Gray	<ul style="list-style-type: none"> - capacity: 25 gal (93.4 Litre) - 16.2"L x 16.2"W x 28.5"H - Rigid liner - All-plastic construction - chip, rust and dent resistant - Rolled rim 	1
63.0	SAFE-01	Safe Box	Commercially Available	Deposit Slot Safe	Fire King	B2020S	Colour: Black	<ul style="list-style-type: none"> - Painted metal frame base to raise top of safe to 650mm - B-rated safe – robbery and theft deterrent - Drop slot – direct deposit to top compartment - Multiple user codes –max. 30 - Time delay feature - Weight: 235 lbs - Exterior Dimensions: 20 1/2"H x 20 1/2" W x 20"D 	1
64.0	SANI-01	Hand Sanitizer	Commercially Available	Touchfree dispenser stand	Deb	92752		<ul style="list-style-type: none"> - base – 13"x13" - Touch free soap dispenser stand - Stand height: 45" (1140mm) - To suit SANI-02 	10
65.0	SANI-02	Hand Sanitizer	Commercially Available	Touchfree sanitizer dispenser	Deb	TF2CHR	Colour: Black and Chrome	<ul style="list-style-type: none"> - Soap dispensing system for use with Deb touch-free stand - D-cell batteries, will provide 5 years of operation in typical usage condition - 1200mL, 170mm W x 100mm D x 277mm H 	12
66.0	SHEL-01	Utility Shelf	Commercially Available	Hooks & Holders with Shelf	Bradley Corp.	9934 Five (5) qty. Hooks & Four (4) Holders	Metal: Stainless Steel 14 ga. , Finish: Satin.	<ul style="list-style-type: none"> - Wall Mounted - Shelf and Bracket: 18 gauge minimum thickness stainless steel - Five (5) qty. Hooks & Four (4) qty. Holders - Hooks: 14 gauge minimum thickness stainless steel - Holders: Spring-activated rubber cams on plated steel retainers, to hold a mop or broom handle with a diameter 13mm (0.5") - 32mm (1.25") Size: 1118mm (44") W x 203mm (8") D x 349mm (13.75") H 	4
67.0	SHEL-02	Metal Shelving	Commercially Available	Industrial Shelving	Uline	H-3353 with Six (6) adjustable shelves	Colour: Gray	<ul style="list-style-type: none"> - Open unit shelving system: posts, shelves and sway braces - Unit size: 889-940mm (35-37") W x 432-483mm (17-19") D x 1880-1930mm (74-76") H - 20-gauge steel shelves, welded box beams front and rear - Posts: 14 gauge - Side and rear braces: 11 gauge - Clip-type shelving components: shelves can be rearranged without the use of tools, nuts or bolts, and without disturbing adjoining units - Front and rear edges of the shelf are formed into a closed, welded box shape, with no ridges or protrusions - Includes side and rear cross braces - To have a minimum of six (6) shelves - Vertical adjustment on 25-44mm (1-1.75") centers - Shelf capacity: 364kg (800 lbs) - Lapped and welded corners - Finish: Powder-coat paint - Colour: Grey 	3

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
68.0	SHEL-03	Metal Shelving	Commercially Available	Industrial Shelving	Uline	H-3354 with Six (6) adjustable shelves	Colour: Gray	<ul style="list-style-type: none"> - Open unit shelving system: posts, shelves and sway braces - Unit size: 889-940mm (35-37") W x 584-635mm (23-25") D x 1880-1930mm (74-76") H - Clip-type shelving components: shelves can be rearranged without the use of tools, nuts or bolts, and without disturbing adjoining units - Front and rear edges of the shelf are formed into a closed, welded box shape, with no ridges or protrusions - 20-gauge steel shelves, welded box beams front and rear - To have minimum six (6) Adjustable Shelves - 14 gauge posts - 11 gauge side and rear braces - Vertical adjustment on 25-44mm (1-1.75") centers - Shelf capacity: 364kg (800 lbs) - Includes side and rear cross braces - Lapped and welded corners - Finish: Powder-coat paint - Colour: Grey 	15
69.0	SHEL-04	Storage Rack	Commercially Available	Wide Span Storage racks with particle board	Uline	H-1061 with Five (5) adjustable particle board shelves	Colour: Gray	<ul style="list-style-type: none"> - shelf capacity 1200 lbs - 5 shelves - Overall weight capacity: not to exceed 13,000 lbs - Particle board shelves - Boltless, fast snap-in metal 14 gauge steel frame - 72" W x 24" D x 84" H - 14 gauge steel 	3
70.0	SHEL-05	Storage Rack	Commercially Available	Wide Span Storage racks with particle board	Uline	H-1537 with Six (6) adjustable particle board shelves	Colour: Gray	<ul style="list-style-type: none"> - shelf capacity 1200 lbs - 6 shelves - Overall weight capacity: not to exceed 13,000 lbs - Particle board shelves - Boltless, fast snap-in metal 14 gauge steel frame - painted grey - 72" W x 18" D x 84" H 	2
71.0	SHEL-06	Storage Rack	Commercially Available	Wide Span Storage racks with particle board	Uline	H-1535 with Five (5) adjustable particle board shelves	Colour: Gray	<ul style="list-style-type: none"> - shelf capacity 1500 lbs - 5 shelves - Overall weight capacity: not to exceed 13,000 lbs - Particle board shelves - Boltless, fast snap-in metal 14 gauge steel frame, - painted grey - 72" W x 18" D x 84" H 	2
72.0	SHEL-07	Storage Rack	Commercially Available	Wide Span Storage racks with particle board	Uline	H-1969 with Seven (7) adjustable particle board shelves	Colour: Gray	<ul style="list-style-type: none"> - Each shelf capacity 1200 lbs - Total shelves: seven (7) - Overall weight capacity: not to exceed 13,000 lbs - Particle board shelves - Boltless, fast snap-in metal 14 gauge steel frame - painted grey - Size: 72" W x 18" D x 96" H - Overall capacity 13,000 lbs 	20
73.0	SHEL-08	Storage Rack	Commercially Available	Wide Span Storage racks with particle board	Uline	H-1966 with Seven (7) adjustable particle board shelves	Colour: Gray	<ul style="list-style-type: none"> - shelf capacity 1500 lbs - 7 (max) shelves - shelf support: 3 - Overall weight capacity: not to exceed 13,000 lbs - Particle board shelves - Boltless, fast snap-in metal 14 gauge steel frame - painted grey - 78" W x 18" D x 96" H 	12
74.0	SHEL-10	Storage Rack	Commercially Available	Wide Span Storage racks with particle board	Uline	H-1527 with Five (5) adjustable particle board shelves	Colour: Gray	<ul style="list-style-type: none"> - shelf capacity 1200 lbs - 5 shelves - Overall weight capacity: each shelf not to exceed 1200 lbs - Particle board shelves - Boltless, fast snap-in metal 14 gauge steel frame - painted grey - Size: 72" W x 18" D x 72" H 	1

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
75.0	SIGN-01	Sign - Wet Floor	Commercially Available	Bilingual "Caution Wet Floor" Floor Sign	Vileda Professional	134775 Wet floor sign	Colour: Yellow	<ul style="list-style-type: none"> - Durable plastic construction - Bilingual "Caution Wet Floor " in English and French imprinted on both sides - Size: 72 x 23 x 33 cm/ 28.35 x 9.06 x 12.99 in - Folding design - ANSI compliant graphics - graphic to be of man slipping within triangular shape 	90
76.1	SIGN-02	Sign - Hanging Closed for Cleaning	Commercially Available	Bilingual "Closed for Cleaning" Door Frame Hanging Sign	Vileda Professional	135029 Sign handle		<ul style="list-style-type: none"> - Adjustable horizontal rod for displaying door frame sign (SIGN-03) - Torsion action to secure pole - To suit doorways from 89 to 122 cm / 35 to 48 inches 	3
76.2	SIGN-03	Sign - Closed for Cleaning	Commercially Available	Bilingual "Closed for Cleaning" Floor Sign	Vileda Professional	135028 Sign flag	Colour: Yellow	<ul style="list-style-type: none"> - English and French Graphics equal in size - heavy duty vinyl sign - Part of SIGN-02. - Black Text: Closed for cleaning / Fermé pour le nettoyage - Sign colour: Yellow - Min. 5mm grommets on all 4 corners - To include hanging rings 	2
77.1	STAN-01	Stanchion	Commercially Available	Stanchion complete with base post & retractable belt See STAN-02	Tensabarrier	890 Slimline Series. Tensabarrier 890 Slimline series Base: 890B-MAX Basics	Include no-scuff ABS Cover.Post: 33S-T Satin Black Powder coat, standard finish. Belt: B9 Black (PMS426)13' belt	<ul style="list-style-type: none"> - Must be compatible with STAN-02 - Powder-coated post - Size: 907mm H x 38-64mm (1.5-2.5") dia. post, - Maximum 9.5kg (21lbs.) - Retractable 13' belt - Standard tape end - Cast iron base, 330-381mm dia. (13-15") c/w with scuff-proof plastic cover - Accessories: - Two (2) sign holder adapter bracket Satin black powder coated post 	48
77.2	STAN-02	Stanchion Cart	Commercially Available	Stanchion cart See STAN-01	Tensator	3035 Deluxe Storage Cart	Finish: Powder Coated: Colour: Black	<ul style="list-style-type: none"> - Must be compatible with STAN-01 - Transportation and storage of 18 stanchions (and accessories) - Size: 787-838mm (31-33") W x 1016-1067mm (40-42") x 1803-1854mm (71-73") H - Maximum 80 kg (175 lbs.) - Heavy gauge steel construction - 127-178mm (5-7") diameter locking casters - Padded slots to protect posts - Storage tray (for accessories) - Rubber bumpers 	3
78.0	STOL-01	Stool	Commercially Available	Aeron Work Stool	Herman Miller	AE712-A-WB-G1-PJ-C7-BK-3D01	Base & Frame Finish: Graphite (G1) - Hard Floor Casters (C7) - Armpad Finish: Black (BK) - Seat and Back: Carbon 3D01	<ul style="list-style-type: none"> - Mesh back and seat - Fully Adjustable arms - Footing mechanism that allows the user to adjust the height of the footing from a seated position - Five (5) star base - Pneumatic seat height adjustment - Tilt limiter that allows the user to select the tilt range to limit the amount of recline - Back support options and an adjustable lumbar support - Adjustable seat height range of 622-737mm (24-1/2"-29") - Size: 660-711mm (26-28") W x 483-533mm (19-21") seat width x 406-457mm (16-18") D; 1327mm (52-1/4") max. height 	10
79.0	STOL-02	Work Stool	Commercially Available	Work Stool	ADI Art Design International	Desire Series: DR-D-F-96-SS-LU Cylinder type = standard	Upholstery: Momentum Millenium Onyx black 2956, Base: black	<ul style="list-style-type: none"> - Cylinder type = standard - Stool height: Mechanism: Multi-Function, Center tilt, Infinite lock (F) - Arms: Multi function Urethane pad (96) - Seat: Sliding Seat Pan (SS) - Back: Air Lumbar (LU) 	1

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
80.0	STOR-01	Storage Cabinet	Commercially Available	2 Door Storage Metal Cabinet	Artopex	47 Series: 47-68-036-YYYY-3067	Color: Black (3067)	<ul style="list-style-type: none"> - 889-940mm (35-37") W x 432-483mm (17-19") D x 1956-2007mm (77-79") H - steel construction - Integrated rectangular pull - Invisible welds - Full height lateral reinforcement - Double-thickness floor - Accessible levellers - Two (2) doors - Four (4) adjustable shelves - Lockable - finish sample to be approved by technical authority after contract award 	1
81.0	STOR-03	Medicine Cabinet	Commercially Available	Stationary Cabinet	Artopex	47 Series: 47-38-030-YY-3067	Color: Black (3067)	<ul style="list-style-type: none"> - 30" W (762mm), 18" D (457mm or 460 it's ok), 40" H (1016mm)cabinet, two doors, two (2)adjustable shelves - Lockable - Handles: Full-length pull (integrated to the design of the door) - steel construction, invisible welds, double-thickness floor, - Enamel colour in standard finish - black Colour: Black sample to be approved by technical authority after contract award 	1
82.0	TAGG-01	Coat Check Tags	Commercially Available	Tags for confiscated items	Ketchum	XKD-653C-076,	Plastic colour, numbering and graphics to be provided	<ul style="list-style-type: none"> - Plastic printed bag tags - Quantity: 500 units x 2 copies - Colour and graphics to be provided by Departmental Representative - 60mmx85mmx2mm. 	1000
83.0	TASK-01	Task Chair	Commercially Available	Standard Office Chair	ADI Art Design International	Desire task chair DR-D-F-96-SS-LU	Upholstery: Momentum Millenium Onyx black 2956, Base: black	<ul style="list-style-type: none"> - Multi-Function mechanism - Center Tilt, Lock - Adjustable air lumbar - Adjustable arms in height/depth/width and pivot - Arms to have urethane pad - Sliding Seat Pan - Casters for soft surface - Fully upholstered - Size: 572-622mm (22.5-24.5") W x 610-660mm (24-26") D x 1118-1168mm (44-46") H - seat width457-508mm (18-20"); seat depth 432-457mm (17-18"); seat height 432-457mm (17-18"); arm height 678-673mm (25.5-26.5") 	14
84.0	TASK-02	Task Chair - B width	Commercially Available	Work Chair - Public Areas	Herman Miller	AE112-A-W-B-G1-PJ-NN-C7-BK-3D01	Base & Frame Finish: Graphite (G1) - Hard Floor or Carpet Casters (C7) - Armpad Finish: Black (BK) - Seat and Back: Carbon 3D01	<ul style="list-style-type: none"> - tilt limiter & seat angle - Fully adjustable arms - Non-upholstered arm pads - Medium chair size (B Width - 69mm) - Adjustable posture fit support - Hard floor or carpet casters 	5
85.0	TASK-03	Task Chair - C width	Commercially Available	Work Chair - Public Areas	Herman Miller	AE112-A-W-C-G1-PJ-NN-C7-BK-3D01	Base & Frame Finish: Graphite (G1) - Hard Floor or Carpet Casters (C7) - Armpad Finish: Black (BK) - Seat and Back: Carbon 3D01	<ul style="list-style-type: none"> - tilt limiter & seat angle - Fully adjustable arms - Non-upholstered arm pads - Large chair size (C width) - 72mm - Adjustable posture fit support - Hard floor or carpet casters 	3
86.0	TELE-02	Television Bracket	Commercially Available	Television Bracket	Peerless-AV	SmartMount - SA746PU	Colour: Semi-gloss Black	<ul style="list-style-type: none"> - Wall Mounted articulated arm for monitor - For 30" to 50" displays - 80 lbs capacity - Post-installation height adjustment of 13mm - one-touch tilt of 15 deg / -5 deg - extends up to 564mm - integrated cable management to conceal cables - adaptor plate to suit different displays. 	1

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
87.0	TROL-01	Cart	Commercially Available	Cleaning \Cart	Vileda Professional	Origo 300FX (147624). Incl. Accessories: Rectangular long pails, Two (2) (120945) - Charing Bucket (131663) - Duo Press Holder (121841) Duo Press (120788) - Sweb Duo MicroPlusmop (143815) Qty:30 - Sweb Duo Mop Frame (137879) - Telescopic Handle (119967)		<ul style="list-style-type: none"> Trolley: - Minimum three (3) shelves - Holds minimum two 25L pails on open bottom shelf - c/w Mop press and press holder. - Other shelves to hold minimum two smaller containers - Waste collection and storage area for cleaning utensils - Drawer system for trays and boxes - One (1) plastic bin bag holder with support bars - Two (2) full trays - Two (2) 6 liter buckets with eight (8) colour coding clips - Four (4) height-adjustable 89-127mm (3.5-5") turning casters - One (1) frame holder set - One (1) extension support for garbage bag - Mop Press: - 100% polypropylene (chassis) with stainless steel (lever) - Mop pressing; Ergonomic lever - Press Holder Regular long pails: - Two (2) 25 liter buckets with colour coding clips - Microfiber mop: - 100% Polyester, cut pile mop Mop Frame: - Plastic frame - Plastic parts: Polypropylene, glass fiber, polyamide - Metal parts: Stainless steel Mop Handle: - Two (2) Telescopic handles: Aluminum construction - Adjustable from 100-180 cm - Handles to have an anti-slip top grip and colour-coded clips 	2
88.0	TRUC-01	Flat Utility Cart	Commercially Available	Heavy-Duty Platform Truck	Kleton	MB 296 2000 lbs Capacity	Finish: Blue Enamel Deck: Hardwood Handle: Chrome	<ul style="list-style-type: none"> - Chrome handle @ 40" - 25-51mm (1-2") removable chrome handle - can be placed at either end of deck - Hardwood deck features minimum 51mm x 51mm (2" x 2") angle iron frame with hardwood decking - 178-229mm (7-9") dia. mold-on rubber casters - Two (2) rigid front casters and two (2) swivel back bolted-on casters - Minimum 907 Kg (2000 lbs) Capacity - Size: 1194-1245mm (47-49") L x 584-635mm (23-25") D x 254-305mm (10-12") deck height 	5
89.0	TRUC-02	Fork Truck	Commercially Available	Walkie Pallet Truck	Raymond	8310		<ul style="list-style-type: none"> - 24 volt - travel speed 3.9mph - electric pallet jack for heavy-duty applications - ergonomic handle - walk-beside truck - 4' (1200mm) forks - 6,000 lbs lift capacity 	8
90.1	TRUC-03	Fork Truck	Commercially Available	Walkie Pallet Truck	Raymond	8310		<ul style="list-style-type: none"> - 24 volt - travel speed 3.9mph - electric pallet jack for heavy-duty applications - ergonomic handle - walk-beside truck - 5' (1524mm) forks - 6,000 lbs lift capacity 	2
90.2	WAST-04	Garbage Container	Commercially Available	Front Load Container	Suncast Commercial	RMTTHD150	Colour: Gray	<ul style="list-style-type: none"> - 1050W x 2180L x 1245H - 1.5 cubic yard heavy duty tilt truck, - smooth surface inside for easy clean - roto-loldd MDPE - industrial strength casters with integrated brakes 14" in diameter - towable design - 2200 lbs capacity - fork-liftable feature to be compatible with TRUC-03 	6

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALLY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
91.0	VACU-01	Vacuum	Commercially Available	15" Upright Vacuum	Windsor Commercial Cleaning Equipment	SRXP15 - Model No.: 1.012-027.0		<ul style="list-style-type: none"> - Vacuum Motor: two-stage, minimum 1.6 hp (1200 watts), minimum 90" (228 cm) waterlift, minimum 105 cfm (50 l/s) airflow - Housing: injection molded, high-impact ABS plastic - On-board extension hose - Brush Drive: Non-slip toothed belt, enclosed, electronic safety clutch and speed control - Brush Speed: minimum 5400 brush contacts per minute, minimum 2700 rpm - Brush Motor: Automatically sets brush height for type of flooring - electronic sensor - Dust Bag: Triple-layer bag, minimum 5.3 L (323 cu.in.), enclosed, top-loading - Filtration: minimum 99.6% at 0.3 microns, minimum 490 sq.cm (76 sq.in.) filtration area HEPA filter, minimum 99.97% at 0.3 microns - Wheels: 51-75mm (2-3") diameter rubberized - Power cord: 12.2m-15.2 (40'-50'), double insulated - Electrical: 120V, 60 cycle 230V, 50 Hz - Agency Approval: Underwriters Laboratories (UL) Listed to U.S. and Canadian Safety Standards - Working Width: 356-406mm (14-16") - Height: 1143-1194mm (45-47") - Handle Weight: maximum 0.7 kg (1.5 lbs) (Weight with power cord: maximum 8.2 kg (18 lbs)) - Tools: On-board crevice and upholstery tools, dusting brush and clip - Industry approvals: CRI Indoor Air Quality Testing Program - Operating sound Level: maximum 69 DBA - No specific colour required 	3
92.0	VACU-02	Vacuum	Commercially Available	12" Upright Vacuum	Windsor Commercial Cleaning Equipment	SRXP12 - Model No.: 1.012-024.0		<ul style="list-style-type: none"> - Vacuum Motor:two-stage, minimum 1.6 hp (1200 watts), minimum 90" (228 cm) waterlift, minimum 105 cfm (50 l/s) airflow - Housing: Injection molded, high-impact ABS plastic - Brush Drive: Non-slip toothed belt, enclosed, electronic safety clutch & speed control - Brush Speed: minimum 5400 brush contacts per minute, minimum 2700 rpm - Brush Motor: Automatically sets brush height for type of flooring - electronic sensor - Dust Bag: Triple-layer bag, minimum 5.3L (323 cu.in.), enclosed, top-loading - Filtration: minimum 99.6% at 0.3 microns, minimum 490 cu.cm (76 cu.in.) filtration area optional HEPA filter, minimum 99.97% at 0.3 microns - Wheels: 50-75mm (2-3") dia. rubberized - Power cord: 12.2m-15.2 (40'-50'), double insulated - Electrical: Operates on 120V, 60 cycle 230V, 50 Hz - Agency Approval: Underwriters Laboratories (UL) Listed to U.S. and Canadian Safety Standards - Working width: 279-330mm (11-13") - Height: 1143-1194mm (45-47") - Handle Weight: maximum 0.7 kg (1.5 lbs) (Weight with power cord: maximum 8.2 kg (18 lbs)) - Tools: On-board crevice and upholstery tools, dusting brush and clip - Industry approvals: CRI Indoor Air Quality Testing Program - Operating sound Level: maximum 69 DBA - No specific colour required 	3

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALLY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
93.0	VACU-03	Vacuum	Commercially Available	High Capacity Wet Vacuum	Nace Care Solutions	WV 1800P WV 1800 Series High Capacity Wet Vacuum		<ul style="list-style-type: none"> - Wet Vacuum - Tank and head constructed in structural foam - Motor: 1,200 W, minimum 1.6 Hp - Minimum 2540mm (100") hose water lift - Airflow: 95 cfm - Minimum 76 liter (20 gallon) tank - Pumps water at a rate of minimum 227 liters (60 gallons) per minute - Dump hose included - Sump pump enabling continuous pumping of fluid - Power Cord Length: 12.8 meters (42') - Hose Length: 3-3.6 meters (10-12') - Weight: Maximum 38.5 KG (81 lbs) - Pump power: 500 Watts - Output: minimum 60 gpm - Noise Level dB(A): Maximum 64 DB(A) - Speeds: One (1) Speed - Vacuum Motor Stages: Two (2) Stages - Type: Centrifugal - Ball float wet shut-off - Structural foam tank and head to be rustproof - Float activated sump pump - Submersible pump made of high-impact plastics - Motor to have a stainless steel shaft and triple seal system and has a thermal protection device to prevent overheating - No specific colour required 	2
94.0	VACU-04	Vacuum	Commercially Available	Cordless Backpack Vacuum	NSS Enterprises Inc.	Outlaw PB		<ul style="list-style-type: none"> - Adjustable Shoulders, Chest, & Waist - 22 lbs - 12V battery - 1.6 gal. capacity - No specific colour required 	2
95.0	WASH-01	Pressure Washer	Commercially Available	Pressure Washer	Dynablast	MPU4500EXUVP		<ul style="list-style-type: none"> - 8.5-9.5m (28-31') pressure hose - Spray Gun with Wand and Nozzle - Wall bracket - Remote box switch - Motor: 3HP TEFC - Volts: 230V - Motor Speed: minimum 1750RPM - Power cord: 7 Meters (23') - Pump: Interpump triplex plunger - Pressure: minimum 1500 psi - Flow: minimum 11 L/mini. (3 gal/min.) - Size: 656-737mm (27-29") x 508-559mm (20-22") x 330-381mm (13-15") - Chemical: Integral adjustable low - pressure injector - Unloader: integral adjustable unloader - No specific colour required. 	1

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
96.0	WASH-02	Can Washer	Commercially Available	Jet Can Washer	Chicago Can Company	Aervoid 5-B Aervoid Jet Can Washer Installation for cold and hot water Two (2) hand shutoff valves, two (2) shock	Bowl: Stainless Steel Bowl Legs: Cast Iron	<ul style="list-style-type: none"> - Non-electrical - Foot pedal operated - Can wash up to a 19 Liter (5 gallon) pail or bucket - Jet spray nozzle - Fastens to floor - Automatic safety locks - Removable drain screen - Installation for cold and hot water - Two (2) hand shutoff valves, two (2) shock - Height: 711-762mm (28-30") - Diameter: 660-711mm (26-28") Bowl: Stainless Steel Bowl Legs: Cast Iron 	1
97.0	WASH-03	Steam cleaner / Vacuum	Commercially Available	Steam cleaner and wet/dry vacuum	Reliable	Tandem Pro 2000CV	Finish: Stainless steel	<ul style="list-style-type: none"> - multi-use unit, steam cleaner, steam extractor and a wet/dry vacuum - accessory kit - 2L detergent tank - 87 psi operating pressure - 5 minute heat up time - Adjustable pressure control - 5L waste water capacity - Light and sound when water level is low 	1
98.0	WAST-01	Waste Receptacle	Commercially Available	Medium Wastebasket	Rubbermaid Commercial Products	2956 Wasterbasket (FG295600 BLA)	Colour: Black	<ul style="list-style-type: none"> - All-plastic construction; chip, rust and dent resistant - Rolled rim - Size: 260mm (10.2") W x 365mm (14.4") D x 381mm (15") H - Capacity: Minimum 26.6 L (28 1/8 qt.) 	24
99.0	WAST-05	Waste Receptacles	Commercially Available	5 ganged waste receptacles	Waste Wize Products Inc.	The Waste Watcher	Colour: Gray	<ul style="list-style-type: none"> - 5 bins 23 gallon capacity - (5 bins x 11"L), 20" D, - Overall size 55"W (1397) X 20"D (508), 30"H (762mm) - All labels to be French & English Bilingual - Connector kit required - Bid: "paper only" label (blue); "Cans & Bottles" label (executive grey); "Organics Only" label (green); "Waste Only" label (black) 	1
100.0	WAST-08	Waste Receptacle	Commercially Available	Rigid liners	Rubbermaid Commercial Products	FG356600	Colour: Gray	<ul style="list-style-type: none"> - 24.7 gallon (93.4 Litre) rigid liner - 1.3 cm x 41.3 cm x 72.4 cm high (16.2" x 16.2" x 28.5") 	7
101.0	WAST-09	Waste Receptacle	Commercially Available	Recycling Station	Steelcase	Victor 2 waste and recycling freestanding station AWR254836	Arctic white 2730 powder coated metal; Rift cut white oak doors	<ul style="list-style-type: none"> - Freestanding 4 unit combined waste unit, metal construction with white metal powder coating with Rift cut white oak doors for access to liners. - All signage to be bilingual - French / English in equal size; - to include liners for waste.F130 	2
102.0	WBRD-01	White Board	Commercially Available	White Board	Egan Visual Inc.	MES4836 Square Corner Marker Board Four (4) Markers One (1) Egan Cloth One (1) Pen Tray	Finish: white board / aluminum frame	<ul style="list-style-type: none"> - Aluminum frame marker board - dry-erase surface that accepts magnetic accessories - Solid extruded aluminum frame, square corners - Full length aluminum marker tray - Wall-mountable - To include: four (4) markers, one (1) cleaning cloth / eraser, one (1) pen tray - Size: 1194-1245mm (47-49") W x 889-940mm (35-37") H x 25-51mm (1-2") D - Finish: Clear Anodized 	3

EP751-173057/A
111 Wellington - Commercially Available Goods
Attachment 1 to Annex A - Line Item Detail

ITEM NUMBER	COMPONENT CODE	COMPONENT NAME	COMMERCIALLY AVAILABLE/ WORKSTATION	DESCRIPTION	MANUFACTURER	MODEL	FINISH	MANDATORY	QUANTITY
103.0	WKBE-01	Workbench	Commercially Available	Workbench	Lee Valley Tools	Veritas Workbenches - 05A01.01	Bench top : Laminated maple slabs, Legs: cast-iron black	<ul style="list-style-type: none"> - bench height: 35" - Hardwood base & top - Twin screw vise (12" clamping) & large screw vise (13" clamping capacity) - Bench complete with double screw vise - Full-width end vise: minimum 305mm (12") clamping capacity that can be used for side or top clamping - Front vise: minimum 28mm (1-1/8") diameter screw, minimum 330mm (13") clamping capacity - Four (4) brass bench dogs - 635-686mm (25-27") x 1905-1956mm (75-77") work surface (vise closed) - Slab pre-drilled with double row of minimum 19mm (3/4") diameter dog holes - Truss-rod construction (all butt-joints, no mortise and tenon work) - Hardwood base: truss-rod assembly 	1
104.0	XRAY-05	Hand Wand	Commercially Available	Hand Held Metal Detector	Garrett Electronics Inc.	Super Scanner V - 1165190	9V battery	<ul style="list-style-type: none"> - three colour LED indication - Included one 9V battery - Detects medium sized pistol from 9" distance, large knife from 6", razor blades and box cutters from 3" distance, foil-wrapped drugs and tiny jewelry from 1" - 8" (20.3cm) scan surface - Rugged, high-impact ABS case with reinforced coil compartment. Exceeds Mil-Std-810F (drop test) Method 516.5, procedures II and IV. 	6
105.0	XRAY-06	X-Ray Tray	Commercially Available	X-Ray Scanner Pass-Through Tray	Rubbermaid Commercial Products	3509 Food/Tote Box (FG350900 WHT)	Colour: White	457mm X 305mm X 152mm - 13.2L capacity. If 6 per pack, 4 packs required. Total # of trays = 24	4
106.0	GUES-01	Guest Chair	Commercially Available	Leg Base Stacking Chair Upholstered Guest Chair with Arms and Hard Casters	Haworth	IMPROV M600-2212	Fabric Manufacturer: Haworth Fabrics Pattern Name & No.: Horizon (Grade A) Color Name & No.: Compass 1N- 002 Frame Color: Black.	<ul style="list-style-type: none"> - Stacking Chair - Upholstered Back - Non Ganging - Hard Casters 	14