

PART 1 - GENERAL

1.1 REFERENCES

- .1 The Aluminum Association (AA)
 - .1 AA DAF-45-R2009, Designation System for Aluminum Finishes - 9th Edition.
- .2 ASTM International
 - .1 ASTM A 53/A 53M-12, Standard Specification for Pipe, Steel, Black and Hot-Dipped, Zinc-Coated Welded and Seamless.
 - .2 ASTM A 123/A 123M-15, Standard Specification for Zinc (Hot-Dip Galvanized) Coatings on Iron and Steel Products.
 - .3 ASTM A 480/A 480M-16b, Standard Specification for General Requirements for Flat-Rolled Stainless and Heat-Resisting Steel Plate, Sheet, and Strip.
 - .4 ASTM B 241/B 241M-16, Standard Specification for Aluminum and Aluminum-Alloy Seamless Pipe and Seamless Extruded Tube.
- .3 Canada Green Building Council (CaGBC)
 - .1 LEED Canada 2009 for Design and Construction-2010, LEED Canada 2009 for Design and Construction Leadership in Energy and Environmental Design Green Building Rating System Reference Guide.

1.2 ACTION AND INFORMATIONAL SUBMITTALS

- .1 Submit in accordance with Section 01 33 00 - Submittal Procedures.
 - .2 Product Data:
 - .1 Submit manufacturer's instructions, printed product literature and data sheets for and include product characteristics, performance criteria, physical size, finish and limitations.
 - .3 Shop Drawings:
 - .1 Indicate dimensions, finishes, base jointing, anchoring and support systems, cleats, halyard boxes, trucks, finials and base collar for flagpoles.
 - .2 Submit electronic copies of drawings of flagploe and bases, showing general layout,
-

- | | |
|---|--|
| 1.2 ACTION AND
INFORMATIONAL
SUBMITTALS
(Cont'd) | .3 Shop Drawings: (Cont'd)
.2 (Cont'd)
jointing and complete anchoring and supporting
systems. |
| | .4 Samples:
.1 Submit finish samples 300 mm x 300 mm. |
| | .5 Manufacturer's Instructions: submit
manufacturer's installation instructions for
each type of flagpole. |
| | .6 Sustainable Design Submittals:
.1 LEED Canada - Submittals: in accordance
with Section 01 35 21 - LEED Requirements. |
| 1.3 QUALITY
ASSURANCE | .1 Provide each flagpole as complete unit
produced by single manufacturer, including
fittings, accessories, bases and anchorage
devices. |
| 1.4 DELIVERY,
STORAGE AND
HANDLING | .1 Deliver, store and handle materials in
accordance with Section 01 61 00 - Common
Product Requirements and with manufacturer's
written instructions. |
| | .2 Delivery and Acceptance Requirements: deliver
materials to site in original factory
packaging, labelled with manufacturer's name
and address.
.1 Spiral wrap each flagpole with heavy
kraft paper, wood strip and steel band, or
polyethylene wrap and pack in tubing for
shipment.
.2 Ship flagpole to installation site in
one piece.
.1 When more than one piece is
required, provide precision joints with
self aligning internal splicing sleeve
arrangement. |
| | .3 Storage and Handling Requirements:
.1 Store materials off ground, indoors in
dry location and in accordance with
manufacturer's recommendations in clean, dry,
well-ventilated area. |
-

1.4 DELIVERY,
STORAGE AND
HANDLING
(Cont'd)

- .3 Storage and Handling Requirements: (Cont'd)
 - .2 Store and protect from nicks, scratches, and blemishes.
 - .3 Replace defective or damaged materials with new.
- .4 Develop Construction Waste Management Plan related to Work of this Section and in accordance with Section 01 35 21 - LEED Requirements.
- .5 Packaging Waste Management: remove for reuse or return of pallets, crates, padding, banding, and packaging materials as specified in Construction Waste Management Plan in accordance with Section 01 74 21 - Construction/Demolition Waste Management and Disposal and Section 01 35 21 - LEED Requirements.

PART 2 - PRODUCTS

2.1 MATERIALS

- .1 Galvanized steel: hot dipped galvanizing with minimum zinc coating 610 g/m² to ASTM A 123/A 123M.
- .2 Stainless steel: seamless stainless steel tubing, AISI type 304.
- .3 Aluminum:
 - .1 Aluminum Association alloy AA 6063-T6 seamless extruded aluminum tubing.
 - .2 Fabricated from seamless extruded tubing in accordance with ASTM B 241, alloy 6063 T6, having minimum tensile strength not less than 20 MPa and a yield point of 17 MPa. Heat treated and age hardened after fabrication.
- .4 Fibreglass: polyester and fibreglass woven cloth, resistant to acids, petroleum and salt water; flame retardant; colour as selected by Departmental Representative.
- .5 Isolation coating: alkali-resistant bituminous paint or epoxy resin solution.

-
- 2.2 DESIGN CRITERIA .1 Flagpole, bases and anchorage devices to resist minimum wind velocity unflagged and flagged to suit the climatic data for wind speed in the National Building Code of Canada.
- .2 Description:
.1 Exposed Height: 7620 mm (25 ft).
.2 Flag Size: 2440 mm x 1220 mm.
- 2.3 FABRICATION .1 Fabricate flagpole as complete unit including base anchorage and fittings.
- .2 Cone tapered flagpole:
.1 Seamless, uniform, straight line tapered section above cylindrical butt section.
.2 Provide internal splicing, self-aligning sleeve of same material as flagpole for snug fitting, watertight field joints.
- .3 Weld in accordance to appropriate CSA Standard, by welders certified by Canadian Welding Bureau. Finish exposed welds flush and smooth.
- 2.4 ACCESSORIES .1 Beaded retainer ring. 25 mm diameter nylon balls strung on 3 mm stainless steel cable. Complete with stainless steel quick links.
- .2 Truck assembly: cast aluminum stainless steel ballbearing, nonfouling, revolving double truck assembly, finish to match flagpole.
- .3 Vinyl covered counter weight to suit installation. Color to match retainer ring beads.
- .4 Halyard: internal, two continuous halyards per flagpole; stainless steel.
- .5 Swivel snaps: two per halyard; stainless steel.
- .6 Winch: gearless and self-locking. Complete with locking cover and removable winch handle. Installation to attach without welding and shall not require maintenance lubrication.
-

2.4 ACCESSORIES .7 Flag Arrangements: 3 mm stainless steel
(Cont'd) cable. Complete with stainless steel quick
links.

2.5 FINISHES .1 Aluminum:
.1 Finish exposed surfaces of aluminum
components in accordance with AA DAF-45.
.1 Clear anodic finish: designation
AA-A31.
.2 Appearance and properties of anodized
finishes designated by the Aluminum
Association as, Architectural Class 2, and
Protective and Decorative.

PART 3 - EXECUTION

3.1 EXAMINATION .1 Verification of Conditions: verify that
conditions of substrate previously installed
under other Sections or Contracts are
acceptable for flagpole installation in
accordance with manufacturer's written
instructions.
.1 Visually inspect substrate in presence
of Departmental Representative.
.2 Inform Departmental Representative of
unacceptable conditions immediately upon
discovery.
.3 Proceed with installation only after
unacceptable conditions have been remedied and
after receipt of written approval to proceed
from Departmental Representative.

3.2 PREPARATION .1 Temporary Erosion and Sedimentation Control:
.1 Provide temporary erosion and
sedimentation control measures to prevent soil
erosion and discharge of soil-bearing water
runoff or airborne dust to adjacent properties
and walkways, according to sediment and
erosion control plan, specific to site, that
complies with EPA 832/R-92-005 or requirements
of authorities having jurisdiction.
.2 Inspect, repair, and maintain erosion
and sedimentation control measures during

- .1 Progress Cleaning: clean in accordance with Section 01 74 11 - Cleaning.
 - .1 Leave Work area clean at end of each day.
- .2 Final Cleaning: upon completion remove surplus materials, rubbish, tools and equipment in accordance with Section 01 74 11 - Cleaning.
- .3 Waste Management: separate waste materials for reuse and recycling in accordance with Section 01 74 21 - Construction/Demolition Waste Management and Disposal and Section 01 35 21 - LEED Requirement].
 - .1 Remove recycling containers and bins from site and dispose of materials at appropriate facility.

- 3.5 PROTECTION
- .1 Protect installed products and components from damage during construction.
 - .2 Repair damage to adjacent materials caused by flagpole installation.