

## DOOR, LITE, & FRAME SCHEDULES

C&P BUILDING										
DOOR, LITE, & FRAME SCHEDULE										
DOOR						FRAME			DOOR & FRAME	REMARKS
No.	WIDTH	HGT.	MAT.	HARDWARE	ELEV.	MAT.	ELEV.	DETAIL	FIRE RATING	
X01	914	2134	FG	X2	D1	FG	F4	C	—	
X02	4267	4267	M	X0	D5	—	—	—	—	INSULATED SECTIONAL DOOR
X03	4267	4267	M	X0	D5	—	—	—	—	INSULATED SECTIONAL DOOR
X04	914	2134	FG	X2	D1	FG	F1	C	—	
X05	914	2134	FG	X2	D1	FG	F1	C	—	
100	914	2134	WD	6	D3	PSF	F8	A	—	
102	914	2134	WD	2	D1	PSF	F1	A	45 min	
107	914	2134	WD	7	D1	PSF	F1	E	—	
108	914	2134	WD	7	D1	PSF	F1	E	—	
109	914	2134	WD	12	D1	PSF	F1	A	—	
110	914	2134	HM	13	D1	PSF	F1	A	1 hour	
111	914	2134	HM	2	D1	PSF	F1	A	45 min	
112	914/ 610	2134	HM	9	2xD1	PSF	F1	A	45 min	
113	914	2134	HM	5	D3	PSF	F1	A	1 hour	
114	914	2134	HM	4	D1	PSF	F1	A	45 min	

DOOR, LITE, & FRAME SCHEDULE										
DOOR					FRAME				DOOR & FRAME	REMARKS
No.	WIDTH	HGT.	MAT.	HARD-WARE	ELEV.	MAT.	ELEV.	DETAIL	FIRE RATING	
X01	--	--	--	--	--	--	--	--	--	EXISTING DOOR.
X02	2438±	3048	M	X0	D6	--	--	--	--	CONFIRM EXISTING OVERHEAD DOOR WIDTH ON SITE. MOTOR REQUIRED
X03	--	--	--	--	--	--	--	--	--	EXISTING/RELOCATED DOOR, FRAME, AND HARDWARE
X04	--	--	--	--	--	--	--	--	--	EXISTING OVERHEAD DOOR; MOTOR REQUIRED
X05	--	--	--	--	--	--	--	--	--	EXISTING OVERHEAD DOOR; MOTOR REQUIRED
X06	2x914	2134	FG	X3	2x01	FG	F1	C	--	
103	--	--	--	--	--	--	--	--	--	EXISTING DOOR
104	--	--	--	--	--	--	--	--	--	EXISTING/RELOCATED DOOR, FRAME, AND HARDWARE
105	--	--	--	--	--	--	--	--	--	EXISTING DOOR

NOTE:

1) PAINT ALL INTERIOR AND EXTERIOR EXISTING DOORS AND FRAMES.

MCTS CENTRE										
DOOR, LITE, & FRAME SCHEDULE										
DOOR						FRAME			DOOR & FRAME	REMARKS
No.	WIDTH	HGT.	MAT.	HARD-WARE	ELEV.	MAT.	ELEV.	DETAIL	FIRE-RATING	
X01	914	2134	FG	X1	D2	FG	F2	B	—	
X02	914	2134	FG	X4	D3	FG	F1	C	—	
X03	2438	2362	M	X0	D5	—	—	—	—	INSULATED SECTIONAL DOOR
X04	914	2134	FG	X2	D3	FG	F1	C	—	
X05	914	2134	FG	X2	D1	FG	F4	C	—	
X06	914	2134	FG	X5	D1	FG	F1	C	—	
X07	914	2134	FG	X5	D1	FG	F1	C	—	SEE 5/A7 FOR DOOR LOCATION
100	914	2134	HM	1	D2	PSF	F3	B	—	
103	914	2134	WD	2	D1	PSF	F1	A	45 min	
104	914	2134	WD	3	D1	PSF	F4	A	—	
105	—	—	—	—	—	PSF	F5	D	—	INTERIOR LITE
106	914	2134	WD	2	D1	PSF	F1	A	—	
107	914	2134	WD	2	D1	PSF	F1	A	45 min	
108	914	2134	WD	2	D1	PSF	F1	A	45 min	
109	914	2134	WD	4	D1	PSF	F1	A	—	
112	914	2134	WD	3	D1	PSF	F1	A	—	
113	1067	2134	WD	3	D1	PSF	F1	A	—	
114	914	2134	WD	2	D1	PSF	F7	A	—	
115	914	2134	HM	13	D3	PSF	F1	A	45 min	
116	1067	2134	WD	3	D1	PSF	F1	A	—	
116A	2438	2362	M	0	D4	—	—	—	—	NON-INSULATED COILING DOOR
117	914	2134	WD	6	D1	PSF	F7	A	—	
120	1067	2134	WD	3	D1	PSF	F9	A	—	
125	—	—	—	—	—	PSF	F10	D	—	INTERIOR LITE
128	914	2134	WD	7	D1	PSF	F1	E	—	
129	914	2134	WD	7	D1	PSF	F1	E	—	
131	914	2134	HM	8	D3	PSF	F1	A	45 min	
200	914	2134	HM	8	D3	PSF	F1	A	45 min	
202	914	2134	WD	7	D1	PSF	F1	E	—	
204	2x914	2134	HM	9	2xD1	PSF	F1	A	45 min	
205	914	2134	WD	4	D1	PSF	F4	A	—	
206	914	2134	WD	7	D1	PSF	F1	E	—	
207	914	2134	WD	7	D1	PSF	F1	E	—	
209	914	2134	WD	4	D1	PSF	F1	A	—	
210	914	2134	WD	2	D1	PSF	F1	A	—	
212	914	2134	WD	4	D1	PSF	F6	A	—	
213	914	2134	WD	3	D1	PSF	F4	A	—	
213A	914	2134	WD	10	D1	PSF	F4	A	—	
214	914	2134	WD	13	D1	PSF	F7	A	—	
215	914	2134	HM	13	D3	PSF	F1	A	45 min	

## ROOM FINISH SCHEDULES

C&P BUILDING								
ROOM FINISH SCHEDULE								
ROOM		FLOOR	BASE	WALLS		CEILING		REMARKS
No.	Name	Finish	Finish	Mat.	Finish	Mat.	Finish	
100	VESTIBULE	PORC	PORC	GB	PT	GB	PT	2700
101	WORK STATIONS	LINO	RB	GB	PT	ACT2	PF	2700
102	LAN ROOM	LINO	RB	GB	PT	EXP	PF	-
103	SHARED EQUIPMENT ROOM	LINO	RB	GB	PT	ACT2	PF	2700
104	OPEN OFFICE AREA	LINO	RB	GB	PT	ACT2	PF	2700
105	KITCHEN	LINO	RB	GB	PT	ACT2	PF	2700
106	CORRIDOR	LINO	RB	GB	PT	ACT2	PF	2700
107	WASHROOM	PORC	CT	CT	PF	GB	PT	2440
108	SHOWER/LOCKER ROOM	PORC	CT	CT	PF	GB	PT	2440
109	SECURE STORAGE	LINO	RB	GB	PT	ACT2	PF	2700
110	WORKSHOP AREA	HC	RB	GB	PT	EXP	PT	-
111	JANITOR	LINO	RB	GB	PT	EXP	PT	-
112	MECHANICAL/ELECTRICAL ROOM	HC	RB	GB	PT	EXP	PT	-
113	HEATED WAREHOUSE	HC	RB	GB	PT	EXP	PT	-
114	RECYCLING ROOM	HC	RB	GB	PT	EXP	PT	-

**NOTE:**

1) ROOM 113: SECURE 19 mm PLYWOOD (PAINTED) AROUND PERIMETER OF ROOM TO 2440 mm ABOVE FLOOR.

2) ROOM 112: SECURE 19 mm PLYWOOD (PAINTED) BACKER BOARDS AS REQUIRED FOR ELECTRICAL ITEMS MOUNTED ON PARTITIONS/WALLS. COORDINATE BACKER BOARD SIZE AND LOCATIONS WITH ELECTRICAL.

ITS STORAGE BUILDING



ROOM FINISH SCHEDULE								
ROOM		FLOOR	BASE	WALLS		CEILING		REMARKS
No.	Name	Finish	Finish	Mat.	Finish	Mat.	Height	
101	STORAGE ROOM	—	—	—	CB/PT	PT	—	
102	MAIN STORAGE ROOM	—	—	—	CB/PT	PT	—	
103	MISC. STORAGE ROOM	—	—	—	CB/PT	PT	—	
104	MISC. STORAGE ROOM	—	—	—	CB/PT	PT	—	
105	LARGE GARAGE BAY	—	—	—	CB/PT	PT	—	
106	GENERATOR ROOM	HC	RB	—	CB/PT	PT	—	

**NOTE:**


1) ROOM 106: SECURE 19 mm PLYWOOD (PAINTED) BACKER BOARDS AS REQUIRED FOR ELECTRICAL ITEMS MOUNTED ON PARTITIONS/WALLS. COORDINATE BACKER BOARD SIZE AND LOCATIONS WITH ELECTRICAL.

MCTS CENTRE									
ROOM FINISH SCHEDULE									
ROOM		FLOOR BASE		WALLS		CEILING		REMARKS	
No.	Name	Finish	Finish	Mot.	Finish	Mot.	Finish		
100	VESTIBULE	PORC	PORC	GB	PT	GB	PT	2700	FIRE RATED GB CEILING SECURED TO U/S OF JOIS
101	LOBBY	LINO	RB	GB	PT	GB	PT	2650	
102	RECEPTION	LINO	RB	GB	PT	GB/PT/PF	PT	2650/2700	
103	ELECTRICAL	LINO	RB	GB	PT	GB	PT	3200±	
104	MCTS OIC	LINO	RB	GB	PT	GB/PT/PF	PT	2650/2700	CT BACKSPLASH BEHIND KITCHEN COUNTER
105	KITCHEN	LINO	RB	GB	PT	GB/PT/PF	PT	2650/2700	
106	JANITOR	LINO	RB	GB	PT	GB	PT	2440	
107	WATER ENTRY	HC	RB	GB	PT	EXP	PT	—	
108	LAN ROOM	LINO	RB	GB	PT	EXP	PT	—	COLOUR CONTRASTING NOSING ON TREADS
109	RECYCLING	LINO	RB	GB	PT	EXP	PT	—	
110	CORRIDOR	LINO	RB	GB	PT	GB/PT/PF	PT	2440/2490	
111	SHARED EQUIPMENT (COPIER)	LINO	RB	GB	PT	ACT2	PF	2440	
112	MCTS STORAGE	LINO	RB	GB	PT	ACT2	PF	2440	COLOUR CONTRASTING NOSING ON TREADS
113	WORKSHOP – DIRTY	HC	RB	GB	PT	EXP	PT	—	
114	E&I ELECTRONICS EQUIPMENT ROOM	EP	IB	GB	PT	EXP	PF	—	
115	STAIR #2	RT/RSI	RB	GB	PT	EXP/GB	PT	—/2438	
116	MOCK-UP SPACE	HC	RB	GB	PT	EXP	PF	—	COLOUR CONTRASTING NOSING ON TREADS
117	VESTIBULE	PORC	PORC	GB	PT	GB	PT	2440	
118	CORRIDOR	LINO	RB	GB	PT	ACT1	PF	2490	
119	PERSONAL STORAGE AREA	EP	IB	GB	PT	EXP	PT	—	
120	E&I CLEAN WORKSHOP	EP	IB	GB	PT	EXP	PT	—	COLOUR CONTRASTING NOSING ON TREADS
121	PACE SOLDERING STATION	EP	IB	GB	PT	EXP	PT	—	
122	WORKSTATION #1	EP	IB	GB	PT	EXP	PT	—	
123	WORKSTATION #2	EP	IB	GB	PT	EXP	PT	—	
124	WORKSTATION #3	EP	IB	GB	PT	EXP	PT	—	COLOUR CONTRASTING NOSING ON TREADS
125	INNVA TECH/AUTOCAD	EP	IB	GB	PT	EXP	PT	—	
126	WORKSTATION #4	EP	IB	GB	PT	EXP	PT	—	
127	WORKSTATION	LINO	RB	GB	PF	ACT1	PF	2700	
128	UNIVERSAL WASHROOM	PORC	CT	CT	PF	GB	PT	2440	COLOUR CONTRASTING NOSING ON TREADS
129	UNIVERSAL WASHROOM	PORC	CT	CT	PF	GB	PT	2440	
130	CORRIDOR	LINO	RB	GB	PT	ACT1	PF	2490	
131	STAIR #1	RT/RSI	RB	GB	PT	EXP/GB	PT	—/2440	
132	ELEVATOR	LINO	PS	PL	PF	PS	PF	—	COLOUR CONTRASTING NOSING ON TREADS
200	STAIR #1	RT/RSI	RB	GB	PT	GB	PT	2440	
201	CORRIDOR	LINO	RB	GB	PT	ACT1	PF	2490	
202	SHOWER ROOM	PORC	CT	CT	PF	GB	PT	2440	
203	LOBBY	LINO	RB	GB	PT	GB/PT/PF	PT	2440/2490	ACCESS FLOORING
204	MECHANICAL ROOM	HC	RB	GB/CONC	PT	EXP	PT	—	
205	MCTS DEBRIEF	LINO	RB	GB	PT	GB/PT/PF	PT	2650/2700	
206	UNIVERSAL WASHROOM	PORC	CT	CT	PF	GB	PT	2440	
207	UNIVERSAL WASHROOM	PORC	CT	CT	PF	GB	PT	2440	ACCESS FLOORING
208	CORRIDOR	LINO	RB	GB	PT	GB	PT	2440	
209	MCTS LOCKER ROOM	LINO	RB	GB	PT	ACT1	PF	2440	
210	JANITOR	LINO	RB	GB	PT	GB	PT	2440	
211	CORRIDOR	LINO	RB	GB	PT	ACT1	PF	2490	CT BACKSPLASH BEHIND KITCHEN COUNTER
212	MCTS KITCHEN	LINO	RB	GB	PT	GB/PT/PF	PT	2650/2700	
213	SHARED BOARDROOM/TRAINING	LINO	RB	GB	PT	GB/PT/PF	PT	2650/2700	
214	MCTS OPERATIONS ROOM	LINOT	RB	GB	PT	GB/PT/PF	PT	2650/2700	
215	STAIR #2	RT/RSI	RB	GB	PT	EXP/GB	PT	—/2440	COLOUR CONTRASTING NOSING ON TREADS
216	ELEVATOR	LINO	PS	PL	PF	PS	PF	—	
NOTE:									
1) ROOM'S 103, 108, 114, 116, AND 113: SECURE 19 mm PLYWOOD (PAINTED) AROUND PERIMETER OF ROOM TO 2440 mm ABOVE FLOOR.									


## DOOR TYPES



## FRAME DETAILS



## FRAME TYPES



E	ISSUED FOR TENDER	JUL 11 2017
D	ISSUED FOR TENDER	JUN 28 2017
C	ISSUED FOR 99% REVIEW	MAY 25 2017
B	ISSUED FOR CLIENT REVIEW	APR 24 2017
A	ISSUED FOR 66% REVIEW	MAR 24 2017
revisions		date