RLED-355

LED RANGE LANTERN WITH MASTERRANGE

Tideland's original RL-355 range lantern was developed for the US Coast Guard as a high intensity range lantern and has earned its spot as our most popular range lantern.

Our new development, RLED-355, is an LED version of the original lantern. Featuring MasterRange, RLED-355 provides exceptional performance over traditional incandescent lamps.

MasterRange is a versatile LED light panel that is used to upgrade RL-355 from existing incandescent lamp technology. This new assembly not only eliminates traditional lampchangers, it also eliminates costly mirrors and does not require focusing.

MasterRange is available with multiple numbers of LEDs, from 2 to 15, allowing for a wide range of effective intensities, with ranges up to 24NM.

Retrofitting

- RLED-355 is available complete or alternatively MasterRange is available as a conversion kit that can be retrofitted to existing RL-355s.
- All control electronics, LEDs, LED drivers, LED lenses (not external spreader lenses), flashers, daylight control circuitry and mounting hardware are included in the conversion kit.
- MasterRange LED panels are available in a range of assembly sizes and can be retrofitted to similar lanterns manufactured by companies other than Tideland Signal.

Optional Equipment

- Optional hood assembly helps keep lens clear of dirt and bird droppings.
- Optional Tideland GPS based system, to maintain flash synchronisation of two or more range lanterns.
- Optional dual power supply for MasterRange MR-2,4,6,8 and 10 lens (standard on MR-12 and 15).





a xylem brand

RLED-355

Characteristics

- Supports all marine signaling industry standards.
- Utilises 1/4 inch thick transparent acrylic lens.
- Spreader lenses are available for varied horizontal divergences.
- Constructed of corrosion resistant, marine grade materials.
- Reliable in the severest of environments.

- All IALA approved colours are available.
- Easy horizontal aiming and adjustment.
- External sunswitch.
- Full monitor and control access.

Technical Details

Applications	Leading light, short or long range; port traffic signal, night or day
Input Voltage	9 to 36VDC
Input Power	2 to 45W (depending on colour and number of LEDs)
Vertical Divergence	2 to 3.5° (depending on colour)
Horizontal Beam Spreaders	3°, 8°, 11°, 20° or 28°
Mounting	Built-in leveling hardware and rotational slip-ring mounting (3 bolt)
Height	520.7mm (20.5")
Weight with MR-15	19.2kg (42.3lb)
Light Colour	White, green, red, blue or yellow

NOTE: Specifications are subject to change.


MasterRange in MR-15, MR-8 and MR-4 lens panel arrangements









DIMENSIONS AND MOUNTING PATTERN







Tideland Signal Corporation (USA) us-sales@tidelandsignal.com

lem

Let's Solve Water

Tideland Signal Ltd (Canada) canada-sales@tidelandsignal.com Tideland Signal Ltd (Burgess Hill, UK) emea-sales@tidelandsignal.com

Tideland Signal (The Netherlands) emea-sales@tidelandsignal.com Tideland Signal Ltd (Dubai, UAE) emea-sales@tidelandsignal.com

Tideland Signal Pte Ltd (Singapore) asia-sales@tidelandsignal.com Tideland Signal Pte Ltd (Tianjin, China) asia-sales@tidelandsignal.com

www.tidelandsignal.com