

PART 1 - GENERAL

1.1 REFERENCES

- .1 Codes and standards referenced in this section refer to the latest edition thereof.
- .2 National Fire Protection Association (NFPA)
 - .1 NFPA 701: Standard Methods of Fire Tests for Flame Resistant Textiles and Films.
- .3 Canada Green Building Council (CaGBC)
 - .1 LEED Canada 2009 for Design and Construction Leadership in Energy and Environmental Design Green Building Rating System Reference Guide.
- .4 Test Reports:
 - .1 Submit certified test reports showing compliance with specified performance characteristics and physical properties.

1.2 ACTION AND INFORMATION SUBMITTALS

- .1 Submit shop drawings, product data, and samples in accordance with 01 33 00 - Submittal Procedures.
 - .2 Indicate fabric dimensions in relation to window openings and operating hardware.
 - .3 Submit one representative working sample of each type sun control roller shade type.
 - .4 After approval samples will be returned for incorporation into the Work.
 - .5 Submit samples of manufacturer's standard colours for selections by Owner's Representative.
 - .6 Sustainable Design Submittals:
 - .1 LEED Canada Submittals: in accordance with Section 01 35 21 - LEED Requirements.
-

1.3 DELIVERY,
STORAGE AND
HANDLING .1 Deliver, store and handle materials in
accordance with Section 01 61 00 - Common
Product Requirements and with manufacturer's
written instructions.

1.4 WARRANTY .1 Provide a written guarantee stating the sun
control roller shades will be free from
manufacturer's defects for a period of five
(5) years.
.2 Contractor to provide a two (2) year warranty
against defects in installation workmanship.

PART 2 - PRODUCTS

2.1 MATERIALS AND
FABRICATION .1 Sun control roller shade of tearproof, basket
weave fabric 3% open weave, inherently flame
retardant; to meet NFPA 101, Class A Rating.
Steel stays keep fabric flat and smooth in
side channels.
.1 Shade mounted on one-piece heavy duty
steel roller, not less than 38 mm diameter.
.2 Provide steel headbox at top of opening
equipped with hinge cover for access.
.3 Provide valances wall-to-wall of window
recess in front of headbox.
.4 Mounting: jamb mount, in window recess.
.5 Antimicrobial fabric: as selected by
Departmental Representative from manufacturers
full range of colours.
.6 Fabric colour: as selected by
Departmental Representative from manufacturers
full range of colours.
.7 Cord tension device: provide spring
loaded cord tension devices.
.2 Blackout roller blinds.
.1 As required for sun control shades but
for solid weave on glass side.
.1 Colour: as selected by Departmental
Representative from manufacturers full
range of colours.

- 2.1 MATERIALS AND FABRICATION (Cont'd)
- .2 (Cont'd)
 - .1 (Cont'd)
 - .2 Mounting: mount in tandem with sun control shade.
 - .1 Tandem mounting brackets 108 mm deep.

- 2.2 OPERATION
- .1 Equip open weave roller shades with stainless steel right hand bead chain operation.
 - .2 Equip blackout roller blinds with stainless steel left hand bead chain operation.

PART 3 - EXECUTION

- 3.1 INSTALLATION
- .1 Install hardware using non-corrosive metal bolts concealed in final assembly.
 - .2 Install square, plumb, true to line with operable parts adjusted for correct function.
 - .3 Install in accordance with reviewed shop drawings.

- 3.2 SCHEDULE
- .1 Install sun control roller shades for all windows at perimeter of building, including sublights and tansoms.
 - .2 Install blackout blinds in addition to sun control roller blinds for windows of MCTS Operations Room and Shared Boardroom/Training Room.