

2.1 Requirement Compliance Matrix

Item #	Window Number	Frame Number	Side	Location	Original Glass	Fixed / Sliding	DWG Letter	Approx. Clear Glass Height	Approx. Clear Glass Width	Replace?	General Remarks	Installation Type	Corner Radius	Set to be Delivered	Set to be Delivered Assembled?	Compliance (Meet/ Not Meet)
The information is for guidance only. The Contractor shall have the onus to validate all dimensional information provided prior to manufacturing all components.																
1	47	58	PORT	AFT Inboard most window	1/2" ARMOUR PLATE	FIXED	A	33"	57" MIN	YES	12mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
2	48	58	PORT	AFT	1/2" ARMOUR PLATE	Horizontal SLIDING	A	33"	57" MIN	YES	12mm Clear Tempered glass	Bolted	4-5/16"	2 Glass Seals	No	
3	49	58	PORT	AFT	1/2" ARMOUR PLATE	FIXED	B	33"	24" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
4	50	58-60	PORT	PORT SIDE	3/4" LAMINATED	FIXED	C	33"	36" MIN	YES	19mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
5	51	60-64	PORT	PORT SIDE UPPER adjacent to Telegraphs	3/4" LAMINATED	Horizontal SLIDING Fore to Aft to access Telegraphs	D	33"	66" MIN	YES	19mm Clear Tempered glass	Bolted	4-5/16"	3 Glass Seals	No	
6	53	HOUSE FRONT	PORT	FRONT	3/4" LAMINATED	FIXED Clearview Screen	F	33"	66" MIN	YES	12mm/6mm CLEAR TEMPERED LAMINATED GLASS WITH VERTICAL CENTER MULLION DIVIDER WITH CVS HOLE ON ONE SIDE TO SUIT A SPEICH CLEARVIEW SCREEN EX38S	Bolted	3-13/16"	1 Glass Seals 1 Speich AC38S.H or equivalent Clearview Screen with drive and control	No	

Item #	Window Number	Frame Number	Side	Location	Original Glass	Fixed / Sliding	DWG Letter	Approx. Clear Glass Height	Approx. Clear Glass Width	Replace?	General Remarks	Installation Type	Corner Radius	Set to be Delivered	Set to be Delivered Assembled?	Compliance (Meet/ Not Meet)
The information is for guidance only. The Contractor shall have the onus to validate all dimensional information provided prior to manufacturing all components.																
7	54	HOUSE FRONT	PORT	FRONT	3/4" LAMINATED	FIXED	G	33"	66" MIN	YES	19mm CLEAR TEMPERED GLASS WITH VERTICAL CENTER MULLION DIVIDER	Bolted	3-13/16"	1 Glass	No	
8	56	HOUSE FRONT	STBD	FRONT	3/4" LAMINATED	FIXED	G	33"	66" MIN	YES	19mm CLEAR TEMPERED GLASS WITH VERTICAL CENTER MULLION DIVIDER	Bolted	3-13/16"	1 Glass	No	
9	59	60-64	STBD	STBD SIDE UPPER adjacent to Telegraphs	3/4" LAMINATED	Horizontal SLIDING Fore to Aft to access Telegraphs	D	33"	66" MIN	YES	19mm Clear Tempered glass	Bolted	4-5/16"	3 Glass Seals	No	
10	60	58-60	STBD	STBD SIDE	3/4" LAMINATED	FIXED	C	33"	36" MIN	YES	19mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
11	61	58	STBD	AFT	1/2" ARMOUR PLATE	FIXED	B	33"	24" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
12	62	58	STBD	AFT	1/2" ARMOUR PLATE	Horizontal SLIDING	A	33"	57" MIN	YES	12 mm Clear Tempered glass	Bolted	4-5/16"	2 Glass Seals	No	
13	63	58	STBD	AFT	1/2" ARMOUR PLATE	FIXED	A	33"	57" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
14	65	58	PORT	AFT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	24" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	

Item #	Window Number	Frame Number	Side	Location	Original Glass	Fixed / Sliding	DWG Letter	Approx. Clear Glass Height	Approx. Clear Glass Width	Replace?	General Remarks	Installation Type	Corner Radius	Set to be Delivered	Set to be Delivered Assembled?	Compliance (Meet/ Not Meet)
The information is for guidance only. The Contractor shall have the onus to validate all dimensional information provided prior to manufacturing all components.																
15	66	58	PORT	AFT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	24" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
16	67	58-60	PORT	PORT SIDE BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	36" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
17	68	60-62	PORT	PORT SIDE BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	33" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
18	69	60-62	STBD	STBD SIDE BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	33" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
19	70	58-60	STBD	STBD SIDE BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	36" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
20	71	58	STBD	AFT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	24" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
21	72	58	STBD	AFT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	27"	24" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
22	74	HOUSE FRONT	PORT	FRONT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	H	30"	30" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
23	75	HOUSE FRONT	PORT	FRONT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	H	30"	30" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	

Item #	Window Number	Frame Number	Side	Location	Original Glass	Fixed / Sliding	DWG Letter	Approx. Clear Glass Height	Approx. Clear Glass Width	Replace?	General Remarks	Installation Type	Corner Radius	Set to be Delivered	Set to be Delivered Assembled?	Compliance (Meet/ Not Meet)
The information is for guidance only. The Contractor shall have the onus to validate all dimensional information provided prior to manufacturing all components.																
24	76	HOUSE FRONT	PORT	FRONT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	30"	31" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
25	79	HOUSE FRONT	STBD	FRONT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	A	30"	31" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
26	80	HOUSE FRONT	STBD	FRONT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	H	30"	30" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	
27	81	HOUSE FRONT	STBD	FRONT BOTTOM	DOUBLE GLAZED SEALED 1/2" ARMOUR PLATE	FIXED	H	30"	30" MIN	YES	12 mm Clear Tempered glass	Bolted	3-13/16"	1 Glass	No	

Bidder's Authorized Representative Name

Bidder's Authorized Representative Signature

Date