



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Travaux publics et Services gouvernementaux
Canada

Place Bonaventure,
800 rue de la Gauchetière Ouest
Voir aux présentes - See herein
Montréal

Québec
H5A 1L6

FAX pour soumissions: (514) 496-3822

**SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Travaux publics et Services gouvernementaux Canada
Place Bonaventure,
800 rue de la Gauchetière Ouest
Voir aux présentes - See herein
Montréal
Québec
H5A 1L6

Title - Sujet Équipement d'optométrie	
Solicitation No. - N° de l'invitation 21301-185095/A	Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client 21301-18-5095	Date 2017-10-04
GETS Reference No. - N° de référence de SEAG PW-SMTA-375-14509	
File No. - N° de dossier MTA-7-40042 (375)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2017-10-11	
Time Zone Fuseau horaire Heure Avancée de l'Est HAE	
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Joseph, Marc	Buyer Id - Id de l'acheteur mta375
Telephone No. - N° de téléphone (514) 496-3666 ()	FAX No. - N° de FAX (514) 496-3822
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

N° de l'invitation - Sollicitation No.
21301-185095/A
N° de réf. du client - Client Ref. No.
21301-185095

N° de la modif - Amd. No.
001
File No. - N° du dossier
MTA-7-40042

Id de l'acheteur - Buyer ID
mta375
N° CCC / CCC No.
N° VME - FMS

AMENDMENT NO.001

The purpose of this amendment is to answer questions raised by potential bidders. This amendment will update the Request for Proposal. Tenderers must take this into account when preparing their proposals.

Question 1)

Annex "A - Requirement", the characteristics of the required searchlight are entered in item # 5 "LED spotlight"

Except, under this list of characteristics, it is added "Test stereo". However, the stereo fly test as well as the 3D glasses are not part of the auto-spotlight. They constitute a separate set.

So our question is: Can the stereo test of the fly be submitted as a separate item and could be # 13 "Stereo test of the fly"?

If so, please indicate how this will be confirmed.

Answer 1)

The stereo test of the fly can be submitted as a separate item. Accordingly, the following amendments are made to Annex A

DELETE

5a. Wall mounted LED - according to industry standards

- _ Auto Projector with Zoom mounted on the wall with random fly Stereo test with glasses - according to industry standards
- _ Auto Projector
- _ Remote
- _ 2.5 to 6 m refraction distance
- _ red/green filter
- Stereo Test
- _ Min 1 pair of standard 3D glasses for adults

INSERT

5a. Wall mounted LED - according to industry standards

- _ Auto Projector with Zoom mounted on the wall – according to industry standards
- _ Auto Projector
- _ Remote
- _ 2.5 to 6 m refraction distance
- _ red/green filter

5b. Stereo fly test - according to industry standards

- _ Random fly Stereo test with glasses
- _ Min 1 pair of standard 3D glasses for adults

N° de l'invitation - Sollicitation No.
21301-185095/A
N° de réf. du client - Client Ref. No.
21301-185095

N° de la modif - Amd. No.
001
File No. - N° du dossier
MTA-7-40042

Id de l'acheteur - Buyer ID
mta375
N° CCC / CCC No.
N° VME - FMS

Question 2)

A) Annex A, point 6: Autorefractor / Keratometer in the requirement, The industry standard CSA approves the broad measure of -20 to +20 (by Health Canada) because -30 to +25 is completely useless when examining the human eye.

My question is: According to industry standard with CSA approval, Autorefractor / Keratometer with wide measuring range -25 to +22 would that be acceptable? If not why.

(B) Annex A, point 8. Lensometer

- Prism: 0 to 17
- Interpupillary distance 40 to 100mm
- Lens diameter: measurable up to 120mm.

Given that the requested parameters are practically non-standard, would the following measures be acceptable according to industry standards and not to a specific brand:

- Prism: 0 ~ 15 Δ 0.01 / 0.12 / 0.25 Δ steps
- Interpupillary distance 40mm ~ 86mm, 0.5mm steps
- Lens diameter measurable up to 100mm.

Answer 2)

A) ANNEX "A" Requirement, item 6. Auto refractor / keratometer

REMOVE

Large measuring range from -30 to +25

INSERT

Large measuring range from **-25 to +22**

B) ANNEX 'A' Requirement, item 8. Lensometer

REMOVE

- Prism: 0 to 17
- Interpupillary distance 40 to 100mm
- Diameter of lens measurable up to 120mm.

INSERT

- Prism: 0 ~ 15 Δ 0.01 / 0.12 / 0.25 Δ steps
- Interpupillary distance 40mm ~ 86mm, 0.5mm steps
- Lens diameter measurable up to 100mm.

ALL CLAUSES AND CONDITIONS OF THE REQUEST FOR PROPOSAL REMAIN UNCHANGED