

ANNEX "C"

(Rev. 01 dated 2017/11/29)

1. DESK AND WORKSTATION COMPONENTS

Refer to sheets for typical layouts:

W1	Activity Based Workspace (ABW) Workstation – floors 2, 14 through 19
W2	ABW Workstation floors 2, 14 through 19
W3	Fixed worker station - floors 2,3 and 4
W4	ABW Workstations - floor 13
W5	Flex Worker - floors 6 through 10
W6	Flex Worker with additional locker - floors 6 through 10
W7	Flex Worker - floors 6 through 10
W8	Flex Worker– reception on 8 th floor
W9	Free Address station - floors 2, 14 through 19
W10	Free Address station – floor 13
W11	Free Address station sit/stand desk - floor 13

CATEGORY A – INTERCONNECTABLE PANELS	
CODE	DESCRIPTION
P1	Seated Privacy Height Add On Maximum Height 1370mm/54in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Frosted Glazed (Includes Frame and Glazing) Width 610mm (24 in.)

CATEGORY A – INTERCONNECTABLE PANELS	
CODE	DESCRIPTION
P2	Seated Privacy Height Add On Maximum Height 1370mm/54in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Frosted Glazed (Includes Frame and Glazing) Width 914mm (36 in.)
P2p	Seated Privacy Height Add On Maximum Height 1370mm/54" Powered outlet(s) Below Work Surface Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Frosted Glazed (Includes Frame and Glazing) Width 914mm (36 in.)
P3	Seated Privacy Height Add On Maximum Height 1370mm/54in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Frosted Glazed (Includes Frame and Glazing) Width 1219mm (48 in.)

CATEGORY A – INTERCONNECTABLE PANELS	
CODE	DESCRIPTION
P4	Seated Privacy Height Add On Maximum Height 1370mm/54in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 610mm (24 in.)
P4p	Seated Privacy Height Add On Maximum Height 1370mm/54in. Powered outlet(s) Below Work Surface Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 610mm (24 in.)
P5	Seated Privacy Height Add On Maximum Height 1370mm/54in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 914mm (36 in.)

CATEGORY A – INTERCONNECTABLE PANELS	
CODE	DESCRIPTION
P5p	Seated Privacy Height Add On Maximum Height 1370mm/54in. Powered outlet(s) Below Work Surface Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 914mm (36 in.)
P6	Seated Privacy Height Add On Maximum Height 1370mm/54in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 1219mm (48 in.)
P7	Seated Privacy Height Add On Maximum Height 1370mm/54in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 1524mm (60 in.)

CATEGORY A – INTERCONNECTABLE PANELS	
CODE	DESCRIPTION
P7p	Seated Privacy Height Add On Maximum Height 1370mm/54in. Powered outlet(s) Below Work Surface Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 1524mm (60 in.)
P8	Base Height Minimum Height 914mm/36in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 1524mm (60 in.)
P9	Base Height Minimum Height 914mm/36in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 914mm (36 in.)

CATEGORY A – INTERCONNECTABLE PANELS	
CODE	DESCRIPTION
P9p	Base Height Minimum Height 915mm/36in. Powered outlet(s) Below Work Surface Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 914mm (36 in.)
P10	Base Height Minimum Height 915mm/36in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Frosted Glazed (Includes Frame and Glazing) Width 1219mm (48 in.)
P11	Base Height Minimum Height 915mm/36in. Non-Powered Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 1524mm (60 in.)

CATEGORY A – INTERCONNECTABLE PANELS	
CODE	DESCRIPTION
P11p	Base Height Minimum Height 915mm/36in. Powered outlet(s) Below Work Surface Lower Element 1 Fabric Lower Element 2 Fabric Upper Element 1 Fabric Width 1524mm (60 in.)
Electrical Notes	<ul style="list-style-type: none"> • Supply electrical and data through a power pole supplied & installed by furniture supplier. Connection in ceiling space above workstation. • 5 wire requirement only. • Two duplex outlets, one data-one voice port per station • Power and data outlets located below work surface height • On central spines of workstation groups/pods, only the shared spine of the workstation shall be powered panels. • Only one side of a workstation requires a powered panel(s).
Panel Notes	<ul style="list-style-type: none"> • All panels at exterior windows must be 915mm (36”) high maximum. • Refer to the associated plans for workstation group/pod configurations and minor variations from typical indicated in this package.

CATEGORY B - WORK SURFACES	
CODE	DESCRIPTION
T1	Work Surface Panel Mounted High Pressure Laminate Rectangular 610mm(24") Depth 1828mm (72") Width
T2	Work Surface Panel Mounted High Pressure Laminate 610mm(24") Depth 610mm(24") Width
T3	Work Surface Panel Mounted High Pressure Laminate Rectangular 610mm(24") Depth 1219mm (48") Width
T4	Work Surface Panel Mounted High Pressure Laminate Rectangular 610mm(24") Depth 1524mm (60") Width
T5	Work Surface 2 Full Gable Ends (w/ modesty) High Pressure Laminate Rectangular 610mm(24") Depth 1524mm (60") Width
T6	Work Surface 2 Half Gables (w/ modesty) High Pressure Laminate Rectangular 610mm(24") Depth 1067mm (42") Width
T7	Work Surface 2 Full Gable Ends (w/ modesty) High Pressure Laminate Rectangular 610mm(24") Depth 1828mm (72") Width

CATEGORY B - WORK SURFACES	
CODE	DESCRIPTION
T8	Work Surface 2 Full Gable Ends (w/ modesty) High Pressure Laminate Rectangular 914mm(36") Depth 1828mm (72") Width

CATEGORY C - STORAGE	
CODE	DESCRIPTION
TS1	Personal Storage Towers Wardrobe one side, 2 file drawers at bottom and closed cupboard above, with lock. 1676mm(66 in.) high 610mm (24 in.) x 610mm (24 in.) - left
TS2	Pedestal Work Surface Supporting, Depth 762mm (30 in.) work surface File, File
TS3	Pedestal Work Surface Supporting, Depth 762mm (30 in.) Box, Box, File
TS4	Pedestals Mobile, Locking Casters, Depth 762mm (30 in.) work surface File, File
TS5	Locking Lateral Filing Cabinets Two (2) fixed front drawers 457mm (18 in.) x 914mm (36 in.)
TS6	Hutches Laminate Rectangular Two Hinged Doors Closed Cupboard 305mm (12") Depth x 1828mm (72") Width

Refer to Workstation sheets 'W#' for typical layouts including Sit Stand desks:

SD1	Sit Stand desk
SD2	Sit Stand desk
SD3	Sit Stand desk
SD4	Computer desk

CATEGORY D - SIT STAND DESKS	
CODE	DESCRIPTION
SD1	Sit/Stand Range Height Adjustable Work Surfaces/ Electrically assisted 762mm(30") Deep 1219mm (48") Long
SD2	Sit/Stand Range Height Adjustable Work Surfaces/ Electrically assisted 610mm(24") Deep 1219mm (48") Long
SD3	Sit/Stand Range Height Adjustable Work Surfaces/ Electrically assisted 610mm(24") Deep 1524mm (60") Long
SD4	Sit/Stand Range Height Adjustable Work Surfaces/ Electrically assisted 762mm (30") Deep 914mm (36") Long

CATEGORY E - ACCESSORIES	
CODE	DESCRIPTION
A1	Single Monitor Arm, Edge Clamp Mount, Height Adjustable.
A2	Dual Monitor Arms, Edge Clamp Mount, Height Adjustable.
A3	Paper sorter, Panel Mounted, Rigid Plastic
A4	in and out trays, Panel Mounted, Rigid Plastic
A5	Task Light –desk base type
A6	Computer Support, Work Surface Mounted

2. TABLES/MEETING ROOMS - SPECIFICATIONS

Refer to sheets for typical layouts:

M1	Small rectangle table (Phone Booth)
M2	Small Round Meeting table for 2
M3	Round Meeting table for 4
M4	Rectangle Meeting table for 4
M5	Rectangle Meeting table for 6
M6	Medium Meeting table for 10 – single table
M7	Training Tables – flip top
M8	Training Tables – flip top
M9	Rectangle Meeting table for 4
M10	High Rectangle Meeting table for 6
M11	Coffee Table
M12	End Table
M13	Lunch Table
M14	Lunch Table
M15	Multi-media Table for 6
M16	Mobile table- rectangle
M17	Mobile table- tear drop

TABLES FOR MEETING AND TRAINING ROOMS	
CODE	DESCRIPTION
M1	Meeting room table Four post metal legs with glides Rectangular High Pressure Laminate top One recessed box with four (4) power and four (4) data outlets with a flexible casing Depth 610mm (24") x Width 1524mm (60")
M2	Meeting room table Four point metal base with glides Round top High Pressure Laminate top 914mm diameter (36")

TABLES FOR MEETING AND TRAINING ROOMS	
CODE	DESCRIPTION
M3	Meeting room table Four point metal base with glides Round top High Pressure Laminate top Center grommet 1219mm diameter (48")
M4	Meeting room table four post metal legs with glides Rectangle High Pressure Plastic laminate top One recessed box with four (4) power and four (4) data outlets with a flexible casing Depth 762mm (30") x Width 1524mm (60")
M5	Meeting room tables Laminate panel base with wire access Boat top High Pressure Laminate top One recessed box with four (4) power and four (4) data outlets with a flexible casing Depth 1067mm (42") x Width 2134mm (84")
M6	Meeting room tables Four point metal base with glides Rectangular High Pressure Laminate top Two recessed box with four (4) power and four (4) data outlets with a flexible casing Depth 914mm (36") x Width 3048mm (120")
M7	Table Flip-top C legs with lockable caster Rectangular Laminate With grommet Depth 762mm (30") x Width 1524mm (60")

TABLES FOR MEETING AND TRAINING ROOMS	
CODE	DESCRIPTION
M8	Table Flip-top C legs with lockable caster Rectangular Laminate With grommet With Laminate Modesty Panel Depth 762mm (30") x Width 1524mm (60")
M9	Meeting room tables Four post metal legs with glides Rectangular High Pressure Laminate top One recessed box with four (4) power and four (4) data outlets with a flexible casing Depth 914mm (36") x Width 2134mm (84")
M10	Meeting room tables Four post metal legs with glides Rectangular High Pressure Laminate top Two recessed box with four (4) power and four (4) data outlets with a flexible casing Depth 914mm (36") x Width 2438mm (96") x Height 914mm (36")
M11	Coffee Table Four Metal Legs Self-Edge Rectangular Laminate Depth 610mm (24") x Width 1219mm (48") x Height 337mm(14") to 533mm(21")
M12	Side Table Four Metal Legs Self-Edge Round top Laminate Diameter 610mm (24") X Height 337mm (14") to 533mm(21")
M13	Meeting room table Four point metal base with glides Square High Pressure Laminate top Depth 762mm (30") x Width 762mm (30"), Height 762mm (30")

TABLES FOR MEETING AND TRAINING ROOMS	
<i>CODE</i>	<i>DESCRIPTION</i>
M14	Meeting room table Four point metal base with glides Round top Diameter 914mm (36"), Height 762mm (30"),
M15	Multi-media table with Monitor Support Mount Seated Height with cable and wire management For Single Monitors D-shaped top High Pressure Laminate top Two recessed box with four (4) power and four (4) data outlets with a flexible casing Depth 1524mm (60") x Width 1981mm (78")
M16	Meeting room table Four post metal legs with lockable casters Rectangular High Pressure Laminate top Width 1219mm (48") x Depth 610mm (24")
M17	Meeting room table Four post metal legs with lockable casters Tear drop shaped High Pressure Laminate top DIAMETER 1118mn (44")

3. COLLABORATIVE SPACE - SPECIFICATION

Refer to sheets for typical layouts:

C1	Banquette bench short
C2	Banquette bench long
C3	Tablet lounge chairs – 2 set
C4	ABW Isolation tablet chairs
C5	Sofa two seat
C6	Sofa three seat
C7	Upholstered side chair

COLLABORATIVE SPACES	
CODE	DESCRIPTION
C1	Ganging Banquette Seating Four legs with non-marking adjustable glides High Back Add-on Screen Without arms two seat Metal frame With Velcro attachment Crypton Depth Range 483mm (19") to 914mm (36") Width Range 1168mm (46") to 1828mm (72") Height 1092mm (43") to 1372mm (54")
C2	Ganging Banquette Seating Four legs with non-marking adjustable glides High Back Add-on Screen Without arms two seat Metal frame With Velcro attachment Crypton Depth 483mm (19") to 914mm (36") Width 1753mm (69") to 2625mm (103.5") Height 1092mm (43") to 1372mm (54")

COLLABORATIVE SPACES	
CODE	DESCRIPTION
C3	Lounge Chair Four casters with two locking Universal Tablet Arm and a 360° turning radius Metal frame With Velcro attachment Fabric
C4	Lounge Chair Four casters with two locking Universal Tablet Arm and a 360o turning radius High Back Screen that Surrounds Three Sides Metal frame With Velcro attachment Fabric Depth 483mm to 889mm (19"to 35") Width 594mm to 1143mm (23.5" to 45") Height 1092mm to 1372mm (43" to 54")
C5	Sofa for two adults Four legs with glides With arms Metal frame With Velcro attachment Crypton
C6	Sofa for three adults Four legs with glides With arms Metal frame With Velcro attachment Crypton
C7	Lounge Chair Four legs with glides for carpets With arms Metal frame With Velcro attachment Fabric

4. SEATING

SEATING – SUPPORT SPACES	
<i>CODE</i>	<i>DESCRIPTION</i>
SS1	Kitchenette Chair Four Legs With Arms Non-Perforated Molded Plastic or Polyamide
SS2	Kitchenette Chair Four Legs Without Arms Non-Perforated Molded Plastic or Polyamide
SS3	Bar Stool Four metal Legs Footrest Without Arms Non-Perforated Molded Plastic or Polyamide Seat Height 610mm(24")
SS4	Bar Stool Four metal Legs Footrest With Arms Upholstered Fabric