



**RETURN BIDS TO:**

**RETOURNER LES SOUMISSIONS À:**

Public Works and Government Services / Travaux  
publics et services gouvernementaux  
Kingston Procurement  
Des Acquisitions Kingston  
86 Clarence Street, 2nd floor  
Kingston  
Ontario  
K7L 1X3  
Bid Fax: (613) 545-8067

**SOLICITATION AMENDMENT  
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise  
indicated, all other terms and conditions of the Solicitation  
remain the same.

Ce document est par la présente révisé; sauf indication contraire,  
les modalités de l'invitation demeurent les mêmes.

**Comments - Commentaires**

**Vendor/Firm Name and Address**  
Raison sociale et adresse du  
fournisseur/de l'entrepreneur

**Issuing Office - Bureau de distribution**  
Public Works and Government Services / Travaux  
publics et services gouvernementaux  
Kingston Procurement  
Des Acquisitions Kingston  
86 Clarence Street, 2nd floor  
Kingston  
Ontario  
K7L 1X3

<b>Title - Sujet</b> Portable Mist Collector	
<b>Solicitation No. - N° de l'invitation</b> W0125-18CR08/A	<b>Amendment No. - N° modif.</b> 001
<b>Client Reference No. - N° de référence du client</b> W0125-18-CR08	<b>Date</b> 2018-01-24
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$KIN-650-7396	
<b>File No. - N° de dossier</b> KIN-7-48151 (650)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2018-01-30</b>	
<b>Time Zone</b> Fuseau horaire Eastern Standard Time EST	
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Rombough, Lori	<b>Buyer Id - Id de l'acheteur</b> kin650
<b>Telephone No. - N° de téléphone</b> (613) 545-8061 ( )	<b>FAX No. - N° de FAX</b> (613) 545-8067
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

**Instructions: See Herein**

**Instructions: Voir aux présentes**

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> Raison sociale et adresse du fournisseur/de l'entrepreneur	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

## AMENDMENT #001

The intent of this amendment is to answer a potential bidder's question and revise some areas of the Request for Proposal.

**Q1.** Portable oil mist collector (Lev-co model 02-065 or equivalent). At a minimum, the portable oil mist collector must possess the following features:

☐ 5 hp motor 208-230V/460V/3/

☐ Variable frequency drive for the motor ☐ Hood with damper ☐ Carbon filter holder ☐ Wall bracket ☐ Hose clamps ☐ Flame retardant hose for extraction arms ☐ Minimum airflow: 2,400 CFM ☐ 10 foot flexible arm ☐ 2 Washable filters, with a minimum life of 5 years

The problem is we are asking for minimum specs that it has a • 5 hp motor 208-230V/460V/3/ and • Minimum airflow: 2,400 CFM; when the specs for (Lev-co model 02-065 or equivalent) are less than the minimum we are asking for, "The notice description is for a Lev-co model 02-065 or equivalent with specs as follows:

- air flow 1200 cfm
- motor 115v, 1.5 hp

Please advise if you want the specs to read motor 115v, 1.5 hp vice 5 hp motor 208-230V/460V/3/ and air flow 1200 cfm vice Minimum airflow: 2,400 CFM.

**A1.** The client has confirmed the equivalent model # 02-065 included the following optional upgrades:

- 5HP motor;
- 2400 CFM; and
- the flexible arm has a 12 inch diameter.

## DELETIONS and INSERTIONS

### **#1. UNDER: PART 6 - RESULTING CONTRACT CLAUSES**

#### **Within: 6.4.2 Delivery Date**

Delete in its entirety and insert: All the deliverables must be received on or before 29 March 2018.

### **#2. UNDER: ANNEX "A" - REQUIREMENT**

#### **Within: 1 Scope**

Delete in its entirety and insert:

The Department of National Defence (DND), 8 Air Maintenance Squadron (EMS), Engine Bay 3 hanger located at Canadian Forces Base Trenton (8 Wing) Ontario, conducts maintenance on C-130 Propellers. During the maintenance performed, there is a requirement to pressurize the system which produces a hydraulic mist that must be captured from the breathable air within the shop work area. EMS requires 3 portable oil mist collectors (Lev-Co model 02-065 with options or equivalent).

#### **Within: Portable oil mist collector (Lev-co model 02-065 or equivalent)**

Delete in its entirety and insert

**Portable oil mist collector (Lev-co model 02-065 with options or equivalent)**

At a minimum, the portable oil mist collector must possess the following features:

- 5 hp motor 208-230V/460V/3/
- Variable frequency drive for the motor
- Hood with damper
- Carbon filter holder
- Wall bracket
- Hose clamps
- Flame retardant hose for extraction arms
- Minimum airflow: 2,400 CFM
- 10 foot flexible arm with 12 inch diameter
- 2 Washable filters, with a minimum life of 5 years

**All other terms and conditions remain unchanged.**