



## RETURN BIDS TO:

## RETOURNER LES SOUMISSIONS À:

Public Works and Government Services / Travaux  
publics et services gouvernementaux  
Kingston Procurement  
Des Acquisitions Kingston  
86 Clarence Street, 2nd floor  
Kingston  
Ontario  
K7L 1X3  
Bid Fax: (613) 545-8067

## SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise  
indicated, all other terms and conditions of the Solicitation  
remain the same.

Ce document est par la présente révisé; sauf indication contraire,  
les modalités de l'invitation demeurent les mêmes.

### Comments - Commentaires

Vendor/Firm Name and Address  
Raison sociale et adresse du  
fournisseur/de l'entrepreneur

### Issuing Office - Bureau de distribution

Public Works and Government Services / Travaux  
publics et services gouvernementaux  
Kingston Procurement  
Des Acquisitions Kingston  
86 Clarence Street, 2nd floor  
Kingston  
Ontario  
K7L 1X3

<b>Title - Sujet</b> Cleaning Equipment	
<b>Solicitation No. - N° de l'invitation</b> W0114-18PS49/A	<b>Amendment No. - N° modif.</b> 001
<b>Client Reference No. - N° de référence du client</b> W0114-18-PS49	<b>Date</b> 2018-02-22
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$KIN-615-7421	
<b>File No. - N° de dossier</b> KIN-7-48216 (615)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2018-02-26</b>	
<b>Time Zone</b> Fuseau horaire Eastern Standard Time EST	
<b>F.O.B. - F.A.B.</b> Specified Herein - Précisé dans les présentes <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input type="checkbox"/> <b>Other-Autre:</b> <input checked="" type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Denbeigh, Andrew	<b>Buyer Id - Id de l'acheteur</b> kin615
<b>Telephone No. - N° de téléphone</b> (613) 484-1586 ( )	<b>FAX No. - N° de FAX</b> (613) 545-8067
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b> DEPARTMENT OF NATIONAL DEFENCE CFB KINGSTON BACCN Warehouse 1 Cable Lane, Bldg VC-21 Kingston, ON K7L 7B4 Canada	

Instructions: See Herein

Instructions: Voir aux présentes

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

---

## AMENDMENT 001

This Amendment 001 is raised in order to respond to supplier inquiries and modify Annex "A".

### Questions and Answers

Question 1:

#### 2.1.2 Carpet Extractor with Accessories (Quantity 10)

**The power for the carpet cleaner shows 220 volt? Should the correct specification be: 50 -60 HrZ 110 V?**

Response 1: The correct specification for the voltage, frequency and power requirement for this item is as follows:

Voltage: Must be within the range of 110 to 120 volts;  
Frequency: Must be within the range of 50 to 60Hz;  
Power Requirement: 1100 to 1250 Watt;

**Question 2:**

**What is a Mini Floor Scrubber- A polisher?**

Response 2:

A mini floor scrubber/polisher is a multiply use cleaning machine that is lightweight handheld that can be used as a floor cleaner, scrubber, polisher and vacuum.

**Question 3:**

#### 2.1.1 Mini Floor Scrubber/Polisher with Accessories (Quantity 10)

**7-10 pounds is very low weight**

Response 3:

The Mini Floor Scrubber/Polisher is a small lightweight handheld floor cleaner, scrubber, polisher and vacuum that has a weight between 7 to 10 pounds.

**Question 4:**

#### 2.1.1 Mini Floor Scrubber/Polisher with Accessories (Quantity 10)

**It says you need 5 inch microfiber pads, we need a better idea of what we are quoting here.**

Response 4:

The majority of the Mini Floor Scrubber/Polisher available for purchase come with multiple floor cleaning accessories pads.  
The 5 inch microfiber pads are reusable pads that are used for cleaning and polishing floors.

**Question 5:**

#### 2.1.1 Mini Floor Scrubber/Polisher with Accessories (Quantity 10)

**The weight of 7-10 pounds for a polisher is an issue. Is it a handheld machine?**

Response 5:

The Mini Floor Scrubber/Polisher is a small lightweight handheld floor cleaner, scrubber, polisher and vacuum that has a weight between 7 to 10 pounds.

**Question 6:**

**2.1.2 Carpet Extractor with Accessories (Quantity 10)**

**2.1.2- The carpet extractor has the accessories listed below but they don't really go with the extractor.**

Response 6:

The majority of the carpet extractor available for purchase come with various accessories such as hoses, wands, power heads and upholstery tools.

The accessories requested are available for carpet extractors that meet the specifications as they have been posted.

**Changes to RFP**

**Under Annex "A" Delete:**

**2.1.1 Mini Floor Scrubber/Polisher with Accessories (Quantity 10)**

The Mini Floor Scrubber/Polisher must:

- Scrubs, clean, and polish tile, wood, stone, marble, concrete, and other hard floors.
- Remove stains from carpets.
- Clean surfaces with any cleaning spray product.
- Manoeuvre into small spaces and under or around furniture and objects.

**2.1.1.1 Accessories**

Each Mini Floor Scrubber Polisher must come with the following accessories:

- 5 inch Nylon Scrub Brushes (Quantity 2);
- 5 inch Carpet Bonnets (Quantity 2);
- 5 inch Microfiber Pads (Quantity 2);
- 5 inch Felt Pads (Quantity 4).

**2.1.1.2 Specifications**

Each Mini Floor Scrubber Polisher must meet the following specifications:

Dimension: Must be within the range of between 10 to 15 inches (length) x 10 to 15 inches (width) x 10 to 15 inch (height);

Weight: Must be within the range of between 7 to 10 pounds;

Cleaning Path: Must be within the range of between 10 to 11 inches;

Handle: Must be steel with a foot activated release pedal;

Brushes: Must be dual counter rotating with the brushes turning at a range between 400 to 600rpm;

Rear Wheels: Must have 2 heavy duty rubber wheels;

Must be non-marking;

---

Must have a size within the range of between 2 to 4 inches;  
Voltage: 120 volts;  
Frequency: 60HZ;  
Power Requirement: 180 Watt;  
Power Cord: Must be 18 gauge with 3 conductor cords;  
Must have a three-prong plug;  
Must have a cord length within the range of between 18 to 50 feet; and  
Power Switch: Must be a foot activated power pedal.

### **2.1.2 Carpet Extractor with Accessories (Quantity 10)**

The Carpet Extractor must:

- Clean small to medium sized carpets, upholstery, and textile flooring.
- Inject and vacuum water and cleaning solution, leaving little moisture residue after cleaning.
- Store the cleaning agent and accessories on the machine.
- Come equipped with a fresh water tank, a removable dirty water tank, accessory storage, easy change couplings, and a carrying handle for ease of transporting.

#### **2.1.2.1 Accessories Included**

Each Carpet Extractor must come with the following accessories:

- 13 feet Spray Hose with Integral Water Feed;
- Suction Tube;
- 9 inch Flexible Floor Nozzle;
- D- Shape Support Handle;
- Upholstery Nozzle Tool;
- 4 to 5 inch Hand Tool Nozzle;
- 24 inch Extension Wand;

#### **2.1.2.2 Specifications**

Each Carpet Extractor must meet the following specifications:

Dimensions: Must be within the range of between 25 to 30 inches (length) x 10 to 15 inches (width) x 15 to 20 (height);  
Weight: Must be within the range of between 20 to 25 pounds;  
Fresh Water Tank: Must have a holding capacity within the range of between 2 to 3 gallons;  
Dirt Water Tank: Must have a holding capacity within the range of between 2 to 3 gallons;  
Vacuum Water Lift: Must be within the range of between 85 to 88 inches;  
Spray Rate: Must be within the range of between 12 to 13 psi;  
Spray Pressure: Must be within the range of between 14 to 15 psi;  
Solution Capacity: Must have a capacity within the range of between 2 to 3 gallons;  
Rear Wheels: Must have 2 heavy duty rubber wheels;  
Must be non-marking;  
Must have a size within the range of between 8 to 10 inches;  
Front Casters: Must have 2 heavy duty rubber casters;  
Must be locking casters;  
Must have a size within the range of between 3 to 4 inches;  
Voltage: Must be within the range of 220 to 240 volts;  
Frequency: Must be within the range of 50 to 60Hz;  
Power Requirement: 1250 Watt;  
Power Cord: Must be 18 gauge with 3 conductor cords;

---

Must have a three-prong plug;  
Must have a cord length within the range of between 18 to 50 feet; and  
Power Switch: Must be a two switch operation.

### **2.1.3 Restroom System with Accessories (Quantity 10)**

The Restroom System must:

- Provide touch-free deep cleaning of porous tile, grout lines, showers, tubs, counters, sinks, and hard to reach places in restrooms.
- Come equipped with on-board storage for accessories for easy transporting.
- Allow for easy access to solution and recovery tanks.
- Provide an automatic cleaning agent feed.
- Have the controls located on the handle.

#### **2.1.3.1 Accessories Included**

Each Restroom System must come with the following accessories:

- Swivel wand with squeegee/brush head
- 25 foot vacuum/solution hose with a minimum hose diameter of 1.5 inch
- Pressure gun
- 25 foot fixture drying hose with a minimum hose diameter of 1.5 inch

#### **2.1.3.2 Specifications**

Each Restroom System must meet the following specifications:

Dimensions: Must be within the range of between 35 to 37 inches (length) x 20 to 22 inches (width) x 35 to 40 inches (height);

Weight: Must be within the range of between 100 to 125 pounds;

Water Lift: Must be within the range of between 100 to 120 inches;

Solution Tank: Must be within the capacity range of between 15 to 17 gallons;

Recovery Tank: Must be within the capacity range of between 15 to 17 gallons;

Pump Pressure: Must be within the pressure range of between 500 to 600 psi;

Nozzle Pressure: Must be within the pressure range of between 450 to 500 psi;

Rear Wheels: Must have 2 heavy duty rubber wheels;

Must be non-marking;

Must be within the size range of between 8 to 10 inches;

Front Casters: Must have 2 heavy duty rubber casters;

Must be locking casters;

Must be within the size range of between 3 to 4 inches:

Voltage: 120 volts;

Frequency: 60HZ;

Power Requirement: 180 Watt;

Power Cord: Must be 18 gauge with 3 conductor cords;

Must have a three-prong plug;

Must be within the cord length range of between 18 to 50 feet; and

Power Switch: Must be a two switch operation.

### **2.1.4 Upright Vacuum with Accessories (Quantity 14)**

The Upright Vacuum must:

- Clean small to medium sized carpets, upholstery, and textile flooring.

- Allow for easy cleaning under furniture.
- Be low maintenance and withstands heavy-duty wear and tear.
- Provide a wide cleaning path and be easily maneuvered, allowing for use in a variety of tasks.
- Be serviced without tools to provide easy clearing of blockages in brush roller or hoses.
- Store accessories on machine.
- Have controls located on the handle.

#### **2.1.4.1 Accessories Included**

Each Upright Vacuum must come with the following accessories:

- 24 inch clog-resistant wand
- 8 foot stretch hose
- 10 pack micro filter bag
- Hepa filter
- Crevice tool
- Upholstery tool

#### **2.1.4.2 Specifications**

Each Upright Vacuum must meet the following specifications:

Dimensions: Must be within the range of between 15 to 22 inches (width) x 40 to 48 inches (height);  
Weight: Must be within the range of between 15 to 20 pounds;  
Handle: Must be lowered by a foot activated release pedal;  
Cleaning Path: Must be within the range of between 10 to 15 inches;  
Static Lift: Must be within the range of between 90 to 95 inches;  
Noise Decibel: Must be within the range of between 65 and 70 dba;  
Recovery Tank: Must be within the capacity range of between 3 to 4 quarts;  
Hose Length: Must be within the range of between 8 to 10 feet;  
Filter: Must have a dual filter system consisting of a replaceable micro filter bag and replaceable Hepa filter;  
Rear Wheels: Must have 2 heavy duty rubber wheels;  
                    Must be non-marking;  
                    Must be within the size range of between 10 to 15 inches;  
Voltage: 120 volts;  
Frequency: 60HZ;  
Power Requirement: 1100 Watt;  
Power Cord: Must be 18 gauge with 3 conductor cords;  
                    Must have a three-prong plug;  
                    Must be within the cord length range of between 18 to 50 feet;  
Power Switch: Must be located on the handle and offer on/off function; and  
Performance Indicator: Must have 3 performance indicator settings - good, replace bag, and requires servicing. This indicator must be displayed on the front panel.

**Insert the following:**

#### **2.1.1 Mini Floor Scrubber/Polisher with Accessories (Quantity 10)**

The Mini Floor Scrubber/Polisher must:

- Scrubs, clean, and polish tile, wood, stone, marble, concrete, and other hard floors.
- Remove stains from carpets.
- Clean surfaces with any cleaning spray product.
- Manoeuvre into small spaces and under or around furniture and objects.

### 2.1.1.1 Accessories

Each Mini Floor Scrubber Polisher must come with the following accessories:

- 5 inch Nylon Scrub Brushes (Quantity 2);
- 5 inch Carpet Bonnets (Quantity 2);
- 5 inch Microfiber Pads (Quantity 2);
- 5 inch Felt Pads (Quantity 4).

### 2.1.1.2 Specifications

Each Mini Floor Scrubber Polisher must meet the following specifications:

Dimension: Must be within the range of between 10 to 15 inches (length) x 10 to 15 inches (width) x 10 to 15 inch (height);

Weight: Must be within the range of between 7 to 11 pounds;

Cleaning Path: Must be within the range of between 9 to 11 inches;

Handle: Must be steel with a foot activated release pedal;

Brushes: Must be dual counter rotating with the brushes turning at a range between 400 to 600rpm;

Rear Wheels: Must have 2 heavy duty rubber wheels;

Must be non-marking;

Must have a size within the range of between 2 to 4 inches;

Voltage: 120 volts;

Frequency: 60HZ;

Power Requirement: 160 to 180 Watt;

Power Cord: Must be 18 gauge with 3 conductor cords;

Must have a three-prong plug;

Must have a cord length within the range of between 18 to 50 feet; and

Power Switch: Must be a foot activated power pedal.

### 2.1.2 Carpet Extractor with Accessories (Quantity 10)

The Carpet Extractor must:

- Clean small to medium sized carpets, upholstery, and textile flooring.
- Inject and vacuum water and cleaning solution, leaving little moisture residue after cleaning.
- Store the cleaning agent and accessories on the machine.
- Come equipped with a fresh water tank, a removable dirty water tank, accessory storage, easy change couplings, and a carrying handle for ease of transporting.

#### 2.1.2.1 Accessories Included

Each Carpet Extractor must come with the following accessories:

- 13 feet Spray Hose with Integral Water Feed;
- Suction Tube;
- Minimum 9 inch Flexible Floor Nozzle;
- D- Shape Support Handle;
- Upholstery Nozzle Tool;
- 3 to 5 inch Hand Tool Nozzle;
- 24 inch Extension Wand;

#### 2.1.2.2 Specifications

Each Carpet Extractor must meet the following specifications:

**Dimensions:** Must be within the range of between 20 to 30 inches (length) x 10 to 15 inches (width) x 15 to 20 (height);

**Weight:** Must be within the range of between 20 to 30 pounds;

Fresh Water Tank: Must have a holding capacity within the range of between 2 to 3 gallons;

Dirt Water Tank: Must have a holding capacity within the range of between 2 to 3 gallons;

Vacuum Water Lift: Must be within the range of between 85 to 88 inches;

Spray Rate: Must be within the range of between 12 to 13 psi;

Spray Pressure: Must be within the range of between 14 to 15 psi;

**Solution Capacity:** Must have a capacity within the range of between 1.5 to 3 gallons;

Rear Wheels: Must have 2 heavy duty rubber wheels;

Must be non-marking;

Must have a size within the range of between 8 to 10 inches;

Front Casters: Must have 2 heavy duty rubber casters;

Must be locking casters;

Must have a size within the range of between 3 to 6 inches;

**Voltage:** Must be within the range of 110 to 120 volts;

Frequency: Must be within the range of 50 to 60Hz;

**Power Requirement:** 1100 to 1250 Watt;

Power Cord: Must be 18 gauge with 3 conductor cords;

Must have a three-prong plug;

**Must have a cord length within the range of between 15 to 50 feet; and**

Power Switch: Must be a two switch operation.

### 2.1.3 Restroom System with Accessories (Quantity 10)

The Restroom System must:

-Provide touch-free deep cleaning of porous tile, grout lines, showers, tubs, counters, sinks, and hard to reach places in restrooms.

-Come equipped with on-board storage for accessories for easy transporting.

-Allow for easy access to solution and recovery tanks.

-Provide an automatic cleaning agent feed.

-Have the controls located on the handle.

#### 2.1.3.1 Accessories Included

Each Restroom System must come with the following accessories:

-Swivel wand with squeegee/brush head

**-25 to 45 foot vacuum/solution hose with a minimum hose diameter of 1.5 inch**

-Pressure gun

**-25 to 45 foot fixture drying hose with a minimum hose diameter of 1.5 inch**

#### 2.1.3.2 Specifications

Each Restroom System must meet the following specifications:

**Dimensions:** Must be within the range of between 25 to 37 inches (length) x 20 to 22 inches (width) x 35 to 40 inches (height);

**Weight:** Must be within the range of between 100 to 125 pounds;

**Water Lift:** Must be within the range of between 100 to 130 inches;

**Solution Tank:** Must be within the capacity range of between 15 to 17 gallons;



Recovery Tank: Must be within the capacity range of between 15 to 17 gallons;  
Pump Pressure: Must be within the pressure range of between 500 to 600 psi;  
Nozzle Pressure: Must be within the pressure range of between 450 to 500 psi;  
Rear Wheels: Must have 2 heavy duty rubber wheels;  
Must be non-marking;  
Must be within the size range of between 8 to 10 inches;  
Front Casters: Must have 2 heavy duty rubber casters;  
Must be locking casters;  
Must be within the size range of between 3 to 6 inches;  
Voltage: 120 volts;  
Frequency: 60HZ;  
Power Requirement: 1740 to 1800 Watt;  
Power Cord: Must be 18 gauge with 3 conductor cords;  
Must have a three-prong plug;  
Must be within the cord length range of between 18 to 50 feet; and  
Power Switch: Must be a two switch operation.

#### **2.1.4 Upright Vacuum with Accessories (Quantity 14)**

The Upright Vacuum must:

- Clean small to medium sized carpets, upholstery, and textile flooring.
- Allow for easy cleaning under furniture.
- Be low maintenance and withstands heavy-duty wear and tear.
- Provide a wide cleaning path and be easily maneuvered, allowing for use in a variety of tasks.
- Be serviced without tools to provide easy clearing of blockages in brush roller or hoses.
- Store accessories on machine.
- Have controls located on the handle.

##### **2.1.4.1 Accessories Included**

Each Upright Vacuum must come with the following accessories:

- 24 inch clog-resistant wand
- 8 foot stretch hose
- 10 pack micro filter bag
- Hepa filter
- Crevice tool
- Upholstery tool

##### **2.1.4.2 Specifications**

Each Upright Vacuum must meet the following specifications:

Dimensions: Must be within the range of between 15 to 22 inches (width) x 40 to 48 inches (height);  
Weight: Must be within the range of between 15 to 20 pounds;  
Handle: Must be lowered by a foot activated release pedal;  
Cleaning Path: Must be within the range of between 10 to 15 inches;  
Static Lift: Must be within the range of between 90 to 95 inches;  
Noise Decibel: Must be within the range of between 65 and 70 dba;  
Recovery Tank: Must be within the capacity range of between 3 to 4 quarts;  
Hose Length: Must be within the range of between 8 to 10 feet;  
Filter: Must have a dual filter system consisting of a replaceable micro filter bag and replaceable Hepa filter;  
Rear Wheels: Must have 2 heavy duty rubber wheels;

---

Must be non-marking;

Must be within the size range of between 10 to 15 inches;

Voltage: 120 volts;

Frequency: 60HZ;

Power Requirement: 1100 Watt;

Power Cord: Must be 18 gauge with 3 conductor cords;

Must have a three-prong plug;

Must be within the cord length range of between 18 to 50 feet;

Power Switch: Must be located on the handle and offer on/off function; and

Performance Indicator: Must have 3 performance indicator settings - good, replace bag, and requires servicing. This indicator must be displayed on the front panel.

**ALL OTHER TERMS AND CONDITIONS OF THE RFP REMAIN UNCHANGED**