



**RETURN BIDS TO:**

**RETOURNER LES SOUMISSIONS À:**

Public Works and Government Services Canada  
ATB Place North Tower  
10025 Jasper Ave./10025 ave. Jasper  
5th floor/5e étage  
Edmonton  
Alberta  
T5J 1S6  
Bid Fax: (780) 497-3510

**SOLICITATION AMENDMENT  
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

**Comments - Commentaires**

**Vendor/Firm Name and Address  
Raison sociale et adresse du  
fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**  
Public Works and Government Services Canada  
ATB Place North Tower  
10025 Jasper Ave./10025 ave Jasper  
5th floor/5e étage  
Edmonton  
Alberta  
T5J 1S6

<b>Title - Sujet</b> Boiler Replacement	
<b>Solicitation No. - N° de l'invitation</b> EW038-182617/A	<b>Amendment No. - N° modif.</b> 001
<b>Client Reference No. - N° de référence du client</b> AFAC EW038-182617	<b>Date</b> 2018-03-09
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$PWU-201-11326	
<b>File No. - N° de dossier</b> PWU-7-40238 (201)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2018-03-28</b>	<b>Time Zone</b> Fuseau horaire Mountain Daylight Saving Time MDT
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Ho (RPC), Hector	<b>Buyer Id - Id de l'acheteur</b> pwu201
<b>Telephone No. - N° de téléphone</b> (780) 901-0989 ( )	<b>FAX No. - N° de FAX</b> (780) 497-3510
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

**Instructions: See Herein**

**Instructions: Voir aux présentes**

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

**This amendment has been raised to address the following:**

**QUESTION:**

This project currently lists Blueskin VP160, Henry Bakor, as acceptable material in Section 07 27 19 2.1.4.4 – Sheet Membrane Air and Vapour Barrier

We would like to request the addition of the following product as a approved alternate on this project, **Wrapshield SA Self-Adhered Water Resistive Vapour Permeable Air Barrier Sheet Membrane** as manufactured by VaproShield, LLC – **no adhesive primer required.**

**ANSWER:**

Regarding the use of WrapShield SA Self-Adhered Water Resistive Vapour Permeable Air Barrier Sheet Membrane as an alternative to Henry, Blueskin VP160. This appears to be an equal product and **therefore is accepted.** Please note that the successful bidder will be required to submit shop drawings detailing the entire wall assembly including all materials as they will be applied.

**QUESTION:**

Currently, **042200 – UNIT MASONRY; 2.6.4.1.1** with regard to above mentioned project calls for PERM-A-BARRIER membrane.

Agriculture and Agri-food Canada Administration Building, Beaverlodge, Alberta PWGSC – Boiler Replacement (R.078148.001)		Section 042200 UNIT MASONRY Page 7 of 12
<b>2.6</b>	<b>FLASHING</b>	
.1	Metal Flashing: Provide metal flashing materials in accordance with Section 07 62 00.	
.2	Butyl Rubber Base Flashing: minimum 1.2 mm thick butyl sheet rubber strips.	
.3	Sheet Steel Base Flashing: minimum 0.60 mm thick, to ASTM A653, formed as detailed, galvanized with Z275 zinc coating.	
.4	Flexible flashing shall not be less than 0.5 mm thick and be compatible with all other materials being used. Mastic for flexible flashing must be compatible and approved for use with the flashing materials.	
.1	Acceptable Manufacturer's:	
.1	Perm-A-Barrier, W.R. Grace & Co.	
.2	Thru Wall Flashing, Bakor Inc.	

We would like to request that our **AIR-SHIELD** membrane please be forwarded for review as alternate approval.

**ANSWER:**

Regarding the use of AIR-SHIELD™ Self-Adhering Air/Vapour and Liquid Moisture Barrier as an alternative to those outlined in Specification Section 042200 - 2.6.4. This appears to be an equal product and **therefore is accepted.** Please note that the successful bidder will be required to submit shop drawings detailing the entire wall assembly including all materials as they will be applied.