



## RETURN BIDS TO:

## RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government  
Services Canada/Réception des soumissions Travaux  
publics et Services gouvernementaux Canada  
Pacific Region  
401 - 1230 Government Street  
Victoria, B.C.  
V8W 3X4  
Bid Fax: (250) 363-3344

## SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise  
indicated, all other terms and conditions of the Solicitation  
remain the same.

Ce document est par la présente révisé; sauf indication contraire,  
les modalités de l'invitation demeurent les mêmes.

### Comments - Commentaires

Vendor/Firm Name and Address  
Raison sociale et adresse du  
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution  
Public Works and Government Services Canada - Pacific  
Region  
401 - 1230 Government Street  
Victoria, B. C.  
V8W 3X4

<b>Title - Sujet</b> Hydraulic Shear	
<b>Solicitation No. - N° de l'invitation</b> W0103-187464/A	<b>Amendment No. - N° modif.</b> 002
<b>Client Reference No. - N° de référence du client</b> W0103-187464	<b>Date</b> 2018-05-29
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$VIC-223-7492	
<b>File No. - N° de dossier</b> VIC-8-41002 (223)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2018-06-07</b>	<b>Time Zone</b> Fuseau horaire Pacific Daylight Saving Time PDT
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Locke, Kelsey	<b>Buyer Id - Id de l'acheteur</b> vic223
<b>Telephone No. - N° de téléphone</b> (250) 507-2482 ( )	<b>FAX No. - N° de FAX</b> ( ) -
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

Instructions: See Herein

Instructions: Voir aux présentes

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> Raison sociale et adresse du fournisseur/de l'entrepreneur	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm (type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

---

**SOLICITATION AMENDMENT 002 RAISED TO RESPOND TO BIDDER QUESTIONS AND REVISE  
ANNEX "A" AS FOLLOWS:**

**THE SOLICITATION CLOSING DATE HAS BEEN EXTENDED TO 2018-06-07 at 2:00pm PDT.**

**QUESTIONS AND ANSWERS:**

**Q1.** 1.3 Shear Force: minimum of 200 tonnes, maximum of 250 tonnes. Is 2500kn (250.9 tonnes) acceptable too?

**A1.** 250.9 tonnes is acceptable. Refer to revised Mandatory Criterion 1.3 below.

**Q2.** 1.8 Power Rating: 18.5 / 25hp. Is 25hp a limit? Will you accept a 50hp motor too? (To gain 8 cut per min a 25hp may not be enough)

**A2.** A 50 HP motor is acceptable. Specification has been revised, see table below.

**Q3.** 1.11 Jaw Fully open: 8 cuts per minute. Will 6 to 11 times/min be acceptable too?

**A3.** 6 to 11 cuts per minute is acceptable. "Jaw fully open: 8 cuts per minute" has been removed from the mandatory requirements; see below.

**Q4.** 1.10 Maximum system pressure 241 Bar / 3500 psi. Will 31.5Mpa be evaluated as responsive too?

**A4.** The specification has been revised, see below.

**Q5.** Is it necessary to include a new set of blades on a new machine too?

**A5.** A second set of blades is required.

**Q6.** What is 1.2 Tip to tip opening?

**A6.** Tip to tip is when the jaws are fully open; the largest opening of the extremity of the shear. Stated as minimum 16 inches in the SOW.

**Q7.** What is cutting capacity 3" round and square?

**A7.** The shear must be able to cut a 3" round or square solid piece of metal.

## AT ANNEX "A" MANDATORY CRITERIA

### DELETE IN ITS ENTIRETY:

Item	Mandatory Requirements	Comments	Yes	No	Bid Page Ref #
<b>MANDATORY MINIMUM REQUIREMENTS</b>					
1.1	Hydraulic shear must be new, or like new. If the shear is reconditioned, it must be no older than 2012. The shear must be restored to its brand new condition: <ul style="list-style-type: none"> <li>- any broken parts must be replaced</li> <li>- it must be newly painted</li> <li>- a new set of spare cutting blades must be included.</li> </ul> It must be certified in writing to be in proper working condition.				
1.2	Tip to tip opening minimum 16 inches.				
1.3	Shear force: minimum of 200 tonnes, maximum of 250 tonnes.				
1.4	Blade length must be a minimum of 900 mm				
1.5	Noise level 82 +/- 3dBA				
1.6	Cut Control: single cut or continuous				
1.7	Standard Electrical Requirements 32A /3ph /max 600v /50 Hz or equivalent				
1.8	Power Rating: 18.5 /25hp				
1.9	Motor speed 1460 rpm				
1.10	Maximum system pressure 241 Bar /3500 psi				
1.11	Jaw fully open: 8 cuts per minute				
1.12	Cutting Capacity: <ul style="list-style-type: none"> <li>1.12.1 76mm (3") round bar</li> <li>1.12.2 70mm (3") square bar</li> </ul>				

### INSERT:

Item	Mandatory Requirements	Comments	Yes	No	Bid Page Ref #
<b>MANDATORY MINIMUM REQUIREMENTS</b>					

Solicitation No. - N° de l'invitation  
W0103-187464/A  
Client Ref. No. - N° de réf. du client  
W0103-187464

Amd. No. - N° de la modif.  
002  
File No. - N° du dossier  
VIC-8-41002

Buyer ID - Id de l'acheteur  
VIC 223  
CCC No./N° CCC - FMS No./N° VME

Item	Mandatory Requirements	Comments	Yes	No	Bid Page Ref #
1.1	Hydraulic shear must be new, or like new. If the shear is reconditioned, it must be no older than 2012. The shear must be restored to its brand new condition: <ul style="list-style-type: none"><li>- any broken parts must be replaced</li><li>- it must be newly painted</li><li>- a new set of spare cutting blades must be included.</li></ul> It must be certified in writing to be in proper working condition.				
1.2	Tip to tip opening minimum 16 inches.				
1.3	Shear force: <b>minimum</b> of 200 tonnes				
1.4	Blade length must be a minimum of 900 mm				
1.5	Noise level 82 +/- 3dBA				
1.6	Cut Control: single cut or continuous				
1.7	Standard Electrical Requirements 32A /3ph /max 600v /50 Hz or equivalent				
1.8	Power Rating: <b>minimum</b> 25 hp				
1.9	Motor speed 1460 rpm				
1.10	System pressure: <b>minimum</b> 2500 psi				
1.11	Cutting Capacity: <ul style="list-style-type: none"><li>1.12.1 76mm (3") round bar</li><li>1.12.2 70mm (3") square bar</li></ul>				

Bidder's best delivery date is \_\_\_\_\_ weeks ARO.

**ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED.**