



**RETURN BIDS TO:**

**RETOURNER LES SOUMISSIONS À:**

**Bid Receiving - PWGSC / Réception des soumissions -  
TPSGC**

**11 Laurier St. / 11, rue Laurier**

**Place du Portage, Phase III**

**Core 0B2 / Noyau 0B2**

**Gatineau, Québec K1A 0S5**

**Bid Fax: (819) 997-9776**

**SOLICITATION AMENDMENT  
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

**Comments - Commentaires**

There is a security requirement associated with this procurement

**Vendor/Firm Name and Address**

**Raison sociale et adresse du  
fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**

Electrical & Electronics Products Division  
11 Laurier St./11, rue Laurier  
7B3, Place du Portage, Phase III  
Gatineau, Québec K1A 0S5

|   |   |
|---|---|
| <b>Title - Sujet</b><br>Audio Visual Systems/Carling Campus   |   |
| <b>Solicitation No. - N° de l'invitation</b><br>W8474-17CA17/A  | <b>Amendment No. - N° modif.</b><br>006                                   |
| <b>Client Reference No. - N° de référence du client</b><br>W8474-17CA17   | <b>Date</b><br>2018-06-15   |
| <b>GETS Reference No. - N° de référence de SEAG</b><br>PW-\$\$HN-331-74824  |   |
| <b>File No. - N° de dossier</b><br>hn331.W8474-17CA17   | <b>CCC No./N° CCC - FMS No./N° VME</b>                                    |
| <b>Solicitation Closes - L'invitation prend fin<br/>at - à 02:00 PM<br/>on - le 2018-06-29</b>  | <b>Time Zone</b><br>Fuseau horaire<br>Eastern Daylight Saving<br>Time EDT |
| <b>F.O.B. - F.A.B.</b><br><b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/> |   |
| <b>Address Enquiries to: - Adresser toutes questions à:</b><br>Turner, Louie  | <b>Buyer Id - Id de l'acheteur</b><br>hn331                               |
| <b>Telephone No. - N° de téléphone</b><br>(873) 469-3342 ( )  | <b>FAX No. - N° de FAX</b><br>( ) -                                       |
| <b>Destination - of Goods, Services, and Construction:</b><br><b>Destination - des biens, services et construction:</b>   |   |

**Instructions: See Herein**

**Instructions: Voir aux présentes**

|  |  |
|--|--|
| <b>Delivery Required - Livraison exigée</b>  | <b>Delivery Offered - Livraison proposée</b> |
| <b>Vendor/Firm Name and Address</b><br><b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>   |  |
| <b>Telephone No. - N° de téléphone</b><br><b>Facsimile No. - N° de télécopieur</b>   |  |
| <b>Name and title of person authorized to sign on behalf of Vendor/Firm<br/>(type or print)</b><br><b>Nom et titre de la personne autorisée à signer au nom du fournisseur/<br/>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b> |  |
| <b>Signature</b>   | <b>Date</b>                                  |

Amendment # 6 is issued to answer a potential bidders questions.

**Question 1:**

DND has stated that they will supply the Equipment Racks, can DND confirm if any additional accessories are provided with the racks, lace bars, power supplies, screws etc.. or will these items be the responsibility of the integrator?

**Answer 1:**

DND confirms that they will supply the Equipment Racks with cable managers and lace bars as indicated below. DND will also provide the 208V power bars and grounding bars. DND will not provide the screws. The screws will be the responsibility of the integrator.

MIDDLE ATL SNE30F-4236 SNE SERIES RACK, 42 RU, 36IND, 30INW  
MIDDLE ATL PHCM-2-3 PLASTIC Vertical CABLE MANAGERS. 2 SPACE; DEPTH 3"  
3 x MIDDLE ATL LBP-2A L BAR, 2" OFFSET 10/PK  
3 x MIDDLE ATL LBP-4A L BAR, 4" OFFSET 10/PK  
3 x MIDDLE ATL LBP-6A L BAR, 6" OFFSET 10/PK

**Question 2:**

Please confirm how audio and video will get to the recorder in the operation booth.

**Answer 2:**

Audio:

The audio from EQT\_5-6 to the Control Booth will be over the fibre optic infrastructure (only 3 channels are to be recorded). Refer to 17-CAMPUS-5E3-100.

Video:

The video from EQT\_5-6 to the Control Booth will be over the fibre optic infrastructure. Although not shown in the drawing package, Thinklogical VQM-OHV003-LCRX (**qty 2**) have already been accounted for in Appendix – Pricing.

**Question 3:**

Please confirm the number of computers to be connected to each Middle Atlantic RM-KB-LCD17HD

**Answer 3:**

The two (2) RM-KB-LCD17HD rackmount LCD keyboards will be connected to two (2) GFE NET 3 PCs. The NET 3 PCs have Internet access. The RM-KB-LCD17HD/NET 3 PC will be used to configure, troubleshoot and maintain the AV system. All configuration and program files are to be stored on the NET 3 PCs as no external IT equipment is to enter the facility once it has been commissioned.

All other terms and conditions remain the same.