



## RETURN BIDS TO:

## RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government  
Services Canada/Réception des soumissions Travaux  
publics et Services gouvernementaux Canada  
Room 100,  
167 Lombard Ave.  
Winnipeg  
Manitoba  
R3B 0T6  
Bid Fax: (204) 983-0338

## SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise  
indicated, all other terms and conditions of the Solicitation  
remain the same.

Ce document est par la présente révisé; sauf indication contraire,  
les modalités de l'invitation demeurent les mêmes.

### Comments - Commentaires

Vendor/Firm Name and Address  
Raison sociale et adresse du  
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution  
Public Works and Government Services Canada -  
Western Region  
Room 100  
167 Lombard Ave.  
Winnipeg  
Manitoba  
R3B 0T6

<b>Title - Sujet</b> Truck with Grain Box	
<b>Solicitation No. - N° de l'invitation</b> 01R11-190097/A	<b>Amendment No. - N° modif.</b> 003
<b>Client Reference No. - N° de référence du client</b> 01R11-190097	<b>Date</b> 2018-07-30
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$WPG-016-10572	
<b>File No. - N° de dossier</b> WPG-8-41051 (016)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2018-08-21</b>	<b>Time Zone</b> <b>Fuseau horaire</b> Central Daylight Saving Time CDT
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Hall, Marlene	<b>Buyer Id - Id de l'acheteur</b> wpg016
<b>Telephone No. - N° de téléphone</b> (204) 230-0147 ( )	<b>FAX No. - N° de FAX</b> (204) 983-7796
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

Instructions: See Herein

Instructions: Voir aux présentes

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

Solicitation No. - N° de l'invitation  
01R11-190097/A  
Client Ref. No. - N° de réf. du client  
01R11-190097

Amd. No. - N° de la modif.  
003  
File No. - N° du dossier  
WPG-8-41051

Buyer ID - Id de l'acheteur  
wpg016  
CCC No./N° CCC - FMS No./N° VME

---

### **Amendment # 003**

This amendment has been raised to modify solicitation # **01R11-190097/A** as follows:

1. Reference **Solicitation Closes**, page 1 of 1, and amend as follows:

**Delete:** Solicitation Closes at 02:00 PM on 2018-08-07.

**Insert:** **Solicitation Closes at 02:00 PM on 2018-08-21.**

1. Reference **Annex A, Compliance Matrix – Performance Specifications**, page 14 of 24, and amend as follows:

**Delete:** Delete in its entirety.

**Insert:** Insert the following revised version:

**ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME**

## COMPLIANCE MATRIX – PERFORMANCE SPECIFICATIONS

Item #	Performance Specification Required	Mandatory	Performance Specification Met? Indicate Either Yes/NO	Performance Specification Offered: Bidder should indicate how they meet the performance specification by recording this information in this column	Cross Reference: In this column, Bidders should cross-reference where this performance specification is indicated in their supporting documents.
<b>1</b>	<b>VEHICLE OVERVIEW</b>				
1.1	2018 OR NEWER, Grain Truck	X			
	Regular Cab and Chassis EQUIPPED WITH grain box capable of transporting a minimum of 700 bushels of grain (approx. 45,000 lbs which includes box, hoist and accessories, and contents of box)  Grain body specifications (See section 11).  Supply and install of body <u>IS</u> a part of this contract	X			
1.2	MINIMUM Tandem Axle, Dual Rear Wheels	X			
1.3	GVWR 55,000 lbs minimum	X			

1.4	Truck must be suitable for pintle hook towing, to tow 8000 lb trailer with a payload of approximately 32,000 lbs (total weight of trailer and payload is 40,000 lbs). The truck will have a load of 45,000 lbs (includes body, payload and passengers) in the vehicle while pulling the trailer. Terrain is off-road and hilly.	X			
1.5	Must come equipped with 7-pin wiring harness	X			
<b>2</b>	<b>ENGINE</b>				
2.1	DIESEL ENGINE	X			
2.2	minimum 280 HP, capable of meeting payload and towing requirements	X			
2.3	Capable of achieving <b>101KMPH/63MPH</b> when fully loaded	X			
2.4	Limited Slip Differential	X			
<b>3</b>	<b>TRANSMISSION</b>				
3.1	Automatic Transmission with transmission cooler	X			
3.2	PTO provision suitable to operate grain body (including accessories)	X			
3.3	Water to oil Transmission cooler	X			
3.4	Driver controlled locking axles on rear axles	X			
<b>4</b>	<b>FRAME</b>				
4.1	Centre of Rear Axles to end of frame as specified by grain body manufacturer	X			

4.2	Cab to Axle (CA) must have no exhaust interference, measure CA from Exhaust stack if exhaust is behind cab. Ensure compatibility with grain body measurements as specified by grain body manufacturer.	X		
4.3	Reinforced frame to accommodate grain body	X		
4.4	Front Tow Hooks, heavy duty frame mounted	X		
4.5	Frame Mounted Pintle Hitch for Pintle hook towing up to 40,000lbs	X		
4.6	Frame Mounted 2" receiver hitch, suitable for ball hitch towing for up to 15,000 lbs	X		
4.7	Additional electrical port for electric over hydraulic brakes and quick-connections (aka glad hands) for brakes and signal lights.	X		
<b>5</b>	<b>BRAKES</b>			
5.1	Air brakes with Auto Slack adjusters	X		
5.2	Anti-Lock Air brake system with traction control	X		
5.3	Parking/Emergency Brake to be separate of regular service brakes	X		
5.4	Brake linings to be non-asbestos	X		
<b>6</b>	<b>FUEL SYSTEM</b>			
6.1	Fuel Tank Capacity, minimum 350L; location must not impede grain body installation	X		
6.2	Pillar mounted tailpipe on passenger side	X		
<b>7</b>	<b>COLD WEATHER STARTING AIDS</b>			
7.1	Minimum 1000 watt block heater, 110-120 volt, complete with connecting cord	X		

7.2	Minimum 150 watt/110-volt oil pre-heater on a common receptacle	X			
7.3	Replaceable element type fuel-filter and water separator incorporating a thermostatically controlled heater	X			
<b>8</b>	<b>TIRES</b>				
8.1	All tires to be steel belted, steel cord, radial tires	X			
8.2	Highway Tread on Front Axle	X			
8.3	Traction Tires on Rear Axle	X			
8.4	Tires must have capacity to carry 100% of the gross axle weight rating and be capable of meeting the load requirements as specified in Vehicle Overview	X			
<b>9</b>	<b>SUSPENSION</b>				
9.1	Front suspension, Leaf spring or equivalent	X			
9.2	Air suspension on rear axle	X			
<b>10</b>	<b>CAB OPTIONS</b>				
10.1	Air ride cab suspension for load adjustment, driver controlled	X			
10.2	Air Conditioning	X			
10.3	Power windows and power door locks	X			
10.4	Cruise control	X			
10.5	Power steering, and adjustable tilt steering column	X			
10.6	AM/FM Radio	X			

10.7	Intermittent windshield wipers	X			
10.8	Canadian instrumentation package with primary speedometer reading in KPH	X			
10.9	Dash lights must include: a) Low oil pressure b) High coolant temperature c) Low Air d) Park Brake with warning indicator	X			
10.10	Gauges: a) Amp meter/Voltmeter b) Temperature c) Oil Pressure, d) Fuel Gauges e) Engine hour f) Fast Idle Switch g) Water Temperature h) Air pressure gauge with low air pressure warning buzzer	X			
10.11	Engine and trip hour meter	X			
10.12	Entry steps and grab handle on both right hand and left hand sides of cab	X			
10.13	Industry Standard Heated Mirrors Both sides power adjustable from cab interior, controls on driver's side	X			
10.14	Convex mirrors (lower mounted on side mirrors, or hood mounted)	X			
10.15	Driver Seat to be Air ride, high back, lumbar support, cloth bucket seat with armrest(s), power controls	X			
10.16	High-back passenger seat	X			

10.17	Vinyl Floor covering	X			
10.18	Electric variable speed Windshield Wipers	X			
10.19	Independent fenders for each rear wheel and rear mud flaps	X			
10.20	Rear window in back of cab	X			
10.21	Color : Production Blue	X			
10.22	Rear Camera & Back-up Alarm	X			
	<b>Service &amp; Warranty</b>				
10.23	Service/warranty and regular maintenance work to be performed within a 100 km radius of the final destination, by an authorized service dealer and/or agent.	X			
10.24	The Bidder must provide the name, address, telephone number and indicate the distance between the delivery location and the authorized service dealer and/or agent to provide after sales service, maintenance, warranty repairs, and a full range of repair parts for the unit offered.	X			