

Project No.: R.082215.001

August 29, 2018

The following changes to the tender documents are effective immediately and will form part of the contract documents:

1. INQUIRIES DURING THE SOLICITATION PERIOD

ITEM #	QUESTION	ANSWER
1	What is the expansion capacity of the existing PLC located in the Door Control cabinet?	There is space for two (2) additional I/O modules.
2	Where is the location of the existing HMI monitors?	Existing HMI monitors are located in Control Room E38 and the MCCP.
3	What is the available space within the existing equipment rack within control room?	There are approximately 12 rack units of space available within the existing ESS equipment rack within the control room.
4	What is the size of the UPS and current load within the equipment rack?	The existing equipment rack UPS units have sufficient capacity for modifications required under this project's scope of work.
5	Where is the network switch location for CCTV etc. a spare capacity?	The existing CCTV network switch is located within the existing ESS equipment rack within the control room and has a spare capacity of approximately 16 ports.
6	Where is the location of the existing DCC (Harding Controller) and available ports?	The existing DCC is located within the existing ESS equipment rack within the control room. It is a VOIP unit and has spare capacity of sufficient for this project.

2. RE: Solicitation Amendment No. 1 – Addendum No. 1

Delete the "Electrical Addendum No. E-1" from Solicitation Amendment No. 1 in it's entirety and replace with Mechanical Addendum No. M-1 (ATT A010.PDF).

3. ELECTRICAL

Electrical Addendum E-1 (ATT A011.PDF)

END OF ADDENDUM NO. 3