

This amendment 1 is raised to answer vendors' questions:

A) Question and answer

Question #1: What is the Total Launch cable length required for Part Number MMC-50-SCSC and MMC-50-LCLC?

Answer #1:

This solicitation is not for a reel of fiber cable. DND requires accessories for test equipment as follows; Part Number MMC-50-LCLC (NSN: 6015-01-674-2792) – Fluke multimode launch cable and Part Number MMC-50-SCSC (NSN: 6015-01-674-2790) – Fluke multimode launch cable in quantities of 1 EA. The cable length in the multimode launch cable for both the MMC-50-LCLC (6015-01-674-2792) and MMC-50-SCSC (NSN: 6015-01-674-2790) is 105 M.

Question #2: What Type of Multimode Fiber is required?

Answer #2:

Both Fluke multimode launch cables MMC-50-SCSC (NSN: 6015-01-674-2790) and MMC-50-LCLC (NSN: 6015-01-674-2792) will be utilized with the Fluke OFP-100-M Time Domain Reflectometer in order to verify and test 50 micron multimode LC and SC terminated fiber runs.

Question #3: There is a soft case that the assembly is housed in, is it mandatory that this case is supplied?

Answer #3:

Both the FLUKE MMC-50-LCLC and MMC-50-SCSC come in a soft case and it is required.