



**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS A :**

Bid Receiving/Réception des sousmissions
Procurement & Contracting Services
c/o Commissionaires, F Division
6101 Dewdney Ave
Regina, SK S4P 3K7

Fax No. - No de FAX:
(306) 780-5232

**SOLICITATION
AMENDMENT**

**MODIFICATION DE
L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments: - Commentaries :

THIS DOCUMENT CONTAINS A SECURITY REQUIREMENT

LE PRÉSENT DOCUMENT COMPORTE UNE EXIGENCE EN MATIÈRE DE SÉCURITÉ

Title – Sujet: Recreational Vehicle/ Toy Hauler 5 th Wheel Trailer, Estevan, SK		Date January 2, 2019
Solicitation No. – N° de l'invitation M5000-19-3717/A – PW-18-00853888		Amendment No. – N° de la modification 002
Client Reference No. - No. De Référence du Client 201903717		
Solicitation Closes – L'invitation prend fin		
At / à :	2 :00 pm	CST (Central Standard Time) HNC (Heure Normale du Centre)
On / le :	January 18, 2019	
Incoterms 2010 "DDP Delivered Duty Paid" See herein — Voir aux présentes	GST – TPS See herein — Voir aux présentes	Duty – Droits See herein — Voir aux présentes
Destination of Goods and Services – Destinations des biens et services See herein — Voir aux présentes		
Instructions See herein — Voir aux présentes		
Address Inquiries to – Adresser toute demande de renseignements à		
Telephone No. – No. de téléphone	Facsimile No. – No. de télécopieur	

Delivery Required – Livraison exigée N/A	Delivery Offered – Livraison proposée N/A
Vendor/Firm Name, Address and Representative – Raison sociale, adresse et représentant du fournisseur/de l'entrepreneur:	
Telephone No. – No. de téléphone	Facsimile No. – No. de télécopieur
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) – Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date



This amendment is raised to address the following:

- To respond to questions received during the solicitation period; and
- To revise the solicitation accordingly, as applicable.

QUESTIONS AND ANSWERS

Question 2: Mandatory Technical Criteria 4. Exterior and Electric m) Frameless windows with safety glass. Would the RCMP accept framed windows?

Answer 2: Yes, the solicitation has been amended accordingly.

Question 3: Mandatory Technical Criteria 5. Interior, Heating and Storage e) 80 Gallon Grey Water Tank – Minimum. Would the RCMP accept 78 gallons?

Answer 3: Yes, the solicitation has been amended accordingly.

Question 4: Mandatory Technical Criteria 5. Interior, Heating and Storage q) Tie down mechanism in floor of garage/cargo area to support minimum 3000 lbs. Would the RCMP accept minimum cargo support of 2500 lbs?

Answer 4: Yes, the solicitation has been amended accordingly.

SOLICITATION REVISIONS

1) On page fourteen (14) Annex "A" Requirement

DELETE:

In it's entirety

INSERT:

ANNEX "A"

REQUIREMENT

The Contractor must supply, deliver, unload and provide service, as required, for one (1) new (2018 Model or Manufacturer Model Year at bid closing) Recreational Vehicle (RV) Toy Hauler 5th Wheel Trailer to the Royal Canadian Mounted Police, to be delivered to Estevan, SK, in accordance with the requirements specifications, terms and conditions detailed herein.

The RV Toy Hauler 5th Wheel Trailer must include the following specifications:

1. **Chassis, Frame and Dimensions**
 - a) 80" Interior Height – Minimum
 - b) 90" Interior Width – Minimum
 - c) 13' garage or cargo area – Minimum
 - d) Dual axles – heavy duty



2. Brakes and Tires

- a) 4 Wheel Braking System
- b) Tires – manufacturer's standard load range

3. Lighting

- a) Exterior Flood Lighting in garage loading and trailer entry areas – Minimum

4. Exterior and Electric

- a) Fresh Water Fill
- b) Tank Monitor (including. Water Tanks and Battery Condition – Minimum)
- c) Medium to large capacity exterior access storage – Minimum
- d) Fiberglass sidewalls
- e) DELETED
- f) 30 Amp electrical service - Minimum
- g) Rear Ramp Door with assist mechanism
- h) Anti-slip covering for ramp door when open
- i) Rear ramp door lockable latch mechanism
- j) R7 Insulated Walls, Ceiling and Floor - Minimum
- k) Vapor Barrier Underbelly
- l) Spare Tire with carrier
- m) Frameless or framed windows with safety glass– Minimum
- n) Rear and front stabilizer jacks with levelling function - Minimum
- o) 30 Gallon Fuel Station – Minimum
- p) Two (2) 26 Litre Propane Gas Bottles – Minimum
- q) RV Generator – 5500 Watt – Minimum
- r) Outside access to fresh water (shower or spray) – Manufacturer's standard
- s) Awning – Manufacturer's standard

5. Interior, Heating and Storage

- a) Forced Air Furnace and Air Conditioner for garage/cargo and living areas (13,500 BTU – Minimum)
- b) 6 Gallon Gas/Electric Water Heater – Minimum
- c) 80 Gallon Fresh water holding tank - Minimum
- d) 40 Gallon Black Water Tank – Minimum
- e) 78 Gallon Grey Water Tank – Minimum
- f) Enclosed heated tanks (above)
- g) Bathroom – to include toilet, shower, sink, power vent, and cabinets/storage - Minimum
- h) 6 Cu. Ft. Gas/Electric Auto Switching Fridge – Minimum
- i) 2 Burner Range w/ Oven and Hood – Minimum
- j) Microwave Oven
- k) Entertainment center – Manufacturer's standard
- l) Dining area for capacity of 4 to 6 people
- m) Sleep Accommodations for 6 people (including cargo area) – Minimum; Manufacturer's Standard
- n) Kitchen sink and storage
- o) Roof Vent in living area and garage/cargo area
- p) Equipment Storage Cabinets in garage/cargo area
- q) Tie down mechanism in floor of garage/cargo area to support minimum 2500 lbs.
- r) Garage/Cargo floor strong/re-enforced to support equipment and fluid spills.

6. Safety and Security

- a) Fire Extinguisher – Manufacturer's Standard
- b) Trailer/tow vehicle disconnect Safety system – Manufacturer's Standard
- c) Carbon Monoxide Detector
- d) Smoke Detector
- e) Liquefied Petroleum Gas (LPG) Leak Detector



- f) Battery Cut-off Switch
- g) Emergency Fuel Shutoff
- h) Entry Door Locks

7. Instrumentation and Other

- a) Pre-Delivery Inspection (PDI) – Included
- b) Manuals: Must include 1 English copy of Operators, Service and Parts Manuals in any media form
- c) Colours: Manufacturer's Standard
- d) Warranty: Copy of warranty to be received with delivery. All costs related to warranty work must be included in price, non-warranty maintenance and after sales service are to be charged separately.
- e) Service: Ability to conduct general and warranty service within 500 km from delivery location. The repairs are to be performed by an authorized representative. Repairs service is to begin within 24 hours of notification at a service facility. The authorized representative to have ready access to regular maintenance and service parts and be able to access all parts not normally stocked from an authorized parts dealer within 72 hours.
- f) Keys: Two (2) Sets of Keys – Minimum

2) On page seventeen (17) Annex "C" Mandatory Technical Criteria

DELETE:

In it's entirety

INSERT:

ANNEX "C"

MANDATORY TECHNICAL CRITERIA

Bidders are required to indicate whether or not they comply with the mandatory specifications. Bidders must include one (1) copy of descriptive literature of the make and model of the items offered in sufficient detail to clearly indicate compliance with each of the individual requirements in the specifications and cross reference where this specification is located within the descriptive literature.

Where weight, dimensions or other characteristics are shown as minimum or maximum, the bidder must indicate the manufacturer's figures.

The Royal Canadian Mounted Police is under no obligation to seek clarification of the bid(s) or the supporting technical documentation provided.

Failure to meet any of the following specifications will render your proposal non-compliant and will be given no further consideration.

BIDDER MUST SUBMIT WITH THEIR BID PROOF OF BEING AN AUTHORIZED MANUFACTURER OR RESELLER FOR THE UNIT OFFERED PRIOR TO AWARD OF CONTRACT.

The following specifications must be met:

No.	Specification	Compliance		Comment(s) / Cross Reference
		Yes	No	
A1.	Guaranteed delivery prior to March 31, 2019			



A2.	New 2018 Model or Manufacturer Model Year at bid closing			
1.	Chassis, Frame and Dimensions			
a)	80" Interior Height – Minimum			
b)	90" Interior Width – Minimum			
c)	13' garage or cargo area – Minimum			
d)	Dual axles – heavy duty			
2.	Brakes and Tires			
a)	4 Wheel Braking System			
b)	Tires – manufacturer's standard load range			
3.	Lighting			
a)	Exterior Flood Lighting in garage loading and trailer entry areas – Minimum			
4.	Exterior and Electric			
a)	Fresh water fill			
b)	Tank Monitor (including. Water Tanks and Battery Condition – Minimum)			
c)	Medium to large capacity exterior access storage – Minimum			
d)	Fiberglass sidewalls			
e)	DELETED			
f)	30 Amp electrical service - Minimum			
g)	Rear Ramp Door with assist mechanism			
h)	Anti-slip covering for ramp door when open			
i)	Rear ramp door lockable latch mechanism			
j)	R7 Insulated Walls, Ceiling and Floor - Minimum			
k)	Vapor Barrier Underbelly			
l)	Spare Tire with carrier			
m)	Frameless or framed windows with safety glass– Minimum			
n)	Rear and front stabilizer jacks with levelling function - Minimum			
o)	30 Gallon Fuel Station – Minimum			
p)	Two (2) 26 Litre Propane Gas Bottles – Minimum			
q)	RV Generator – 5500 Watt – Minimum			
r)	Outside access to fresh water (shower or spray) – Manufacturer's standard			
s)	Awning – Manufacturer's standard			
5.	Interior, Heating and Storage			



a)	Forced Air Furnace and Air Conditioner for garage/cargo and living areas (13,500 BTU – Minimum)			
b)	6 Gallon Gas/Electric Water Heater – Minimum			
c)	80 Gallon Fresh water holding tank - Minimum			
d)	40 Gallon Black Water Tank – Minimum			
e)	78 Gallon Grey Water Tank – Minimum			
f)	Enclosed heated tanks (above)			
g)	Bathroom – to include toilet, shower, sink, power vent, and cabinets/storage - Minimum			
h)	6 Cu. Ft. Gas/Electric Auto Switching Fridge – Minimum			
i)	2 Burner Range w/ Oven and Hood – Minimum			
j)	Microwave Oven			
k)	Entertainment center – Manufacturer’s standard			
l)	Dining area for capacity of 4 to 6 people			
m)	Sleep Accommodations for 6 people (including cargo area) – Minimum; Manufacturer’s Standard			
n)	Kitchen sink and storage			
o)	Roof Vent in living area and garage/cargo area			
p)	Equipment Storage Cabinets in garage/cargo area			
q)	Tie down mechanism in floor of garage/cargo area to support minimum 2500 lbs.			
r)	Garage/Cargo floor strong/re-enforced to support equipment and fluid spills.			
6.	Safety and Security			
a)	Fire Extinguisher – Manufacturer’s Standard			
b)	Trailer/tow vehicle disconnect Safety system – Manufacturer’s Standard			
c)	Carbon Monoxide Detector			
d)	Smoke Detector			
e)	Liquefied Petroleum Gas (LPG) Leak Detector			
f)	Battery Cut-off Switch			
g)	Emergency Fuel Shutoff			
h)	Entry Door Locks			
7.	Instrumentation and Other			
e)	<p>Service: Service/warranty and regular maintenance work to be performed within a 500 km radius of the final destination, by an authorized service dealer and/or agent. The repairs service is to begin within 24 hours of notification at a service facility.</p> <p>The authorized representative to have ready access to regular maintenance and service parts and be able to access all parts not normally stocked from an authorized parts dealer within 72 hours.</p>			<p>Distance between the delivery location and the service dealer and/or agent: _____ km</p> <p>Name: _____ _____ _____</p>



	The Bidder must provide the name, address, telephone number and indicate the distance between the delivery location and the authorized service dealer and/or agent to provide after sales service, maintenance, warranty repairs, and a full range of repair parts for the unit offered.			Address: _____ _____ _____ Telephone: _____ _____

ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME