



**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:**

**Bid Receiving
PWGSC
33 City Centre Drive
Suite 480C
Mississauga
Ontario
L5B 2N5
Bid Fax: (905) 615-2095**

**SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

**Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur**

Issuing Office - Bureau de distribution
Public Works and Government Services Canada
Ontario Region
33 City Centre Drive
Suite 480
Mississauga
Ontario
L5B 2N5

Title - Sujet Magnetic Particle Wet Benches	
Solicitation No. - N° de l'invitation W3474-193091/A	Amendment No. - N° modif. 002
Client Reference No. - N° de référence du client W3474-193091	Date 2019-01-24
GETS Reference No. - N° de référence de SEAG PW-\$TOR-033-7676	
File No. - N° de dossier TOR-8-41142 (033)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2019-01-28	
Time Zone Fuseau horaire Eastern Standard Time EST	
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Martin, Lesley	Buyer Id - Id de l'acheteur tor033
Telephone No. - N° de téléphone (905) 615-2076 ()	FAX No. - N° de FAX () -
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

AMENDMENT 002 ADDRESSES QUESTIONS FROM POTENTIAL BIDDERS

Question and Answer

- Q1. Can we ask for a later date than March 29th for delivery and install?
A1. The delivery and installation date remains unchanged
- Q2. Specification (i) – will a Footswitch activated pneumatic headstock be acceptable?
A2. Yes, see amendment below
- Q3. Specification (j) – will a hand moved coil be acceptable?
A3. Yes, see amendment below
- Q4. Specification (q) – can there be an EXCEPTION to this overall size?
A4. Size is based on actual machine foot print, see amendment below
- Q5. Can be manuals and schematics be provided on a USB drive?
A5. No
- Q6. Is it possible for the end user to provide their own electrician at time of installation?
A6. Yes this can be coordinated

Amendment

At ANNEX A – REQUIREMENT, 2.0 Specifications

Delete: in its entirety

Insert:

2.0 Specifications

- (a) Three phase, full wave direct current (FWDC) rectification up to 6000 amperes with selectable A/C waveform mode with up to 2,500 amps
- (b) Contact and coil output modes including independently selectable output dials and ammeter display for circular and longitudinal field strengths
- (c) Five cable wraps on coil
- (d) Current (amperage) "on" safety indicator light.
- (e) Quick break feature.
- (f) Demagnetization capability
- (g) 600 (575) Volts operating voltage and 60 Hz operating frequency.
- (h) A maximum test part length of 54 inches, maximum test part diameter of 18 inches, and a maximum test part weight of 300 lbs.
- (i) Foot switch activated pneumatic tail stock or headstock.
- (j) Ratcheting coil crank handle or hand moved coil
- (k) An external pump.
- (l) Shot activating push bar.
- (m) Hand held wet magnetic media applicator with ergonomic trigger.
- (n) Stainless steel particle tank.
- (o) Hard wood grills.
- (p) Flexible copper contact plates.
- (q) Maximum overall size of machine foot print is 8 feet x 5 feet (2.44 meters X 1.52 meters).
- (r) LED UV light with inspection enclosure hood.
- (s) Equipment must meet or exceed current CSA standards at time of delivery.
- (t) Must provide the following documents at time of delivery

Solicitation No. - N° de l'invitation
W3474-193091/A
Client Ref. No. - N° de réf. du client
W3474-193091

Amd. No. - N° de la modif.
002
File No. - N° du dossier
TOR-8-41142

Buyer ID - Id de l'acheteur
TOR033
CCC No./N° CCC - FMS No./N° VME

-
- a. A minimum of one set of manuals for each machine either printed or soft copy (CD or DVD)
in both English and French
 - b. A certificate of conformity for each machine

ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED