



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government
Services Canada/Réception des soumissions Travaux
publics et Services gouvernementaux Canada
Pacific Region
401 - 1230 Government Street
Victoria, B.C.
V8W 3X4
Bid Fax: (250) 363-3344

**SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise
indicated, all other terms and conditions of the Solicitation
remain the same.

Ce document est par la présente révisé; sauf indication contraire,
les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Public Works and Government Services Canada - Pacific
Region
401 - 1230 Government Street
Victoria, B. C.
V8W 3X4

Title - Sujet Office Furniture - PSPC 1611 Main	
Solicitation No. - N° de l'invitation EZ966-192251/B	Amendment No. - N° modif. 004
Client Reference No. - N° de référence du client EZ966-192251	Date 2019-01-25
GETS Reference No. - N° de référence de SEAG PW-\$VIC-216-7669	
File No. - N° de dossier VIC-8-41182 (216)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2019-01-31	
Time Zone Fuseau horaire Pacific Standard Time PST	
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Thorne, Darlene	Buyer Id - Id de l'acheteur vic216
Telephone No. - N° de téléphone (250) 216-3168 ()	FAX No. - N° de FAX () -
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

Amendment 004

This amendment modifies the RFB in accordance with the responses provided to the questions herein.

Q15: The separate specifications mentioned to complete NSA items 4, 5, & 6 for CAT1/2/5 combined and the "additional performance spec" mentioned for CAT6 NSA do not appear in the RFB. Please provide.

A15: Please find additional performance spec attached hereto as "ANNEX A 1.1 – SPECIFICATIONS FOR WORK SPACES"

ANNEX A 1.1 – SPECIFICATIONS FOR WORK SPACES

Part 1 General

1.1 SCOPE

- .1 This specification details the technical requirements, which apply to the furniture for work spaces purchased by the federal government.
- .2 These specifications must be read in conjunction with the full supply arrangement solicitation. All products must meet the latest publications and testing requirements in effect at date of arrangement in response to the Request for Supply Arrangement (RFSA)
- .3 The supplier is responsible for supplying all necessary hardware, trim, connectors, supports, components (including electrical components) and wall mounts etc. to allow the furniture to be installed.
- .4 All categories must be read in conjunction with the latest version of the Government of Canada Workplace Fit-up Standards.

1.2 LIST OF PRODUCTS

- .1 Work Spaces are separated into five categories to support the furniture requirements related to the General-purpose Office Space office space as detailed in the latest Government of Canada Workplace Fit-up-Standards. General-purpose Office Space office space requirements are comprised of the following Categories and items:
 - .1 Category 1:
 - .1 A) Interconnecting Panels:

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

- .1 N/A
- .2 B) Freestanding systems:
 - .1 N/A
- .2 Category 2 – Freestanding height adjustable *work surfaces*
 - .1 Modular height *sit-stand benching*
- .3 Category 3 – Metal filing and storage cabinets
 - .1 N/A
- .4 Category 4 – Wood veneer – freestanding products
 - .1 N/A
- .5 Category 5 – *Ancillary* items
 - .1 Power module
- .6 Category 6 - Support space furniture
 - .1 Multimedia table for small meeting rooms
 - .2 Multimedia table for Lounge
- .2 Seating:
 - .1 Lounge sofa with rear ledge
- .3 Open area collaborative furniture
 - .1 Individual work pods
 - .2 Individual private lounge chairs
 - .3 Enclosed Telephone Booth

1.3 REFERENCE STANDARDS

To meet the same requirements as outlined in the current PSPC Furniture Supply Arrangement.

1.4 SUBMITTALS

To meet the same requirements as outlined in the current PSPC Furniture Supply Arrangement.

1.5 PRIORITY OF DOCUMENTS

To meet the same requirements as outlined in the current PSPC Furniture Supply Arrangement.

1.6 DEFINITIONS

To meet the same requirements as outlined in the current PSPC Furniture Supply Arrangement.

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

1.7 ENVIRONMENTAL ATTRIBUTES

To meet the same requirements as outlined in the current PSPC Furniture Supply Arrangement.

Part 2 Products

2.1 WORKMANSHIP

To meet the same requirements as outlined in the current PSPC Furniture Supply Arrangement.

2.2 GENERAL FEATURES

To meet the same requirements as outlined in the current PSPC Furniture Supply Arrangement.

Part 3 DETAILED PRODUCT REQUIREMENTS

3.1 Category 2

.1 Modular Height Adjustable *Benching*

.1 Description

- .1 All *work surfaces* must be height adjustable in a *sit-stand* range.
- .2 Work surfaces must be inter-connected by a shared support structure which extends the full length of the unit. A central spine and/or trough must be provided for power and data pathways.
- .3 Must be *4-work-surfaces-long*.
 - .1 One unit must be single-sided
 - .2 One unit must be double-sided
- .4 The controls for *continuous height adjustable work surfaces* must be electric.
- .5 Must include *privacy screens* along the length of the *work surfaces*, between users. Privacy screens can be attached to each height adjustable desk surface and move with the desk, or fixed to centre spine so that screens provide privacy maintained throughout all *work surface* height ranges.

.2 Dimensions

- .1 Each individual *work surface* must have a depth of 762 mm (30 in.).

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

- .2 The length of each *work surface* must be 1219 mm (48 in.).
- .3 Overall length must be no longer than 4876 mm (16'-0")
- .4 The height adjustability of the *sit-stand* range height adjustable *work surfaces* must be capable of adjusting between 762 mm to 1245 mm (30 in. to 49 in.).
 - .1 Height adjustability ranges may deviate from the specified range: $\pm 25\text{mm}$ (± 1 in.).
- .5 Privacy screens must:
 - .1 Be between 305 mm and 406 mm (12 in. to 16 in.) in height.
 - .2 A must extend the full length of the worksurface, with a tolerance of -1/4 the width of the *work surface*.
- .6 The central spine and/or trough must extend the full length of the total length of the *benching*, a tolerance of -51 mm (-2 in.) on both ends is acceptable.
- .3 Finishes
 - .1 Work surfaces must be high pressure laminate.
 - .2 Privacy screen must be provided in fabric or acrylic/acrylic glass. Acrylic/acrylic glass must be provided in a clear, frosted, or tinted finish.
 - .3 Work surface supports must be high pressure laminate, metal, or painted metal.
- .4 Power/Data
 - .1 Cable Pathway
 - .1 A shared central spine and/or trough must have a cable pathway to accommodate the electrical, voice and data cables.
 - .2 The cable pathway must accommodate a minimum of three (3) eight-wire circuits as well as nine (9) 5mm (0.20 in.) diameter communication cables with no more than a 60% fill capacity.
 - .3 Cable pathway covers must open and close firmly without the use of proprietary tools. Cables must be capable of extending into the trough without requiring that the cover remain open.

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

- .4 Communication and electrical cabling may be placed in the same cable pathway as long as metal separation is provided.
- .5 Vertical wire management system must conceal wires running from the floor, wall, or ceiling feed to the cable pathway.

.2 Electrical Wiring System

- .1 The electrical wiring system must be made of components which are *modular* and provide power at predetermined locations. When electrical wiring alterations or disassembly are required, the workstation must not be dismantled.
- .2 The system must provide for power from the wall.
- .3 The electrical system must provide electrical distributing service to all workstations from one central feed point.
- .4 The electrical system must provide as a minimum, a seven (7) wire, three (3)-circuit per feed capability.
- .5 An electrical system rated with a minimum of a 115 volt, 15 or 20 amps consisting of a minimum of 2 circuits must be available for older buildings when specified.
- .6 Each station must be provided with two (2) duplex power receptacles. Each workstation must have one (1) voice / data outlet.
- .7 Receptacles: Must be interchangeable within the manufacturer predetermined locations and located within the central trough.

.5 Base/Supports

- .1 Hardware to secure *privacy screen* to *tabletops* does not need to be *concealed* but must be compatible with the table's supports and wire management.
- .2 *Benching* frame must allow for a minimum of ± 51 mm (± 2 in.) of levelling, ± 6 mm ($\pm 1/2$ in.)

3.2 Category 5

.1 Power Modules

.1 Description:

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

- .1 Power modules must be *work surface* mounted.
- .2 Dimensions:
 - .1 N/A
- .3 Finishes:
 - .1 Power module must be white.
- .4 Power and data:
 - .1 Power modules must provide a minimum of three (2) simplex power outlets and one (1) USB outlet.
 - .2 Must provide a minimum 2438 mm (96 in.) power cord.
- .5 Support/Bases:
 - .1 The *work surface* mounted power module must clamp to the edge of the desk.

3.3 Category 6

- .1 Multi-Media Tables for small meeting rooms
 - .1 Fixed Height Multi-Media Tables
 - .1 Description
 - .1 The *work surface* of the multimedia table must be square shaped
 - .2 Multi-media tables must have an integrated monitor support panel which must accommodate the placement of a single 42" monitor.
 - .3 Multi-media tables must be designed to accommodate equipment such as flat-screen monitors, wireless transmitters, and associated control equipment. However, the equipment does not form part of these specifications.
 - .4 Counter height table must be equipped with a footrest that extends to serve the full extension of all three useable sides.
 - .2 Dimensions
 - .1 Multi-media tables must be provided in two heights:
 - .1 Seated height table surface must be 737mm (30 in.) above finished floor, +/- 38mm (1.5 in.)

Buyer ID - Id de l'acheteur
vic216

CCC No./N° CCC - FMS No./N° VME

- .2 Counter height tables must be between 864 mm to 991 mm (34 in. to 39 in.) above finished floor.
 - .2 The length must be 1524 mm (60 in.)
 - .3 The width must be 1524 mm (60 in.)
 - .4 A tolerance of ± 50.8 mm (± 2 in.) is acceptable for both the length and width.
 - .3 Finishes
 - .1 Table top must be high pressure laminate.
 - .2 Legs and/or base must be painted metal.
 - .3 Table top must have a 3mm (0.1 in.) radius edge
 - .4 Power and Data
 - .1 Tables must be provided with a recessed power module consisting of a minimum of four recessed simplex plugs on the table top.
 - .2 Data module must be integrated into the table in the recessed power module consisting of a minimum of 2 data outlets in the table top.
 - .3 *Shroud* must have a minimum of 1 power outlet and 1 data outlet.
 - .4 Power and data cable management must be provided to conceal all power/data cables integral to the unit.
 - .1 Power and data will be provided from the adjacent partition.
 - .5 Support/Table Bases
 - .1 Multi-media table bases must accommodate cable and wire management. Cable and wire management may not impede seating.
 - .2 Monitor supports must accommodate flat screen monitor ranging in diagonal sizes from 1016 mm (40 in.) to 1067 mm (42 in.).
 - .3 Frame must allow for ± 51 mm (± 2 in.) of levelling minimum, ± 6 mm ($\pm 1/2$ in.).
- .2 Multi-Media Tables for Lounge
- .1 Fixed Height Multi-Media Tables
 - .1 Description

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

- .1 The *work surface* of the multimedia table must be *D-shaped*
- .2 Multi-media tables must have an integrated monitor support panel which must accommodate the placement of a single monitor.
- .3 Multi-media tables must be designed to accommodate equipment such as flat-screen monitors, wireless transmitters, and associated control equipment. However, the equipment does not form part of these specifications.
- .2 Dimensions
 - .1 Multi-media tables must be provided in lounge height table surface must be 610mm (24 in.) +/- 25mm (1 in.) above finished floor.
 - .2 The length must be range 1524 mm (60 in.).
 - .3 The width must be 1524 mm (60 in.).
 - .4 A tolerance of ± 50.8 mm (± 2 in.) is acceptable for both the length and width.
- .3 Finishes
 - .1 Table top must be high pressure laminate.
 - .2 Legs and/or base must be painted metal.
 - .3 Table top must have a 3mm (0.1 in.) radius edge
- .4 Power and Data
 - .1 Tables must be provided with a recessed power module consisting of a minimum of four recessed simplex plugs on the table top.
 - .2 Data module must be integrated into the table in the recessed power module consisting of a minimum of two data outlets in the table top.
 - .3 *Shroud* must have a minimum of 1 power, and 1 Data
 - .4 Power and data cable management must be provided to conceal all power/data cables integral to the unit.
 - .1 Power and data will be provided from the adjacent partition.
- .5 Support/Table Bases

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

- .1 Multi-media table bases must accommodate cable and wire management. Cable and wire management may not impede seating.
- .2 Monitor supports must accommodate flat screen monitor ranging in diagonal sizes from 1016 mm (40 in.) to 1067 mm (42 in.).
- .3 Frame must allow for ± 51 mm (± 2 in.) of levelling minimum, ± 6 mm ($\pm 1/2$ in.)

.3 Lounge Sofa with Rear Surface

.1 Description

- .1 U-shaped lounge sofa complete with seat back and rear worksurface(s) on all sides.
- .2 Rear ledge must be connected to, and supported by, the seating unit.

.2 Dimension

- .1 Refer to plan:
 - .1 Overall width to be 4068mm (156 in.) +/- 12"
 - .2 Overall depth to be 2134mm (84 in) +/- 6"
- .2 *Inside seat depth* must be no less than 432 mm (17 in).
- .3 Seat height must be between 406 mm and 508 mm (16 in. and 20 in.) above floor, ± 13 mm ($\pm 1/2$ in.).
- .4 Overall height must be no less than 686 mm (27 in. high).
- .5 Rear ledge must be counter height and must be between 864 mm to 991 mm (34 in. to 39 in.) above finished floor.

.3 Finishes

- .1 Seat and back must be fully upholstered with fabric with stitch detailing for a *tailored appearance*.
- .2 Back must allow for different fabric option than the seat.
- .3 Base/legs must be chrome, painted metal, or wood.
- .4 Rear ledge must be laminate, molded plywood, painted MDF, or wood veneer.

.4 Power and Data

- .1 N/a

.5 Base/Supports

- .1 Must have legs with levelling glides. Legs to be no more than 101 mm (4 in.) in height.

.4 Individual Work Pods

.1 Description

- .1 Freestanding unit must include a *work surface* for a single user and *privacy screen(s)*.
- .2 Seat, *work surface*, and *privacy screen(s)* must be from the same product line.
- .3 Privacy screen(s) must surround the users on no less than three sides, including both the *work surface* and the user.
- .4 Seat will be provided separately and does not form part of this specification.

.2 Dimension

- .1 Work surface must be 762mm (30 in). When measured from the floor to the top of the *work surface*.
- .2 Privacy screen(s) height to be a minimum of 1194mm (47 in.) and a maximum of 1549mm (61 in.).
- .3 Overall *diameter footprint* of unit to be 1829mm (72 in.), ± 150 mm (6 in.)

.3 Finishes

- .1 Work surface or *tablet arm* must be painted MDF, or high pressure laminate.
- .2 Privacy screens must be fabric covered or high pressure laminate.

.4 Power and Data

- .1 Must provide one duplex outlet and data outlet.

.5 Support/Table Bases

- .1 Floor supports must be minimal, no higher than 50.4mm (2 in.). Corners of panels must be rounded; panels which connect at a square or 90 degree angle are not acceptable
- .2 Supports/legs for the *work surface* must be formed to the privacy panels and must appear to be supported by the panels, however may be supported on itself.

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

.5 Individual Private Lounge Chair

.1 Description

- .1 Freestanding unit including upholstered lounge chair with *privacy screen(s)*.
- .2 Integrated or attached side *work surface* or *tablet arm*.
- .3 Lounge chair to allow for a single user.
- .4 High *privacy screen(s)* surrounding the user on three sides.
- .5 A footstool must be provided.
- .6 The seat, the screen, and the footstool seat must be from the same product line.

.2 Dimension

- .1 Lounge chair seat height must be 381 mm (15 in.) to 483 mm (19 in.)
- .2 Overall height including privacy screen(s) must be a minimum of 1168 mm (46 in.) minimum and a maximum of 1626mm (64 in.).
- .3 Overall *diameter footprint* of unit must be 1067mm (42 in.) minimum and 1524mm (60 in.) maximum, not including footstool.

.3 Finishes

- .1 Lounge chair, seat and back, must be:
 - .1 Fully upholstered with fabric with a stitch detailing for a *tailored appearance*.
 - .2 Seat and back must allow for different fabric option than the seat.
- .2 Work surface and *tablet arm* must be painted MDF, high pressure laminate, or wood veneer.
- .3 Screens must be fabric covered or high pressure laminate.

.4 Power and Data

- .1 N/A

.5 Support/Table Bases

- .1 Seat must have either a *pedestal base* with auto return mechanism, 4 post legs, or sled base.

.6 Enclosed Telephone Booth

Solicitation No. - N° de l'invitation
EZ966-192251/B

Amd. No. - N° de la modif.
004

Buyer ID - Id de l'acheteur
vic216

Client Ref. No. - N° de réf. du client
EZ966-192251

File No. - N° du dossier
VIC-8-41182

CCC No./N° CCC - FMS No./N° VME

.1 Description

- .1 Fully enclosed booth complete with ceiling, door, and small table, and stool.
 - .1 Door swing varies, refer to plan.
- .2 Booth must provide internal mechanical air circulation.
- .3 An internal task light must be provided. Task light must be fixed to the unit.

.2 Dimension

- .1 Height to be:
 - .1 Exterior: 2134mm to 2438 mm (84 in. to 96 in.)
 - .2 Interior: 1930mm (76 in.) minimum
- .2 Width to be:
 - .1 Exterior: 965mm to 1067mm (38 in. to 42 in.)
 - .2 Interior: 812 mm (32 in.) minimum
- .3 Depth to be:
 - .1 Exterior: 965 mm to 1067 mm (38 in. to 42 in.)
 - .2 Interior: 812 mm (32 in.) minimum
- .4 Table must not interfere with the use of the interior of the unit.

.3 Finishes

- .1 Exterior must be painted metal or stainless steel. Laminated glass door and rear window.
- .2 Interior must contain acoustic materials. Worksurface to be veneer, plywood, or laminate.

.4 Power and Data

- .1 One simplex power outlet and 2 USB outlets must be provided within the unit.

.5 Base/Supports

- .1 Unit must be self supporting.
 - .1 Additional seismic supports are required. Seismic supports must be local seismic requirements and will require approval from local authorities.