

JOB NO. 90615

C7/194

INLET TEMPERATURE TRANSMITTER SETTINGS (FOLLOWING WORKS TEST)

INLET TEMP °C	SIGNAL		MAX IGV POSITION, DEGREES
	VOLTS	%	
18.93	5	100	-10
0	4.37	84.3	4.13
-20	3.71	67.7	19.07
-40	3.04	51.1	34.00
-101.58	1	0	(80)

MAX IGV = -10° (MECH STOP)
MIN " = 75° (" ")

