



## RETURN BIDS TO:

## RETOURNER LES SOUMISSIONS À:

Travaux publics et Services gouvernementaux  
Canada

Place Bonaventure, portail Sud-Oue

800, rue de La Gauchetière Ouest

7e étage, suite 7300

Montréal

Québec

H5A 1L6

## SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

### Comments - Commentaires

### Vendor/Firm Name and Address

Raison sociale et adresse du  
fournisseur/de l'entrepreneur

### Issuing Office - Bureau de distribution

Travaux publics et Services gouvernementaux Canada

Place Bonaventure, portail Sud-Oue

800, rue de La Gauchetière Ouest

7e étage, suite 7300

Montréal

Québec

H5A 1L6

<b>Title - Sujet</b> Achat et instal. mobilier de bureau	
<b>Solicitation No. - N° de l'invitation</b> EF970-192988/A	<b>Amendment No. - N° modif.</b> 003
<b>Client Reference No. - N° de référence du client</b> EF970-192988	<b>Date</b> 2019-05-02
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$MTA-160-15291	
<b>File No. - N° de dossier</b> MTA-8-41405 (160)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2019-05-10</b>	
<b>Time Zone</b> Fuseau horaire Heure Avancée de l'Est HAE	
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Asquino, Carolina	<b>Buyer Id - Id de l'acheteur</b> mta160
<b>Telephone No. - N° de téléphone</b> (514) 348-4129 ( )	<b>FAX No. - N° de FAX</b> ( ) -
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

Instructions: See Herein

Instructions: Voir aux présentes

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

## AMENDMENT 003

This amendment is raised to respond to questions received to date on May 1, 2019.

### Questions & answers:

**Q10. Credenzas:** Workstation W1a-b-c and W2 : you describe credenzas divided into 3 equal parts, in one piece and as long as possible. It's impossible to do this module in one piece but do you accept standard dimensions of 30-36" in length. We wouldn't make it into equal modules of 32-34".

**A10.** It's not necessary to have the credenza in one piece but the countertop must be in one hole length.  
For longer credenzas, you could use the following standard dimensions : 2x36" for drawers and 1x30" for the open module.  
For shorter credenzas : you could use the following standard dimensions : 2x30" for drawers and 1x36" for the open module.

**Q11. White plastic laminate support:** Workstation W1a-b-c and W2 : you describe a support in white plastic laminate (item no.9 on sheet F161). Can we eliminate this support if our hardware is strong enough? We don't have this type of support because our hardware is made differently.

**A11.** Ok, this support can be omitted if the structure is strong enough.

**Q12. Legs:** Sheet F161 Workstation elevations 1-3-5 seem to have metal legs supporting surfaces but the description on page 25 of 57 doesn't mention legs because it says supports are connected to dividing panels. Can you please clarify.

**A12.** We prefer no legs but they must be added if needed for strength.  
If legs are required then ensure they don't conflict with any side storage

**Q13. Electrical connection:** Electricity from ceiling or from floor?

**A13.** Electricity comes from walls or from floor. There is no "colonnette" from ceiling.

**Q14. Credenzas:** You describe a credenza elevated from floor. Would a standard kick base be acceptable or do you want a legging that creates a gap from floor to underside of credenza?

**A14.** We want a legging that creates a gap from floor to underside of credenza.

**Q15. Stopping block in filing drawers:** Point 2.7.7.2: for this module, you request a stopping block with 2 removable dividers. Can you please explain in more details what you want? Generally, modules come with file-hanging system for filing. The module is not so deep to accommodate all this.

**A15.** We want a standard file hanging system, fitting in the available depth.

**Q16. Back painted glass panel:** Point 2.7.18.2 : You describe a white back-painted glass panel. We don't have this. Do you accept standard white boards or pinnable fabric-covered panels?

**A16.** You must provide a white back-painted glass panel.

**Q17. Reference for locks:** P.26 of 57 : you refer to point 2.2.20 for locks. Is it possible to indicate on what page we can find point 2.2.20

**A17.** The reference for locks is not at point 2.2.20 but at point 2.7.19.

**Q18. Max dimensions in elevators:** Can we fit pieces greater than 108" in elevators? Please provide the dimensions of the elevator.

**A18.** Dimensions of freight elevator #1 : 3660 x 1715 x 2540mm  
Elevator doors : 1220mm in width.

**Q19. Doors in copy/print furniture:** Annex B - item 6: Please clarify if doors for these modules are to be as per item 14.

**A19.** Refer to elevation #7/F161 for door configuration and to plan #6/F161 for dimensions.  
Material and finish : similar to construction of credenzas  
We need 2 of these, with different dimensions:  
- one in a standard furniture panel system  
- one in a room with gypsum walls.

**Q20. Pencil tray:** Annex B - item 9: can the pencil tray (box) be replaced by a pencil tray (flat)? We don't have any alternative.

**A20.** The flat pencil tray is acceptable if it has a lip around its perimeter to prevent pencils from falling.

**Q21. Table flip top & electrified:** Annex B - Item 12-13: you ask for « electrified », how many outlets are required?

**A21.** Refer to addendum F02: the tables are no longer electrified but each table must be equipped with an adjustable power module.

**Q22. Lateral files:** Annex B - Item 15-16-17-18: the depth of plastic laminate storage should be 20" (500mm) instead of 18" (457mm). Is it OK if we have 457mm in metal?

**A22.** Also refer to answer to Q23.  
Yes, it's OK to have 457mm in metal.

**Q23. Number of drawers in lateral file:** Annex B - Item 18: it is impossible to have 5 drawers in plastic laminate for safety reasons (too heavy). The maximum allowable would be 4 drawers. We can make one lateral file with 5 drawers but in metal. Here are our available dimensions and finishes

- in plastic laminate : 36" maximum width with 4 drawers max.
- In metal : we can provide widths of 30-36-42" with up to 6 drawers high.

If you accept, please indicate which dimensions and finish are selected.

**A23.** Refer to addendum F02 (modification to sheet F160) for changes in heights.

It's OK to provide metal filing cabinets instead of plastic laminate but their paint colour should match the white plastic laminate of the workstations.

If the 5 high cabinets are built in metal then the 3 high cabinets should also be built in metal.

Refer to plans for required widths (usually of 42")

**Q24. Installation and delivery:** Annex B - Installation and delivery: Is it possible to clarify whether we can deliver and install by day on weekdays if the work involved is not noisy. Point 1.3.1 isn't clear.

**A24.** Yes, furniture can be installed during daytime on a weekday as long as it's not noisy.

**Q25. Hoop leg:** For office type B2, it is required to provide a hoop leg but is it also required for the return? Is it acceptable to have a full panel for the return?

**A25.** The design intention is to have a hoop leg at both ends of the main worksurface. The worksurface of the return can be supported otherwise.

**ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME.**