



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government
Services Canada/Réception des soumissions Travaux
publics et Services gouvernementaux Canada
Government of Canada Building
101 - 22nd Street East, Suite 110
Saskatoon
Saskatchewan
S7K 0E1
Bid Fax: (306) 975-5397

Revision to a Request for a Standing Offer

Révision à une demande d'offre à commandes

Regional Individual Standing Offer (RISO)

Offre à commandes individuelle régionale (OCIR)

The referenced document is hereby revised; unless
otherwise indicated, all other terms and conditions of
the Offer remain the same.

Ce document est par la présente révisé; sauf
indication contraire, les modalités de l'offre demeurent
les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Public Works and Government Services
Canada/Réception des soumissions Travaux publics et
Services gouvernementaux Canada
Government of Canada Building
101 - 22nd Street East
Suite 110
Saskatoon
Saskatche
S7K 0E1

Title - Sujet Appliances	
Solicitation No. - N° de l'invitation W0142-20X002/B	Date 2019-07-15
Client Reference No. - N° de référence du client W0142-20X002	Amendment No. - N° modif. 004
File No. - N° de dossier STN-8-41079 (204)	CCC No./N° CCC - FMS No./N° VME
GETS Reference No. - N° de référence de SEAG PW-\$STN-205-5168	
Date of Original Request for Standing Offer 2019-05-31	
Date de la demande de l'offre à commandes originale	
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2019-07-29	
Time Zone Fuseau horaire Central Standard Time CST	
Address Enquiries to: - Adresser toutes questions à: Simonson, Sheena	Buyer Id - Id de l'acheteur stn204
Telephone No. - N° de téléphone (306) 241-1169 ()	FAX No. - N° de FAX (306) 975-5397
Delivery Required - Livraison exigée	
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction: DEPARTMENT OF NATIONAL DEFENCE CMTT. Bldg 322 Ralston Alberta T0J2N0 Canada	
Security - Sécurité This revision does not change the security requirements of the Offer. Cette révision ne change pas les besoins en matière de sécurité de la présente offre.	

Instructions: See Herein

Instructions: Voir aux présentes

Acknowledgement copy required Accusé de réception requis	Yes - Oui <input type="checkbox"/>	No - Non <input type="checkbox"/>
The Offeror hereby acknowledges this revision to its Offer. Le proposant constate, par la présente, cette révision à son offre.		
Signature	Date	
Name and title of person authorized to sign on behalf of offeror. (type or print) Nom et titre de la personne autorisée à signer au nom du proposant. (taper ou écrire en caractères d'imprimerie)		
For the Minister - Pour le Ministre		

Solicitation No. - N° de l'invitation
W0142-20X002/B
Client Ref. No. - N° de réf. du client
W0142-20X002

Amd. No. - N° de la modif.
004
File No. - N° du dossier
STN-8-41079

Buyer ID - Id de l'acheteur
STN205
CCC No./N° CCC - FMS No./N° VME

This amendment is raised to respond to:

A. Respond to the following questions:

Question:

Regarding the specifications in Table A – Appliances I had a couple of questions. When it says white/silver – are you asking for both models or the least expensive?

Response:

Either. Potential bidder should bid their best price.

Question:

When dimensions are provided, is there some leeway + or – on either side?

Response:

Due to the dimensions of the doorway the max sizes have no tolerance. All residential appliances must be able to fit through the door way – 29 x 79". Also certain appliances must fit within kitchen spaces, so that is why there are specific measurements. Maximum measurements have been provided.

Question:

For example microwave states Max: 15.5d x 11.5 h x 20.5w. If we quoted one 15.7d x 12.2h x 20.6w is that acceptable?

Response:

The microwave fits in a dedicated area within the kitchen. As all houses have potential to be different. All microwaves supplied must measure these dimensions or less: 15.5d x 11.5h x 20.5w.

Question:

Some dimensions and features are not available in market for some requested items, and also some of them would make the product more expensive but without a good benefit for the end user. So in favor of being able to propose Canada our best available price/performance, I would like to kindly ask if you could also evaluate a proposal with the following features:

- Item 4: Microwave: turntable size: 10.7 inches
- Item 5: Washer (residential use): with 32 inches depth
- Item 6: Dryer (residential use): with 32 inches depth
- Item 9: Vacuum: Cord length of 9.5m
- Item 10: Chest Freezer: height of 33.7 inches

Response:

(Item 4: Microwave: turntable size: 10.7 inches): **Size requirement of turntable removed.**

(Item 5: Washer (residential use): with 32 inches depth): **The washer has to fit through a doorway which is 29 x 79".**

(Item 6: Dryer (residential use): with 32 inches depth): **The dryer has to fit through a doorway which is 29 x 79".**

(Item 9: Vacuum: Cord length of 9.5m) – **9m minimum would be acceptable**

(Item 10: Chest Freezer: height of 33.7 inches): **Has to fit through a doorway which is 29 x 79".**

B. To delete from to Annex "A" – Requirement, Table A – Appliances, and replace with:

Item#	Deliverables	Warranty	Manuals
1	Fridge <ul style="list-style-type: none"> White or silver in colour Total capacity (Cu.Ft.) 18 cu ft (+/- 2 cu ft) Fridge capacity min 14.1 cu ft (+/- 1cu ft) Freezer capacity 3.98 cu ft (+/- 1cu ft) Shelves min 4 CSA Certified Max size: 29" Depth with no Door attached 66-1/8" Height 30" Width Must be able to fit through a doorway that is 29" x 79" 120V 	Min 1 Year Warranty	Include Manual
2	Stove, Gas (free-standing) <ul style="list-style-type: none"> White or silver in colour Max: 30" wide x 47" Height x 28" Depth Must be able to fit through a doorway that is 29" x 79" Min 4 gas burners Ignition Type: Electronic Oven Capacity: min 4.2 cu ft Oven racks: min 2 Oven rack positions: min 5 Oven Light broil CSA Certified 120V Rear Power Connection Location 	Min 1 Year Warranty	Include Manual
3	Stove, Electric <ul style="list-style-type: none"> White or silver in colour Max: 30" wide x 47" Height x 28" Depth Must be able to fit through a doorway that is 29" x 79" Min 4 electric elements Oven Capacity: min 4.8 cu ft Oven racks: min 2 Oven rack positions: min 5 Oven Light 	Min 1 Year Warranty	Include Manual

Solicitation No. - N° de l'invitation
W0142-20X002/B
Client Ref. No. - N° de réf. du client
W0142-20X002

Amd. No. - N° de la modif.
004
File No. - N° du dossier
STN-8-41079

Buyer ID - Id de l'acheteur
STN205
CCC No./N° CCC - FMS No./N° VME

	<ul style="list-style-type: none">• broil• 120V• Rear Power Connection Location		
4	Microwave <ul style="list-style-type: none">• White, black or stainless steel colour• Min Capacity 0.9 Cu.Ft.• Adjustable Power Level• Electronic• Min 10 Power Levels• Power Requirement 1000W• Turntable is includedSide venting• Max: 15.5" Depth x 11.5" High x 20.5 Width• 120V	Min 1 Year Warranty	Include Manual
5	Washer (residential use) <ul style="list-style-type: none">• White or silver in colour• Front loader• Min Capacity: 3.8 cu ft• Electric• Min: 1100 washer spin• Min 9 wash cycles• 120V• ENERGY STAR Qualified• High Efficiency• Quick cycle• Must be able to fit through a doorway that is 29" x 79"• Including hot and cold water hose(s)	Min 1 Year Warranty	Include Manual
6	Dryer (residential use) <ul style="list-style-type: none">• White or Silver in colour• Electric• Capacity: Minimum 7 cu ft (+/- 2 cu ft)• Front loader• 120v• Must be able to fit through a doorway that is 29" x 79"• End of cycle signal• Removable easy to access lint filter• 1 way venting back• Including flexible ducting and two clamps	Min 1 Year Warranty	Include Manual
7	Washer, Heavy Duty (Commercial)	Min 10 Year Limited Parts	Include Manual

	<ul style="list-style-type: none"> Designed as a Commercial Grade Washer Top load Capacity 5 cu. Ft (tolerance +/- 1 cu ft) Stainless steel drum Commercial grade water fill hoses with brass couplings Fast spin speed Automatic water levels Automatic temperature controls Cold wash, warm wash and hot wash options Colour cycle Electric 120V Including hot and cold water hose(s) 	Warranty	
8	Dryer, Heavy Duty (commercial) <ul style="list-style-type: none"> Capacity 7 cu. ft (tolerance +/- 1 cu ft) Designed as a Commercial Grade Dryer Min 3 different cycles Min 3 heat selections Auto dry control Drum light Removable easy to access lint filter Gas Including flexible ducting and two clamps 120V 	Min 10 Year Limited Parts Warranty	Include Manual
9	Vacuum <ul style="list-style-type: none"> Upright Adjustable cleaner head flexi crevice tool, combination tool and stair tool Bagless Suction power over 200air watts Cord over 9m Weight less than 8.2kg 120V 	Min 1 Year Warranty	Include Manual
10	Chest Freezer <ul style="list-style-type: none"> White or silver or black in colour Chest freezer Adjustable Thermostat 8.7 cu ft (+/- 1.5 cu ft) 120V Must be able to fit through a doorway that is 29" x 79" 	Min 1 Year Warranty	Include Manual