



**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS A :**

Bid Receiving/Réception des sousmissions
Procurement & Contracting Services
c/o Commissionaires, F Division
6101 Dewdney Ave
Regina, SK S4P 3K7

**SOLICITATION
AMENDMENT**

**MODIFICATION DE
L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments: - Commentaries :

THIS DOCUMENT DOES NOT CONTAIN A
SECURITY REQUIREMENT

LE PRÉSENT DOCUMENT NE COMPORTE PAS
UNE EXIGENCE EN MATIÈRE DE SÉCURITÉ

Title – Sujet: Evidence Storage Lockers		Date : July 26, 2019
Solicitation No. – N° de l'invitation M5000-20-0999/A		Amendment No. – N° de la modification 002
Client Reference No. - No. De Référence du Client 202000999		
Solicitation Closes – L'invitation prend fin		
At /à :	2 :00 pm	CST (Central Standard Time) HNC (Heure Normale du Centre)
On / le :	August 27, 2019	
Incoterms 2010 "DDP Delivered Duty Paid" See herein — Voir aux présentes	GST – TPS See herein — Voir aux présentes	Duty – Droits See herein — Voir aux présentes
Destination of Goods and Services – Destinations des biens et services See herein — Voir aux présentes		
Instructions See herein — Voir aux présentes		
Address Inquiries to – Adresser toute demande de renseignements à Tania Sentes		
Telephone No. – No. de téléphone 639-625-3463		Facsimile No. – No. de télécopieur 306-780-5232
Delivery Required – Livraison exigée N/A	Delivery Offered – Livraison proposée N/A	
Vendor/Firm Name, Address and Representative – Raison sociale, adresse et représentant du fournisseur/de l'entrepreneur:		
Telephone No. – No. de téléphone		Facsimile No. – No. de télécopieur
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) – Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur (taper ou écrire en caractères d'imprimerie)		
Signature	Date	



This amendment is raised to address the following:

- To respond to questions received during the solicitation period; and
- To revise the solicitation accordingly, as applicable.

QUESTIONS AND ANSWERS

Question 3: The requirements of the custom evidence storage lockers are difficult to match. Is there a product that the RCMP has purchased in the past that meets these requirements? If so can you provide an example of the requested product or shop drawing of the requested build? -

Answer 3: The evidence storage lockers are a custom design therefore a picture or drawing is not available. The RCMP haven't purchased this specific product before.

Question 4: Please show diagram or Image of required 4 Inch diameter vent connection. What will it be connecting to? (Requirement E)

Answer 4: The vent connection is a 4 inch diameter circular hole to allow for a standard Heating, Ventilation and Air Conditioning (HVAC) vent pipe to be connected for negative air draw ventilation.

Question 5: Please show the positioning of the 12 inch wide x 6.5 inch deep cut outs on the left hand side of the shelf. What is the intended purpose of the cut out? (Requirement H and I)

Answer 5: The cut out on the shelf is intended to allow storage of taller items by placing them upright through the cut out fixed shelf and movable shelf. The cut out should be positioned centered between the mid-point of the shelf and the left side of the locker. If the left door of the locker is open, the cut out will be centered in that half of the cabinet.

Question 6: Please explain necessity of Stainless Steel Shelves. Should the one fixed shelf be stainless steel as well? Would Epoxy Powder Coat be acceptable? (Requirement H)

Answer 6: All shelves are to be stainless steel as per the specifications. Stainless steel shelves are required to ensure a nonporous surface that can be easily cleaned, rust-proof, and have the structural integrity to hold heavy items.

Question 7: Requirement B - Is it acceptable for the unit to be constructed with mixture of 18, 20, 22 gauge material?

Answer 7: No.

Question 8: Requirement H - Is a grommet to be included on the cut out?

Answer 8: Yes

Question 9: Requirement H - Would 1.6 inch increments be acceptable?

Answer 9: Yes

Question 10: Requirement K - What are the hole sizes and patterns required for the perforated shelves?

Answer 10: The holes must be 1 cm or smaller, no specific pattern is required, the manufacturer standard is acceptable. The shelves must be perforated to allow sufficient airflow.



SOLICITATION REVISIONS

1) On page thirteen (13) Annex "A" Requirement

DELETE: in it's entirety

INSERT:

ANNEX "A"

REQUIREMENT

The Contractor must supply, deliver and unload custom Evidence Storage Lockers to the Royal Canadian Mounted Police (RCMP), to be delivered to Red Deer, Alberta, in accordance with the requirements specifications, terms and conditions detailed herein.

The Evidence Storage Lockers must include the following specifications:

The evidence storage lockers must arrive fully assembled and be constructed in a fashion to ensure items placed within the storage locker can only be removed if the locking mechanism is disengaged. The lockers must be designed to ensure secure storage to prevent unauthorized handling and to maintain a secure chain of custody.

- A. Dimensions of 84 inches high by 36 inches wide by 24 inches deep.
- B. Constructed with 18 gauge cold rolled steel
- C. Epoxy powder coat finish.
- D. Lockers to be neutral colour such as tan, beige or grey. Colour to be selected upon Contract Award.
- E. 4" diameter vent connection on the top centre of the unit.
- F. Louvered vents on the bottom of the doors for fresh air intake
- G. Lock capability, either padlock or locking mechanism built into the door, one lock per cabinet. The RCMP will supply the padlocks.
- H. Four adjustable stainless steel shelves with adjustments in 1 to 1.6 inch increments. One of the adjustable shelves require a 12 inch wide and 6 ½ inch deep cut out on the left half of the front portion of the shelf.
- I. One fixed shelf with a 12 inch wide and 6 ½ inch deep cut out on the left half of the front portion of the shelf.
- J. Double door access
- K. All shelves are to be perforated to allow airflow. The holes must be 1 cm or smaller, no specific pattern is required, the manufacturer standard is acceptable.

ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME