



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government
Services Canada/Réception des soumissions Travaux
publics et Services gouvernementaux Canada
1713 Bedford Row
Halifax, N.S./Halifax, (N.É.)
Halifax
Nova Scotia
B3J 1T3
Bid Fax: (902) 496-5016

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise
indicated, all other terms and conditions of the Solicitation
remain the same.

Ce document est par la présente révisé; sauf indication contraire,
les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Atlantic Region Acquisitions/Région de l'Atlantique
Acquisitions
1713 Bedford Row
Halifax, N.S./Halifax, (N.É.)
Halifax
Nova Scotia
B3J 1T3

Title - Sujet Industrial Furniture	
Solicitation No. - N° de l'invitation W7707-196544/B	Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client W7707-19-6544	Date 2019-11-13
GETS Reference No. - N° de référence de SEAG PW-SHAL-207-10815	
File No. - N° de dossier HAL-8-81289 (207)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2019-12-09	
Time Zone Fuseau horaire Atlantic Standard Time AST	
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Grieve, Bronwen	Buyer Id - Id de l'acheteur hal207
Telephone No. - N° de téléphone (902) 943-2394 ()	FAX No. - N° de FAX (902) 496-5016
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Amendment 001 is raised to:

- 1. Address Bidder Questions;**
- 2. Amend Annex "A"; and**
- 3. Amend Annex "C".**

1. Bidder Questions

Question 1: For item #18, is 56" long acceptable?

Answer 1: Yes, 56" long is acceptable.

Question 2: For item #19, is 64" acceptable?

Answer 2: Yes, 64" wide is acceptable.

Question 3: For items #22 and #29, is 3 uprights acceptable?

Answer 3: Yes, 3 uprights are acceptable.

Question 4: For items #22 and #29, is 28" center to center for the uprights acceptable?

Answer 4: Yes, 28" centre-to-centre is acceptable.

Question 5: For items #23, #27 and #29 is 26"D for the mounting arms for the light acceptable?

Answer 5: Yes, 26" mounting arms is acceptable.

Question 6: For items #23, #27 and #29, is LED light acceptable?

Answer 6: Yes, LED lights are acceptable.

Question 7: For items #24 and #25, is 200lbs capacity acceptable?

Answer 7: Yes, 200 lbs capability is acceptable.

Question 8: For item #29, is the drawer dimensions of 6"H x 18"W x 21"D acceptable?

Answer 8: Yes, 6" x 18" x 21" is acceptable.

Question 9: For item 6 & 7, would 81.1 x 29.5 x 44.6 (Height/Width/Depth) be acceptable?

Answer 9: Yes, that would be acceptable.

Question 10: For item 6 & 7, would a rack space of 42u be acceptable?

Answer 10: Yes, that would be acceptable.

Question 11: For item 6 & 7, would an attenuation of 15dB be acceptable?

Answer 11: No, that would not be acceptable.

Question 12: For item 6 & 7, is the product able to be light grey in colour?

Answer 12: Yes, that would be acceptable.

Question 13: Should the required items be delivered fully assembled?

Answer 13: Assembly is not required.

2. Under Annex "A":

DELETE: In its entirety

INSERT: *(See next page)*

ANNEX "A"
REQUIREMENT

Defence Research and Development Canada (DRDC) has a requirement for the purchase and delivery of industrial furniture and accessories to their Atlantic Research Centre in Dartmouth, Nova Scotia as per specifications outlined in table below.

NOTE TO BIDDER: Equivalent products **will be accepted** for all items listed below. Equivalent product information must be provided in Annex "C" – Evaluation Criteria.

Item	Description
1	<p><u>Standard Lab Shelving (v1)</u></p> <p>Description: Adjustable, 650 lbs to 1,775 pound capacity (4 shelves)</p> <p>Dimensions (Height/Width/Depth): 72 to 75 inches / 42 inches / 18 inches</p> <p>Colour: Light Blue</p> <p>OEM: Pucel</p> <p>Part Number: DR-1842</p>
2	<p><u>Standard Lab Shelving (v2)</u></p> <p>Description: Adjustable, 650 lbs to 1,775 pound capacity (4 shelves)</p> <p>Dimensions (Height/Width/Depth): 72 to 75 inches / 48 inches / 24 inches</p> <p>Colour: Light Blue</p> <p>OEM: Pucel</p> <p>Part Number: DR-2448</p>
3	<p><u>Roll-Out Shelving (v1)</u></p> <p>Description: 1,500lbs per shelf capacity (3 shelves)</p> <p>Dimensions (Height/Width/Depth): 80 inches / 57 inches / 32 inches</p> <p>Colour: Light Blue</p> <p>OEM: Vestil</p> <p>Part Number: VRSOR-54</p>

Item	Description
4	<u>Roll-Out Shelving (v2)</u> Description: 1,500lbs per shelf capacity (6 shelves) Dimensions (Height/Width/Depth): 80 inches / 114 inches / 32 inches Colour: Light Blue OEM: Vestil Part Number: VRSOR-14
5	<u>Extra Shelf</u> Description: For Roll-Out VRSOR shelving Dimensions (Width/Depth): 114 inches / 32 inches Colour: Light Blue OEM: Vestil Part Number: VRSOR-SLF
6	<u>Sound-Reducing Cabinet (v1)</u> Description: Attenuates up to 20.7 dB(A) – 42u or 44u Dimensions (Height/Width/Depth): 81 to 85 inches / 24 to 29.5 inches / 41 to 44.6 inches Colour: Dark Grey or Light Grey OEM: Rackmount Solutions Part Number: AQ772036
7	<u>Sound-Reducing Cabinet (v2)</u> Description: Attenuates up to 20.7 dB(A) - 42u or 44u Dimensions (Height/Width/Depth): 81 to 85 inches / 24 to 29.5 inches / 44.6 to 47 inches Colour: Dark Grey or Light Grey OEM: Rackmount Solutions Part Number: AQ772042

Item	Description
8	<u>Blanketing Panel</u> Description: Blanketing Panel for Sound-reducing Cabinets (1u) Dimensions (Width/Depth): 19 inches / 8 inches OEM: Upsite Technologies Part Number: HotLok-10031 1U BP
9	<u>Storage Bin Cabinet</u> Description: High Density Storage & Security; multiple, durable bins to hold small, medium and large components inside of a lockable storage unit. Dimensions (Height/Width/Depth): 72 inches / 36 inches / 24 inches Colour: Grey OEM: Vestil Part Number: VSC-3501-132
10	<u>Storage Cabinet</u> Description: Eye-level storage cabinet with 7 drawers of usable height (5", 7" and 9") and 66 compartments distributed over the 7 drawers. Dimensions (Height/Width/Depth): 59.5-60 inches / 40.25-42 inches / 22.5-24 inches Colour: Blue OEM: Lista Part Number: XSHS1350-0702
11	<u>Adjustable Workbench (v1)</u> Description: Crank adjustable height Dimensions (Height/Width/Depth): 30-42 inches / 48 inches / 36 inches Colour: F63A31 OEM: Proline Part Number: ELH4836SM Note: Top - Maple

Item	Description
12	<u>Adjustable Workbench (v2)</u> Description: Crank adjustable height Dimensions (Height/Width/Depth): 30-42 inches / 60 to 64 inches / 30 inches Colour: F63A31 OEM: Proline Part Number: ELH6030SM Note: Top - Maple
13	<u>Adjustable Workbench (v3)</u> Description: Crank adjustable height Dimensions (Height/Width/Depth): 30-42 inches / 72 inches / 30 inches Colour: F63A31 OEM: Proline Part Number: ELH7230SM Note: Top - Maple
14	<u>Fixed Workbench (v1)</u> Description: Standard workbench 2,750 to 5,000 pound capacity Dimensions (Height/Width/Depth): 30 inches / 60 inches / 30 inches Colour: F63A31 OEM: Proline Part Number: HD6030M Note: Top - Maple

Item	Description
15	<u>Fixed Workbench (v2)</u> Description: Standard workbench - 2,750 to 5,000 pound capacity Dimensions (Height/Width/Depth): 30 inches / 72 inches / 36 inches Colour: F63A31 OEM: Proline Part Number: HD7236M Note: Top - Maple
16	<u>Power Supply</u> Description: 12 outlets, 15 amp 120 Volt OEM: Proline Part Number: ES48
17	<u>Mounting Rail</u> Description: For Power Supply OEM: Proline Part Number: ESMR60
18	<u>Bin Holder (v1)</u> Description: Heavy gauge formed steel which mounts to upright system for unlimited adjustments of bins. Dimensions (Width): 56 to 60 inches OEM: Proline Part Number: BH60
19	<u>Bin Holder (v2)</u> Description: Heavy gauge formed steel which mounts to upright system for unlimited adjustments of bins. Dimensions (Width): 64 to 72 inches OEM: Proline Part Number: BH72

Item	Description
20	<u>Ground Wrist Strap</u> Description: Includes Electrostatic Discharge (ESD) wrist strap (one size fits all), and a 6 foot long cord that plugs into Ground Kit (see Line Item 21). OEM: Proline Part Number: SGS-4
21	<u>Ground Kit</u> Description: For Conductive Stations includes Ground Bolt, Ground Wire and (2) Banana Jacks Dimensions (Height/Width/Depth): 3 inches / 6 inches / 8 inches OEM: Proline Part Number: SGK-J2
22	<u>Upright Supports (2 per or 3 per)</u> Dimensions (Length): 48 inches 28 inch center to center for the uprights Colour: F63A31 OEM: Proline Part Number: UR60
23	<u>Overhead Light</u> Description: Frame with 2 bulb fixture Powder-coated steel construction. LED light acceptable. Dimensions (Height/Width/Depth): 6 inches / 60 inches / 16 inches 26 inch mounting arms for the light Colour: F63A31(or a light grey) OEM: Proline Part Number: OLF60
24	<u>Cantilever Shelf</u> Description: Laminate cantilever shelf; load bearing minimum 125lbs. Dimensions (Width/Depth): 60 inches / 12 inches OEM: Proline Part Number: CSPL1260P

Item	Description
25	<u>Cantilever Shelf</u> Description: Laminate cantilever shelf; load bearing minimum 125lbs. Dimensions (Width/Depth): 72 inches / 12 inches OEM: Proline Part Number: CSPL1272P
26	<u>Shelf Riser</u> Description: 6 Outlets, ESD Laminate surface Dimensions (Height/Width/Depth): 18 inches / 60 inches / 12 inches Colour: F63A31 OEM: Proline Part Number: R6012-3ESD
27	<u>Overhead Light Frame</u> Description: Frame with bulb fixtures; powder coated steel. LED light acceptable. Dimensions (Height/Length/Depth): 24 inches / 72 inches / 6 inches 26 inch mounting arms for the light Colour: F63A31 OEM: Proline Part Number: OLF72
28	<u>Castors (4pkg)</u> Description: Stem Caster (with brake) - max 400lbs capacity OEM: Proline Part Number: C-4

Item	Description												
29	<p><u>Workbench-in-a-box</u></p> <p>Description: 6" drawer, bin holder, power supply, overhead light, shelf. LED light acceptable.</p> <p>Dimensions (Height/Width/Depth):</p> <p>30-42 inches / 60 inches / 30 inches 28 inch center to center for the uprights 26 inch mounting arms for the light</p> <p>Colour: Light Blue</p> <p>OEM: Proline</p> <p>Part Number: BIB15</p> <p>Note: Top - Plastic Laminate (White)</p>												
30	<p><u>Task Stool (v1)</u></p> <p>Description: Adjustable Height Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <table> <tr> <td>Back Size</td><td>: 17.25" W x 17.75" H</td></tr> <tr> <td>Overall Depth</td><td>: 26.25"</td></tr> <tr> <td>Overall Height</td><td>: 44.5" – 48.74"</td></tr> <tr> <td>Overall Width</td><td>: 26.25"</td></tr> <tr> <td>Seat Height</td><td>: 27.25" – 31.50"</td></tr> <tr> <td>Seat Size</td><td>: 19" W x 17.75" D</td></tr> </table> <p>Colour: A04 - Navy</p> <p>OEM: OFM</p> <p>Part Number: 130-DK</p>	Back Size	: 17.25" W x 17.75" H	Overall Depth	: 26.25"	Overall Height	: 44.5" – 48.74"	Overall Width	: 26.25"	Seat Height	: 27.25" – 31.50"	Seat Size	: 19" W x 17.75" D
Back Size	: 17.25" W x 17.75" H												
Overall Depth	: 26.25"												
Overall Height	: 44.5" – 48.74"												
Overall Width	: 26.25"												
Seat Height	: 27.25" – 31.50"												
Seat Size	: 19" W x 17.75" D												
31	<p><u>Task Stool (v2)</u></p> <p>Description: Adjustable Height Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <table> <tr> <td>Back Size</td><td>: 17.25" W x 17.75" H</td></tr> <tr> <td>Overall Depth</td><td>: 26.25"</td></tr> <tr> <td>Overall Height</td><td>: 44.5" – 48.74"</td></tr> <tr> <td>Overall Width</td><td>: 26.25"</td></tr> <tr> <td>Seat Height</td><td>: 27.25" – 31.50"</td></tr> <tr> <td>Seat Size</td><td>: 19" W x 17.75" D</td></tr> </table> <p>Colour: A03 - Red</p> <p>OEM: OFM</p> <p>Part Number: 130-DK</p>	Back Size	: 17.25" W x 17.75" H	Overall Depth	: 26.25"	Overall Height	: 44.5" – 48.74"	Overall Width	: 26.25"	Seat Height	: 27.25" – 31.50"	Seat Size	: 19" W x 17.75" D
Back Size	: 17.25" W x 17.75" H												
Overall Depth	: 26.25"												
Overall Height	: 44.5" – 48.74"												
Overall Width	: 26.25"												
Seat Height	: 27.25" – 31.50"												
Seat Size	: 19" W x 17.75" D												

Item	Description																
32	<p><u>Task Chair (v1)</u></p> <p>Description: With Arms Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <table><tr><td>Arm Height</td><td>: 26" – 33"</td></tr><tr><td>Back Size</td><td>: 17.25" W x 17.75" H</td></tr><tr><td>Base Size</td><td>: 25"</td></tr><tr><td>Overall Depth</td><td>: 26.25"</td></tr><tr><td>Overall Height:</td><td>38.50" – 42.75"</td></tr><tr><td>Overall Width</td><td>: 26.25"</td></tr><tr><td>Seat Height</td><td>: 19.25" – 23.50"</td></tr><tr><td>Seat Size</td><td>: 19" W x 17.75" D</td></tr></table> <p>Colour: A04 - Navy</p> <p>OEM: OFM</p> <p>Part Number: 130-AA3</p>	Arm Height	: 26" – 33"	Back Size	: 17.25" W x 17.75" H	Base Size	: 25"	Overall Depth	: 26.25"	Overall Height:	38.50" – 42.75"	Overall Width	: 26.25"	Seat Height	: 19.25" – 23.50"	Seat Size	: 19" W x 17.75" D
Arm Height	: 26" – 33"																
Back Size	: 17.25" W x 17.75" H																
Base Size	: 25"																
Overall Depth	: 26.25"																
Overall Height:	38.50" – 42.75"																
Overall Width	: 26.25"																
Seat Height	: 19.25" – 23.50"																
Seat Size	: 19" W x 17.75" D																
33	<p><u>Task Chair (v2)</u></p> <p>Description: With Arms Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <table><tr><td>Arm Height</td><td>: 26" – 33"</td></tr><tr><td>Back Size</td><td>: 17.25" W x 17.75" H</td></tr><tr><td>Base Size</td><td>: 25"</td></tr><tr><td>Overall Depth</td><td>: 26.25"</td></tr><tr><td>Overall Height:</td><td>38.50" – 42.75"</td></tr><tr><td>Overall Width</td><td>: 26.25"</td></tr><tr><td>Seat Height</td><td>: 19.25" – 23.50"</td></tr><tr><td>Seat Size</td><td>: 19" W x 17.75" D</td></tr></table> <p>Colour: A03 - Red</p> <p>OEM: OFM</p> <p>Part Number: 130-AA3</p>	Arm Height	: 26" – 33"	Back Size	: 17.25" W x 17.75" H	Base Size	: 25"	Overall Depth	: 26.25"	Overall Height:	38.50" – 42.75"	Overall Width	: 26.25"	Seat Height	: 19.25" – 23.50"	Seat Size	: 19" W x 17.75" D
Arm Height	: 26" – 33"																
Back Size	: 17.25" W x 17.75" H																
Base Size	: 25"																
Overall Depth	: 26.25"																
Overall Height:	38.50" – 42.75"																
Overall Width	: 26.25"																
Seat Height	: 19.25" – 23.50"																
Seat Size	: 19" W x 17.75" D																

3. Under Annex "C":

DELETE: In its entirety

INSERT:

ANNEX "C"

EVALUATION CRITERIA

MANDATORY REQUIREMENTS:

Bids **MUST** meet the mandatory requirements specified below. To demonstrate that all requirements of the technical specifications are respected bidders **MUST** respond with complete specifications and/or descriptive literature of the equipment being offered.

Any proposal which fails to meet all mandatory requirements will be deemed non-responsive. Each requirement should be addressed separately.

Note: Bidders are required to provide OEM items or equivalent products as per SACC B3000T (2006-06-16).

When offering equivalent products, the bidder must fully demonstrate how the form, fit and function of suggested products are fully interchangeable with the item specified.

The evaluation will only be based on the information provided with the bid. References to Internet sites or information that is not included will not be evaluated.

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
1		<u>Standard Lab Shelving (v1)</u> Description: Adjustable, 650 lbs to 1,775 pound capacity (4 shelves) Dimensions (Height/Width/Depth): 72 to 75 inches / 42 inches / 18 inches Colour: Light Blue OEM: Pucel Part Number: DR-1842		
2		<u>Standard Lab Shelving (v2)</u> Description: Adjustable, 650 lbs to 1,775 pound capacity (4 shelves) Dimensions (Height/Width/Depth): 72 to 75 inches / 48 inches / 24 inches Colour: Light Blue OEM: Pucel Part Number: DR-2448		
3		<u>Roll-Out Shelving (v1)</u> Description: 1,500lbs per shelf capacity (3 shelves) Dimensions (Height/Width/Depth): 80 inches / 57 inches / 32 inches Colour: Light Blue OEM: Vestil Part Number: VRSOR-54		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
4		<u>Roll-Out Shelving (v2)</u> Description: 1,500lbs per shelf capacity (6 shelves) Dimensions (Height/Width/Depth): 80 inches / 114 inches / 32 inches Colour: Light Blue OEM: Vestil Part Number: VRSOR-14		
5		<u>Extra Shelf</u> Description: For Roll-Out VRSOR shelving Dimensions (Width/Depth): 114 inches / 32 inches Colour: Light Blue OEM: Vestil Part Number: VRSOR-SLF		
6		<u>Sound-Reducing Cabinet (v1)</u> Description: Attenuates up to 20.7 dB(A) – 42u or 44u Dimensions (Height/Width/Depth): 81 to 85 inches / 24 to 29.5 inches / 41 to 44.6 inches Colour: Dark Grey or Light Grey OEM: Rackmount Solutions Part Number: AQ772036		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
7		<u>Sound-Reducing Cabinet (v2)</u> Description: Attenuates up to 20.7 dB(A) - 42u or 44u Dimensions (Height/Width/Depth): 81 to 85 inches / 24 to 29.5 inches / 44.6 to 47 inches Colour: Dark Grey or Light Grey OEM: Rackmount Solutions Part Number: AQ772042		
8		<u>Blanketing Panel</u> Description: Blanketing Panel for Sound-reducing Cabinets (1u) Dimensions (Width/Depth): 19 inches / 8 inches OEM: Upsite Technologies Part Number: HotLok-10031 1U BP		
9		<u>Storage Bin Cabinet</u> Description: High Density Storage & Security; multiple, durable bins to hold small, medium and large components inside of a lockable storage unit. Dimensions (Height/Width/Depth): 72 inches / 36 inches / 24 inches Colour: Grey OEM: Vestil Part Number: VSC-3501-132		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
10		<u>Storage Cabinet</u> Description: Eye-level storage cabinet with 7 drawers of usable height (5", 7" and 9") and 66 compartments distributed over the 7 drawers. Dimensions (Height/Width/Depth): 59.5-60 inches / 40.25-42 inches / 22.5-24 inches Colour: Blue OEM: Lista Part Number: XSHS1350-0702		
11		<u>Adjustable Workbench (v1)</u> Description: Crank adjustable height Dimensions (Height/Width/Depth): 30-42 inches / 48 inches / 36 inches Colour: F63A31 OEM: Proline Part Number: ELH4836SM Note: Top - Maple		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
12		<u>Adjustable Workbench (v2)</u> Description: Crank adjustable height Dimensions (Height/Width/Depth): 30-42 inches / 60 to 64 inches / 30 inches Colour: F63A31 OEM: Proline Part Number: ELH6030SM Note: Top - Maple		
13		<u>Adjustable Workbench (v3)</u> Description: Crank adjustable height Dimensions (Height/Width/Depth): 30-42 inches / 72 inches / 30 inches Colour: F63A31 OEM: Proline Part Number: ELH7230SM Note: Top - Maple		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
14		<u>Fixed Workbench (v1)</u> Description: Standard workbench 2,750 to 5,000 pound capacity Dimensions (Height/Width/Depth): 30 inches / 60 inches / 30 inches Colour: F63A31 OEM: Proline Part Number: HD6030M Note: Top - Maple		
15		<u>Fixed Workbench (v2)</u> Description: Standard workbench - 2,750 to 5,000 pound capacity Dimensions (Height/Width/Depth): 30 inches / 72 inches / 36 inches Colour: F63A31 OEM: Proline Part Number: HD7236M Note: Top - Maple		
16		<u>Power Supply</u> Description: 12 outlets, 15 amp 120 Volt OEM: Proline Part Number: ES48		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
17		<u>Mounting Rail</u> Description: For Power Supply OEM: Proline Part Number: ESMR60		
18		<u>Bin Holder (v1)</u> Description: Heavy gauge formed steel which mounts to upright system for unlimited adjustments of bins. Dimensions (Width): 56 to 60 inches OEM: Proline Part Number: BH60		
19		<u>Bin Holder (v2)</u> Description: Heavy gauge formed steel which mounts to upright system for unlimited adjustments of bins. Dimensions (Width): 64 to 72 inches OEM: Proline Part Number: BH72		
20		<u>Ground Wrist Strap</u> Description: Includes Electrostatic Discharge (ESD) wrist strap (one size fits all), and a 6 foot long cord that plugs into Ground Kit (see Line Item 21). OEM: Proline Part Number: SGS-4		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
21		<p><u>Ground Kit</u></p> <p>Description: For Conductive Stations includes Ground Bolt, Ground Wire and (2) Banana Jacks</p> <p>Dimensions (Height/Width/Depth): 3 inches / 6 inches / 8 inches</p> <p>OEM: Proline</p> <p>Part Number: SGK-J2</p>		
22		<p><u>Upright Supports (2 per or 3 per)</u></p> <p>Dimensions (Length): 48 inches 28 inch center to center for the uprights</p> <p>Colour: F63A31</p> <p>OEM: Proline</p> <p>Part Number: UR60</p>		
23		<p><u>Overhead Light</u></p> <p>Description: Frame with 2 bulb fixture Powder-coated steel construction. LED light acceptable.</p> <p>Dimensions (Height/Width/Depth): 6 inches / 60 inches / 16 inches 26 inch mounting arms for the light</p> <p>Colour: F63A31(or a light grey)</p> <p>OEM: Proline</p> <p>Part Number: OLF60</p>		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
24		<u>Cantilever Shelf</u> Description: Laminated cantilever shelf; load bearing minimum 125lbs. Dimensions (Width/Depth): 60 inches / 12 inches OEM: Proline Part Number: CSPL1260P		
25		<u>Cantilever Shelf</u> Description: Laminated cantilever shelf; load bearing minimum 125lbs. Dimensions (Width/Depth): 72 inches / 12 inches OEM: Proline Part Number: CSPL1272P		
26		<u>Shelf Riser</u> Description: 6 Outlets, ESD Laminated surface Dimensions (Height/Width/Depth): 18 inches / 60 inches / 12 inches Colour: F63A31 OEM: Proline Part Number: R6012-3ESD		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
27		<p><u>Overhead Light Frame</u></p> <p>Description: Frame with bulb fixtures; powder coated steel. LED light acceptable.</p> <p>Dimensions (Height/Length/Depth): 24 inches / 72 inches / 6 inches 26 inch mounting arms for the light</p> <p>Colour: F63A31</p> <p>OEM: Proline</p> <p>Part Number: OLF72</p>		
28		<p><u>Casters (4pkg)</u></p> <p>Description: Stem Caster (with brake) - max 400lbs capacity</p> <p>OEM: Proline</p> <p>Part Number: C-4</p>		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
29		<p><u>Workbench-in-a-box</u></p> <p>Description: 6" drawer, bin holder, power supply, overhead light, shelf. LED light acceptable.</p> <p>Dimensions (Height/Width/Depth):</p> <p>30-42 inches / 60 inches / 30 inches</p> <p>28 inch center to center for the uprights</p> <p>26 inch mounting arms for the light</p> <p>Colour: Light Blue</p> <p>OEM: Proline</p> <p>Part Number: BIB15</p> <p>Note: Top - Plastic Laminate (White)</p>		
30		<p><u>Task Stool (v1)</u></p> <p>Description: Adjustable Height Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <p>Back Size : 17.25" W x 17.75" H</p> <p>Overall Depth : 26.25"</p> <p>Overall Height : 44.5" – 48.74"</p> <p>Overall Width : 26.25"</p> <p>Seat Height : 27.25" – 31.50"</p> <p>Seat Size : 19" W x 17.75" D</p> <p>Colour: A04 - Navy</p> <p>OEM: OFM</p> <p>Part Number: 130-DK</p>		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
31		<p><u>Task Stool (v2)</u></p> <p>Description: Adjustable Height Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <ul style="list-style-type: none">Back Size : 17.25" W x 17.75" HOverall Depth : 26.25"Overall Height : 44.5" – 48.74"Overall Width : 26.25"Seat Height : 27.25" – 31.50"Seat Size : 19" W x 17.75" D <p>Colour: A03 - Red</p> <p>OEM: OFM</p> <p>Part Number: 130-DK</p>		
32		<p><u>Task Chair (v1)</u></p> <p>Description: With Arms Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <ul style="list-style-type: none">Arm Height : 26" – 33"Back Size : 17.25" W x 17.75" HBase Size : 25"Overall Depth : 26.25"Overall Height: 38.50" – 42.75"Overall Width : 26.25"Seat Height : 19.25" – 23.50"Seat Size : 19" W x 17.75" D <p>Colour: A04 - Navy</p> <p>OEM: OFM</p> <p>Part Number: 130-AA3</p>		

Item	Part #	Description	OEM items offered Yes / No	Equivalent Brand Proposed**
33		<p><u>Task Chair (v2)</u></p> <p>Description: With Arms Comfort, Ergonomic Mesh-backed chair with 3" seat and 250lbs weight capacity.</p> <p>Dimensions:</p> <div><div>Arm Height</div><div>: 26" – 33"</div></div> <div><div>Back Size</div><div>: 17.25" W x 17.75" H</div></div> <div><div>Base Size</div><div>: 25"</div></div> <div><div>Overall Depth</div><div>: 26.25"</div></div> <div><div>Overall Height</div><div>: 38.50" – 42.75"</div></div> <div><div>Overall Width</div><div>: 26.25"</div></div> <div><div>Seat Height</div><div>: 19.25" – 23.50"</div></div> <div><div>Seat Size</div><div>: 19" W x 17.75" D</div></div> <p>Colour: A03 - Red</p> <p>OEM: OFM</p> <p>Part Number: 130-AA3</p>		

** WHEN EQUIVELANT PRODUCTS ARE PROPOSED, THE BIDDER SHOULD INDICATE PAGE REFERENCE NUMBER FOR SPECIFICATIONS PROVIDED SUPPORTING THE EQUIVELANCY OF THE PROPOSED PRODUCT.

ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED