

**DRAFT**

# MARINO KITCHEN EQUIPMENT LLC

P.O. BOX 80571, DUBAI, U.A.E.






Tel # +9714 2977966







E-mail Address : marinodb2@emirates.net.ae / marinodb2@gmail.com


## QUOTATION







Offer No	<b>DB2-000715.REV03</b>	Tel #	<b>04 438 4080</b>
Client Name	<b>ELLISDON PROJECT AND CONSTRUCTION MANAGEMENT</b>	Fax #	<b>04 515 3401</b>
Attn Mr. / Mrs.	<b>MR. AYMAN HASSAN EL HALABI</b>	Mobile #	<b>055 3001881</b>
Date	<b>18-Sep-18</b>	Email	<a href="mailto:aelhalabi@ellisdon.com">aelhalabi@ellisdon.com</a>

last rev. 21.10.19

No.	S. Code	Model	Description	Images
<b>DISH WASH, COOKING &amp; PREPARATION AREA</b>				
A1	694	GS50 ECO	Electric Under Counter Type Dishwasher AISI 304 structure Rack/Hour: 30 Rack dim: 500x500mm Tank Cap: 29 Lt Voltage: 230V-50Hz Dim: 590x600x850mm Useful height 345mm Made by: DIHR, Italy	
A2		Custom	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Double Bowl Sink with bottom left side 61 cm open space for Dish Washer, back and right side splash 10 cm, thickness 1.2 mm, 4x4 cm square tube type legs and adjustable feet, etc. Dim: 190 x 70 x 90 + 10 cm Made by: Marino UAE <i>mixer tap tap, accessories and drainage pipe not included</i>	
A3		Custom	S/STEEL FLOOR GRATING UNIT WITH FULL BOWL AND TOP (SQUARE TYPE HOLE TOP) ALL OF AISI 304 18/10 S/STEEL. DIM: 50 x 30 x 10 cm Made by: Marino UAE	
A4		Custom	S/s custom fabrication heavy duty Single Wall Shelf AISI 304 brush finish thickness 1.2mm Dim: 225 x 35 x 30 + 4 cm Made by: Marino UAE	
A5		Custom	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Work Table with bottom shelf, back and left side splash 10 cm, thickness 1.2 mm, 4x4 cm square tube type legs and adjustable feet, etc. Dim: 110 x 70 x 90 + 10 cm Made by: Marino UAE	
A6		Custom	S/s custom fabrication heavy duty Single Wall Shelf AISI 304 brush finish thickness 1.2mm Dim: 220 x 35 x 30 + 4 cm Made by: Marino UAE	

A7			Spare Number	
A8			Spare Number	
A9		Custom	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Work Table with bottom shelf, back splash 10 cm, thickness 1.2 mm, 4x4 cm square tube type legs and adjustable feet, etc. Dim: 120 x 70 x 90 + 10 cm Made by: Marino UAE	
A10	1627	RCS511TS	Commercial Microwave cooking Stainless Steel construction inside and outside with 100 programmable menu items, 4 stages of cooking, 5 microwave power levels and braille touch pads Versatile program options Power: 230V/50Hz 20 A single Watts: 1100-M Plug Configuration: CEE 7/7 Capacity: 34 Liters Dim: 483(D) x 559(W) x 350(H) mm Item Weight: 19 kg ship weight: 22 kg Menu Master, Made in USA Assembly in Korea	
A11	4756	ECEYA4SCR2MN	MC NEW ELEGANCE CONTROL DISPLAY 2 GR BLACK Espresso Coffee machine, 4 Different display. Boiler 11.5 Liters Power Supply: 4.78kW 400v 50HZ 3N Dim: 710x610x520 mm (W*D*H) Made by: Expobar, Spain	
A12	4761	0C000321	NEW GREY MARFIL COFFEE GRINDER AC : 1-phase: 356 W Net weight : Weight: 9 Kg Electricity : 1-phase W Dimension: Depth: 380, Height: 600, Width: 210 Made by: Expobar, Spain	
A13		Custom	S/s custom fabrication heavy duty Single Wall Shelf AISI 304 brush finish thickness 1.2mm Dim: 360 x 35 x 30 + 4 cm Made by: Marino UAE	
A14		Custom	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Work Table with bottom shelf, thickness 1.2 mm, 4x4 cm square tube type legs and adjustable feet, etc. Dim: 110 x 70 x 90 cm Made by: Marino UAE	
A15		Custom	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Heated Overhead Shelf, thickness 1.2 mm, etc. Dim: 110 x 35 x 76 cm Made by: Marino UAE	

A16	346	<b>BS2DC4</b> (BS2DC4/C)	S/S Double door undercounter chiller with 4 shelf C handle & 4 feet blower system Cap : 278 L; Temp: 2-8°C Shelves: 4 pcs; Clip: 16 pcs Power: 220/230V-50/60Hz-1/6Hp 400W Weight: 86 kg ~125mm adjustable s/s legs Dim 1200x(760+30)x840 mm Made by: Berjaya, Malaysia	
A17			Spare Number	
A18	855	<b>LP- 1</b>	AISI 304 S/S handwash sink Knee operated Water flush activated by valve Dim: 400x295x220 mm Made by: GISP, Spain	
A19	630	<b>AF07PKMBT</b> (AF07EKOMBT) <b>ANDROMEDA BT1</b>	ARMADIO BT-S/S single door freezer - PERFEKT Cap: 700 L Power: 640W; Temp: -18 to -20 C Dim: 715x810x2050 mm Thickness: 60 mm Weight: 150 kg Made by: Tecnodom, Italy	
A20	629	<b>AF07PKMTN</b> (AF07EKOMTN) <b>ANDROMEDA TN1</b>	ARMADIO TN-S/S single door chiller - PERFEKT Cap: 700 L Power: 345W; Temp: 0 to 10 C Dim: 715x810x2050 mm Thickness: 60 mm Weight: 150 kg Made by: Tecnodom, Italy	
A21		<b>Custom</b>	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Infill Table with bottom shelf and back splash 10 cm, thickness 1.2 mm, 4x4 cm square tube type legs and adjustable feet, etc. Dim: 50 x 70 x 90 + 10 cm Made by: Marino UAE	
A22		<b>Custom</b>	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Corner Type Infill Table with bottom shelf and back splash 10 cm, thickness 1.2 mm, 4x4 cm square tube type legs and adjustable feet, etc. Back Dim: 11 + 14 x 70 x 90 + 10 cm Front Dim: 30 + 33 cm Made by: Marino UAE	
A23		<b>Custom</b>	S/S in AISI 304 grade, no. 4 brush finish custom fabricated Corner Type Infill Table with bottom shelf and back splash 10 cm, thickness 1.2 mm, 4x4 cm square tube type legs and adjustable feet, etc. Dim: 20 + 30 x 70 x 90 + 10 cm Made by: Marino UAE	

A24	5133	MQOF0M20000	<p>QUEEN M2 - FILTER COFFEE MACHINE</p> <p>Single Brewer, 2 hotplates, Manual water refill</p> <p>Capacity: 15 liters / hr, Power supply 230V IN/2390W</p> <p>Dim: 205x360x430 mm (WDH)</p> <p>Made by Queen, Spain</p>	
A25	2350	SS15045	<p>Stainless steel #304- 4 tier wire shelving unit</p> <p>Dim: 1525 x 455 x 1850 mm</p> <p>Made by: Marino</p>	
Suspended Lamps	5398	NEM6006/6	<p>Nemco 6006-6 Suspension Bar Heat Lamp 6 Bulb - 120V</p>	
BAR AREA				
B1	1698	SL140A	<p>Ice cube maker 68kg/24hr w/ bin 40kg</p> <p>Power: 700W-220/240V-50Hz-1Ph</p> <p>Net weight/Gross weight: 67/79 kg</p> <p>Dim: 73.5x60.3x90.7 cm</p> <p>Foot: 11-15cm adjustable</p>	
B2	1060	S100601L/DR	<p>Top 1000x600x1 bowl 500x400 D.R.</p> <p>Made by: Italy</p>	
B8	846	BC03SP BBT350 (S/S)	<p>S/S Three Hinged Door Bar Cooler</p> <p>Capacity: 320 Liters</p> <p>Temp. : 0-8 R134a Interior Light: LED</p> <p>Power: 260w 50/60Hz</p> <p>Cooling System: Fan cooling</p> <p>Digital Thermostat: Elitech Compressor Zanussi</p> <p>Dim: 1350x520x900 mm Weight: 68kg</p> <p>Made by: Honthink</p>	
B9	625	AF07EKOMTNPV AF07MIDMTNPV (AF07SIRTNPV) <b>AVALON TN1</b>	<p>Avalon TN1-S/S single glass door chiller</p> <p>Cap: 700 L</p> <p>Power: 345W; Temp: 0 to 10 C</p> <p>Dim: 715x810x2050 mm</p> <p>Thickness: 60 mm</p> <p>Weight: 150 kg</p> <p>Made by: Tecnodom, Italy</p>	