

ANNEX "B"
BASIS OF PAYMENT

PRODUCT REQUIREMENTS LIST						ESTIMATED QUANTITY	ALL-INCLUSIVE FIRM UNIT PRICE
GROUP	ITEMS	COMPONENT CODE (FOR PSPC USE ONLY)	DESCRIPTION	PRODUCT			
				MANUFACTURER (OR EQUIVALENT)	MODEL (OR EQUIVALENT)		
1	a	A06	Sensor kit	TBD	TBD	7	\$ TBD
	b	A11B	Laser microscan kit	TBD	TBD	4	\$ TBD
2	a	A07	Faceplate	TBD	TBD	9	\$ TBD
	b	A05	Restroom kit with annunciator	TBD	TBD	2	\$ TBD
	c	A04	Push plate switch	TBD	TBD	13	\$ TBD
	d	A04B	Push plate switch	TBD	TBD	8	\$ TBD
	e	A12B	Door controls	TBD	TBD	8	\$ TBD
3	a	E6	Junction box	TBD	TBD	44	\$ TBD
	b	A09	Security Bollard	TBD	TBD	3	\$ TBD
	c	A08	Security Bollard	TBD	TBD	7	\$ TBD
4	a	E18	Latch protector	TBD	TBD	4	\$ TBD

5	a	P1	Heavy duty floor bearing	TBD	TBD	8	\$ TBD
	b	P2	Heavy duty top pivot	TBD	TBD	8	\$ TBD
6	a	A02	Door operator	TBD	TBD	3	\$ TBD
	b	A01	Door operator	TBD	TBD	1	\$ TBD
	c	A01B	Door operator	TBD	TBD	6	\$ TBD
	d	A03	Door operator	TBD	TBD	7	\$ TBD
7	a	DS1B	Door stop	TBD	TBD	2	\$ TBD
	b	DS1B	Door stop	TBD	TBD	2	\$ TBD
	c	DS5B	Door stop	TBD	TBD	8	\$ TBD
	d	DS3	Door stop	TBD	TBD	2	\$ TBD
	e	DS4B	Door stop	TBD	TBD	10	\$ TBD
	f	DS4	Door stop	TBD	TBD	2	\$ TBD
	g	M3B	Hat and coat hook	TBD	TBD	1	\$ TBD
	h	M3	Hat and coat hook	TBD	TBD	6	\$ TBD
	i	M2	Roller latch	TBD	TBD	2	\$ TBD
	j	KP2B	Kickplate	TBD	TBD	9	\$ TBD

	k	KP1B	Kickplate	TBD	TBD	13	\$ TBD
	l	KP6B	Kickplate	TBD	TBD	2	\$ TBD
	m	KP4	Kickplate	TBD	TBD	2	\$ TBD
	n	KP5	Kickplate	TBD	TBD	2	\$ TBD
	o	KP2	Kickplate	TBD	TBD	10	\$ TBD
	p	KP1	Kickplate	TBD	TBD	9	\$ TBD
	q	KP3	Kickplate	TBD	TBD	4	\$ TBD
8	a	M4	Permanent surface mount box	TBD	TBD	4	\$ TBD
9	a	OH7B	Overhead door stop	TBD	TBD	8	\$ TBD
	b	OH6	Overhead door stop	TBD	TBD	1	\$ TBD
	c	OH1B	Overhead door stop	TBD	TBD	2	\$ TBD
	d	OH1	Overhead door stop	TBD	TBD	20	\$ TBD
	e	OH5	Overhead door stop	TBD	TBD	4	\$ TBD
	f	OH3B	Overhead door stop	TBD	TBD	2	\$ TBD
	g	OH3	Overhead door stop	TBD	TBD	6	\$ TBD
	h	OH8	Overhead door stop	TBD	TBD	2	\$ TBD

10	a	FB1	Flush bolt metal door	TBD	TBD	2	\$ TBD
	b	FB2	Dust proof strike	TBD	TBD	1	\$ TBD
	c	FB3B	Flish bolt latching top	TBD	TBD	2	\$ TBD
	d	M1	Door silencer	TBD	TBD	50	\$ TBD
11	a	TH3	Frost barrier threshold	TBD	TBD	1	\$ TBD
	b	WS8	Automatic door bottom	TBD	TBD	9	\$ TBD
	c	WS6	Automatic door bottom	TBD	TBD	3	\$ TBD
	d	TH5	Threshold	TBD	TBD	2	\$ TBD
	e	TH4	Threshold	TBD	TBD	7	\$ TBD
	f	TH1	Frost barrier threshold	TBD	TBD	8	\$ TBD
	g	TH2	Frost barrier threshold	TBD	TBD	4	\$ TBD
	h	WS3B	Weatherstrip	TBD	TBD	2	\$ TBD
	i	WS3	Weatherstrip	TBD	TBD	2	\$ TBD
	j	WS9B	Weatherstrip - door sweep	TBD	TBD	5	\$ TBD
	k	WS10B	Astragal	TBD	TBD	2	\$ TBD
	l	WS4B	Weatherstrip	TBD	TBD	1	\$ TBD

	m	WS4	Weatherstrip	TBD	TBD	5	\$ TBD
	n	WS5B	Weatherstrip - door sweep	TBD	TBD	4	\$ TBD
	o	WS5	Weatherstrip - door sweep	TBD	TBD	13	\$ TBD
	p	WS1	Self-adhesive weatherstrip	TBD	TBD	9	\$ TBD
	q	WS2	Self-adhesive weatherstrip	TBD	TBD	2	\$ TBD
	r	WS7	Astragal	TBD	TBD	2	\$ TBD
12	a	WS13B	Perimeter seal	TBD	TBD	8	\$ TBD
	b	WS12B	Door sweep with silicone seal	TBD	TBD	16	\$ TBD
	c	TH6B	Thermal threshold	TBD	TBD	4	\$ TBD
13	a	CH3B	Continuous hinge	TBD	TBD	1	\$ TBD
	b	CH3B	Continuous hinge	TBD	TBD	1	\$ TBD
	c	CH3	Continuous hinge	TBD	TBD	2	\$ TBD
	d	CH3	Continuous hinge	TBD	TBD	1	\$ TBD
	e	CH2	Continuous hinge	TBD	TBD	2	\$ TBD
	f	CH8	Continuous hinge	TBD	TBD	7	\$ TBD
	g	CH5	Continuous hinge	TBD	TBD	8	\$ TBD

	h	CH5	Continuous hinge	TBD	TBD	3	\$ TBD
	i	CH5	Continuous hinge	TBD	TBD	1	\$ TBD
	j	CH7B	Continuous hinge	TBD	TBD	3	\$ TBD
	k	CH7B	Continuous hinge	TBD	TBD	3	\$ TBD
	l	CH7B	Continuous hinge	TBD	TBD	1	\$ TBD
	m	CH6B	Continuous hinge	TBD	TBD	1	\$ TBD
14	a	DP1	Door pull	TBD	TBD	2	\$ TBD
	b	DP2	Door pull	TBD	TBD	41	\$ TBD
	c	DP3	Door pull	TBD	TBD	3	\$ TBD
15	a	H2B	Steel full mortise hinge	TBD	TBD	6	\$ TBD
	b	H2	Steel full mortise hinge	TBD	TBD	21	\$ TBD
	c	H4B	Steel full mortise hinge	TBD	TBD	3	\$ TBD
	d	H8	Full mortise hinge	TBD	TBD	6	\$ TBD
	e	H1B	Steel full mortise hinge	TBD	TBD	6	\$ TBD
	f	H1	Steel full mortise hinge	TBD	TBD	24	\$ TBD
	g	H3B	Steel full mortise hinge	TBD	TBD	3	\$ TBD

	h	H7	Full mortise hinge	TBD	TBD	6	\$ TBD
16	a	FB4	Retracting arm door coordinator	TBD	TBD	2	\$ TBD