

REVISED (AMENDMENT #4)
ATTACHMENT 1 TO ANNEX A
PRODUCT REQUIREMENTS LIST

PRODUCT REQUIREMENTS LIST						ESTIMATED QUANTITY
GROUP	ITEMS	COMPONENT CODE (FOR PSPC USE ONLY)	DESCRIPTION	LISTED PRODUCT EXAMPLE		
				MANUFACTURER (OR EQUIVALENT)	MODEL (OR EQUIVALENT)	
1	a	A06	Sensor kit	BEA	Superscan 1+2/Bodyguard	7
	b	A11B	Laser microscan kit	BEA	10LZR-MICROSCAN 2 x SIM	4
2	a	A07	Faceplate	Camden	CM-35N-2 DP C32D	9
	b	A05	Restroom kit with annunciator	Camden	CM-CX-WC11 x CX-WEC10	2
	c	A04	Push plate switch	Camden	CM41-2 DP C32D	13
	d	A04B	Push plate switch	Camden	CM41-2-OB-DP	8
	e	A12B	Door controls	Camden	CX33-Dual	8

3	a	E6	Junction box	CFS	JB7	44
	b	A09	Door Closer Security Bollard	CFS	DCV-AL-C-C-Sloped x BFA x 48" xC40/BA	3
	c	A08	Door Closer Security Bollard	CFS	DCV-AL-C-C-Sloped x CR x IC x BFA x 48" x C40/BA	7
4	a	E18	Latch protector	Don-Jo	MELP-210-SL	4
5	a	P1	Heavy duty floor bearing	Dorma	7471HD x 7421	8
	b	P2	Heavy duty top pivot	Dorma	EHD8062-4W	8
6	a	A02	Door operator	Entrematic	HDLR3000-HA 115VAC (Pull) AL	3
				Besam	SW200 complete with ECET	
				Dorma	ED200-FC complete with Network Card	
	b	A01	Door operator	Entrematic	HDLR3000-HA 115VAC (Push) AL	1
				Besam	SW200 complete with ECET	
				Dorma	ED200-FC complete with Network Card	

	c	A01B	Door operator	Entrematic	HDLR3000-HA 115VAC (Push) C40/BA	6
				Besam	SW200 complete with ECET	
				Dorma	ED200-FC complete with Network Card	
	d	A03	Door operator	Entrematic	HDLR50000-FA 115VAC (Push) AL	7
				Besam	SW200 complete with ECET	
				Dorma	ED200-FC complete with Network Card	
	e	A10B-DELETED	Push open inswing operator-DELETED	Entrematic-DELETED	NB500MS Dual Master x Push C/W Custom Arm 120VAC-DELETED	4-DELETED
	a	DS1B	Door stop	Gallery	GSH 209 C10B	2
	b	DS1B	Door stop	Gallery	GSH 209 C26D	2
	c	DS5B	Door stop	Gallery	GSH 2100 C10B	8
	d	DS3	Door stop	Gallery	GSH 273 C26D	2
	e	DS4B	Door stop	Gallery	GSH 281B C10B	10

7	f	DS4	Door stop	Gallery	GSH 281B C26D	2
	g	M3B	Hat and coat hook	Gallery	GSH 308B C10B	1
	h	M3	Hat and coat hook	Gallery	GSH 308B C26D	6
	i	M2	Roller latch	Gallery	GSH 404H C26D	2
	j	KP2B	Kickplate	Gallery	GSH 80A C10B (101 x 889) 3MT	9
	k	KP1B	Kickplate	Gallery	GSH 80A C10B (203 x 876) 3MT	13
	l	KP6B	Kickplate	Gallery	GSH 80A C10B (800 x 889) 3MT	2
	m	KP4	Kickplate	Gallery	GSH 80A C32D (101 x 686) 3MT	2
	n	KP5	Kickplate	Gallery	GSH 80A C32D (101 x 889) 3MT	2
	o	KP2	Kickplate	Gallery	GSH 80A C32D (101 x 889) 3MT	10
	p	KP1	Kickplate	Gallery	GSH 80A C32D (203 x 876) 3MT	9
	q	KP3	Kickplate	Gallery	GSH 80A C32D (203 x 876) 3MT	4

8	a	M4	Permanent surface mount box	GE	GE Supra Max BLK	4
9	a	OH7B	Overhead door stop	Glynn-Johnson	103S C10B	8
	b	OH6	Overhead door stop	Glynn-Johnson	104H C32D	1
	c	OH1B	Overhead door stop	Glynn-Johnson	104S C10B	2
	d	OH1	Overhead door stop	Glynn-Johnson	104S C32D	20
	e	OH5	Overhead door stop	Glynn-Johnson	452S C32D	4
	f	OH3B	Overhead door stop	Glynn-Johnson	904S C10B	2
	g	OH3	Overhead door stop	Glynn-Johnson	904S C32D	6
	h	OH8	Overhead door stop	Glynn-Johnson	GJ906S C32D	2
10	a	FB1	Flush bolt metal door	Ives	458B C26D x 305mm	2
	b	FB2	Dust proof strike	Ives	DP1 C26D	1
	c	FB3B	Flish bolt latching top	Ives	FB62 x AFL C10B	2

	d	M1	Door silencer	Ives	SR64 GRY	50
11	a	TH3	Frost barrier threshold	K.N. Crowder	CT-46A x 1219	1
	b	WS8	Automatic door bottom	K.N. Crowder	CT-52S-CA x 915	9
	c	WS6	Automatic door bottom	K.N. Crowder	CT-53S-AL x 915	3
	d	TH5	Threshold	K.N. Crowder	CT-65 x 1828	2
	e	TH4	Threshold	K.N. Crowder	CT-65 x 915	7
	f	TH1	Frost barrier threshold	K.N. Crowder	CT-87A x 1219	8
	g	TH2	Frost barrier threshold	K.N. Crowder	CT-87A x 2134	4
	h	WS3B	Weatherstrip	K.N. Crowder	W-20S-BA x 1 @ 915 + 2 @ 2134	2
	i	WS3	Weatherstrip	K.N. Crowder	W-20S-CA x1 @ 915 + 2 @ 2134	2
	j	WS9B	Weatherstrip - door sweep	K.N. Crowder	W-24S-BA x 915	5
	k	WS10B	Astragal	K.N. Crowder	W-25P-BA x 2134	2

	l	WS4B	Weatherstrip	K.N. Crowder	W-32S-BA x 1 @ 915 + 2 @ 2134	1
	m	WS4	Weatherstrip	K.N. Crowder	W-32S-CA x 1 @ 915 + 2 @ 2134	5
	n	WS5B	Weatherstrip - door sweep	K.N. Crowder	W-35-1-BA x 915	4
	o	WS5	Weatherstrip - door sweep	K.N. Crowder	W-35-1-CA x 915	13
	p	WS1	Self-adhesive weatherstrip	K.N. Crowder	W-63-BRN x 17' (1 @ 915 + 2 @ 2134)	9
	q	WS2	Self-adhesive weatherstrip	K.N. Crowder	W-63-BRN x 21' (1 @ 2134 + 2 @ 2134)	2
	r	WS7	Astragal	K.N. Crowder	W-8S x 2134	2
12	a	WS13B	Perimeter seal	NGP	130SBR x 2743mm	8
	b	WS12B	Door sweep with silicone seal	NGP	200SBR x 1220mm	16
	c	TH6B	Thermal threshold	NGP	NG8430BR x 2134mm	4
	a	CH3B	Continuous hinge	Select	SL11 BR HD x 2108 EPT - LH	1
	b	CH3B	Continuous hinge	Select	SL11 BR HD x 2108 EPT - RH	1

13	c	CH3	Continuous hinge	Select	SL11 CL HD x 2108 EPT - LH	2
	d	CH3	Continuous hinge	Select	SL11 CL HD x 2108 EPT - RH	1
	e	CH2	Continuous hinge	Select	SL11 CL HD x 2143	2
	f	CH8	Continuous hinge	Select	SL11 CL HD x 2718	7
	g	CH5	Continuous hinge	Select	SL11 CL HD x 2718 EPT - LH	8
	h	CH5	Continuous hinge	Select	SL11 CL HD x 2718 EPT - RH	3
	i	CH5	Continuous hinge	Select	SL11 CL HD x 2718 EPT	1
	j	CH7B	Continuous hinge	Select	SL24 BR HD x 2108 EPT - LH	3
	k	CH7B	Continuous hinge	Select	SL24 BR HD x 2108 EPT - RH	3
	l	CH7B	Continuous hinge	Select	SL24 BR HD x 2108 EPT	1
	m	CH6B	Continuous hinge	Select	SL24 BR HD x 2108	1
	a	DP1	Door pull	Standard Metal	2107-2 C32D TB	2

14	b	DP2	Door pull	Standard Metal	D503 #4B mtg. C32D	41
	c	DP3	Door pull	Standard Metal	D503 x D503 #5 mtg. C32D	3
15	a	H2B	Steel full mortise hinge	Stanley	NRP-CB1900R 114 x 101 C10A	6
	b	H2	Steel full mortise hinge	Stanley	NRP-CB1900R 114 x 101 C26D	21
	c	H4B	Steel full mortise hinge	Stanley	NRP-CB1901R 114 x 101 C10A (Heavy Weight)	3
	d	H8	Full mortise hinge	Stanley	NRP-CB1961R 114 x 101 C32D (Heavy Weight)	6
	e	H1B	Steel full mortise hinge	Stanley	CB1900R 114 x 101 C10A	6
	f	H1	Steel full mortise hinge	Stanley	CB1900R 114 x 101 C26D	24
	g	H3B	Steel full mortise hinge	Stanley	CB1901R 114 x 101 C10A (Heavy Weight)	3
	h	H7	Full mortise hinge	Stanley	CB1961R 114 x 101 C32D (Heavy Weight)	6
16	a	FB4	Retracting arm door coordinator	Trimco	3092 Black	2