



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government
Services Canada/Réception des soumissions Travaux
publics et Services gouvernementaux Canada
800 Burrard Street, Room 219
800, rue Burrard, pièce 219
Vancouver
British Columbia
V6Z 0B9
Bid Fax: (604) 775-9381

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise
indicated, all other terms and conditions of the Solicitation
remain the same.

Ce document est par la présente révisé; sauf indication contraire,
les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Public Works and Government Services Canada - Pacific
Region
800 Burrard Street, Room 219
800, rue Burrard, pièce 219
Vancouver
British C
V6Z 0B9

| | |
|--|--|
| Title - Sujet Canteen Relocation, Building M | |
| Solicitation No. - N° de l'invitation EZ899-202574/A | Amendment No. - N° modif. 003 |
| Client Reference No. - N° de référence du client | Date 2020-03-09 |
| GETS Reference No. - N° de référence de SEAG PW-\$PWY-028-8745 | |
| File No. - N° de dossier PWY-9-42221 (028) | CCC No./N° CCC - FMS No./N° VME |
| Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2020-03-19 | Time Zone Fuseau horaire Pacific Daylight Saving Time PDT |
| F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/> | |
| Address Enquiries to: - Adresser toutes questions à: Lam (PWY), Tian | Buyer Id - Id de l'acheteur pwy028 |
| Telephone No. - N° de téléphone (604) 363-7968 () | FAX No. - N° de FAX (604) 775-6633 |
| Destination - of Goods, Services, and Construction: Destination - des biens, services et construction: CSC - Building M, Mission Institution - Mission, BC | |

Instructions: See Herein

Instructions: Voir aux présentes

| | |
|--|--|
| Delivery Required - Livraison exigée | Delivery Offered - Livraison proposée |
| Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur | |
| Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur | |
| Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie) | |
| Signature | Date |

Solicitation No. - N° de l'invitation
EZ899-202574/A

Amd. No. - N° de la modif.
003

Buyer ID - Id de l'acheteur
pwy028

Client Ref. No. - N° de réf. du client

File No. - N° du dossier CCC No./N°

CCC - FMS No./N° VME

The Solicitation Amendment 003 is raised to issue Addendum 002.

Please see Addendum 002 herein.

All other terms and conditions remain unchanged.

Location: 8751 Stave Lake Street, Mission BC
Building: Mission Medium Institution, Building M
Canteen Relocation

The following changes in the tender documents are effective immediately. This addendum will form part of the contract documents.

1. Specification:

.1 Section 28 23 00 – IP CCTV System

Clause 2.1:

- (1) Replace the entire Clause 2.1 with the following:

2.1 IP CAMERA

- .1 Compatible with existing “Genetec”, Version 4.8 operating System.
- .2 IP Cameras shall meet the following requirements;
 - .1 Camera case and dome must measure a base diameter less than 200mm and weigh less than 2.5kg.
 - .2 Camera case and dome must be vandal-resistant (IK10), dust-resistant and water-resistant (IP66), wall-mount / ceiling mount housing.
 - .3 Capable of continuous operation; start and operate from -40 Deg. To 50 Deg. C; start and operate from 20% to 90% non-condensing humidity
 - .4 Certified compliant to IEC EN 61000-4-3, Radiated RF immunity
 - .5 Mean Time Between Failures (MTBF) of at least 25,000 hours
 - .6 Meet safety standard IEC 60950-1 or CSA C22.2
 - .7 Front plate to have two polycarbonate windows to protect camera.
 - .8 Front plate to be recessed and secured to frame with security screws
 - .9 Adjustable mount to tilt camera up or down.
 - .10 1080P (1920 x 1080) resolution
 - .11 True day/night camera with 2.6 mm lens. Camera lense must have a 35 Deg. to 80 Degree or greater horizontal angular view varifocal lens. The camera lens must be approved by the manufacturer of the camera for that camera
 - .12 Digital wide dynamic range
 - .13 0.00 lux low light capability @ 50 IRE (IR ON)
 - .14 Power-over-Ethernet (IEEE 802.3af), 24 VAC or 12 VDC

Location: 8751 Stave Lake Street, Mission BC
Building: Mission Medium Institution, Building M
Canteen Relocation

- .15 Streaming: H.264, MPEG-4 or M-JPEG - Support Dual Streaming.
- .16 Must interface over IPV4 TCP/IP; be able to operate on 100Base-TX (IEEE 802.3u); connect using an RJ45 connector and be ONVIF compliant
- .17 Camera model must be identified as "Certified" or "Supported by Design" in the Genetec Omnicast Supported Hardware camera list
- .18 Must retain its configuration over a power cycle
- .19 Automatic or remote back focus
- .20 Automatic Gain Control (AGC)
- .21 Automatic removable infrared cut filter for day/night transition
- .22 Camera case and dome must have threaded openings for conduits; a threaded plug to seal all unused openings; set screws to secure all conduit and plugs from inside the dome; tamper resistant heads on all externally accessible screws; permanently affixed label on the interior and exterior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement.
- .23 All outdoor camera housings shall have heaters compatible with the weather conditions.
- .24 Provide suitable mounting brackets for indoor and outdoor cameras (mounted on vestibule ceiling and on top of parapets of the building LU-2).
- .25 Acceptable Product: Sony – SNC-EM602RC
- .26 Submit shop drawings of cameras and mounting brackets for review and approval.

End of Addendum #2
