



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government
Services Canada/Réception des soumissions Travaux
publics et Services gouvernementaux Canada
800 Burrard Street, Room 219
800, rue Burrard, pièce 219
Vancouver
British Columbia
V6Z 0B9
Bid Fax: (604) 775-9381

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise
indicated, all other terms and conditions of the Solicitation
remain the same.

Ce document est par la présente révisé; sauf indication contraire,
les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Public Works and Government Services Canada - Pacific
Region
800 Burrard Street, Room 219
800, rue Burrard, pièce 219
Vancouver
British C
V6Z 0B9

Title - Sujet Canteen Relocation, Building M	
Solicitation No. - N° de l'invitation EZ899-202574/A	Amendment No. - N° modif. 003
Client Reference No. - N° de référence du client	Date 2020-03-09
GETS Reference No. - N° de référence de SEAG PW-\$PWY-028-8745	
File No. - N° de dossier PWY-9-42221 (028)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2020-03-19	Time Zone Fuseau horaire Pacific Daylight Saving Time PDT
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Lam (PWY), Tian	Buyer Id - Id de l'acheteur pwy028
Telephone No. - N° de téléphone (604) 363-7968 ()	FAX No. - N° de FAX (604) 775-6633
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction: CSC - Building M, Mission Institution - Mission, BC	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation
EZ899-202574/A

Amd. No. - N° de la modif.
003

Buyer ID - Id de l'acheteur
pwy028

Client Ref. No. - N° de réf. du client

File No. - N° du dossier CCC No./N°

CCC - FMS No./N° VME

Les documents seront disponibles en français sur demande.

The Solicitation Amendment 003 is raised to issue Addendum 002.

Please see Addendum 002 herein.

All other terms and conditions remain unchanged.

Location: 8751 Stave Lake Street, Mission BC
Building: Mission Medium Institution, Building M
Canteen Relocation

The following changes in the tender documents are effective immediately. This addendum will form part of the contract documents.

1. Specification:

.1 Section 28 23 00 – IP CCTV System

Clause 2.1:

(1) Replace the entire Clause 2.1 with the following:

2.1 IP CAMERA

- .1 Compatible with existing “Genetec”, Version 4.8 operating System.
- .2 IP Cameras shall meet the following requirements;
 - .1 Camera case and dome must measure a base diameter less than 200mm and weigh less than 2.5kg.
 - .2 Camera case and dome must be vandal-resistant (IK10), dust-resistant and water-resistant (IP66), wall-mount / ceiling mount housing.
 - .3 Capable of continuous operation; start and operate from -40 Deg. To 50 Deg. C; start and operate from 20% to 90% non-condensing humidity
 - .4 Certified compliant to IEC EN 61000-4-3, Radiated RF immunity
 - .5 Mean Time Between Failures (MTBF) of at least 25,000 hours
 - .6 Meet safety standard IEC 60950-1 or CSA C22.2
 - .7 Front plate to have two polycarbonate windows to protect camera.
 - .8 Front plate to be recessed and secured to frame with security screws
 - .9 Adjustable mount to tilt camera up or down.
 - .10 1080P (1920 x 1080) resolution
 - .11 True day/night camera with 2.6 mm lens. Camera lense must have a 35 Deg. to 80 Degree or greater horizontal angular view varifocal lens. The camera lens must be approved by the manufacturer of the camera for that camera
 - .12 Digital wide dynamic range
 - .13 0.00 lux low light capability @ 50 IRE (IR ON)
 - .14 Power-over-Ethernet (IEEE 802.3af), 24 VAC or 12 VDC

Location: 8751 Stave Lake Street, Mission BC
Building: Mission Medium Institution, Building M
Canteen Relocation

- .15 Streaming: H.264, MPEG-4 or M-JPEG - Support Dual Streaming.
- .16 Must interface over IPV4 TCP/IP; be able to operate on 100Base-TX (IEEE 802.3u); connect using an RJ45 connector and be ONVIF compliant
- .17 Camera model must be identified as "Certified" or "Supported by Design" in the Genetec Omnicast Supported Hardware camera list
- .18 Must retain its configuration over a power cycle
- .19 Automatic or remote back focus
- .20 Automatic Gain Control (AGC)
- .21 Automatic removable infrared cut filter for day/night transition
- .22 Camera case and dome must have threaded openings for conduits; a threaded plug to seal all unused openings; set screws to secure all conduit and plugs from inside the dome; tamper resistant heads on all externally accessible screws; permanently affixed label on the interior and exterior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement.
- .23 All outdoor camera housings shall have heaters compatible with the weather conditions.
- .24 Provide suitable mounting brackets for indoor and outdoor cameras (mounted on vestibule ceiling and on top of parapets of the building LU-2).
- .25 Acceptable Product: Sony – SNC-EM602RC
- .26 Submit shop drawings of cameras and mounting brackets for review and approval.

End of Addendum #2
