



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Travaux publics et Services gouvernementaux
Canada

Voir dans le document/

See herein

NA

Québec

NA

Revision to a Request for a Standing Offer

Révision à une demande d'offre à commandes

Regional Individual Standing Offer (RISO)

Offre à commandes individuelle régionale (OCIR)

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Offer remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'offre demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Travaux publics et Services gouvernementaux
Canada
Place Bonaventure, portail Sud-Oue
800, rue de La Gauchetière Ouest
7e étage, suite 7300
Montréal
Québec
H5A 1L6

Title - Sujet Rental of construction site equipme		
Solicitation No. - N° de l'invitation W0106-20S006/A		Date 2020-08-17
Client Reference No. - N° de référence du client W0106-20S006		Amendment No. - N° modif. 001
File No. - N° de dossier MTA-0-43014 (490)	CCC No./N° CCC - FMS No./N° VME	
GETS Reference No. - N° de référence de SEAG PW-\$MTA-490-15750		
Date of Original Request for Standing Offer Date de la demande de l'offre à commandes originale		2020-06-03
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2020-08-21		Time Zone Fuseau horaire Heure Avancée de l'Est HAE
Address Enquiries to: - Adresser toutes questions à: Sirois, Richard		Buyer Id - Id de l'acheteur mta490
Telephone No. - N° de téléphone (514) 718-5993 ()	FAX No. - N° de FAX (514) 496-3822	
Delivery Required - Livraison exigée		
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:		
Security - Sécurité This revision does not change the security requirements of the Offer. Cette révision ne change pas les besoins en matière de sécurité de la présente offre.		

Instructions: See Herein

Instructions: Voir aux présentes

Acknowledgement copy required Accusé de réception requis	Yes - Oui <input type="checkbox"/>	No - Non <input type="checkbox"/>
The Offeror hereby acknowledges this revision to its Offer. Le proposant constate, par la présente, cette révision à son offre.		
Signature	Date	
Name and title of person authorized to sign on behalf of offeror. (type or print) Nom et titre de la personne autorisée à signer au nom du proposant. (taper ou écrire en caractères d'imprimerie)		
For the Minister - Pour le Ministre		

AMENDMENT 001

This amendment is required to provide questions/answers and to modify the Request for Standing Offer (RFSO)

1) Questions and answers

Annex "A", part 4.2.1: description of articles related to generators:

Q1. Is that 50 meters the length of the extensions, maybe it should read 50 feet?

A1. there is an error in the document: it is rather 50 feet (15 meters).

Q2. do the 50 feet cables have to be supplied in one length or can we go with more than one length?

A2. a cable of at least 50 feet in one length should be included. However, the customer can accept various lengths of cable according to his needs.

Q3. for item Type 3 (10KW), is the description of terminals L0, L1, L2 and L3 applicable for this size of generator?

A3. the terminal description L0, L1, L2 and L3 is applicable for item Type 3 (10KW).

Annex "A", part 4.2.2: Description of the heaters:

Q4. for Type 1, usually it is a single cylinder heater that does not come with ducts etc., would you have a reference model?

A4. if Type 1 heaters do not usually come with ducts, this is acceptable. No reference model can be provided.

2) Modification

Annex "A"

DELETE

4.2.1 GENERATORS

Categories	Technical specifications
Type 1: 2 kW or equivalent	<ul style="list-style-type: none">- Portable model- 15 amp output- Cable at least 50 metres long able to handle 100% of the rented generator's load
Type 2: 5 kW or equivalent	<ul style="list-style-type: none">- Wheel-mounted model or one with a handle- Terminal or outlet- Output of 15 amperes per phase- Cable at least 50 metres long able to handle 100% of the rented generator's load
Type 3: 10 kW or equivalent	<ul style="list-style-type: none">- Wheel-mounted model- Terminals L0, L1, L2 and L3- Output of 15 amperes per phase- Cable at least 50 metres long able to handle 100% of the rented generator's load
Type 4: 30 kW or equivalent	<ul style="list-style-type: none">- Trailer-mounted model- 1-phase/3-phase output selector- Terminals L0, L1, L2 and L3- Output of 50-60 amperes per phase- Cable at least 50 metres long able to handle 100% of the rented generator's load
Type 5: 60 kW and over, or equivalent	<ul style="list-style-type: none">- Trailer-mounted model- 1-phase/3-phase output selector- Terminals L0, L1, L2 and L3- Output of 100 amperes per phase- Cable at least 50 metres long able to handle 100% of the rented generator's load

4.2.2 HEATERS

Categories	Technical specifications
Type 1: 175,000 BTU	<ul style="list-style-type: none">- Diesel fuel or oil;- Tank capacity at least 40 gallons (151 litres);- The fuel tank shall be delivered full and will be returned full as well, unless otherwise stated by the user;- Heater rentals shall include: two (2) flexible air hoses at least 12 feet in length and 10 to 12 inches in diameter, one (1) thermostat, one (1) electric cable (extension cord) for outside use measuring 7 metres (25 feet) long, and a holding basin for fuel leaks;- Circuit breaker;- Heating system with 2 air outlets, 10 to 12 inches in diameter;- Electrical characteristics: 115 V, 60 Hz, 15 amp.
Type 2: 350,000 BTU to 400,000 BTU	

AND REPLACE BY

4.2.1 GENERATORS

Categories	Technical specifications
Type 1: 2 kW or equivalent	<ul style="list-style-type: none">- Portable model- 15 amp output- Cable at least 50 feet long able to handle 100% of the rented generator's load
Type 2: 5 kW or equivalent	<ul style="list-style-type: none">- Wheel-mounted model or one with a handle- Terminal or outlet- Output of 15 amperes per phase- Cable at least 50 feet long able to handle 100% of the rented generator's load
Type 3: 10 kW or equivalent	<ul style="list-style-type: none">- Wheel-mounted model- Terminals L0, L1, L2 and L3- Output of 15 amperes per phase- Cable at least 50 feet long able to handle 100% of the rented generator's load
Type 4: 30 kW or equivalent	<ul style="list-style-type: none">- Trailer-mounted model- 1-phase/3-phase output selector- Terminals L0, L1, L2 and L3- Output of 50-60 amperes per phase- Cable at least 50 feet long able to handle 100% of the rented generator's load
Type 5: 60 kW and over, or equivalent	<ul style="list-style-type: none">- Trailer-mounted model- 1-phase/3-phase output selector- Terminals L0, L1, L2 and L3- Output of 100 amperes per phase- Cable at least 50 feet long able to handle 100% of the rented generator's load

4.2.2 HEATERS

Categories	Technical specifications
Type 1: 175,000 BTU	<ul style="list-style-type: none">- Diesel fuel or oil;- Tank capacity at least 40 gallons (151 litres);- The fuel tank shall be delivered full and will be returned full as well, unless otherwise stated by the user;- Heater rentals shall include: one (1) thermostat, one (1) electric cable (extension cord) for outside use measuring 7 metres (25 feet) long, and a holding basin for fuel leaks;- Circuit breaker;- Heating system with 2 air outlets, 10 to 12 inches in diameter;- Electrical characteristics: 115 V, 60 Hz, 15 amp.

All other terms and conditions remain unchanged.