



LEGEND	
	DUPLEX RECEPTACLE
	ELECTRICAL DATA
	FLOOR MONUMENT LOCATION
	BASE FEED LOCATION HARDWIRED SYSTEMS FURNITURE BASE FEED TO BE PROVIDED BY FURNITURE SUPPLIER.
	POWER POLE LOCATION HARDWIRED SYSTEMS FURNITURE POWER POLE IS TO BE PROVIDED BY FURNITURE SUPPLIER. NOTE: IT IS NOT AN OPEN CEILING. SYSTEMS FURNITURE POWER POLE HEIGHT RANGE MUST BE BETWEEN (2743 – 3048mm (108 – 120”) FROM THE FINISHED FLOOR TO THE TOP OF THE POLE. FURNITURE SUPPLIER IS NOT RESPONSIBLE FOR SECURING THE POWER POLE TO THE SLAB.

CATEGORY 6--SOFT SEATING & SCREENS	
	Lounge Chair #1 (LC-1) Must have two casters and two legs
	Lounge Chair #2 (LC-2) Must have two casters and two legs
	Lounge Chair #3 (LC-3)
	Tablet Chair #1 (Left & Right) (TC1L & TC1R)
	Ottoman #1 (18" Round) (OR-1)
	Ottoman #3 (24" Square) (OR-2)
	Ottoman #4 (48" Square) (OS-4)
	Ottoman #5 (42" Round) (OR-5)

CATEGORY 6--MEETING & TRAINING TABLES	
	Meeting Table #1 (30"x60")
	Meeting Table #2 (30"x72") All tables must be supplied with ganging or linking devices to ensure they can be joined together in horizontal positions and/or 90 and/or 180 degrees to each other while still allowing for the provision of power and data connectivity across the entire multi-table configuration. Power must be able to be daisy chained. Table top – 737mm (29") AFF and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions
	Meeting Table #3 (60"x120") Table top – 737mm (29") AFF (tolerance +/- 1") and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions Glides must allow for +/-51mm (+/- 2") of levelling
	Meeting Table #4 (60"x144") Table top – 737mm (29") AFF (tolerance +/- 1") and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions Glides must allow for +/-51mm (+/- 2") of levelling
	Meeting Table #5 (36"x96") Table top – 737mm (29") AFF (tolerance +/- 1") and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions Glides must allow for +/-51mm (+/- 2") of levelling
	Meeting Table #6 (36" Round)
	Meeting Table #7 (30"x30")

CATEGORY 6--SOFT SEATING & SCREENS	
	This Banquette seating configuration consists of the following (3) components listed below: BA1, BA2 – 3seater, BA3 to be all of the same series and collection Must be supplied with ganging or linking devices to ensure they can be joined
	2 each – Banquette Armless / Low Back Bench (+/- 63" to 75") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16")
	4 each – Banquette Armless / Low Back Bench (+/- 24" to 31") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16")
	2 each – Banquette Armless/ Backless Bench (+/- 24" to 31")
	Engagement Space This Banquette seating configuration consists of the following (4) components listed below: BA1, BA2 – 3seater, BA2 – 3seater, Screen and BA3 to be all of the same series and collection Must be supplied with ganging or linking devices to ensure they can be joined This Banquette seating configuration consists of the following (4) components listed below:
	2 each – Banquette Armless / Medium Back Privacy Screen Bench (+/- 63" to 75") Overall screen height to be 1117mm-1720mm (44" – 50")
	2 each – Banquette Armless / Low Back Bench (+/- 63" to 75") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16")
	1 each – Banquette Armless / Low Back Bench (+/- 24" to 31") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16")
	4 each – Banquette Armless/ Backless Bench (+/- 24" to 31")
	Modular Benching (MBP1) (+/- 25" to 39") 2 each – Banquette Armless / No Back Bench (+/- 24" to 31"), with power Must be supplied with ganging or linking devices to ensure they can be joined
	Modular Benching (MB2) with backrest (+/- 25" to 39") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16") Must be supplied with ganging or linking devices to ensure they can be joined
	Modular Benching (MB3) (+/- 48" to 62") 1 each – Banquette Armless / No Back
	Modular Benching (MB4) (+/- 48" to 54") 1 each – Banquette Armless / No Back Bench DIMENSIONS 18" X 54" MAXIMUM

CATEGORY 6--OPEN AREA WORKSPACE	
	Individual Work Pod w/ Worksurface Task Light (WP1) Description: 1. Free-standing unit must include a work surface and task light for a single user and primary screen(s). 2. Work surface and primary screen(s) must be from the same product line. 3. Privacy screen(s) must surround the users on no less than three sides, including both the work surface and the user, interconnecting systems panels are not an acceptable solution. Connect of panels must be rounded; panels which connect at a square or 90-degree angle are not acceptable. 4. Seat will be provided separately and does not form part of this specification. Dimension: 1. Work surface must be a maximum height of 762mm (30 in.) with a tolerance of +/- 76.2mm (-3 in.) when measured from the floor to the top of the work surface. 2. Privacy screen(s) height must be a minimum of 1194mm (47 in.) to a maximum of 1549mm (61 in.). 3. Overall diameter footprint of unit must be 1829mm (72 in.) maximum, ±102 mm (4 in.) Finishes: 1. Work surface must be painted MDF, or high-pressure laminate. 2. Privacy screens must be fabric covered, high-pressure laminate, or low-pressure laminate. Power and Data: 1. Must provide a combination of one duplex and one USB as a minimum. Support/Table Bases: 1. Floor supports must be minimal, no higher than 64 mm (2.5 in.). 2. Supports/legs for the work surface must be formed to the privacy panels and must appear to be supported by the panels, however may be supported on feet. Individual Work Pod w/ Worksurface Task Light (WP2) Description: 1. Free-standing unit must include a work surface a single user and primary screen(s). 2. Work surface and primary screen(s) must be from the same product line. 3. Privacy screen(s) must surround the users on no less than three sides, including both the work surface and the user, interconnecting systems panels are not an acceptable solution. Connect of panels must be rounded; panels which connect at a square or 90-degree angle are not acceptable. 4. Seat will be provided separately and does not form part of this specification. Dimension: 1. Table surface must be a minimum of 15" x 15". 2. Privacy screen(s) height must be a minimum of 1194mm (47 in.) to a maximum of 1549mm (61 in.). 3. Overall diameter footprint of unit must be a maximum of 1829mm (72 in.) ±102 mm (4 in.) Finishes: 1. Table surface must be painted MDF or high-pressure laminate. 2. Privacy screens must be fabric covered, high-pressure laminate, or low-pressure laminate. Power and Data: 1. Must provide a combination of one duplex and one USB as a minimum. Support/Table Bases: 1. Floor supports must be minimal, no higher than 64 mm (2.5 in.). 2. Supports/legs for the work surface must be formed to the privacy panels and must appear to be supported by the panels, however may be supported on feet. Lounge Chair w/ Foot Stool (PLC1) 1. Should there be armrests, they must be the same finish as the chair seat and integrated with the chair. 2. Must be reclined back. 3. Chair must have high back with wings or side panels to provide some support behind primary to the user. 4. Back and seat cushions must be fixed. 5. Must be modern and tailored in appearance. Foot Stool: 6. Various shapes are acceptable. Dimensions: Chair: 1. Overall width of the chair must be between 660 – 914mm (26 – 36"). 2. Back must be high and able to provide head support. Foot Stool: 3. Must be of an appropriate height to function as a foot stool for the chair. 4. Must be a minimum of 406mm (16") wide and no wider than the width of the chair being provided. Finishes: Chair: 1. Seat and back must be fully upholstered with stitch detailing for a tailored appearance. 2. Base/legs must be brushed or painted metal, wood or fabric covered. Foot Stool: 3. Must be available in the same finishes as the chair. Base/Supports: 1. If seat base is provided, it must have an auto-return mechanism that retracts on the underside. Group Work Pods 1. Free-standing unit which must include two upholstered lounge sofas, work surface, and primary enclosure/screens. 2. Each lounge sofa must allow for two adults to sit comfortably side-by-side. 3. Seat, work surface, and primary screens must be from the same product line. All parts must be strongly fixed into one structure. 4. Backrests/screens must form an enclosure surrounding 100% of all users and interior furniture combined. Interconnecting systems panels are not an acceptable solution. Connect of panels must be rounded; panels which connect at a square or 90-degree angle are not acceptable. 5. Worksurface must be situated between the lounge sofas to provide useable work surface space to all 4 users. Dimension: 1. Sofa seat must be 381mm (15 in.) to 457mm (18 in.) when measured from the top of the seat to the finished floor, ±25 mm (±1 in.). 2. Work surface must be compatible with the lounge height seating. 3. Privacy screen(s) height must be a minimum of 1194mm (47 in.) and a maximum of 1549mm (61 in.). 4. Overall foot diameter footprint of the unit must be 2007mm (79 in.) diameter to 2291mm (102 in.) diameter, ±152 mm (±6 in.). Finishes: 1. The seat and back of the sofas must be: - Fully upholstered with stitch detailing for a tailored appearance. - Back must allow for different fabric option than the seat. 2. Work surface must be painted MDF or high-pressure laminate. 3. Work surface support(s) must be chrome or painted metal. 4. Privacy screens must be fabric covered, high-pressure laminate or low-pressure laminate. Power and Data: 1. Must provide one duplex outlet as a minimum. Support/Table Bases: 1. Floor supports must be minimal, no higher than 50.8mm (2 in.). 2. Supports/legs for the work surface must be formed to the privacy panels and must appear to be supported by the panels, however may be supported on feet. 3. Table must be from the same line as the privacy panels and seating. Table must have only one visible pedestal leg.

CATEGORY 6--KITCHENETTE CHAIRS	
	Kitchenette Chair (KC1)
	Bar Stool (with arms) (BS1)

CHAIR LEGEND	
	Task Chair #1 (S1)
	Drafting Chair #1 (with arms) (DC1)
	Drafting Chair #2 (DC2)
	Side Chair #1 (with arms) (SC1)
	Side Chair #2 (SC2)
	Meeting Chair (MC1)

Non - RFSO	
	Phone Booth
	Treadmill


CATEGORY 1B--CREDENZAS AND HUTCHES	
	Credenza #1 (508mmx1829mm) – open shelving (CR1)
	Credenza #2 (457mmx1067mm) – with doors (CR2)

CHAIR LEGEND	
	Task Chair #1 (S1)
	Drafting Chair #1 (with arms) (DC1)
	Drafting Chair #2 (DC2)
	Side Chair #1 (with arms) (SC1)
	Side Chair #2 (SC2)
	Meeting Chair (MC1)

CATEGORY 3 -- FILING AND STORAGE CABINETS	
	Storage Lockers – One High – Pressure Laminate 18"x20", Both Left and Right pulls

CATEGORY 5--ANCILLARY PRODUCTS	
	Keyboard Tray (KT1)
	Power Source (PM1)
	Table Lamp (TL1)
	Dual Monitor Arm #1 (MA2) Must allow for both monitors to be horizontally adjusted for side by side alignment so they touch while still allowing them to be positioned close to the back of the surface
	Monitor Arm Single #2 (MA1)

FURNITURE PLAN – CATEGORY 6



CATEGORY 6--COLLABORATIVE TABLES	
	Coffee Table #1 (18" Round)
	Coffee Table #2 (24" Round)
	Coffee Table #2 (24" Square)
	Laptop Table
	Hgt. Adj. Screening Table #1
	Fixed Seat –Screening Table #2

Location: **9 MONTCLAIR HUB - 2ND FLOOR - LEGEND**

Project Name: _____

No.	Description	Date

Approval: _____

Date: 2020-12-13

Drawn by: Louise Durivage

Scale: NTS

Page: 1/1