



LEGEND	
	DUPLEX RECEPTACLE
	ELECTRICAL DATA
	FLOOR MONUMENT LOCATION
	BASE FEED LOCATION HARDWIRED SYSTEMS FURNITURE BASE FEED TO BE PROVIDED BY FURNITURE SUPPLIER.
	POWER POLE LOCATION HARDWIRED SYSTEMS FURNITURE POWER POLE IS TO BE PROVIDED BY FURNITURE SUPPLIER. NOTE: IT IS NOT AN OPEN CEILING. SYSTEMS FURNITURE POWER POLE HEIGHT RANGE MUST BE BETWEEN (2743 – 3049mm (108 – 120") FROM THE FINISHED FLOOR TO THE TOP OF THE POLE. FURNITURE SUPPLIER IS NOT RESPONSIBLE FOR SECURING THE POWER POLE TO THE SLAB.

CATEGORY 6--SOFT SEATING & SCREENS	
	Lounge Chair #1 (LC-1) Must have two casters and two legs
	Lounge Chair #2 (LC2) Must have two casters and two legs
	Lounge Chair #3 (LC3)
	Tablet Chair #1 (Left & Right) (TC1-L & TC2R)
	Ottoman #1 (18" Round) (OR-1)
	Ottoman #3 (24" Square) (OS3)
	Ottoman #4 (48" Square) (OS4)
	Ottoman #5 (42" Round) (OR5)
	Stool with casters #6 (18" Round) (OS6)
	Stool with casters #7 (24" Square) (OS7)
	Whiteboard (OS-7) LS2
	Ottoman #5 (25"x66" Rectangular) (MT3)

CATEGORY 6--MEETING & TRAINING TABLES	
	Meeting Table #1 (30"x60")
	Meeting Table #2 (30"x72") Table 762mmX1829mm All tables must be supplied with ganging or linking devices to ensure they can be joined together in horizontal positions and/or 90 and/or 180 degrees to each other while still allowing for the provision of power and data connectivity across the entire multi-table configuration. Power must be able to be daisy chained. Table top – 737mm (29") AFF and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions
	Meeting Table #3 (60"x120") – T60x120 Table top – 737mm (29") AFF (tolerance +/- 1") and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions Glides must allow for +/-51mm (+/- 2") of levelling
	Meeting Table #4 (60"x144") T60x144 Table top – 737mm (29") AFF (tolerance +/- 1") and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions Glides must allow for +/-51mm (+/- 2") of levelling
	Meeting Table #5 (36"x96") Table top – 737mm (29") AFF (tolerance +/- 1") and composed of one piece, minimum 3mm (0.1") radius edge Table top – High pressure laminate Base/Support – in brushed metal or painted metal Table base must allow for seating on all sides with no knee obstructions Glides must allow for +/-51mm (+/- 2") of levelling
	Meeting Table #6 (36" Round) TR6
	Meeting Table #7 (30"x30") T30x30
	Narrow Table #8 (18"x60") NST1

CHAIR LEGEND	
	Task Chair #1 (S1)
	Drafting Chair #1 (with arms) (DC1)
	Drafting Chair #2 (DC2)
	Side Chair #1 (with arms) (SC1)
	Side Chair #2 (SC2)
	Meeting Chair (MC1)

CATEGORY 1B--CREDENZAS AND HUTCHES	
	Credenza #1 (508mmx1829mm) – open shelving (CR1)
	Credenza #2 (457mmx1067mm) – with drawers and door (CR2)

CATEGORY 3 -- FILING AND STORAGE CABINETS	
	Storage Lockers – One High – Pressure Laminate 18"x20". Both Left and Right pulls L18x20(L1)
	Storage Lockers – Two High – Pressure Laminate 18"x20". Both Left and Right pulls L18x20L

CATEGORY 5--ANCILLARY PRODUCTS	
	Keyboard Tray (KT1)
	Power Source (PM1)
	Table Lamp (TL1)
	Dual Monitor Arm #1 (MA2) Must allow for both monitors to be horizontally adjusted for side by side alignment so they touch while still allowing them to be positioned close to the back of the surface
	Monitor Arm Single #2 (MA1)

CATEGORY 6--COLLABORATIVE TABLES	
	Coffee Table #1 (18" Round) ST1
	Coffee Table #2 (24" Round) ST2
	Coffee Table #3 (24" Square) ST3
	Laptop Table LT1
	Hgt. Adj. Screening Table #1 MMT1
	Fixed Seat --Screening Table #2 MMT2

CATEGORY 6--SOFT SEATING & SCREENS	
	This Banquette seating configuration consists of the following (3) components listed below: BA1, BA2 – Seater, BA3 to be all of the same series and collection Must be supplied with ganging or linking devices to ensure they can be joined 2 each – Banquette Armless / Low Back Bench (+/- 63" to 75") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16") 4 each – Banquette Armless / Low Back Bench (+/- 24" to 31") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16") 2 each – Banquette Armless/ Backless Bench (+/- 24" to 31")
	Engagement Space This Banquette seating configuration consists of the following (4) components listed below: BA1, BA2 – Seater, BA2 – Seater, Screen and BA3 to be all of the same series and collection Must be supplied with ganging or linking devices to ensure they can be joined This Banquette seating configuration consists of the following (4) components listed below: 2 each – Banquette Armless / Medium Back / Privacy Screen Bench (+/- 63" to 75") Overall screen height to be 1117mm-1720mm (44" – 50") 2 each – Banquette Armless / Low Back Bench (+/- 63" to 75") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16") 1 each – Banquette Armless / Low Back Bench (+/- 24" to 31") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16") 4 each – Banquette Armless/ Backless Bench (+/- 24" to 31") Modular Benching (MBP1) (+/- 25" to 39") 2 each – Banquette Armless / No Back Bench (+/- 24" to 31"), with power Must be supplied with ganging or linking devices to ensure they can be joined Modular Benching (MB2) with backrest (+/- 25" to 39") Backrest to be same length as seat, and have a minimum backrest height of 406mm (16") Must be supplied with ganging or linking devices to ensure they can be joined Modular Benching (MB3) (+/- 48" to 62") 1 each – Banquette Armless / No Back Modular Benching (MB4) (+/- 48" to 54") 1 each – Banquette Armless / No Back Bench DIMENSIONS 18" X 54" MAXIMUM

CATEGORY 6--OPEN AREA WORKSPACE	
	Individual Work Pod w/ Worksurface Task Light (WPP1) Description 1. Free-standing unit must include a work surface and task light for a single user and privacy screen(s). 2. Work surface and privacy screen(s) must be from the same product line. 3. Privacy screen(s) must surround the users on no less than three sides, including both the work surface and the user. Interconnecting systems panels are not an acceptable solution. Corners of panels must be rounded; panels which connect at a square or 90-degree angle are not acceptable. 4. Seat will be provided separately and does not form part of this specification. Dimension 1. Work surface must be a maximum height of 762mm (30 in.) with a tolerance of +/- 76.2mm (-3 in.) when measured from the floor to the top of the work surface. 2. Privacy screen(s) height must be a minimum of 1194mm (47 in.) to a maximum of 1549mm (61 in.). 3. Overall diameter footprint of unit must be 1829mm (72 in.) maximum, ±102 mm (4 in.) Finishes 1. Work surface must be painted MDF or high-pressure laminate. 2. Privacy screen must be fabric covered, high-pressure laminate, or low-pressure laminate. Power and Data 1. Must provide a combination of one duplex and one USB as a minimum. Support/Table Bases 1. Floor supports must be minimal, no higher than 64 mm (2.5 in.). 2. Support/legs for the work surface must be formed to the privacy panels and must appear to be supported by the panels, however may be supported on their own. Individual Work Pod w/ Worksurface Task Light (WPP2) Description 1. Free-standing unit must include a work surface a single user and privacy screen(s). 2. Work surface and privacy screen(s) must be from the same product line. 3. Privacy screen(s) must surround the users on no less than three sides, including both the work surface and the user. Interconnecting systems panels are not an acceptable solution. Corners of panels must be rounded; panels which connect at a square or 90-degree angle are not acceptable. 4. Seat will be provided separately and does not form part of this specification. 5. Should have integrated footstool or stand alone ottoman. Various shapes are acceptable. Dimension 1. Tablet surface must be a minimum of 157x157". 2. Privacy screen(s) height must be a minimum of 1194mm (47 in.) to a maximum of 1549mm (61 in.). 3. Overall diameter footprint of unit must be a maximum of 1829mm (72 in.) maximum, ±102 mm (4 in.) Finishes 1. Tablet surface must be painted MDF or high-pressure laminate. 2. Privacy screen must be fabric covered, high-pressure laminate, or low-pressure laminate. Power and Data 1. Must provide a combination of one duplex and one USB as a minimum. Support/Table Bases 1. Floor supports must be minimal, no higher than 55.4mm (2.2 in.). 2. Support/legs for the work surface must be formed to the privacy panels and must appear to be supported by the panels, however may be supported on their own. Lounge Chair w/ Work Surface (PLC1) 1. Should there be armrests, they must be the same finish as the chair itself and integrated with the chair. 2. Must have a reclined position. 3. Chair must have high back with wings or side panels to provide some peripheral visual privacy to the user. 4. Back and seat cushions must be fixed. 5. Must be modern and tailored in appearance. Foot Stool 1. Various shapes are acceptable. Dimensions Chair 1. Overall width of the chair must be between 660 – 914mm (26 – 36 in.). 2. Seat must be high and able to provide head support. Foot Stool 1. Must be of an appropriate height to function as a foot stool for the chair. 2. Must be a minimum of 406mm (16") wide and no wider than the width of the chair being provided. Finishes Chair 1. Seat and back must be fully upholstered with stitch detailing for a tailored appearance. 2. Base/legs must be brushed or painted metal, wood or fabric covered. Foot Stool 1. Must be available in the same finishes as the chair. Base/Supports 1. If swivel base is provided, it must have an auto-return mechanism that pivots on the pedestal axis. Group Work Pods GWP1 1. Free-standing unit which must include two upholstered lounge seats, work surface, and privacy enclosure/screens. 2. Each lounge seat must allow for two adults to sit comfortably side-by-side. 3. Sofa, work surface, and privacy screens must be from the same product line. All parts must be snugly fitted into one another. Backrests/screens must form an enclosure surrounding 75% of all users and interior furniture components. Interconnecting systems panels are not an acceptable solution. Corners of panels must be rounded; panels which connect at a square or 90-degree angle are not acceptable. 4. Worksurface must be situated between the lounge seats to provide usable work surface space to all 4 users. Dimension 1. Sofa seat must be 381mm (15 in.) to 457mm (18 in.) when measured from the top of the seat to the finished floor, ±25 mm (1 in.). 2. Work surface must be compatible with the lounge height seating. 3. Privacy screen(s) height must be a minimum of 1194mm (47 in.) and a maximum of 1549mm (61 in.). 4. Overall total diameter footprint of the unit must be 2007mm (79 in.) diameter to 2581mm (102 in.) diameter, ±152 mm (6 in.). Finishes 1. The seat and back of the sofas must be: – Fully upholstered with stitch detailing for a tailored appearance. – Back must allow for different fabric options from the seat. 2. Work surface must be painted MDF or high-pressure laminate. 3. Work surface support(s) must be chrome or polished metal. 4. Privacy screen must be fabric covered, high-pressure laminate or low-pressure laminate. Power and Data 1. Must provide one duplex outlet as a minimum. Support/Table Bases 1. Floor supports must be minimal, no higher than 55.4mm (2.2 in.). 2. Support/legs for the work surface must be formed to the privacy panels and must appear to be supported by the panels, however may be supported on their own. 3. Table must be from the same lines as the privacy panels and seating. Table must have only one visible pedestal leg.

CATEGORY 6--KITCHENETTE CHAIRS	
	Kitchenette Chair (KC1)
	Bar Stool (with arms) (BS1)

CHAIR LEGEND	
	Task Chair #1 (S1)
	Drafting Chair #1 (with arms) (DC1)
	Drafting Chair #2 (DC2)
	Side Chair #1 (with arms) (SC1)
	Side Chair #2 (SC2)
	Meeting Chair (MC1)

Non - RFSO	
	Phone Booth
	Treadmill

Location	9 MONTCLAIR HUB - 2ND FLOOR - LEGEND			Approval:	Date:
Project Name	9 MONTCLAIR HUB - 2ND FLOOR - GATINEAU - QUEBEC			Drawn by:	Scale:
No.	Description	Date		Louise Durivage	NTS
					Page:
					1/1