



<b>CHAIR TYPE</b>	<b>QTY: 11</b>
<input checked="" type="checkbox"/> Rotary Chair (up to 275 lbs) <input type="checkbox"/> Rotary Chair large occupant (275 to 400 lbs) <input type="checkbox"/> Rotary Stool	

**Continuance of Certifications and additional information:**

Canada may request copies of any SA certification(s) or additional information to confirm/review chair criteria of product proposed prior to contract award within a time period specified by the Identified User.

Criteria Instructions		Requirement Choices (dimensions reflect Specifications for Office Seating (SA))							
<b>A</b>	<b>Headrest</b> choose only 1	<input type="checkbox"/> Yes – Adjustable and Removable (if applicable, indicate type of adjustment in additional criteria below) *Recommended with Standard Back Height <input checked="" type="checkbox"/> No							
<b>B</b>	<b>Backrest Height</b> choose only 1	<input checked="" type="checkbox"/> Standard = height between 450 mm (17.7 in.) to 660 mm (26.0 in.) <input type="checkbox"/> High = height greater than 660 mm (26.0 in.) <input type="checkbox"/> No preference							
<b>B</b>	<b>Backrest Style Preference(s)</b> choose ALL that are acceptable	<input checked="" type="checkbox"/> No preference note: style represents overall shape, design may vary 							
<b>C</b>	<b>Lumbar Support</b> choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable <input type="checkbox"/> Up/Down = min. 50 mm (2.0 in.) height adjustment between 150mm (5.9 in.) to 250 mm (9.8 in.) <input checked="" type="checkbox"/> Up/Down & In/Out <input type="checkbox"/> Fixed = between 150 mm (5.9 in.) to 250 mm (9.8 in.) above seat							
<b>D</b>	<b>Armrests</b> choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable <input checked="" type="checkbox"/> Height adjustable = min. 63 mm (2.5 in.) adjustment between 176 mm (6.9 in.) to 289 mm (11.4 in.) <input checked="" type="checkbox"/> Width adjustable = min. 75 mm (3.0 in.) adjustment between 443 mm (17.0 in.) to 493 mm (19.4 in.) <input checked="" type="checkbox"/> Pivot adjustable = min. 20 degrees inward and min. 10 degrees outward <input type="checkbox"/> Fixed = height range between 200 mm (7.9 in.) to 250 mm (9.8 in.) <input type="checkbox"/> None							
<b>E</b>	<b>Seat Depth</b> choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable = min. 50 mm (2.0 in.) adjustment within the range 420 mm (16.5 in.) to 460 mm (18.1 in.) <input type="checkbox"/> Fixed <table border="1" style="margin-left: 20px;"> <tr> <td><input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)</td> </tr> <tr> <td><input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)</td> </tr> <tr> <td><input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)</td> </tr> </table>		<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)	<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)	<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)			
<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)									
<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)									
<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)									
<b>F</b>	<b>Seat Width</b>	Refer to chair type above Rotary chairs and stools = min. width of 450 mm (17.7in.) Rotary Large Occupant models = min. width of 560 mm (22.0 in.)							
<b>G</b>	<b>Seat Height</b> choose ALL that are acceptable	<table border="1"> <tr> <td><b>Rotary Chair</b></td> <td> <input checked="" type="checkbox"/> Adjustable  <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more  <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.)  <input type="checkbox"/> other = *specify additional criteria below                             </td> </tr> <tr> <td colspan="2"><input type="checkbox"/> Fixed = between 417 mm (16.4 in.) to 512 mm (20.2 in.)</td> </tr> </table>	<b>Rotary Chair</b>	<input checked="" type="checkbox"/> Adjustable <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> other = *specify additional criteria below	<input type="checkbox"/> Fixed = between 417 mm (16.4 in.) to 512 mm (20.2 in.)		<table border="1"> <tr> <td><b>Rotary Stool</b> choose 1</td> <td> <input type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.)  <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in)                             </td> </tr> </table>	<b>Rotary Stool</b> choose 1	<input type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in)
<b>Rotary Chair</b>	<input checked="" type="checkbox"/> Adjustable <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> other = *specify additional criteria below								
<input type="checkbox"/> Fixed = between 417 mm (16.4 in.) to 512 mm (20.2 in.)									
<b>Rotary Stool</b> choose 1	<input type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in)								
<b>H</b>	<b>Tilt Mechanism</b> choose ALL that are acceptable	<input checked="" type="checkbox"/> Synchro-tilt = Typically pivot point is under center of seat and when reclined the users feet are lifted off the floor. (seat and backrest tilt together in a ratio > 1:1) <input checked="" type="checkbox"/> Unison-tilt = Typically pivot point is under front of seat and when reclined users feet remain on the floor. (seat and backrest tilt together in a ratio of 1:1) <input checked="" type="checkbox"/> Independent-tilt = Seat and backrest angle adjust independently of each other							
<b>I</b>	<b>Seat and Backrest Locks</b> choose ALL that are acceptable	<input type="checkbox"/> Setup Position = chair locks into position with seat flat and backrest straight <input checked="" type="checkbox"/> Multiple Positions = chair locks into setup position plus other angles for seat and backrest							
<b>J</b>	<b>Casters</b>	<input type="checkbox"/> carpet <input checked="" type="checkbox"/> hard surface							
<b>L</b>	<b>Foot Ring</b>	Standard with stool models only							
	<b>Finishes (Upholstery / Non-Upholstery)</b>	<table border="1"> <tr> <td><b>Backrest</b></td> <td> <input checked="" type="checkbox"/> Upholstery  <input type="checkbox"/> Breathable material (Mesh)                             </td> <td> <input type="checkbox"/> Other _____ *specify additional criteria below                             </td> </tr> <tr> <td><b>Seat</b></td> <td> <input checked="" type="checkbox"/> Upholstery  <input type="checkbox"/> Breathable material (Mesh)                             </td> <td> <input type="checkbox"/> Other _____ *specify additional criteria below                             </td> </tr> </table>	<b>Backrest</b>	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below	<b>Seat</b>	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below	
<b>Backrest</b>	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below							
<b>Seat</b>	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below							
	<b>Additional Criteria:</b> If applicable:	Black base finish.							