

CHAIR BUILDER (G3) 08 2020



CHAIR TYPE	QTY: 3
<input type="checkbox"/> Rotary Chair (up to 275 lbs) <input type="checkbox"/> Rotary Chair large occupant (275 to 400 lbs) <input checked="" type="checkbox"/> Rotary Stool	

Continuance of Certifications and additional information:

Canada may request copies of any SA certification(s) or additional information to confirm/review chair criteria of product proposed prior to contract award within a time period specified by the Identified User.

Criteria Instructions		Requirement Choices (dimensions reflect Specifications for Office Seating (SA))							
A	Headrest choose only 1	<input type="checkbox"/> Yes – Adjustable and Removable (if applicable, indicate type of adjustment in additional criteria below) *Recommended with Standard Back Height <input checked="" type="checkbox"/> No							
B	Backrest Height choose only 1	<input checked="" type="checkbox"/> Standard = height between 450 mm (17.7 in.) to 660 mm (26.0 in.) <input type="checkbox"/> High = height greater than 660 mm (26.0 in.) <input type="checkbox"/> No preference							
B	Backrest Style Preference(s) choose ALL that are acceptable	<input checked="" type="checkbox"/> No preference note: style represents overall shape, design may vary 							
C	Lumbar Support choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable <input type="checkbox"/> Up/Down = min. 50 mm (2.0 in.) height adjustment between 150mm (5.9 in.) to 250 mm (9.8 in.) <input checked="" type="checkbox"/> Up/Down & In/Out <input type="checkbox"/> Fixed = between 150 mm (5.9 in.) to 250 mm (9.8 in.) above seat							
D	Armrests choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable <input checked="" type="checkbox"/> Height adjustable = min. 63 mm (2.5 in.) adjustment between 176 mm (6.9 in.) to 289 mm (11.4 in.) <input checked="" type="checkbox"/> Width adjustable = min. 75 mm (3.0 in.) adjustment between 443 mm (17.0 in.) to 493 mm (19.4 in.) <input checked="" type="checkbox"/> Pivot adjustable = min. 20 degrees inward and min. 10 degrees outward <input type="checkbox"/> Fixed = height range between 200 mm (7.9 in.) to 250 mm (9.8 in.) <input type="checkbox"/> None							
E	Seat Depth choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable = min. 50 mm (2.0 in.) adjustment within the range 420 mm (16.5 in.) to 460 mm (18.1 in.) <input type="checkbox"/> Fixed <table border="1" style="margin-left: 20px;"> <tr> <td><input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)</td> </tr> <tr> <td><input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)</td> </tr> <tr> <td><input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)</td> </tr> </table>		<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)	<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)	<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)			
<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)									
<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)									
<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)									
F	Seat Width	Refer to chair type above Rotary chairs and stools = min. width of 450 mm (17.7in.) Rotary Large Occupant models = min. width of 560 mm (22.0 in.)							
G	Seat Height choose ALL that are acceptable	<table border="1"> <tr> <td>Rotary Chair</td> <td> <input type="checkbox"/> Adjustable <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> other = *specify additional criteria below </td> </tr> <tr> <td>Rotary Stool choose 1</td> <td> <input checked="" type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in) </td> </tr> </table>	Rotary Chair	<input type="checkbox"/> Adjustable <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> other = *specify additional criteria below	Rotary Stool choose 1	<input checked="" type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in)	<input type="checkbox"/> Fixed = between 417 mm (16.4 in.) to 512 mm (20.2 in.)		
Rotary Chair	<input type="checkbox"/> Adjustable <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> other = *specify additional criteria below								
Rotary Stool choose 1	<input checked="" type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in)								
H	Tilt Mechanism choose ALL that are acceptable	<input checked="" type="checkbox"/> Synchro-tilt = Typically pivot point is under center of seat and when reclined the users feet are lifted off the floor. (seat and backrest tilt together in a ratio > 1:1) <input checked="" type="checkbox"/> Unison-tilt = Typically pivot point is under front of seat and when reclined users feet remain on the floor. (seat and backrest tilt together in a ratio of 1:1) <input checked="" type="checkbox"/> Independent-tilt = Seat and backrest angle adjust independently of each other							
I	Seat and Backrest Locks choose ALL that are acceptable	<input type="checkbox"/> Setup Position = chair locks into position with seat flat and backrest straight <input checked="" type="checkbox"/> Multiple Positions = chair locks into setup position plus other angles for seat and backrest							
J	Casters	<input type="checkbox"/> carpet <input checked="" type="checkbox"/> hard surface							
L	Foot Ring	Standard with stool models only							
	Finishes (Upholstery / Non-Upholstery)	<table border="1"> <tr> <td>Backrest</td> <td> <input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh) </td> <td> <input type="checkbox"/> Other _____ *specify additional criteria below </td> </tr> <tr> <td>Seat</td> <td> <input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh) </td> <td> <input type="checkbox"/> Other _____ *specify additional criteria below </td> </tr> </table>	Backrest	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below	Seat	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below	
Backrest	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below							
Seat	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below							
	Additional Criteria: If applicable:	Black base finish.							