



**CHAIR BUILDER (G3) 08 2020**

<b>CHAIR TYPE</b>	<b>QTY: 3</b>
<input type="checkbox"/> Rotary Chair (up to 275 lbs) <input type="checkbox"/> Rotary Chair large occupant (275 to 400 lbs) <input checked="" type="checkbox"/> Rotary Stool	

**Continuance of Certifications and additional information:**

Canada may request copies of any SA certification(s) or additional information to confirm/review chair criteria of product proposed prior to contract award within a time period specified by the Identified User.

Criteria Instructions	Requirement Choices (dimensions reflect Specifications for Office Seating (SA))				
<b>A</b> Headrest choose only 1	<input type="checkbox"/> Yes – Adjustable and Removable (if applicable, indicate type of adjustment in additional criteria below) <b>*Recommended with Standard Back Height</b> <input checked="" type="checkbox"/> No				
<b>B</b> Backrest Height choose only 1	<input checked="" type="checkbox"/> Standard = height between 450 mm (17.7 in.) to 660 mm (26.0 in.) <input type="checkbox"/> High = height greater than 660 mm (26.0 in.) <input type="checkbox"/> No preference				
<b>B</b> Backrest Style Preference(s) choose ALL that are acceptable	<input checked="" type="checkbox"/> No preference note: style represents overall shape, design may vary 				
<b>C</b> Lumbar Support choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable <input type="checkbox"/> Up/Down = min. 50 mm (2.0 in.) height adjustment between 150mm (5.9 in.) to 250 mm (9.8 in.) <input checked="" type="checkbox"/> Up/Down & In/Out <input type="checkbox"/> Fixed = between 150 mm (5.9 in.) to 250 mm (9.8 in.) above seat				
<b>D</b> Armrests choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable <input checked="" type="checkbox"/> Height adjustable = min. 63 mm (2.5 in.) adjustment between 176 mm (6.9 in.) to 289 mm (11.4 in.) <input checked="" type="checkbox"/> Width adjustable = min. 75 mm (3.0 in.) adjustment between 443 mm (17.0 in.) to 493 mm (19.4 in.) <input checked="" type="checkbox"/> Pivot adjustable = min. 20 degrees inward and min. 10 degrees outward <input type="checkbox"/> Fixed = height range between 200 mm (7.9 in.) to 250 mm (9.8 in.) <input type="checkbox"/> None				
<b>E</b> Seat Depth choose ALL that are acceptable	<input checked="" type="checkbox"/> Adjustable = min. 50 mm (2.0 in.) adjustment within the range 420 mm (16.5 in.) to 460 mm (18.1 in.) <input type="checkbox"/> Fixed <table border="1" style="margin-left: 20px;"> <tr> <td><input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)</td> </tr> <tr> <td><input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)</td> </tr> <tr> <td><input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)</td> </tr> </table>		<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)	<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)	<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)
<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)					
<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)					
<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)					
<b>F</b> Seat Width	Refer to chair type above Rotary chairs and stools = min. width of 450 mm (17.7in.) Rotary Large Occupant models = min. width of 560 mm (22.0 in.)				
<b>G</b> Seat Height choose ALL that are acceptable	<input checked="" type="checkbox"/> Rotary Chair <input type="checkbox"/> Rotary Stool choose 1	<input type="checkbox"/> Adjustable <table border="1" style="margin-left: 20px;"> <tr> <td> <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more  <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.)  <input type="checkbox"/> other = *specify additional criteria below           </td> </tr> </table> <input type="checkbox"/> Fixed = between 417 mm (16.4 in.) to 512 mm (20.2 in.) <input checked="" type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in.)	<input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> other = *specify additional criteria below		
<input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> other = *specify additional criteria below					
<b>H</b> Tilt Mechanism choose ALL that are acceptable	<input type="checkbox"/> Synchro-tilt = Preset ratio >1:1 <input type="checkbox"/> Unison-tilt = Preset ratio of 1:1 <input type="checkbox"/> Independent-tilt = Seat and backrest angle adjust independently of each other				
<b>I</b> Seat and Backrest Locks choose ALL that are acceptable	<input type="checkbox"/> Setup Position = chair locks into position with seat flat and backrest straight <input checked="" type="checkbox"/> Multiple Positions = chair locks into setup position plus other angles for seat and backrest				
<b>J</b> Casters	<input type="checkbox"/> carpet <input checked="" type="checkbox"/> hard surface				
<b>L</b> Foot Ring	Standard with stool models only				
<b>Finishes (Upholstery / Non-Upholstery)</b>	Backrest <input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below			
	Seat <input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other _____ *specify additional criteria below			
<b>Additional Criteria:</b> If applicable:	Black Base Finish				