

Solicitation No. - N° de l'invitation l'acheteur EQ754-212348/A	Amd. No. - N° de la modif. 04	Buyer ID - Id de PWL003
Client Ref. No. - N° de réf. du client FMS No./N° VME R.080037.042 R.080037.032	File No. - N° du dossier PWL-0-43060	CCC No./N° CCC -

Questions and Answers

Q: Is there a specification for the new floor monuments to be installed? Surface mount, flush mount, poke through?

A: Floor boxes are required to be poke-through style. The electrical legend and specification section 26 05 32 – 2.3 includes description of the floor boxes.

Q: Who will be responsible for the removal of the existing light fixtures from the jobsite? I believe there is approximately 500 fixtures?

A: The electrical contractor is responsible for removal and proper disposal of the light fixtures per specification section 26 05 05.

Q: Can you please provide information regarding the assembly needed for the construction of the plenum barriers above new/existing partitions?

A: Plenum information is included in specification Section 09 51 15 – ACOUSTICAL PLENUM PANELS, 2.1

Q: Can you provide clarification on the following:

Q: Drawing #A-10: the room finish schedule states “ Open Area” A-G, but I could not find on the drawings where these are located, can you please provide clarification.

A: We do not see this reference.

Q: Drawing 3/A-7: Would glazing receive two films? Install on interior or exterior of the rooms? No specification were provided.

A: Glazing has one film. (Gloss dual fine dot gradient). Opaque strip is not a separate glazing type, just ensure the more dense portion of the film falls in this portion.

Q: Drawing 2/A-4, only sidelights of frame type F3 would receive films, and the frosted gradient would be installed only one side of frame?

A: No, glazing will be installed on both sides.

Solicitation No. - N° de l'invitation l'acheteur EQ754-212348/A	Amd. No. - N° de la modif. 04	Buyer ID - Id de PWL003
Client Ref. No. - N° de réf. du client FMS No./N° VME R.080037.042 R.080037.032	File No. - N° du dossier PWL-0-43060	CCC No./N° CCC -

Q: The Specification states that a Kantech System is to be installed for access control.

“The Access Control System shall be installed based on Kantech KT-400 control panels installed in Kantech enclosures as shown on the drawings.”

A: CRA has requested that access control be based on the Kantech system as this is the existing. Security is being managed by CRA.

Q: Can you please provide information regarding the assembly needed for the construction of the plenum barriers above new/existing partitions?

A: Plenum information is included in specification Section 09 51 15 – ACOUSTICAL PLENUM PANELS, 2.1